


NOTES: 1. ELECTRICAL: A. IMPEDANCE: 50Ω (NOMINAL) B. FREQUENCY RANGE: 0-6 GHz C. CONTACT RESISTANCE: CENTER: 20mΩ MAX.: MEASURED AT 10mA MAX. 25 mΩ MAX AFTER CYCLING OUTSIDE: 10mΩ MAX. 15 mΩ MAX AFTER CYCLING D. INSULATION RESISTANCE: 500mΩ MIN.: MEASURED AT 100 VDC. E. WITHSTANDIN VOLTAGE: NO LINE OR INSULATION BREAKDOWN: 200 VAC FOR 1 MIN. F. V.S.W.R. : 1.3 MAX. AT DC TO 3GHz, 1.4 MAX. AT 3 TO 6GHz 2. PHYSICAL: A. FEMALE CONTACT HOLDING FORCE: .15N MIN. : MEASURED WITH A Ø.475MM PIN GAUGE. B. DURABILITY: 30 CYCLES C. TEMPERATURE RANGE: -40°C TO +90°C. D. AMC CONNECTOR MATING FORCE: 15N TYPICAL E. AMC CONNECTOR DEMATING FORCE: 10N TYPICAL F. AMC INTERFACE IS FULLY COMPATIBLE WITH "U.FL" SERIES PRODUCT. 3. MATERIALS AND FINISHES: CONNECTOR BODY: PHOSPHOR BRONZE, SILVER PLATED (.08u MIN.) OVER COPPER (1-2u) CONNECTOR CENTER CONTACT: PHOSPHOR BRONZE, GOLD PLATED (0.2u MIN.) OVER NICKEL (2-3u) CONNECTOR INSULATOR: PBT CABLE JACKET: FEP CABLE DIELECTRIC: FEP CABLE CENTER CONDUCTOR: 32AWG ANNEALED COPPER WIRE STRANDED, SILVER PLATED CABLE OUTER CONDUCTOR: ANNEALED COPPER WIRE BRAID, SILVER PLATED	A-IPA-113-XXXYZ		REVISIONS			
	DRAWING NO.	REV	DESCRIPTION	DATE	ECO	APPR
	THIRD ANGLE PROJ. 	A	RELEASE TO MFG.	2/20/03	44376	ORB
		B	A) ADDED CABLE MATERIAL & MATE/DEMATE NOTES	3/6/03	44396	ORB
		C	A) BODY PLATING WAS: GOLD PLATED OVER NICKEL B) NOTE 2D WAS: 25N TYPICAL	4/2/03	44402	BCG

CABLE ASSEMBLY OVERALL LENGTH TOLERANCE

OVERALL LENGTH L (mm)	STANDARD TOLERANCE (mm)
35<L<200	± 4
200 < L 500	± 8
500 < L 1000	± 12
1000 < L	±1.5 %



CABLE ASSEMBLY LENGTH "L" (SEE TABLE FOR TOLERANCE)

A - I P A - 1 1 3 - X X X Y Z

SERIES NAME (A=AMC)


AMC RIGHT ANGLE PLUG

CABLE DIAMETER IN mm (113 = 1.13 mm)

NO. OF TERMINATED ENDS (1 OR 2)

CABLE COLOR: G=GRAY
B=BLACK
W=WHITE

CABLE ASSEMBLY LENGTH IN mm
(SHORTEST LENGTH IS 35mm)



5.19
[.205]

3.99
[.157]

2.01
[.079]

2.21
[.087]

2.68
[.106]

AMC RIGHT ANGLE PLUG

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES AND TOLERANCES ARE: 2 PLACE DECIMAL ±.015 (0,381 mm) NOTICE - These drawings, specifications, or other data (1) are, and remain the property of Amphenol Corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. The furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights or permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.	MATERIAL	DRAWN G. ANTONINI	DATE 29-Jan-03	TITLE RIGHT ANGLE PLUG JUMPER		Amphenol Amphenol Corporation Communication and Network Products Division Danbury, CT U.S.A. 06810	
		ENGINEER G. ANTONINI	DATE 29-Jan-03				
		APPROVED O. BARTHELMES	DATE 2/20/03				
	REFERENCE GEN# CASSY68	CAD FILE I:\AMC\A-IPA-113-XXXYZ		CODE ID 74868	DWG SIZE B	DRAWING NO. A-IPA-113-XXXYZ	REV C