

Pin strip - PST 1,3/ 8-5,0 R56 - 1720356

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid
(<http://phoenixcontact.com/download>)



Header, Nominal current: 12 A, Rated voltage (III/2): 320 V, Number of positions: 8, Pitch: 5 mm, Color: black, Contact surface: Tin, Assembly: Taped SMD/THT/THR components, Voltage and current depend on the plug-in terminal block used.

Product Features

- ✓ Various pin lengths and pin geometries available on request
- ✓ Pin strip with pad pushed on for suction pipette for optional tape-on-reel packing
- ✓ 5.0 mm pitch
- ✓ Optimum pin geometry so as to not damage the plug
- ✓ Pin strip available in machine-capable packaging (tube magazine or tape)
- ✓ Reflow solderable pin strip, optimized for COMBICON compact connectors



Key commercial data

Packing unit	1 pc
Minimum order quantity	250 pc
Weight per Piece (excluding packing)	3.5 GRM
Custom tariff number	85366990
Country of origin	Germany

Technical data

Dimensions

Length	2.8 mm
Pitch	5 mm
Dimension a	35 mm
Pin dimensions	1,3 mm
Hole diameter	1.6 mm

General

Range of articles	PST 1,3/..-V
-------------------	--------------

Pin strip - PST 1,3/ 8-5,0 R56 - 1720356

Technical data

General

Insulating material group	IIIa
Rated surge voltage (III/3)	4 kV
Rated surge voltage (III/2)	4 kV
Rated surge voltage (II/2)	4 kV
Rated voltage (III/3)	250 V
Rated voltage (III/2)	320 V
Rated voltage (II/2)	400 V
Connection in acc. with standard	EN-VDE
Nominal current I_N	12 A (depends on the plug used)
Maximum load current	12 A (depends on the plug used)
Insulating material	PA
Inflammability class according to UL 94	V0
Color	black
Number of positions	8

Classifications

eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27260704
eCl@ss 7.0	27440402
eCl@ss 8.0	27440402

ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC002637
ETIM 5.0	EC002637

UNSPSC

UNSPSC 6.01	30211801
UNSPSC 7.0901	39121432
UNSPSC 11	34131203
UNSPSC 12.01	39121432
UNSPSC 13.2	39121432

Pin strip - PST 1,3/ 8-5,0 R56 - 1720356

Approvals

Approvals

Approvals

CSA / UL Recognized / SEV / cUL Recognized / GOST / GOST / cULus Recognized

Ex Approvals

Approvals submitted

Approval details

CSA 		
	B	D
Nominal current I _N	5 A	5 A
Nominal voltage U _N	300 V	300 V

UL Recognized 		
	B	D
Nominal current I _N	16 A	10 A
Nominal voltage U _N	300 V	300 V

SEV	
Nominal current I _N	10 A
Nominal voltage U _N	250 V

cUL Recognized 		
	B	D
Nominal current I _N	16 A	10 A
Nominal voltage U _N	300 V	300 V

Pin strip - PST 1,3/ 8-5,0 R56 - 1720356

Approvals


GOST 

GOST 


cULus Recognized 

Drawings


Drilling diagram



Dimensioned drawing



Dimensioned drawing



Dimensioned drawing

