

# HiPerFET™

## Power MOSFETs

### Single Die MOSFET


**IXFN 34N100**

$$V_{DSS} = 1000V$$

$$I_{D25} = 34A$$

$$R_{DS(on)} = 0.28\Omega$$


N-Channel Enhancement Mode  
Avalanche Rated, High dv/dt, Low  $t_{rr}$



| Symbol     | Test Conditions                                                                                                                         | Maximum Ratings  |                        |
|------------|-----------------------------------------------------------------------------------------------------------------------------------------|------------------|------------------------|
| $V_{DSS}$  | $T_J = 25^\circ\text{C}$ to $150^\circ\text{C}$                                                                                         | 1000             | V                      |
| $V_{DGR}$  | $T_J = 25^\circ\text{C}$ to $150^\circ\text{C}$ ; $R_{GS} = 1\text{ M}\Omega$                                                           | 1000             | V                      |
| $V_{GS}$   | Continuous                                                                                                                              | $\pm 20$         | V                      |
| $V_{GSM}$  | Transient                                                                                                                               | $\pm 30$         | V                      |
| $I_{D25}$  | $T_C = 25^\circ\text{C}$ , Chip capability                                                                                              | 34               | A                      |
| $I_{DM}$   | $T_C = 25^\circ\text{C}$ , pulse width limited by $T_{JM}$                                                                              | 136              | A                      |
| $I_{AR}$   | $T_C = 25^\circ\text{C}$                                                                                                                | 34               | A                      |
| $E_{AR}$   | $T_C = 25^\circ\text{C}$                                                                                                                | 64               | mJ                     |
| $E_{AS}$   | $T_C = 25^\circ\text{C}$                                                                                                                | 4                | J                      |
| dv/dt      | $I_S \leq I_{DM}$ , $di/dt \leq 100\text{ A}/\mu\text{s}$ , $V_{DD} \leq V_{DSS}$ ,<br>$T_J \leq 150^\circ\text{C}$ , $R_G = 2\ \Omega$ | 5                | V/ns                   |
| $P_D$      | $T_C = 25^\circ\text{C}$                                                                                                                | 700              | W                      |
| $T_J$      |                                                                                                                                         | -55 ... +150     | $^\circ\text{C}$       |
| $T_{JM}$   |                                                                                                                                         | 150              | $^\circ\text{C}$       |
| $T_{stg}$  |                                                                                                                                         | -55 ... +150     | $^\circ\text{C}$       |
| $V_{ISOL}$ | 50/60 Hz, RMS $t = 1\text{ min}$<br>$I_{ISOL} \leq 1\text{ mA}$ $t = 1\text{ s}$                                                        | 2500<br>3000     | V~<br>V~               |
| $M_d$      | Mounting torque<br>Terminal connection torque                                                                                           | 1.5/13<br>1.5/13 | Nm/lb.in.<br>Nm/lb.in. |
| Weight     |                                                                                                                                         | 30               | g                      |

miniBLOC, SOT-227 B (IXFN)

 E153432



G = Gate  
S = Source  
D = Drain  
TAB = Drain

Either Source terminal at miniBLOC can be used as Main or Kelvin Source

#### Features

- International standard packages
- miniBLOC, with Aluminium nitride isolation
- Low  $R_{DS(on)}$  HDMOS™ process
- Rugged polysilicon gate cell structure
- Unclamped Inductive Switching (UIS) rated
- Low package inductance
- Fast intrinsic Rectifier

#### Applications


- DC-DC converters
- Battery chargers
- Switched-mode and resonant-mode power supplies
- DC choppers
- Temperature and lighting controls

#### Advantages

- Easy to mount
- Space savings
- High power density

| Symbol       | Test Conditions                                                                                                          | Characteristic Values<br>( $T_J = 25^\circ\text{C}$ , unless otherwise specified) |      |                                                                                    |
|--------------|--------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|------|------------------------------------------------------------------------------------|
|              |                                                                                                                          | min.                                                                              | typ. | max.                                                                               |
| $V_{DSS}$    | $V_{GS} = 0\text{ V}$ , $I_D = 3\text{ mA}$                                                                              | 1000                                                                              |      | V                                                                                  |
| $V_{GS(th)}$ | $V_{DS} = V_{GS}$ , $I_D = 8\text{ mA}$                                                                                  | 3.0                                                                               |      | 5.5 V                                                                              |
| $I_{GSS}$    | $V_{GS} = \pm 20\text{ V}_{DC}$ , $V_{DS} = 0$                                                                           |                                                                                   |      | $\pm 200\text{ nA}$                                                                |
| $I_{DSS}$    | $V_{DS} = V_{DSS}$ , $V_{GS} = 0\text{ V}$                                                                               |                                                                                   |      | $T_J = 25^\circ\text{C}$<br>100 $\mu\text{A}$<br>$T_J = 125^\circ\text{C}$<br>2 mA |
| $R_{DS(on)}$ | $V_{GS} = 10\text{ V}$ , $I_D = 0.5 \cdot I_{D25}$<br>Pulse test, $t \leq 300\ \mu\text{s}$ ,<br>duty cycle $d \leq 2\%$ |                                                                                   | 0.25 | 0.28 $\Omega$                                                                      |

| Symbol       | Test Conditions                                                                                              | Characteristic Values<br>( $T_J = 25^\circ\text{C}$ , unless otherwise specified) |      |      |
|--------------|--------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|------|------|
|              |                                                                                                              | min.                                                                              | typ. | max. |
| $g_{fs}$     | $V_{DS} = 15\text{ V}; I_D = 0.5 \cdot I_{D25}$ , pulse test                                                 | 18                                                                                | 40   | S    |
| $C_{iss}$    | $V_{GS} = 0\text{ V}, V_{DS} = 25\text{ V}, f = 1\text{ MHz}$                                                |                                                                                   | 9200 | pF   |
| $C_{oss}$    |                                                                                                              |                                                                                   | 1200 | pF   |
| $C_{rss}$    |                                                                                                              |                                                                                   | 300  | pF   |
| $t_{d(on)}$  | $V_{GS} = 10\text{ V}, V_{DS} = 0.5 \cdot V_{DSS}, I_D = 0.5 \cdot I_{D25}$<br>$R_G = 1\ \Omega$ (External), |                                                                                   | 41   | ns   |
| $t_r$        |                                                                                                              |                                                                                   | 65   | ns   |
| $t_{d(off)}$ |                                                                                                              |                                                                                   | 110  | ns   |
| $t_f$        |                                                                                                              |                                                                                   | 30   | ns   |
| $Q_{g(on)}$  | $V_{GS} = 10\text{ V}, V_{DS} = 0.5 \cdot V_{DSS}, I_D = 0.5 \cdot I_{D25}$                                  |                                                                                   | 380  | nC   |
| $Q_{gs}$     |                                                                                                              |                                                                                   | 65   | nC   |
| $Q_{gd}$     |                                                                                                              |                                                                                   | 185  | nC   |
| $R_{thJC}$   |                                                                                                              |                                                                                   | 0.18 | K/W  |
| $R_{thCK}$   |                                                                                                              |                                                                                   | 0.05 | K/W  |

**miniBLOC, SOT-227 B**


M4 screws (4x) supplied

| Dim. | Millimeter |       | Inches |       |
|------|------------|-------|--------|-------|
|      | Min.       | Max.  | Min.   | Max.  |
| A    | 31.50      | 31.88 | 1.240  | 1.255 |
| B    | 7.80       | 8.20  | 0.307  | 0.323 |
| C    | 4.09       | 4.29  | 0.161  | 0.169 |
| D    | 4.09       | 4.29  | 0.161  | 0.169 |
| E    | 4.09       | 4.29  | 0.161  | 0.169 |
| F    | 14.91      | 15.11 | 0.587  | 0.595 |
| G    | 30.12      | 30.30 | 1.186  | 1.193 |
| H    | 38.00      | 38.23 | 1.496  | 1.505 |
| J    | 11.68      | 12.22 | 0.460  | 0.481 |
| K    | 8.92       | 9.60  | 0.351  | 0.378 |
| L    | 0.76       | 0.84  | 0.030  | 0.033 |
| M    | 12.60      | 12.85 | 0.496  | 0.506 |
| N    | 25.15      | 25.42 | 0.990  | 1.001 |
| O    | 1.98       | 2.13  | 0.078  | 0.084 |
| P    | 4.95       | 5.97  | 0.195  | 0.235 |
| Q    | 26.54      | 26.90 | 1.045  | 1.059 |
| R    | 3.94       | 4.42  | 0.155  | 0.174 |
| S    | 4.72       | 4.85  | 0.186  | 0.191 |
| T    | 24.59      | 25.07 | 0.968  | 0.987 |
| U    | -0.05      | 0.1   | -0.002 | 0.004 |

**Source-Drain Diode**

| Symbol   | Test Conditions                                                                                                                                         | Characteristic Values<br>( $T_J = 25^\circ\text{C}$ , unless otherwise specified) |      |               |
|----------|---------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|------|---------------|
|          |                                                                                                                                                         | min.                                                                              | typ. | max.          |
| $I_S$    | $V_{GS} = 0\text{ V}$                                                                                                                                   |                                                                                   |      | 34 A          |
| $I_{SM}$ | Repetitive;<br>pulse width limited by $T_{JM}$                                                                                                          |                                                                                   |      | 136 A         |
| $V_{SD}$ | $I_F = I_S, V_{GS} = 0\text{ V}$ ,<br>Pulse test, $t \leq 300\ \mu\text{s}$ , duty cycle $d \leq 2\%$                                                   |                                                                                   |      | 1.3 V         |
| $t_{rr}$ | $I_F = I_S, -di/dt = 100\text{ A}/\mu\text{s}, V_R = 100\text{ V}$<br>$T_J = 25^\circ\text{C}$<br>$T_J = 125^\circ\text{C}$<br>$T_J = 25^\circ\text{C}$ | 180                                                                               |      | ns            |
|          |                                                                                                                                                         | 330                                                                               |      | ns            |
| $Q_{RM}$ |                                                                                                                                                         | 2                                                                                 |      | $\mu\text{C}$ |
| $I_{RM}$ |                                                                                                                                                         | 8                                                                                 |      | A             |

IXYS reserves the right to change limits, test conditions, and dimensions.

IXYS MOSFETs and IGBTs are covered by one or more of the following U.S. patents:

4,835,592 4,881,106 5,017,508 5,049,961 5,187,117 5,486,715 6,306,728B1 6,259,123B1 6,306,728B1  
4,850,072 4,931,844 5,034,796 5,063,307 5,237,481 5,381,025 6,404,065B1 6,162,665 6,534,343




Figure 1. Output Characteristics at 25°C




Figure 2. Output Characteristics at 125°C




Figure 3.  $R_{DS(on)}$  normalized to 0.5  $I_{D25}$  value vs.  $I_D$




Figure 4.  $R_{DS(on)}$  normalized to 0.5  $I_{D25}$  value vs.  $T_J$




Figure 5. Drain Current vs. Case Temperature




Figure 6. Admittance Curves




Figure 7. Gate Charge




Figure 8. Capacitance Curves




Figure 9. Forward Voltage Drop of the Intrinsic Diode




Figure 10. Transient Thermal Resistance

IXYS reserves the right to change limits, test conditions, and dimensions.

IXYS MOSFETs and IGBTs are covered by one or more of the following U.S. patents:

|           |           |           |           |           |           |             |             |             |
|-----------|-----------|-----------|-----------|-----------|-----------|-------------|-------------|-------------|
| 4,835,592 | 4,881,106 | 5,017,508 | 5,049,961 | 5,187,117 | 5,486,715 | 6,306,728B1 | 6,259,123B1 | 6,306,728B1 |
| 4,850,072 | 4,931,844 | 5,034,796 | 5,063,307 | 5,237,481 | 5,381,025 | 6,404,065B1 | 6,162,665   | 6,534,343   |