



MARKETING SALES DRAWING


DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING

DIMENSIONS IN METRIC - []

Electrical Testing
per Tusonix standard
test plans and Mil-Std-202
Test Methods.



PHENOLIC RESIN
WAX IMPREGNATED.



TINNED COPPER

SPECIFICATIONS

TUSONIX PART NO.	838-553-C0G0-200J	
D (Diameter):	.290 MAX. [7.37]	
T (Thickness):	.156 MAX. [3.96]	
S (Lead Wire Spacing):	.250 ±.031 [6.35 ± 0.79]	
L (Lead Wire Length):	1.5 MIN. [38.10 MIN.]	
E (Lead Wire Diameter):	.025 [0.63] (22 AWG.)	
P (Coating on Leads Max.):	.000 [0.00]	
Capacitance Value:	20 pF	
Capacitance Tolerance:	± 5 %	
Temperature Coefficient:	C0G	
Voltage:	Working:	1000 VDC
	Test:	1750 VDC
	Life:	1500 VDC
Marking:	STAMP: TMK, CAP, TOL., T.C. & WVDC	

REVISION RECORD Original Release C.O. 20030611-2-01 0	--TOLERANCES-- Unless Otherwise Specified		Title HI-VOLTAGE DISC	
	DECIMAL ±		Drawn L.E. 06-11-03	
	ANGLES ±		Approved B.Mc. 06-11-03	
	TUSONIX TUCSON, ARIZONA		A	838-553-C0G0-200J