



49.72	45.72	10-32-1101	5281-10A	10
44.64	40.64	↑ -109I	↑ -09A	9
39.56	35.56	↑ -108I	↑ -08A	8
34.48	30.48	↑ -107I	↑ -07A	7
29.4	25.4	↑ -106I	↑ -06A	6
24.32	20.32	↑ -105I	↑ -05A	5
19.24	15.24	↑ -104I	↑ -04A	4
14.16	10.16	↑ -103I	↑ -03A	3
9.08	5.08	10-32-1021	5281-02A	2
B	A	EDP NO.	ENG. NO.	極数 NO. OF CKTS.

注記
NOTE

- 1 ウエハーのそりは、長さ 25.4 に対して 0.24 MAX.. CAMBER MUST BE 0.24 MAX. PER 25.4
- △ 全極数が偶数の場合のみ適用。 TO BE APPLIED ONLY WHEN ALL CKTS. ARE EVEN.

REVISED EC NO: J2014-1442 DRWN:TYAJIMA01 2014/03/25 CHKD:KASAKAWA 2014/03/26 APPR:NUKITA 2014/03/26	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 4:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION	
	10 UNDER	±0.15	DRAWN BY TYAJIMA01	DATE 2014/03/13	TITLE KK 5.08 WAFER ASSY WITH LOCK			
	10 OVER 30 UNDER	±---	CHECKED BY KASAKAWA	DATE 2014/03/13				
	30 OVER	±---	APPROVED BY NUKITA	DATE 2014/03/13	SHEET NO. 1 OF 1			
ANGULAR ±1 °		MATERIAL NO. SEE DRAWING		DOCUMENT NO. SD-5281-001				
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						