

GaAs MMIC FUNDAMENTAL MIXER MODULE, 11 - 20 GHz




Typical Applications

The HMC-C051 is ideal for:

- Point-to-Point Radios
- Point-to-Multi-Point Radios & VSAT
- Test Equipment & Sensors
- Military End-Use

Functional Diagram



Features

- High LO/RF Isolation: 43 dB
- Passive Double Balanced Topology
- Low Conversion Loss: 7 dB
- Wide IF Bandwidth: DC - 6 GHz
- Robust 1,000V ESD, Class 1C
- Hermetically Sealed Module
- Field Replaceable 2.92 mm (RF and LO) and SMA (IF) Connectors
- 55 to +85 °C Operating Temperature

General Description

The HMC-C051 is a general purpose double balanced mixer housed in a miniature hermetic module that can be used as an upconverter or downconverter between 11 and 20 GHz. This mixer is fabricated in a GaAs MESFET process, and requires no external components or matching circuitry. The HMC-C051 provides excellent LO to RF and LO to IF isolation due to optimized balun structures. The module features removable 2.92 mm (RF and LO) and SMA (IF) connectors which can be detached to allow direct connection of the I/O pins to a microstrip or coplanar circuit.

Electrical Specifications, $T_A = +25^\circ\text{C}$, $IF = 100\text{ MHz}$, $LO = +13\text{ dBm}^*$

Parameter	Min.	Typ.	Max.	Min.	Typ.	Max.	Units
Frequency Range, RF & LO		12 - 16		11 - 20			GHz
Frequency Range, IF		DC - 6		DC - 6			GHz
Conversion Loss		7	9		8	11	dB
Noise Figure (SSB)		6			7.5		dB
LO to RF Isolation	38	44		32	43		dB
LO to IF Isolation	36	40		36	41		dB
RF to IF Isolation	19	28		19	29		dB
IP3 (Input)		17			18		dBm
IP2 (Input)		44			41		dBm
1 dB Gain Compression (Input)		10			11		dBm

*Unless otherwise noted, all measurements performed as downconverter, $IF = 100\text{ MHz}$.

HMC-C051* PRODUCT PAGE QUICK LINKS

Last Content Update: 02/23/2017

COMPARABLE PARTS

View a parametric search of comparable parts.

DOCUMENTATION

Data Sheet

- HMC-C051 Data Sheet

TOOLS AND SIMULATIONS

- HMC-C051 S-Parameter

DESIGN RESOURCES

- HMC-C051 Material Declaration
- PCN-PDN Information
- Quality And Reliability
- Symbols and Footprints

DISCUSSIONS

View all HMC-C051 EngineerZone Discussions.

SAMPLE AND BUY

Visit the product page to see pricing options.

TECHNICAL SUPPORT


Submit a technical question or find your regional support number.

DOCUMENT FEEDBACK


Submit feedback for this data sheet.

**GaAs MMIC FUNDAMENTAL
MIXER MODULE, 11 - 20 GHz**


**Conversion Gain vs.
Temperature @ LO = +13 dBm**




Isolation @ LO = +13 dBm




Conversion Gain vs. LO Drive




Return Loss @ LO = +13 dBm








IF Bandwidth @ LO = +13 dBm



**Upconverter Performance
Conversion Gain vs. LO Drive**



GaAs MMIC FUNDAMENTAL MIXER MODULE, 11 - 20 GHz

Input IP3 vs. LO Drive *

**Input IP3 vs.
Temperature @ LO = +13 dBm***

Input IP2 vs. LO Drive *

**Input IP2 vs.
Temperature @ LO = +13 dBm***

**Input P1dB vs.
Temperature @ LO = +13 dBm**


* Two-tone input power = -10 dBm each tone, 1 MHz spacing.

Information furnished by Analog Devices is believed to be accurate and reliable. However, no responsibility is assumed by Analog Devices for its use, nor for any infringements of patents or other rights of third parties that may result from its use. Specifications subject to change without notice. No license is granted by implication or otherwise under any patent or patent rights of Analog Devices. Trademarks and registered trademarks are the property of their respective owners.

For price, delivery, and to place orders: Analog Devices, Inc., One Technology Way, P.O. Box 9106, Norwood, MA 02062-9106 Phone: 781-329-4700 • Order online at www.analog.com Application Support: Phone: 1-800-ANALOG-D

**GaAs MMIC FUNDAMENTAL
MIXER MODULE, 11 - 20 GHz**
Absolute Maximum Ratings

RF / IF Input	+25 dBm
LO Drive	+25 dBm
Storage Temperature	-65 to +150 °C
Operating Temperature	-55 to +85 °C
ESD Sensitivity (HBM)	Class 1C




**ELECTROSTATIC SENSITIVE DEVICE
OBSERVE HANDLING PRECAUTIONS**

MxN Spurious Outputs

mRF	nLO				
	0	1	2	3	4
0	xx	15	34	32	xx
1	26	0	43	47	61
2	77	74	60	72	99
3	95	94	98	72	92
4	xx	108	108	103	106

RF Frequency= 15 GHz @ -10 dBm
LO Frequency= 14.9 GHz @ +13 dBm
All values in dBc below IF power level (1RF - 1LO).

**GaAs MMIC FUNDAMENTAL
MIXER MODULE, 11 - 20 GHz**
Outline Drawing

Package Information

Package Type	C-11
Package Weight ^[1]	20 gms (Typ.)
Spacer Weight	2.6 gms (Typ.)



[1] Package weight includes the connectors

[2] ±1 gms Tolerance

NOTES:

1. PACKAGE, LEADS, COVER MATERIAL: KOVAR™
2. PLATING: GOLD PLATE OVER NICKEL PLATE.
3. MOUNTING SPACER: NICKEL PLATED ALUMINUM.
4. ALL DIMENSIONS ARE IN INCHES [MILLIMETERS].
5. TOLERANCES: ±0.010 [0.23] UNLESS OTHERWISE SPECIFIED
6. FIELD REPLACEABLE 2.92mm CONNECTORS. TENSOLITE 231CCSF OR EQUIVALENT.

**GaAs MMIC FUNDAMENTAL
MIXER MODULE, 11 - 20 GHz**
Pin Descriptions

Pin Number	Function	Description	Interface Schematic
1	LO	This pin is DC coupled and matched to 50 Ohms.	
2	IF	This pin is DC coupled. For applications not requiring operation to DC, this port should be DC blocked externally using a series capacitor whose value has been chosen to pass the necessary IF frequency range. For operation to DC, this pin must not source or sink more than 2 mA of current or part non-function and possible part failure will result.	
3	RF	This pin is DC coupled and matched to 50 Ohms.	