



LEADWIRES (2)

24 AWG, 7x32 STRANDED,
SILVER PLATED COPPER,
BLACK TEFLON INSULATION,
TWISTED 2 1/2 TO 3 1/2
TWISTS PER INCH

HOUSING

ANODIZED ALUMINUM

RESISTANCE

10,000 OHMS AT 25°C
±0.2°C FROM 32°C TO 42°C

R-T CURVE

16

TOLERANCES		DRAWN	DATE	FENWAL ELECTRONICS	
UNLESS OTHERWISE NOTED, ALL DIMENSIONS ARE IN INCHES, AND TOLERANCES ARE AS SHOWN HERE.		HS	17SEP98		
FRACTIONS = ±1/64		CHECKED	DATE		
DECIMALS .XX = .01 .XXX = .005					
ANGLES = 0°30'		APPROVED	DATE	TITLE PROBE ASSEMBLY OUTLINE	
USED ON				This information is the property of FENWAL ELECTRONICS. It is submitted in confidence, and is not to be disclosed or utilized without written permission.	
SHEET	OF	DO NOT SCALE DRAWING		SCALE	SIZE
1	1	DRAWING		--	B
590-32AC36-103				REV.	01