


TC7MP01FK

Low-Voltage Triple Gate(6-input AND + 4-input OR + inverter)

The TC7MP01FK is a high-performance CMOS triple gate (6-input AND + 4-input OR + inverter). Designed for use in 1.8 V, 2.5 V, or 3.3 V systems, it achieves high-speed operation while maintaining the CMOS low power dissipation.

It is also designed with overvoltage tolerant inputs and outputs up to 3.6V.

All inputs are equipped with protection circuits against static discharge.




Weight : 0.03 g (typ.)


Features

- Low-voltage operation : $V_{CC} = 1.65$ to $3.6V$
- Quiescent supply current : $I_{CC} = 2 \mu A$ (max) ($V_{CC}=3.6V$)
- High-speed operation : 6 input AND
 - $t_{pd}=3.7ns$ (max) ($V_{CC}=3.3\pm0.3V$)
 - $t_{pd}=5.5ns$ (max) ($V_{CC}=2.5\pm0.2V$)
 - $t_{pd}=11.0ns$ (max) ($V_{CC}=1.8\pm0.15V$)
- 4 input OR
 - $t_{pd}=3.5ns$ (max) ($V_{CC}=3.3\pm0.3V$)
 - $t_{pd}=5.0ns$ (max) ($V_{CC}=2.5\pm0.2V$)
 - $t_{pd}=10.0ns$ (max) ($V_{CC}=1.8\pm0.15V$)
- INV.
 - $t_{pd}=3.8ns$ (max) ($V_{CC}=3.3\pm0.3V$)
 - $t_{pd}=5.2ns$ (max) ($V_{CC}=2.5\pm0.2V$)
 - $t_{pd}=9.5ns$ (max) ($V_{CC}=1.8\pm0.15V$)
- Output current : $I_{OH}/I_{OL}=\pm 12mA$ (min) ($V_{CC}=3.0V$)
: $I_{OH}/I_{OL}=\pm 9mA$ (min) ($V_{CC}=2.3V$)
: $I_{OH}/I_{OL}=\pm 2mA$ (min) ($V_{CC}=1.65V$)
- Latch-up performance : $\pm 300mA$
- ESD performance : Machine model $> \pm 200V$
: Human body model $> \pm 2000V$
- Ultra-small package : VSSOP (US16)
- Power-down protection provided on all inputs and outputs.

Pin Assignment (top view)



IEC Logic Symbol



Truth Table (AND Logic)

A	B	C	D	E	F	Y1
L	x	x	x	x	x	L
x	L	x	x	x	x	L
x	x	L	x	x	x	L
x	x	x	L	x	x	L
x	x	x	x	L	x	L
x	x	x	x	x	L	L
H	H	H	H	H	H	H

Truth Table (OR Logic)

G	H	I	J	Y2
H	x	x	x	H
x	H	x	x	H
x	x	H	x	H
x	x	x	H	H
L	L	L	L	L

Truth Table (INV. Logic)

K	Y3
L	H
H	L

Maximum Ratings

Characteristics	Symbol	Rating	Unit
Power supply voltage	V_{CC}	−0.5 to 4.6	V
DC input voltage	V_{IN}	−0.5 to 4.6	V
DC output voltage	V_{OUT}	−0.5 to 4.6 (Note 1)	V
		−0.5 to $V_{CC}+0.5$ (Note 2)	
Input diode current	I_{IK}	−50	mA
Output diode current	I_{OK}	±50 (Note 3)	mA
DC output current	I_{OUT}	±50	mA
DC V_{CC} /ground current	I_{CC}/I_{GND}	±100	mA
Power dissipation	P_D	180	mW
Storage temperature	T_{stg}	−65 to 150	°C

(Note 1) $V_{CC}=0V$

(Note 2) High or low state.

(Note 3) $V_{OUT} < GND$, $V_{OUT} > V_{CC}$

Recommended Operating Range

Characteristics	Symbol	Rating	Unit
Power supply voltage	V_{CC}	1.65 to 3.6	V
		1.2 to 3.6 (Note 4)	
DC input voltage	V_{IN}	−0.3 to 3.6	V
DC output voltage	V_{OUT}	0 to 3.6 (Note 5)	V
		0 to V_{CC} (Note 6)	
Output current	I_{OH}/I_{OL}	±12 (Note 7)	mA
		±9 (Note 8)	
		±2 (Note 9)	
Operating Temperature	T_{opr}	−40 to 85	°C
Input rise and fall time	dt / dv	0 to 10 (Note 10)	ns/V

(Note 4) Data retention only

(Note 5) $V_{CC}=0V$

(Note 6) High or low state

(Note 7) $V_{CC}=3.0$ to 3.6V

(Note 8) $V_{CC}=2.3$ to 2.7V

(Note 9) $V_{CC}=1.65$ to 1.95V

(Note 10) $V_{IN}=0.8$ to 2.0V, $V_{CC}=3.0V$

Electrical Characteristics
DC Characteristics (Ta=-40 to 85°C, 2.7V < Vcc ≤ 3.6V)

Characteristics		Symbol	Test condition		Vcc(V)	Min	Max	Unit
Input Voltage	H-level	V _{IH}	—		2.7 to 3.6	2.0	—	V
	L-level	V _{IL}	—		2.7 to 3.6	—	0.8	
Output voltage	H-level	V _{OH}	V _{IN} = V _{IH} or V _{IL}	I _{OH} = -100uA	2.7 to 3.6	Vcc-0.2	—	V
				I _{OH} = -6mA	2.7	2.2	—	
				I _{OH} = -9mA	3.0	2.4	—	
				I _{OH} = -12mA	3.0	2.2	—	
	L-level	V _{OL}	V _{IN} = V _{IH} or V _{IL}	I _{OL} = 100uA	2.7 to 3.6	—	0.2	
				I _{OL} = 6mA	2.7	—	0.4	
				I _{OL} = 9mA	3.0	—	0.4	
				I _{OL} = 12mA	3.0	—	0.55	
Input leakage current		I _{IN}	V _{IN} =0 to 3.6V		2.7 to 3.6	—	±2.0	μ A
Power-off leakage current		I _{OFF}	V _{IN} ,V _{OUT} =0 to 3.6V		0	—	2.0	μ A
Quiescent supply current		I _{CC}	V _{IN} =V _{CC} or GND		2.7 to 3.6	—	2.0	μ A
		Δ I _{CC}	V _{IN} =V _{CC} -0.6V (per input)		2.7 to 3.6	—	750	μ A

DC Characteristics (Ta=-40 to 85°C, 2.3V ≤ Vcc ≤ 2.7V)

Characteristics		Symbol	Test condition		Vcc(V)	Min	Max	Unit
Input voltage	H-level	V _{IH}	—		2.3 to 2.7	1.6	—	V
	L-level	V _{IL}	—		2.3 to 2.7	—	0.7	
Output voltage	H-level	V _{OH}	V _{IN} = V _{IH} or V _{IL}	I _{OH} =-100uA	2.3 to 2.7	Vcc-0.2	—	V
				I _{OH} = -3mA	2.3	2.0	—	
				I _{OH} = -6mA	2.3	1.8	—	
				I _{OH} = -9mA	2.3	1.7	—	
	L-level	V _{OL}	V _{IN} = V _{IH} or V _{IL}	I _{OL} = 100uA	2.3 to 2.7	—	0.2	
				I _{OL} = 6mA	2.3	—	0.4	
				I _{OL} = 9mA	2.3	—	0.6	
Input leakage current			V _{IN} =0 to 3.6V		2.3 to 2.7	—	±2.0	μ A
Power-off leakage current		I _{OFF}	V _{IN} , V _{OUT} =0 to 3.6V		0	—	2.0	μ A
Quiescent supply current		I _{CC}	V _{IN} =V _{CC} or GND		2.3 to 2.7	—	2.0	μ A

DC Characteristics (Ta=-40 to 85°C, 1.65V ≤ Vcc < 2.3V)

Characteristics		Symbol	Test condition		Vcc(V)	Min	Max	Unit
Input voltage	H-Level	V _{IH}	—		1.65 to 2.3	0.7 × Vcc	—	V
	L-Level	V _{IL}	—		1.65 to 2.3	—	0.13 × Vcc	
Output voltage	H-Level	V _{0H}	V _{IN} = V _{IH} or V _{IL}	I _{OH} =-100uA	1.65	Vcc-0.2	—	V
				I _{OH} =-2mA	1.65	1.3	—	
	L-Level	V _{0L}	V _{IN} = V _{IH} or V _{IL}	I _{OL} =2mA	1.65	—	0.2	
Input leakage current		I _{IN}	V _{IN} =0 to 3.6V		1.65	—	±2.0	μ A
Power-off leakage current		I _{OFF}	V _{IN} , V _{OUT} =0 to 3.6V		0	—	2.0	μ A
Quiescent supply current		I _{CC}	V _{IN} =V _{CC} or GND		1.65	—	2.0	μ A

AC Characteristics (Ta=-40 to 85°C, Input: tr=tf=2.0ns, CL=30pF, RL=500Ω)

Characteristics	Symbol	Test condition		Vcc(V)	Min	Max	Unit
Propagation delay time	tpLH tpHL	6 input AND	Figure 1, Figure 2	1.8±0.15	1.0	11.0	ns
				2.5±0.2	0.8	5.5	
				3.3±0.3	0.6	3.7	
		4 input OR		1.8±0.15	1.0	10.0	
				2.5±0.2	0.8	5.0	
				3.3±0.3	0.6	3.5	
		INV.		1.8±0.15	1.0	9.5	
				2.5±0.2	0.8	5.2	
				3.3±0.3	0.6	3.8	
Output to output skew	tosLH tosHL	(Note 11)		1.8±0.15	—	0.5	ns
				2.5±0.2	—	0.5	
				3.3±0.3	—	0.5	

For CL=50pF, add approximately 300ps to the AC maximum specification.

Note 11: Parameter guaranteed by design.

$$(tosLH = |t_{pLHm} - t_{pLHn}|, \quad tosHL = |t_{pHLm} - t_{pHLn}|)$$

Capacitive Characteristics(Ta=25°C)

Characteristics	Symbol	Test Condition		Vcc(V)	Typ.	Unit
Input Capacitance	C _{IN}	—		1.8, 2.5, 3.3	6	pF
Power dissipation capacitance	C _{PD}	6 input AND	fin=10MHz Table 1、(Note12)	1.8, 2.5, 3.3	18	pF
		4 input OR		1.8, 2.5, 3.3	17	
		INV.		1.8, 2.5, 3.3	14	

Note12: C_{PD} is defined as the value of the internal equivalent capacitance which is calculated from the operating current consumption without load.

Average operating current can be obtained by the equation.

$$I_{CC(opr)} = C_{PD} \cdot V_{CC} \cdot V_{IN} + I_{CC}/3 \text{ (per gate)}$$

Table1 C_{PD} Test Condition

Function	Pin															
	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16
6 input AND	P	H	H	H	H	H	X	G	O	X	O	X	X	X	C	V
4 input OR	X	X	X	X	X	X	P	G	C	X	O	L	L	L	O	V
INV.	X	X	X	X	X	X	X	G	O	P	C	X	X	X	O	V

—Symbol explanation—

V=V_{CC}(+3.3V)

G=GND(0V)

H=Logic1(V_{CC})

L=Logic0(GND)

X=Don't care(Fixed to V_{CC} or GND)

O=Open

C=Connect a condenser(30pF) between output terminal and GND.

P=Input pulse with 50% duty cycle.

AC Test Circuit





Figure 1

AC Waveform




Symbol	Vcc		
	3.3±0.3V	2.5±0.2V	1.8±0.15V
V_{IH}	2.7V	Vcc	Vcc
V_M	1.5V	Vcc/2	Vcc/2

Figure 2 t_{pLH} , t_{pHL}

Package Dimensions

VSSOP16-P-0030-0.50

Unit : mm



Weight: 0.03 g (typ.)

RESTRICTIONS ON PRODUCT USE

000707EBA

- TOSHIBA is continually working to improve the quality and reliability of its products. Nevertheless, semiconductor devices in general can malfunction or fail due to their inherent electrical sensitivity and vulnerability to physical stress. It is the responsibility of the buyer, when utilizing TOSHIBA products, to comply with the standards of safety in making a safe design for the entire system, and to avoid situations in which a malfunction or failure of such TOSHIBA products could cause loss of human life, bodily injury or damage to property.
In developing your designs, please ensure that TOSHIBA products are used within specified operating ranges as set forth in the most recent TOSHIBA products specifications. Also, please keep in mind the precautions and conditions set forth in the "Handling Guide for Semiconductor Devices," or "TOSHIBA Semiconductor Reliability Handbook" etc..
- The TOSHIBA products listed in this document are intended for usage in general electronics applications (computer, personal equipment, office equipment, measuring equipment, industrial robotics, domestic appliances, etc.). These TOSHIBA products are neither intended nor warranted for usage in equipment that requires extraordinarily high quality and/or reliability or a malfunction or failure of which may cause loss of human life or bodily injury ("Unintended Usage"). Unintended Usage include atomic energy control instruments, airplane or spaceship instruments, transportation instruments, traffic signal instruments, combustion control instruments, medical instruments, all types of safety devices, etc.. Unintended Usage of TOSHIBA products listed in this document shall be made at the customer's own risk.
- The products described in this document are subject to the foreign exchange and foreign trade laws.
- The information contained herein is presented only as a guide for the applications of our products. No responsibility is assumed by TOSHIBA CORPORATION for any infringements of intellectual property or other rights of the third parties which may result from its use. No license is granted by implication or otherwise under any intellectual property or other rights of TOSHIBA CORPORATION or others.
- The information contained herein is subject to change without notice.