



Switches > Tactile Switches



Actuator Style: Side Actuator

Contact Base Material: Stainless Steel

Switch Contact Plating Material: Silver

Low Profile: Yes

Contact Current Rating: 10 mA

Features

Product Type Features

Leg Style	Gull Wing
Actuator Style	Side Actuator

Configuration Features

Switch Feedback Type	Non-Tactile
ESD Grounding Terminal	Without
Ganged	Without
Configuration (Pole-Throw)	Single Pole - Single Throw
Number of Actuators	Single

Body Features

Actuator Material	Thermoplastic
Actuator Force	150 g[5.29 oz]
Product Orientation	Right Angle
Actuator Color	Black

Contact Features

--	--



Contact Base Material	Stainless Steel
Switch Contact Plating Material	Silver
Contact Current Rating	10 mA

Termination Features

Termination Method to PCB	Surface Mount
---------------------------	---------------

Housing Features

Low Profile	Yes
Process Sealed	No

Usage Conditions

Operating Temperature Range	-10 – 60 °C[14 – 140 °F]
-----------------------------	--------------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUL 2021 (219) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts





TE Part # 2331365-1
DET SW4.7X3.8X2.3 GW VERT. NO
AG RL




TE Part # 2331370-1
DET SW4.7X3.8X2.3 GW VERT. NO
AG RL



TE Part # 2331398-1
DET SW6.5X3.9X6.0 GW VERT. NO
AG TB



TE Part # 2331393-1
DET SW5.7X4.0X2.0 GW HORZ. NO
AG RL



TE Part # 2331394-1
DET SW4.7X3.5X2.25 GW VERT. NOH
AG RL

Also in the Series | ALCOSWITCH JJ




Tactile Switches(52)

Customers Also Bought



TE Part #ANT-418-HETH
Antenna 1/4 Wave Coil 418MHz THM



TE Part #ANT-418-HESM
Antenna 1/4 Wave Coil 418MHz SMT




TE Part #8-1879377-6
CRGH0805 5% 3K3 0.33W




TE Part #2267078-1
TMS6T5B2M2RE



TE Part #1-2307813-0
10P,2MM,BB,REC,SRVT,SMD,0.1AU,TR,
W/CP



TE Part #2331393-1
DET SW5.7X4.0X2.0 GW HORZ. NO
AG RL



TE Part #2331415-1
DET SW4.2X3.6X1.2 JB VERT(DW) NO
AGAU RL



TE Part #CAT-P851-T1
PCB Power Relay: 30 amp, Monostable
DC



Documents

Product Drawings

DET SW5.7X4.0X2.0 GW HORZ. NC AG RL

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2331391-1_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2331391-1_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2331391-1_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

JJ Series Detector Switches Data Sheet

English