


TOSHIBA CMOS DIGITAL INTEGRATED CIRCUIT SILICON MONOLITHIC

TC7SA08F, TC7SA08FU

LOW-VOLTAGE 2-INPUT AND GATE WITH 3.6 V TOLERANT INPUTS AND OUTPUTS

FEATURES

- Low Voltage Operation : $V_{CC} = 1.8 \sim 3.6 \text{ V}$
- High Speed Operation : $t_{pd} = 2.8 \text{ ns (max.)}$
at $V_{CC} = 3.0 \sim 3.6 \text{ V}$
 $t_{pd} = 3.7 \text{ ns (max.)}$
at $V_{CC} = 2.3 \sim 2.7 \text{ V}$
 $t_{pd} = 7.4 \text{ ns (max.)}$
at $V_{CC} = 1.8 \text{ V}$
- 3.6 V Tolerant inputs and outputs.
- Output Current : $I_{OH}/I_{OL} = \pm 24 \text{ mA (min.)}$
at $V_{CC} = 3.0 \text{ V}$
 $I_{OH}/I_{OL} = \pm 18 \text{ mA (min.)}$ at
 $V_{CC} = 2.3 \text{ V}$
 $I_{OH}/I_{OL} = \pm 6 \text{ mA (min.)}$ at
 $V_{CC} = 1.8 \text{ V}$
- Latch-up Performance : $\pm 300 \text{ mA}$
- ESD Performance : Human Body Model $> \pm 2000 \text{ V}$
Machine Model $> \pm 200 \text{ V}$
- Power Down Protection is provided on all inputs and outputs.
- TC74VCX08FT Equivalent



Weight

SSOP5-P-0.95 : 0.016g (Typ.)
SSOP5-P-0.65A : 0.006g (Typ.)

000707EBA1

- TOSHIBA is continually working to improve the quality and reliability of its products. Nevertheless, semiconductor devices in general can malfunction or fail due to their inherent electrical sensitivity and vulnerability to physical stress. It is the responsibility of the buyer, when utilizing TOSHIBA products, to comply with the standards of safety in making a safe design for the entire system, and to avoid situations in which a malfunction or failure of such TOSHIBA products could cause loss of human life, bodily injury or damage to property. In developing your designs, please ensure that TOSHIBA products are used within specified operating ranges as set forth in the most recent TOSHIBA products specifications. Also, please keep in mind the precautions and conditions set forth in the "Handling Guide for Semiconductor Devices," or "TOSHIBA Semiconductor Reliability Handbook" etc..
- The TOSHIBA products listed in this document are intended for usage in general electronics applications (computer, personal equipment, office equipment, measuring equipment, industrial robotics, domestic appliances, etc.). These TOSHIBA products are neither intended nor warranted for usage in equipment that requires extraordinarily high quality and/or reliability or a malfunction or failure of which may cause loss of human life or bodily injury ("Unintended Usage"). Unintended Usage include atomic energy control instruments, airplane or spaceship instruments, transportation instruments, traffic signal instruments, combustion control instruments, medical instruments, all types of safety devices, etc.. Unintended Usage of TOSHIBA products listed in this document shall be made at the customer's own risk.
- The products described in this document are subject to the foreign exchange and foreign trade laws.
- The information contained herein is presented only as a guide for the applications of our products. No responsibility is assumed by TOSHIBA CORPORATION for any infringements of intellectual property or other rights of the third parties which may result from its use. No license is granted by implication or otherwise under any intellectual property or other rights of TOSHIBA CORPORATION or others.
- The information contained herein is subject to change without notice.

MAXIMUM RATINGS

PARAMETER	SYMBOL	RATING	UNIT
Power Supply Voltage	V_{CC}	$-0.5 \sim 4.6$	V
DC Input Voltage	V_{IN}	$-0.5 \sim 4.6$	V
DC Output Voltage	V_{OUT}	$-0.5 \sim 4.6$ (Note 1)	V
		$-0.5 \sim V_{CC} + 0.5$ (Note 2)	
Input Diode Current	I_{IK}	-50	mA
Output Diode Current	I_{OK}	± 50 (Note 3)	mA
DC Output Current	I_{OUT}	± 50	mA
Power Dissipation	P_D	200	mW
DC V_{CC} / Ground Current	I_{CC} / I_{GND}	± 100	mA
Storage Temperature	T_{stg}	$-65 \sim 150$	$^{\circ}\text{C}$

(Note 1) : $V_{CC} = 0\text{ V}$ (Note 2) : High or Low State. I_{OUT} absolute maximum rating must be observed.(Note 3) : $V_{OUT} < \text{GND}$, $V_{OUT} > V_{CC}$

RECOMMENDED OPERATING RANGE

PARAMETER	SYMBOL	RATING	UNIT
Supply Voltage	V_{CC}	1.8~3.6	V
		1.2~3.6 (Note 4)	
Input Voltage	V_{IN}	$-0.3 \sim 3.6$	V
Output Voltage	V_{OUT}	0~3.6 (Note 5)	V
		0~ V_{CC} (Note 6)	
Output Current	I_{OH} / I_{OL}	± 24 (Note 7)	mA
		± 18 (Note 8)	
		± 6 (Note 9)	
Operating Temperature	T_{opr}	$-40 \sim 85$	$^{\circ}\text{C}$
Input Rise And Fall Time	dt / dv	0~10 (Note 10)	ns / V

(Note 4) : Data Retention Only

(Note 5) : $V_{CC} = 0\text{ V}$

(Note 6) : High or Low State

(Note 7) : $V_{CC} = 3.0 \sim 3.6\text{ V}$ (Note 8) : $V_{CC} = 2.3 \sim 2.7\text{ V}$ (Note 9) : $V_{CC} = 1.8\text{ V}$ (Note 10) : $V_{IN} = 0.8 \sim 2.0\text{ V}$, $V_{CC} = 3.0\text{ V}$

ELECTRICAL CHARACTERISTICS

DC characteristics (Ta = -40~85°C, 2.7 V < V_{CC} ≤ 3.6 V)

PARAMETER		SYMBOL	TEST CONDITION		V _{CC} (V)	MIN.	MAX.	UNIT
Input Voltage	“H” Level	V _{IH}			2.7~3.6	2.0	—	V
	“L” Level	V _{IL}			2.7~3.6	—	0.8	
Output Voltage	“H” Level	V _{OH}	V _{IN} = V _{IH}	I _{OH} = - 100 μA	2.7~3.6	V _{CC} - 0.2	—	V
				I _{OH} = - 12 mA	2.7	2.2	—	
				I _{OH} = - 18 mA	3.0	2.4	—	
				I _{OH} = - 24 mA	3.0	2.2	—	
	“L” Level	V _{OL}	V _{IN} = V _{IH} or V _{IL}	I _{OL} = 100 μA	2.7~3.6	—	0.2	
				I _{OL} = 12 mA	2.7	—	0.4	
				I _{OL} = 18 mA	3.0	—	0.4	
				I _{OL} = 24 mA	3.0	—	0.55	
Input Leakage Current		I _{IN}	V _{IN} = 0~3.6 V		2.7~3.6	—	± 5.0	μA
Power Off Leakage Current		I _{OFF}	V _{IN} , V _{OUT} = 0~3.6 V		0	—	10.0	μA
Quiescent Supply Current		I _{CC}	V _{IN} = V _{CC} or GND		2.7~3.6	—	20.0	μA
			V _{CC} ≤ (V _{IN} , V _{OUT}) ≤ 3.6 V		2.7~3.6	—	± 20.0	
Increase In I _{CC} Per Input		ΔI _{CC}	V _{IH} = V _{CC} - 0.6 V		2.7~3.6	—	750	μA

ELECTRICAL CHARACTERISTICS

DC characteristics (Ta = -40~85°C, 2.3 V ≤ V_{CC} ≤ 2.7 V)

PARAMETER		SYMBOL	TEST CONDITION		V _{CC} (V)	MIN.	MAX.	UNIT
Input Voltage	“H” Level	V _{IH}			2.3~2.7	1.6	—	V
	“L” Level	V _{IL}			2.3~2.7	—	0.7	
Output Voltage	“H” Level	V _{OH}	V _{IN} = V _{IH}	I _{OH} = - 100 μA	2.3~2.7	V _{CC} - 0.2	—	V
				I _{OH} = - 6 mA	2.3	2.0	—	
				I _{OH} = - 12 mA	2.3	1.8	—	
				I _{OH} = - 18 mA	2.3	1.7	—	
	“L” Level	V _{OL}	V _{IN} = V _{IH} or V _{IL}	I _{OL} = 100 μA	2.3~2.7	—	0.2	
				I _{OL} = 12 mA	2.3	—	0.4	
				I _{OL} = 18 mA	2.3	—	0.6	
Input Leakage Current		I _{IN}	V _{IN} = 0~3.6 V		2.3~2.7	—	± 5.0	μA
Power Off Leakage Current		I _{OFF}	V _{IN} , V _{OUT} = 0~3.6 V		0	—	10.0	μA
Quiescent Supply Current		I _{CC}	V _{IN} = V _{CC} or GND		2.3~2.7	—	20.0	μA
			V _{CC} ≤ (V _{IN} , V _{OUT}) ≤ 3.6 V _{CC}		2.3~2.7	—	± 20.0	

ELECTRICAL CHARACTERISTICS

DC characteristics (Ta = -40~85°C, 1.8 V ≤ V_{CC} < 2.3 V)

PARAMETER		SYMBOL	TEST CONDITION			V _{CC} (V)	MIN.	MAX.	UNIT
Input Voltage	“H” Level	V _{IH}				1.8~2.3	0.7 × V _{CC}	—	V
	“L” Level	V _{IL}				1.8~2.3	—	0.2 × V _{CC}	
Output Voltage	“H” Level	V _{OH}	V _{IN} = V _{IH}	I _{OH} = - 100 μA	1.8	V _{CC} - 0.2	—	V	
				I _{OH} = - 6 mA	1.8	1.4	—		
	“L” Level	V _{OL}	V _{IN} = V _{IH} or V _{IL}	I _{OL} = 100 μA	1.8	—	0.2		
				I _{OL} = 6 mA	1.8	—	0.3		
Input Leakage Current		I _{IIN}	V _{IN} = 0~3.6 V			1.8	—	± 5.0	μA
Power Off Leakage Current		I _{OFF}	V _{IN} , V _{OUT} = 0~3.6 V			0	—	10.0	μA
Quiescent Supply Current		I _{CC}	V _{IN} = V _{CC} or GND			1.8	—	20.0	μA
			V _{CC} ≤ (V _{IN} , V _{OUT}) ≤ 3.6 V			1.8	—	± 20.0	

AC characteristics (Ta = -40~85°C, Input t_r = t_f = 2.0 ns, C_L = 30 pF, R_L = 500 Ω)

PARAMETER		SYMBOL	TEST CONDITION		V _{CC} (V)	MIN.	MAX.	UNIT
Propagation Delay Time		t _{pLH} t _{pHL}	(Fig.1, 2)		1.8	1.5	7.4	ns
					2.5 ± 0.2	1.0	3.7	
					3.3 ± 0.3	0.8	2.8	

For C_L = 50 pF, add approximately 300 ps to the AC maximum specification.Dynamic switching characteristics (Ta = 25°C, Input t_r = t_f = 2.0 ns, C_L = 30 pF)

PARAMETER		SYMBOL	TEST CONDITION		V _{CC} (V)	TYP.	UNIT
Quiet Output Maximum Dynamic V _{OL}		V _{OLP}	V _{IH} = 1.8 V, V _{IL} = 0 V (Note 11)		1.8	0.25	V
			V _{IH} = 2.5 V, V _{IL} = 0 V (Note 11)		2.5	0.6	
			V _{IH} = 3.3 V, V _{IL} = 0 V (Note 11)		3.3	0.8	
Quiet Output Minimum Dynamic V _{OL}		V _{OLV}	V _{IH} = 1.8 V, V _{IL} = 0 V (Note 11)		1.8	-0.25	V
			V _{IH} = 2.5 V, V _{IL} = 0 V (Note 11)		2.5	-0.6	
			V _{IH} = 3.3 V, V _{IL} = 0 V (Note 11)		3.3	-0.8	
Quiet Output Minimum Dynamic V _{OH}		V _{OHV}	V _{IH} = 1.8 V, V _{IL} = 0 V (Note 11)		1.8	1.5	V
			V _{IH} = 2.5 V, V _{IL} = 0 V (Note 11)		2.5	1.9	
			V _{IH} = 3.3 V, V _{IL} = 0 V (Note 11)		3.3	2.2	

(Note 11) : Parameter guaranteed by design.

Capacitive characteristics (Ta = 25°C)

PARAMETER	SYMBOL	TEST CONDITION	V _{CC} (V)	TYP.	UNIT
			1.8, 2.5, 3.3		
Input Capacitance	C _{IN}	—	1.8, 2.5, 3.3	6	pF
Power Dissipation Capacitance	C _{PD}	f _{IN} = 10 MHz (Note 12)	1.8, 2.5, 3.3	20	pF


(Note 12) : C_{PD} is defined as the value of the internal equivalent capacitance which is calculated from the operating current consumption without load.

Average operating current can be obtained by the equation :

$I_{CC} (opr.) = C_{PD} \cdot V_{CC} \cdot f_{IN} + I_{CC}$


TEST CIRCUIT

Fig.1




AC WAVEFORM

Fig.2 t_{pLH}, t_{pHL}




SYMBOL	V _{CC}		
	3.3 ± 0.3 V	2.5 ± 0.2 V	1.8 V
V _{IH}	2.7 V	V _{CC}	V _{CC}
V _M	1.5 V	V _{CC} / 2	V _{CC} / 2

MARKING



PIN ASSIGNMENT (TOP VIEW)



TRUTH TABLE


INPUTS		OUTPUTS
A	B	Y
L	L	L
L	H	L
H	L	L
H	H	H

LOGIC DIAGRAM



PACKAGE DIMENSIONS
SSOP5-P-0.95


Unit : mm



Weight : 0.016 g (Typ.)

PACKAGE DIMENSIONS
SSOP5-P-0.65A

Unit : mm



Weight : 0.006 g (Typ.)