



No.390, Yong He Road,
Shanghai 200072, China

TECHNICAL DATA SHEET CABLE ASSEMBLY

PART NUMBER :R284C0351028

Issue : NA

Date : NA


Customer :

Specification : NA

Issue : NA

Date : N/A

All dimensions are in mm



Connectors designation :

Connector 1 :BNC straight plug crimp type cable
2.6/50 S (R141.075.000)

Connector 2 : SMB straight plug crimp type
cable 2.6/50+75 S (R114.075.000)

Cable designation :

Flexible Cable 2.6/50S (RG174)

Nominal length :

C291.150.000
Lg: 1000 mm

Cable colour :

Black

Outer diameter :

2.79 mm

Accessories :

Plastic Boots (R280.560.000 / R280.566.000)

ELECTRICAL CHARACTERISTICS :

High Frequency

Characteristic impedance : 50 ± 2 Ohms

Frequency range : DC-1GHz

Insertion Loss : 1.64 dB max @ 1GHz & 20°C

VSWR. : TBT

Low Frequency

Insulation Resistance : 1000 MOhms min

Voltage Rating : 335 Veff max

MECHANICAL CHARACTERISTICS :

Recommend min. bend radius : 10 mm

Cable crush resistance : NA

Life (connectors) : 500 cycles

ENVIRONMENTAL CHARACTERISTICS :

Operating temperature range : -40 ° C to +85 ° C

Remark : NA

Attachment : R141.075.000-TDS , R114.075.000-TDS

C291.150.000 (RG174)-TDS

Cable Assembly is RoHS compliant.

CUSTOMER'S APPROVAL

Service or
Company's stamp

Name
Date

Jacob	A	2007-6-11	Creation	Willy
Name	Issue	Date	Modification	Checked by



No.390, Yong He Road,
Shanghai 200072, China

TECHNICAL DATA SHEET CABLE ASSEMBLY

PART NUMBER :R284C0351029

Issue : NA

Date : NA


Customer :

Specification : NA

Issue : NA

Date : N/A

All dimensions are in mm



Connectors designation :

Connector 1 : N straight plug full crimp type cable 5/50 S (R161.082.000) Connector 2 : N straight plug full crimp type cable 5/50 S (R161.082.000)

Cable designation :

Flexible Cable 5/50S (RG58)

Nominal length :

C291.305.000
Lg: 500 mm

Cable colour :

Black

Outer diameter :

4.95 mm

Accessories :

Plastic Boots (R280.570.000)

ELECTRICAL CHARACTERISTICS :

High Frequency

Characteristic impedance : 50 ± 2 Ohms

Frequency range : DC-1GHz

Insertion Loss : 0.55 dB max @ 1GHz & 20°C

VSWR. : TBT

Low Frequency

Insulation Resistance : 5000 MOhms min

Voltage Rating : 850 Veff max

MECHANICAL CHARACTERISTICS :

Recommend min. bend radius : 20 mm

Cable crush resistance : NA

Life (connectors) : 500 cycles

ENVIRONMENTAL CHARACTERISTICS :

Operating temperature range : -40 ° C to +85 ° C

Remark : NA

Attachment : R161.082.000-TDS

C291.305.000 (RG58)-TDS

Cable Assembly is RoHS compliant.

CUSTOMER'S APPROVAL

Service or
Company's stamp

Name
Date

Jacob

A

2007-6-11

Creation

Willy

Name

Issue

Date

Modification

Checked by



No.390, Yong He Road,
Shanghai 200072, China

TECHNICAL DATA SHEET CABLE ASSEMBLY

PART NUMBER :R284C0351030

Issue : NA

Date : NA


Customer :

Specification : NA

Issue : NA

Date : N/A

All dimensions are in mm



Connectors designation :

Connector 1 : N straight plug full crimp type cable 5/50 S (R161.082.000) Connector 2 : N straight plug full crimp type cable 5/50 S (R161.082.000)

Cable designation :

Flexible Cable 5/50S (RG58)

Nominal length :

C291.305.000
Lg: 1000 mm

Cable colour :

Black

Outer diameter :

4.95 mm

Accessories :

Plastic Boots (R280.570.000)

ELECTRICAL CHARACTERISTICS :

High Frequency

Characteristic impedance : 50 ± 2 Ohms

Frequency range : DC-1GHz

Insertion Loss : 1.01 dB max @ 1GHz & 20°C

VSWR. : TBT

Low Frequency

Insulation Resistance : 5000 MOhms min

Voltage Rating : 850 Veff max

MECHANICAL CHARACTERISTICS :

Recommend min. bend radius : 20 mm

Cable crush resistance : NA

Life (connectors) : 500 cycles

ENVIRONMENTAL CHARACTERISTICS :

Operating temperature range : -40°C to $+85^{\circ}\text{C}$

Remark : NA

Attachment : R161.082.000-TDS

C291.305.000 (RG58)-TDS

Cable Assembly is RoHS compliant.

CUSTOMER'S APPROVAL

Service or
Company's stamp

Name
Date

Jacob

A

2007-6-11

Creation

Willy

Name

Issue

Date

Modification

Checked by



No.390, Yong He Road,
Shanghai 200072, China

TECHNICAL DATA SHEET CABLE ASSEMBLY

PART NUMBER :R284C0351031

Issue : NA

Date : NA


Customer :

Specification : NA

Issue : NA

Date : N/A

All dimensions are in mm



Connectors designation :

Connector 1 : N straight plug full crimp type cable 5/50 S (R161.082.000) Connector 2 : N right angle plug crimp type cable 5/50 S (R161.182.000)

Cable designation :

Flexible Cable 5/50S (RG58)

Nominal length :

C291.305.000
Lg: 500 mm

Cable colour :

Black

Outer diameter :

4.95 mm

Accessories :

Plastic Boots (R280.570.000)

ELECTRICAL CHARACTERISTICS :

High Frequency

Characteristic impedance : 50 ± 2 Ohms

Frequency range : DC-1GHz

Insertion Loss : 0.55 dB max @ 1GHz & 20°C

VSWR. : TBT

Low Frequency

Insulation Resistance : 5000 MOhms min

Voltage Rating : 850 Veff max

MECHANICAL CHARACTERISTICS :

Recommend min. bend radius : 20 mm

Cable crush resistance : NA

Life (connectors) : 500 cycles

ENVIRONMENTAL CHARACTERISTICS :

Operating temperature range : -40 ° C to +85 ° C

Remark : NA

Attachment : R161.082.000-TDS, R161.182.000-TDS

C291.305.000 (RG58)-TDS

Cable Assembly is RoHS compliant.

CUSTOMER'S APPROVAL

Service or
Company's stamp

Name
Date

Jacob

A

2007-6-11

Creation

Willy

Name

Issue

Date

Modification

Checked by



No.390, Yong He Road,
Shanghai 200072, China

TECHNICAL DATA SHEET CABLE ASSEMBLY

PART NUMBER :R284C0351032

Issue : NA

Date : NA


Customer :

Specification : NA

Issue : NA

Date : N/A

All dimensions are in mm



Connectors designation :

Connector 1 : N straight plug full crimp type cable 5/50 S (R161.082.000) Connector 2 : N right angle plug crimp type cable 5/50 S (R161.182.000)

Cable designation :

Flexible Cable 5/50S (RG58)

Nominal length :

C291.305.000

Lg: 1000 mm

Cable colour :

Black

Outer diameter :

4.95 mm

Accessories :

Plastic Boots (R280.570.000)

ELECTRICAL CHARACTERISTICS :

High Frequency

Characteristic impedance : 50 ± 2 Ohms

Frequency range : DC-1GHz

Insertion Loss : 1.01 dB max @ 1GHz & 20°C

VSWR. : TBT

Low Frequency

Insulation Resistance : 5000 MOhms min

Voltage Rating : 850 Veff max

MECHANICAL CHARACTERISTICS :

Recommend min. bend radius : 20 mm

Cable crush resistance : NA

Life (connectors) : 500 cycles

ENVIRONMENTAL CHARACTERISTICS :

Operating temperature range : -40 ° C to +85 ° C

Remark : NA

Attachment : R161.082.000-TDS, R161.182.000-TDS

C291.305.000 (RG58)-TDS

Cable Assembly is RoHS compliant.

CUSTOMER'S APPROVAL

Service or
Company's stamp

Name
Date

Jacob	A	2007-6-11	Creation	Willy
Name	Issue	Date	Modification	Checked by



No.390, Yong He Road,
Shanghai 200072, China

TECHNICAL DATA SHEET CABLE ASSEMBLY

PART NUMBER :R284C0351033

Issue : NA

Date : NA


Customer :

Specification : NA

Issue : NA

Date : N/A

All dimensions are in mm



Connectors designation :

Connector 1 : N straight plug full crimp type cable 5/50 D (R161.083.000) Connector 2 : N straight plug full crimp type cable 5/50 D (R161.083.000)

Cable designation :

Flexible Cable 5/50D (RG142)

Nominal length :

C291.320.007

Lg: 500 mm

Cable colour :

Black

Outer diameter :

4.95 mm

Accessories :

Plastic Boots (R280.570.000)

ELECTRICAL CHARACTERISTICS :

High Frequency

Characteristic impedance : 50 ± 2 Ohms

Frequency range : DC-11GHz

Insertion Loss : 0.56 dB max @ 3GHz & 20°C

VSWR. : TBT

Low Frequency

Insulation Resistance : 5000 MOhms min

Voltage Rating : 850 Veff max

MECHANICAL CHARACTERISTICS :

Recommend min. bend radius : 25 mm

Cable crush resistance : NA

Life (connectors) : 500 cycles

ENVIRONMENTAL CHARACTERISTICS :

Operating temperature range : -55 ° C to +155 ° C

Remark : NA

Attachment : R161.083.000-TDS

C291.320.007 (RG142)-TDS

Cable Assembly is RoHS compliant.

CUSTOMER'S APPROVAL

Service or
Company's stamp

Name
Date

Jacob	A	2007-6-11	Creation	Willy
Name	Issue	Date	Modification	Checked by



No.390, Yong He Road,
Shanghai 200072, China

TECHNICAL DATA SHEET CABLE ASSEMBLY

PART NUMBER :R284C0351034

Issue : NA

Date : NA


Customer :

Specification : NA

Issue : NA

Date : N/A

All dimensions are in mm



Connectors designation :

Connector 1 :N straight plug full crimp type cable 5/50 D (R161.083.000) Connector 2 : N straight plug full crimp type cable 5/50 D (R161.083.000)

Cable designation :

Flexible Cable 5/50D (RG142)

Nominal length :

C291.320.007

Lg: 1000 mm

Cable colour :

Black

Outer diameter :

4.95 mm

Accessories :

Plastic Boots (R280.570.000)

ELECTRICAL CHARACTERISTICS :

High Frequency

Characteristic impedance : 50 ± 2 Ohms

Frequency range : DC-11GHz

Insertion Loss : 1.01 dB max @ 3GHz & 20°C

VSWR. : TBT

Low Frequency

Insulation Resistance : 5000 MOhms min

Voltage Rating : 850 Veff max

MECHANICAL CHARACTERISTICS :

Recommend min. bend radius : 25 mm

Cable crush resistance : NA

Life (connectors) : 500 cycles

ENVIRONMENTAL CHARACTERISTICS :

Operating temperature range : -55 ° C to +155 ° C

Remark : NA

Attachment : R161.082.000-TDS

C291.320.007 (RG142)-TDS

Cable Assembly is RoHS compliant.

CUSTOMER'S APPROVAL

Service or
Company's stamp

Name
Date

Jacob

A

2007-6-11

Creation

Willy

Name

Issue

Date

Modification

Checked by



No.390, Yong He Road,
Shanghai 200072, China

TECHNICAL DATA SHEET CABLE ASSEMBLY

PART NUMBER :R284C0351035

Issue : NA

Date : NA


Customer :

Specification : NA

Issue : NA

Date : N/A

All dimensions are in mm



Connectors designation :

Connector 1 : N straight plug full crimp type cable 5/50 D (R161.083.000) Connector 2 : N right angle plug crimp type cable 5/50 D (R161.183.000)

Cable designation :

Flexible Cable 5/50D (RG142)

Nominal length :

C291.320.007
Lg: 500 mm

Cable colour :

Black

Outer diameter :

4.95 mm

Accessories :

Plastic Boots (R280.570.000)

ELECTRICAL CHARACTERISTICS :

High Frequency

Characteristic impedance : 50 ± 2 Ohms

Frequency range : DC-11GHz

Insertion Loss : 0.56 dB max @ 3GHz & 20°C

VSWR. : TBT

Low Frequency

Insulation Resistance : 5000 MOhms min

Voltage Rating : 850 Veff max

MECHANICAL CHARACTERISTICS :

Recommend min. bend radius : 25 mm

Cable crush resistance : NA

Life (connectors) : 500 cycles

ENVIRONMENTAL CHARACTERISTICS :

Operating temperature range : -55 ° C to +155 ° C

Remark : NA

Attachment : R161.083.000-TDS, R161.183.00-TDS

C291.320.007 (RG142)-TDS

Cable Assembly is RoHS compliant.

CUSTOMER'S APPROVAL

Service or
Company's stamp

Name
Date

Jacob

A

2007-6-11

Creation

Willy

Name

Issue

Date

Modification

Checked by



No.390, Yong He Road,
Shanghai 200072, China

TECHNICAL DATA SHEET CABLE ASSEMBLY

PART NUMBER :R284C0351036

Issue : NA

Date : NA


Customer :

Specification : NA

Issue : NA

Date : N/A

All dimensions are in mm



Connectors designation :

Connector 1 : N straight plug full crimp type cable 5/50 D (R161.083.000) Connector 2 : N right angle plug crimp type cable 5/50 D (R161.183.000)

Cable designation :

Flexible Cable 5/50D (RG142)

Nominal length :

C291.320.007

Lg: 1000 mm

Cable colour :

Black

Outer diameter :

4.95 mm

Accessories :

Plastic Boots (R280.570.000)

ELECTRICAL CHARACTERISTICS :

High Frequency

Characteristic impedance : 50 ± 2 Ohms

Frequency range : DC-11GHz

Insertion Loss : 1.01 dB max @ 3GHz & 20°C

VSWR. : TBT

Low Frequency

Insulation Resistance : 5000 MOhms min

Voltage Rating : 850 Veff max

MECHANICAL CHARACTERISTICS :

Recommend min. bend radius : 25 mm

Cable crush resistance : NA

Life (connectors) : 500 cycles

ENVIRONMENTAL CHARACTERISTICS :

Operating temperature range : -55 ° C to +155 ° C

Remark : NA

Attachment : R161.082.000-TDS, R161.183.000-TDS

C291.320.007 (RG142)-TDS

Cable Assembly is RoHS compliant.

CUSTOMER'S APPROVAL

Service or
Company's stamp

Name
Date

Jacob

A

2007-6-11

Creation

Willy

Name

Issue

Date

Modification

Checked by



No.390, Yong He Road,
Shanghai 200072, China

TECHNICAL DATA SHEET CABLE ASSEMBLY

PART NUMBER :R284C0351037

Issue : NA

Date : NA


Customer :

Specification : NA

Issue : NA

Date : N/A

All dimensions are in mm



Connectors designation :

Connector 1 : N straight plug full crimp type cable 10/50 S (R161.075.000) Connector 2 : N straight plug full crimp type cable 10/50 S (R161.075.000)

Cable designation :

Flexible Cable 10/50S (RG213)
C291.510.000

Nominal length :

Lg: 1000 mm

Cable colour :

Black

Outer diameter :

10.30 mm

Accessories :

HeatShrink Sleeves (9.11.95.000.94)

ELECTRICAL CHARACTERISTICS :

High Frequency

Characteristic impedance : 50 ± 2 Ohms

Frequency range : DC-1GHz

Insertion Loss : 0.45 dB max @ 1GHz & 20°C

VSWR. : TBT

Low Frequency

Insulation Resistance : 5000 MOhms min

Voltage Rating : 1400 Veff max

MECHANICAL CHARACTERISTICS :

Recommend min. bend radius : 40 mm

Cable crush resistance : NA

Life (connectors) : 500 cycles

ENVIRONMENTAL CHARACTERISTICS :

Operating temperature range : -40 ° C to +85 ° C

Remark : NA

Attachment : R161.075.000-TDS

C291.510.000 (RG213)-TDS

Cable Assembly is RoHS compliant.

CUSTOMER'S APPROVAL

Service or
Company's stamp

Name
Date

Jacob

A

2007-6-11

Creation

Willy

Name

Issue

Date

Modification

Checked by



No.390, Yong He Road,
Shanghai 200072, China

TECHNICAL DATA SHEET CABLE ASSEMBLY

PART NUMBER :R284C0351038

Issue : NA

Date : NA


Customer :

Specification : NA

Issue : NA

Date : N/A

All dimensions are in mm



Connectors designation :

Connector 1 : N straight plug full crimp type cable 10/50 S (R161.075.000) Connector 2 : N straight plug full crimp type cable 10/50 S (R161.075.000)

Cable designation :

Flexible Cable 10/50S (RG213)
C291.510.000

Nominal length :

Lg: 2000 mm

Cable colour :

Black

Outer diameter :

10.30 mm

Accessories :

HeatShrink Sleeves (9.11.95.000.94)

ELECTRICAL CHARACTERISTICS :

High Frequency

Characteristic impedance : 50 ± 2 Ohms

Frequency range : DC-1GHz

Insertion Loss : 0.82 dB max @ 1GHz & 20°C

VSWR. : TBT

Low Frequency

Insulation Resistance : 5000 MOhms min

Voltage Rating : 1400 Veff max

MECHANICAL CHARACTERISTICS :

Recommend min. bend radius : 40 mm

Cable crush resistance : NA

Life (connectors) : 500 cycles

ENVIRONMENTAL CHARACTERISTICS :

Operating temperature range : -40 ° C to +85 ° C

Remark : NA

Attachment : R161.075.000-TDS

C291.510.000 (RG213)-TDS

Cable Assembly is RoHS compliant.

CUSTOMER'S APPROVAL

Service or
Company's stamp

Name
Date

Jacob

A

2007-6-11

Creation

Willy

Name

Issue

Date

Modification

Checked by



PART NUMBER: R284C0351039

Issue : NA

Date : NA


Customer :

Specification : NA

Issue : NA

Date : N/A

All dimensions are in mm



Connectors designation :

Connector 1 :N straight plug full crimp type cable 10/50 S (R161.075.000)	Connector 2 : N straight plug full crimp type cable 10/50 S (R161.075.000)
--	---

Cable designation :

Flexible Cable 10/50S (RG213)

Nominal length :

Lg: 3000 mm

Cable colour :

Black

Outer diameter :

10.30 mm

Accessories :

HeatShrink Sleeves (9.11.95.000.94)

ELECTRICAL CHARACTERISTICS :

High Frequency

Characteristic impedance : **50 ± 2 Ohms**

Frequency range : **DC-1GHz**

Insertion Loss : **1.19 dB max @ 1GHz & 20°C**

VSWR. : TBT

Low Frequency

Insulation Resistance : **5000 MOhms min**

Voltage Rating : **1400 V_{eff} max**

MECHANICAL CHARACTERISTICS :

Recommend min. bend radius : 40 mm

Cable crush resistance : **NA**

Life (connectors) : **500 cycles**

ENVIRONMENTAL CHARACTERISTICS :

Operating temperature range : **-40 ° C to +85 ° C**

Remark : NA

Attachment : **R161.075.000-TDS**

C291.510.000 (RG213)-TDS

Cable Assembly is RoHS compliant.

CUSTOMER'S APPROVAL

Service or
Company's stamp

Name
Date

Jacob	A	2007-6-11	Creation	Willy
Name	Issue	Date	Modification	Checked by



No.390, Yong He Road,
Shanghai 200072, China

TECHNICAL DATA SHEET CABLE ASSEMBLY

PART NUMBER :R284C0351040

Issue : NA

Date : NA


Customer :

Specification : NA

Issue : NA

Date : N/A

All dimensions are in mm



Connectors designation :

Connector 1 : N straight plug full crimp type cable 10/50 S (R161.075.000) Connector 2 : N straight plug full crimp type cable 10/50 S (R161.075.000)

Cable designation :

Flexible Cable 10/50S (RG213)

Nominal length :

C291.510.000
Lg: 5000 mm

Cable colour :

Black

Outer diameter :

10.30 mm

Accessories :

HeatShrink Sleeves (9.11.95.000.94)

ELECTRICAL CHARACTERISTICS :

High Frequency

Characteristic impedance : 50 ± 2 Ohms

Frequency range : DC-1GHz

Insertion Loss : 1.92 dB max @ 1GHz & 20°C

VSWR. : TBT

Low Frequency

Insulation Resistance : 5000 MOhms min

Voltage Rating : 1400 Veff max

MECHANICAL CHARACTERISTICS :

Recommend min. bend radius : 40 mm

Cable crush resistance : NA

Life (connectors) : 500 cycles

ENVIRONMENTAL CHARACTERISTICS :

Operating temperature range : -40 ° C to +85 ° C

Remark : NA

Attachment : R161.075.000-TDS

C291.510.000 (RG213)-TDS

Cable Assembly is RoHS compliant.

CUSTOMER'S APPROVAL

Service or
Company's stamp

Name
Date

Jacob

A

2007-6-11

Creation

Willy

Name

Issue

Date

Modification

Checked by



No.390, Yong He Road,
Shanghai 200072, China

TECHNICAL DATA SHEET CABLE ASSEMBLY

PART NUMBER :R284C0351041

Issue : NA

Date : NA


Customer :

Specification : NA

Issue : NA

Date : N/A

All dimensions are in mm



Connectors designation :

Connector 1 : N straight plug full crimp type cable 11/50 D (R161.088.000) Connector 2 : N straight plug full crimp type cable 11/50 D (R161.088.000)

Cable designation :

Flexible Cable 11/50D (RG214)

Nominal length :

C291.600.000
Lg: 1000 mm

Cable colour :

Black

Outer diameter :

10.80 mm

Accessories :

HeatShrink Sleeves (9.11.95.000.12)

ELECTRICAL CHARACTERISTICS :

High Frequency

Characteristic impedance : 50 ± 2 Ohms

Frequency range : DC-11GHz

Insertion Loss : 0.63 dB max @ 3GHz & 20°C

VSWR. : TBT

Low Frequency

Insulation Resistance : 5000 MOhms min

Voltage Rating : 1400 Veff max

MECHANICAL CHARACTERISTICS :

Recommend min. bend radius : 40 mm

Cable crush resistance : NA

Life (connectors) : 500 cycles

ENVIRONMENTAL CHARACTERISTICS :

Operating temperature range : -40 ° C to +85 ° C

Remark : NA

Attachment : R161.088.000-TDS

C291.600.000 (RG214)-TDS

Cable Assembly is RoHS compliant.

CUSTOMER'S APPROVAL

Service or
Company's stamp

Name
Date

Jacob

A

2007-6-11

Creation

Willy

Name

Issue

Date

Modification

Checked by



No.390, Yong He Road,
Shanghai 200072, China

TECHNICAL DATA SHEET CABLE ASSEMBLY

PART NUMBER :R284C0351042

Issue : NA

Date : NA


Customer :

Specification : NA

Issue : NA

Date : N/A

All dimensions are in mm



Connectors designation :

Connector 1 : N straight plug full crimp type cable 11/50 D (R161.088.000) Connector 2 : N straight plug full crimp type cable 11/50 D (R161.088.000)

Cable designation :

Flexible Cable 11/50D (RG214)

Nominal length :

C291.600.000

Lg: 2000 mm

Cable colour :

Black

Outer diameter :

10.80 mm

Accessories :

HeatShrink Sleeves (9.11.95.000.12)

ELECTRICAL CHARACTERISTICS :

High Frequency

Characteristic impedance : 50 ± 2 Ohms

Frequency range : DC-11GHz

Insertion Loss : 1.14 dB max @ 3GHz & 20°C

VSWR. : TBT

Low Frequency

Insulation Resistance : 5000 MOhms min

Voltage Rating : 1400 Veff max

MECANICAL CHARACTERISTICS :

Recommend min. bend radius : 40 mm

Cable crush resistance : NA

Life (connectors) : 500 cycles

ENVIRONMENTAL CHARACTERISTICS :

Operating temperature range : -40 ° C to +85 ° C

Remark : NA

Attachment : R161.088.000-TDS

C291.600.000 (RG214)-TDS

Cable Assembly is RoHS compliant.

CUSTOMER'S APPROVAL

Service or
Company's stamp

Name
Date

Jacob

A

2007-6-11

Creation

Willy

Name

Issue

Date

Modification

Checked by



No.390, Yong He Road,
Shanghai 200072, China

TECHNICAL DATA SHEET CABLE ASSEMBLY

PART NUMBER :R284C0351043

Issue : NA

Date : NA


Customer :

Specification : NA

Issue : NA

Date : N/A

All dimensions are in mm



Connectors designation :

Connector 1 : N straight plug full crimp type cable 11/50 D (R161.088.000) Connector 2 : N straight plug full crimp type cable 11/50 D (R161.088.000)

Cable designation :

Flexible Cable 11/50D (RG214)

Nominal length :

C291.600.000
Lg: 3000 mm

Cable colour :

Black

Outer diameter :

10.80 mm

Accessories :

HeatShrink Sleeves (9.11.95.000.12)

ELECTRICAL CHARACTERISTICS :

High Frequency

Characteristic impedance : 50 ± 2 Ohms

Frequency range : DC-11GHz

Insertion Loss : 1.66 dB max @ 3GHz & 20°C

VSWR. : TBT

Low Frequency

Insulation Resistance : 5000 MOhms min

Voltage Rating : 1400 Veff max

MECANICAL CHARACTERISTICS :

Recommend min. bend radius : 40 mm

Cable crush resistance : NA

Life (connectors) : 500 cycles

ENVIRONMENTAL CHARACTERISTICS :

Operating temperature range : -40 ° C to +85 ° C

Remark : NA

Attachment : R161.088.000-TDS

C291.600.000 (RG214)-TDS

Cable Assembly is RoHS compliant.

CUSTOMER'S APPROVAL

Service or
Company's stamp

Name
Date

Jacob

A

2007-6-11

Creation

Willy

Name

Issue

Date

Modification

Checked by



No.390, Yong He Road,
Shanghai 200072, China

TECHNICAL DATA SHEET CABLE ASSEMBLY

PART NUMBER :R284C0351044

Issue : NA

Date : NA


Customer :

Specification : NA

Issue : NA

Date : N/A

All dimensions are in mm



Connectors designation :

Connector 1 : N straight plug full crimp type cable 11/50 D (R161.088.000) Connector 2 : N straight plug full crimp type cable 11/50 D (R161.088.000)

Cable designation :

Flexible Cable 11/50D (RG214)

Nominal length :

C291.600.000
Lg: 5000 mm

Cable colour :

Black

Outer diameter :

10.80 mm

Accessories :

HeatShrink Sleeves (9.11.95.000.12)

ELECTRICAL CHARACTERISTICS :

High Frequency

Characteristic impedance : 50 ± 2 Ohms

Frequency range : DC-11GHz

Insertion Loss : 2.68 dB max @ 3GHz & 20°C

VSWR. : TBT

Low Frequency

Insulation Resistance : 5000 MOhms min

Voltage Rating : 1400 Veff max

MECHANICAL CHARACTERISTICS :

Recommend min. bend radius : 40 mm

Cable crush resistance : NA

Life (connectors) : 500 cycles

ENVIRONMENTAL CHARACTERISTICS :

Operating temperature range : -40 ° C to +85 ° C

Remark : NA

Attachment : R161.088.000-TDS

C291.600.000 (RG214)-TDS

Cable Assembly is RoHS compliant.

CUSTOMER'S APPROVAL

Service or
Company's stamp

Name
Date

Jacob

A

2007-6-11

Creation

Willy

Name

Issue

Date

Modification

Checked by