


 8.0 ± 0.26
 $(.31 \pm .01)$ TYP.


 $14.0 \pm .50$
 $(.55 \pm .02)$ TYP.

The drawing shows three horizontal dimension lines with arrows at both ends:

- Top Dimension:** A long dimension line spanning most of the width, labeled 2000 ± 3.3 with a tolerance box below it containing $(78.74 \pm .13)$.
- Middle Dimension:** A shorter dimension line starting from the left edge, labeled 1950 REF with a tolerance box below it containing (76.77) . To its right are two triangular feature callouts labeled 'C' and 'F'.
- Bottom Dimension:** A short dimension line near the bottom right, labeled 50.0 ± 0.76 with a tolerance box below it containing $(1.97 \pm .03)$. The word "TYP." is written to the right of this dimension.

50.0 ± 0.76 TYP.
(1.97 ± 0.03)

- 4.5 ± 0.26
(- 1.8 + 0.1) TYP.

-25.0 ± 0.50
(.98 + .02)

$$-12.5 \pm 0.76$$

$$(.49 \pm .03)$$
$$-6.5 \pm 0.26_{\text{TYP.}} \\ (.26 \pm .01)$$
 $\pm 0.5 \quad (\pm .020)$ $\pm 0.5 \quad (\pm .020)$

MOUNTING HOLE DIMENSIONS

B

1. "B" MEASURED AT BASE.
2. STANDARD LENGTH: 2 METER.
3. SEE CURRENT CATALOG FOR PART NUMBER DESIGNATIONS FOR TYPE, COLOR, AND LENGTH.
4. DUCT TYPE "NNC" PACKAGED WITH TYPE "NC" COVER.
5. DIMENSIONS ARE METRIC (INCHES).


Technical drawing of a U-shaped profile. The drawing shows a cross-section of the profile with the following dimensions and tolerances:

- Height:** H REF
- Width:** B REF
- Thickness:** T
- Positional Tolerance:** ± 0.50

FOR 75mm WALL HGT.

FOR 37.5mm AND 50mm
76 WALL HGT.

CHANNEL EXAMPLE:
NNC 37 x 50 LG 2
 TYPE 37mm WIDE 50mm HIGH
 COLOR (LIGHT GRAY) LENGTH (m)

D38539AA_DC_NNC_01B.PRT

PANDUIT

CORP. TINLEY PARK, ILLINOIS

WIRING DUCT AND COVER
TYPE "NNC" METRIC
CUSTOMER DRAWING

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:

(.X)	±	(.XXX)	±
(.XX)	± 3.1	ANGLES	±

UNLESS OTHERWISE SPECIFIED

ALL DIMENSIONS ARE GIVEN
IN INCHES. THIRD ANGLE PROJECTION.

DRAWN BY
JHNU

DATE	8-2-02
------	--------

CHK'D	JKG
-------	-----

MAT'L: HALOGEN FREE
MODIFIED
POLYPHENYLENE
OXIDE
(PPO)

SCALE

NONE

DRAWING NO.
38539-04
Sht 1 of 3


DWG
A
SIZE

---	-----	---	---	F. CHANGED TOLERANCE E. REMOVED THE ".5"	-----	---	---		
---	-----	---	---	D. RE-ORDERED CHART (WAS SORTED BY "H") C. CHANGED DIMENSION TO REF. DIMENSION	-----	---	---		
I	9-18-06	JCST	JKG	B. CHANGED NOTES A. ADDED NEW SIZES	38539-04	JKG	JKG		
R	11-2-02	JHNU JCST	JKG	RELEASED TO PRODUCTION	38539-04	HIW	HIW		
REV	DATE	BY	CHK	DESCRIPTION	ECN - R	CUST	SUP		

$$\triangle E$$
$$\triangle E$$

SLOT DIMENSION		
NOMINAL DUCT HEIGHT	D ±.8 (.03)	R ±.75 (.02)
25	13.6 (.54)	-----
37	24.7 (.97)	-----
50	34.8 (1.37)	-----
75	57.6 (2.27)	26.26 (1.03)
100	81.0 (3.19)	38.0 (1.50)

CAD FILENAME/LAYERS		D38539AA_DC_NNC_01B.PRT	
PANDUIT		CORP. TINLEY PARK, ILLINOIS	
WIRING DUCT AND COVER TYPE "NNC" METRIC CUSTOMER DRAWING			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± (.XXX) ± (.XX) ± 3.1 (.12) ANGLES ±		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
DRAWN BY JHNU	MAT'L: HALOGEN FREE MODIFIED POLYETHYLENE OXIDE (PPG)	SCALE NONE	
DATE 8-2-02		DRAWING NO. 38539-04	DWG A SIZE
CHK'D JKG		SHT 2 OF 3	



NOMINAL DUCT SIZE (W)	C REF	HC	TC
25	$\frac{24.6}{(.97)}$	$\frac{8.9}{(.35)}$	$\frac{1.30}{(.05)}$
37	$\frac{37.1}{(1.46)}$	$\frac{8.9}{(.35)}$	$\frac{1.30}{(.05)}$
50	$\frac{49.6}{(1.95)}$	$\frac{8.9}{(.35)}$	$\frac{1.40}{(.06)}$
75	$\frac{74.6}{(2.94)}$	$\frac{9.4}{(.37)}$	$\frac{1.40}{(.06)}$
100	$\frac{99.6}{(3.92)}$	$\frac{9.4}{(.37)}$	$\frac{1.40}{(.06)}$

CAD FILENAME/LAYERS

PANDUIT CORP TINLEY PARK, ILLINOIS

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:

(.X) ±	(.XXX) ± .005
(.XX) ± .01	ANGLES ± 1°

DRAWING NO.
38539-04
SHT 3 OF 3

DWG
A
SIZE