

This range of panel mounting indicators consists of **many different LED and Neon types**, bezel styles and colours. The range has developed to meet the many different needs of panel design including **IP66 environmentally sealed versions** for use where a front panel seal is needed.



ELECTROUSTIC
DISTRIBUTION OF CONNECTIVITY SOLUTIONS

- Available types: Ultra-thin, Miniature, Twin unit, Miniature round and Standard
- Rating from 10A, 250V ac up to 20A, 277V ac
- Single & double pole variants available
- Push-on, solder & PCB terminals
- Illuminated and non-illuminated options
- High in-rush (ON-OFF types)
- Matching Indicators
- Splash resistant options
- Choice of bezel styles and sizes, panel cut-outs and actuators
- Choice of switching circuits including 3 position



8800 Thinline Rocker Switches

10A 250Vac



Key Features

- Ultra thin rocker switch
- Ratings up to 15A, 250Vac
- Single and twin gang
- Panel cut out:
Single 19.3 x 6.8
Twin 19.3 x 13.4

Approvals and specifications


- 10(6)A 250Vac T100 1E4 (10,000 Operations)
6(2)A 250Vac T100 5E4 (50,000 Operations)
Inrush rating 10/50A 1E4 (10,000 Operations)
- UL CSA 15A 250Vac (Twin unit is 10A 250Vac)
UL CSA 125Vac 1/2hp
UL 100°C, file E45221, CSA file LR10990

3mm contact gap.


Terminal	Function	Rocker	Body	Body Colour	Rocker Colour
H 9.7	 Switches are ON when pressed over terminal 1 8800 ON - OFF Single pole		A. Single pole Panel Cut Bezel *Optional profile for orientation	B Black R Red W White	B Black R Red W White
T 8.8 1.5	 Switches are ON when pressed over terminal 1 or 3 8800 ON - OFF Twin pole		B. Single pole - Twin Panel Cut Bezel *Optional profile for orientation Panel thickness 0.75-1.2 1.25-1.99 2.00-3.00 Dim X 19.1/19.2 19.3/19.4 19.7/19.8	W White	W White
X 4.0 7.5	8800 ON - OFF Twin pole		Cut-outs must be punched in the direction of insertion		

Dimensions

8800VA (H terminals shown)



8800V/8800VA (H terminals shown)



Legend	Legend Colour	Options
Blank 132	Blank B Black W White	Finish Matt finish only. Colour Call sales for custom colours. A full range is available for large orders. Legend printing Select from the examples or call sales for custom legends.

Examples



X8800VA



X8800VA
T8800VA - - -



X8800VA
T8800VA - - -



H8800V/H8800VA
T8800V/T8800VA



H8800V/H8800VA
T8800V/T8800VA

8500 Rocker Switches - Miniature

10A 250Vac Single & Double Pole



Key Features

- Miniature rocker switch
- Ratings up to 15A, 250Vac
- Single & double pole in same body size
- Illuminated & non-illuminated
- Matching indicators
- Industry standard panel cut-out
- Rotary and push button actuator options
- BioCote antimicrobial option
- Panel cut out: 19.3 x 12.9

Approvals and specifications

10(6)A 250Vac T125 IE4 (non lit types)
6(4)A 250Vac T125 5E4 (50,000 Operations)
10(6)A 250Vac T100 (lit types)

UL CSA 15A Non Ind 250Vac, 14A Ind 250Vac, 10A 277Vac
UL CSA 250Vac 1/2hp, 125Vac 1/4hp
UL 105°C, (non lit) file E45221, CSA file LR10990


BioCote antimicrobial additive. Independently verified to ISO22196:2007.

3mm contact gap.



Terminal	Function	Rocker	Body	Body Colour	Rocker Colour
H 	 ON OFF Switches are ON when pressed over terminal 1	H Slotted for custom caps 	B Standard body with terminal barrier Panel cut out: 12.9 x 21.0 Bezel: 15.0 x 21.0	B Black	B Black
K 	8500 ON - OFF Single pole (Uses terminals 1a & 2a)	R Semi-rotary (not lit) 	BC Body without terminal barrier Panel cut out: 12.9 x 21.0 Bezel: 15.0 x 21.0	R Red	R Red
L 	8503 ON (lit) - OFF Single pole	D Paddle lever (not lit) 	Dimensions for snap-in fixing Panel thickness: 0.75-1.25, 1.25-2.00, 2.00-3.00 Dim X: 19.1/19.2, 19.3/19.4, 19.7/19.8	W White	W White
L Right angle version of K terminal available on 8500 only	8550 ON - OFF Double pole	V Curved (not lit) 	Cut-outs must be punched in the direction of insertion		
R 	8553 ON (lit) - OFF Double pole	X Two colour (not lit) 			
T 	8580 Available with H terminals only Indicator UL/CSA E83363	A Softline lens 			
T Solder	P Push button operation (8500 only) See drawing opposite				

Dimensions



"B" body with barrier for H, T and K terminals



"BC" body w/o barrier primarily for L or R terminals (can be used for all terminals)



'PO' Actuator and body - push button function (8500 only)



Insert Colour	Lamp Voltage	Legend	Legend Colour	Options	Biocote
X Rocker Only	Blank	Blank	Blank	Finish Matt finish only.	B Biocote
R Red	2 125V Neon	076	B Black	Colour Call sales for custom colours. A full range is available for large orders.	
W White	3 250V Neon		W White	Legend printing Select from the examples or call sales for custom legends.	
Leave blank for other Rocker types	7 12V Filament			Lamp voltage Call sales for details of available voltages.	
	8 24V Filament			Protective cover L167 Snaps on to bodies with V or X style rockers and A lens. This reduces panel thickness by 0.8mm.	
					
				BioCote Antimicrobial Additive Moulded components have antimicrobial properties using BioCote silver ion technology.	

Examples



H8500VB
T8500VB ---



H8550VB
T8550VB



H8550HB ---
T8550HB ---



H8550XB ---
T8550XB ---



H8550RB Semi-rotary
A splash proofing option



H8500PO ---
Pushbutton option



H8553VB ---
T8553VB ---



H8580AB ---

8600 Rocker Switches - Miniature

10A 250Vac Single & Double Pole



Key Features

- Miniature rocker switch
- Ratings up to 16A, 250Vac
- Single & double pole
- ON/OFF, C/O, biased and centre off switching
- Push on, solder and PCB terminals
- Illuminated and non illuminated
- Matching indicators
- Panel cut out single: 19.3 x 12.9 double: 19.3 x 21.9

Approvals and specifications

10(4)A 250Vac T90 (unless noted below)


UL CSA See ratings below
UL 65°C, file E45221, CSA file LR10990

3mm contact gap except where marked μ .


Terminal	Function	Rocker	Body	Body Colour
H 4.8 x 0.8 7.4	Approvals & ratings vary with function 8600 10(4)A 16A 250V, 10A 277V 1/2HP 277V, 1/4HP 125V ON - OFF 8650 10(4)A 10A 277V 1/2HP 277V, 1/4HP 125V ON - OFF 	V Curved V Curved (lit) H Slotted for actuator (8600 and 8610 only) F Flat Indicator only (Single pole) 	B Single pole Panel cut out Bezel Single Pole dimensions for snap-in fixing Panel thickness 0.75-1.25 1.25-1.99 2.00-3.00 Dim X 19.1/19.2 19.3/19.4 19.7/19.8 B (Double Pole) with terminal barrier BC (Double Pole) w/o terminal barrier Panel cut out Bezel Double Pole dimensions for snap-in fixing Panel thickness 0.75-1.24 1.25-1.99 2.00-3.00 Dim X 19.1/19.2 19.3/19.4 19.7/19.8 Cut-outs must be punched in the direction of insertion	B Black R Red W White
T 3.5 x 0.8 6.4 Solder	8601 6(1)A 16A 250V, 6A 277V ON - OFF (momentary ON) 8651 6(1)A 6A 277V ON - OFF (momentary ON) 			
X 3.7 3.5 x 0.85 5.3 PCB 0.85q	8602 10A 6A 277V ON - OFF (momentary OFF) 8652 10(4)A 6A 277V ON - OFF (momentary OFF) 			
N/A ON - OFF Lit	8653 10(4)A 6A 277V ON - OFF Lit 			
8610 6(1)A 10A 277V 1/2HP 277V, 1/4HP 125V ON - OFF 	8660 6(1)A 10A 277V 1/2HP 277V, 1/4HP 125V ON - OFF 			
8611 6A 277V ON - OFF (momentary 1 side) 	8660 6A 277V ON - OFF (momentary 1 side) 			
8620 μ ON - OFF - ON 	8670 μ ON - OFF - ON 			
8630 6(1)A UL E63363 CSA LR29381 KEMA-KUER Indicators	N/A			

Dimensions

Single pole



Double pole



Rocker Colour	Lamp Voltage	Legend	Legend Colour	Options
Lit (DP)	Blank	Blank	Blank	Finish Matt finish only. Colour Call sales for custom colours. A full range is available for large orders. Legend printing Select from the examples or call sales for custom legend. Lamp voltage Call sales for details of available voltages. Blanking plate A8634FB Dummy unit to fill unused panel holes. Single pole size only. Protective covers L167 for SP L180 for DP Snap on to bodies with V rocker or F lens. This reduces panel thickness by 2.2mm.  Single Pole options Most switches shown can have single pole switching in double pole bodies.
A Amber	2 125V Neon	076	B Black	
C Clear	3 250V Neon		W White	
G Green	7 12V Filament			
R Red	8 24V Filament			
Lit (DP)				
B Black				
R Red				
W White				

Examples



H8600VB ---
T8600VB ---



H8600VB ---
T8600VB ---



H8630FB ---
T8630FB ---



H8650VB ---
T8650VB ---




H8660VB ---
T8660VB ---



H8653VB ---
T8653VB ---

8620 & 8670 Rocker Switches

3 Positions - 10A 250Vac



Key Features


- 3 position miniature rocker switch
- Panel cut out:
single: 19.3 x 12.9
double: 19.3 x 21.9
- Ratings up to 15A, 250Vac
- Single & double pole
- Centre off switching
- Push on, solder and PCB terminals
- Matching indicators

Approvals and specifications

- 10(4)A 250Vac T90
- UL CSA 15A 277Vac (Single pole)
- UL CSA 250Vac 1/2hp (Single pole)
- UL CSA 125Vac 1/4hp (Single pole)
- UL CSA 10A 277Vac (Double pole)
- UL CSA 277Vac 1/2hp (Single & Double pole)
- UL 90°C, file E45221, CSA file LR10990
- μ contact gap.

Terminal	Function	Rocker	Body	Body Colour	Rocker Colour
H 4.8 x 0.8	8620 ON - OFF - ON Single pole	V Curved	B Single pole Panel thickness 0.75-1.24 1.25-1.99 2.00-3.00 Dim X 19.1/19.2 19.3/19.4 19.7/19.8	B Black	Lit (DP) A Amber
T Ø2.15 Solder	8670 ON - OFF - ON Double pole	H Slotted for actuator (8620 only)	B Single pole - Twin Panel thickness 0.75-1.24 1.25-1.99 2.00-3.00 Dim X 19.1/19.2 19.3/19.4 19.7/19.8	R Red W White	C Clear G Green R Red
X PCB 0.8sq Double pole switches with X terminals are supplied without terminal barriers			Cut-outs must be punched in the direction of insertion		Lit (DP) B Black R Red W White

Dimensions



Lamp Voltage	Legend	Legend Colour	Options
Blank	Blank	Blank	Finish Matt finish only. Colour Call sales for custom colours. A full range is available for large orders. Legend printing Select from the examples or call sales for custom legend. Lamp voltage Call sales for details of available voltages. Blanking plate A8634FB Dummy unit to fill unused panel holes. Single pole size only. Protective covers L167 for SP L180 for DP Snap on to bodies with V rocker or F lens. This reduces panel thickness by 2.2mm.  Single Pole options Most switches shown can have single pole switching in double pole bodies.
2 125V Neon	076	B Black	
3 250V Neon		W White	
7 12V Filament			
8 24V Filament			



○ Standard rocker switch	○ Panel cut out: 27.2 x 12.4 (snap in)
○ Double pole in single pole body	26.3 x 12.4 (sub panel mount)
○ Snap in or sub panel mount	
○ Integral terminal barrier	
○ Push on or PCB terminals	


Cut-outs must be punched in the direction of insertion

Approvals and specifications

-  10(6)A 250Vac T100
 6A 400Vac T100
 1A 30Vdc

 UL CSA 10A 250Vac
 UL CSA 16A 250Vac Resistive
 UL CSA 125Vac 1/2hp
 UL CSA 1A 30Vdc
 UL 100°C, file E45221, CSA file LR10990
 3mm contact gap

Dimensions



Legend	Legend Colour	Options
Blank	Blank	Finish Matt finish only. Colour Call sales for custom colours. A full range is available for large orders. Legend printing Select from the examples or call sales for custom legend.
085	B Black W White	

6000 SP Splash Resistant Rocker Switches

16A 250Vac



Key Features

- Ratings up to 20A, 277Vac
- Positive switch action
- Distinctive styling
- Illuminated & nonilluminated
- Single pole
- Panel cut out: 30.1 x 11.1mm

Approvals and specifications


European 16(4)A 250Vac T125, 10A 400Vac T125

UL = 20A 277Vac, 1 1/2HP 250Vac 1HP 125Vac
CSA = 20A 277Vac, 1HP 125Vac, 1/2HP 125Vac

3mm contact gap with Positive Break switching.
Call factory for IP details.

Terminal	Function	Rocker	Body	Body Colour	Rocker Colour	Lamp Voltage
C 6.3 x 0.8	6000 ON - OFF 6001 ON - OFF (momentary ON)	A Softline Matt 	L Panel cut-out ** Bezel 30.0/30.1 11.0/11.1 31.5 14.0 R2.0 Cut-outs must be punched in the direction of insertion	B Black W White	Lit (DP) A Amber C Clear G Green R Red Lit (DP) B Black R Red W White	Blank 2 125V Neon 3 250V Neon 5 12Vdc LED (P Rocker) 6 24Vdc LED (P Rocker) 7 12V Filament 8 24Vdc Filament
H 4.8 x 0.8	6002 ON - OFF (momentary OFF) 6003 ON - OFF Lit	A Softline Matt P Lit window Matt 				
S 9.7 Screw & Clamp N/A for assemblies with 3 terminals	6008 ON - OFF Lit (Unswitched neutral) 6009 ON - OFF (momentary ON) Lit (Unswitched neutral) 6010 ON - ON 6011 ON - ON (momentary 1 side)					

Dimensions



Panel thickness
L 0.75 to 2.5mm
** For cut-out details
on momentary switches
call sales

Integral Splash Resistance



Current carrying parts are protected from moisture. Droplets which may enter the switch are channelled out through ports in the switch body.
For IP65 see options below

Legend	Legend Colour	Options
Blank	Blank	G74 Protective Cover
1223	B Black	Finish Matt is standard. Colour Call sales for custom colours. A full range is available for large orders. Legend printing Select from the examples or call sales for custom legends. Lamp voltage Call sales for details. Protective cover A snap on cover is available (add G after body code), this reduces panel thickness by 2mm.  Panel sealing washer W46 is available, this reduces panel thickness by 1.2mm. Covers are not suitable for momentary types. For all options call the factory
	W White	

Examples



☐ C6000AL - - -



☐ C6000AL - - -



☐ C6010AL - - -



☐ C6003AL - - -



☐ C6003PL - - -



☐ C6030AL - - -

6050 DP Splash Resistant Switches

& Twin Switches - 16A 250Vac



Key Features

- Ratings up to 20A, 277V ac
- Positive switch action
- Distinctive styling
- Illuminated & non-illuminated
- Double pole
- BioCote antimicrobial option (Double pole only)
- DC LED Illumination Available
- Panel cut out: 30.1 x 22.2mm

Approvals and specifications

European 16(4)A 250Vac T125, 10A 400Vac T125

UL CSA 20A 277Vac, 250Vac 11/2hp, 125Vac 1hp


UL 100°C, file E45221, CSA file LR10990

BioCote antimicrobial additive. Independently verified to ISO22196:2007.

3mm contact gap with Positive Break switching.

Terminal	Function		Rocker	Body	Body Colour
C 6.3 x 0.8	6050 ON - OFF	6059 ON - OFF (Single pole) (momentary ON) Isolated light	A Softline Matt	L Double Pole Panel cut-out ** Bezel	Lit (DP) A Amber
H 4.8 x 0.8	6051 ON - OFF (momentary ON)		A Softline Matt	L Twin units Contact sales for information on splash resistance and IP ratings	C Clear
	6052 ON - OFF (momentary OFF)				G Green
	6053 ON - OFF Lit		P Lit window Matt		R Red
	6054 ON - OFF (momentary ON) Lit		 Lit window		Un-Lit (DP)
S 9.7 Screw & Clamp N/A for assemblies with 3 terminals	6055 ON - OFF (Single pole) (momentary ON) Lit				B Black
	6056 ON - OFF (Single pole) Isolated light				R Red
	6057 ON - OFF Isolated light				W White
	6058 ON - OFF (Single pole) Lit				


Integral Splash Resistance



Current carrying parts are protected from moisture. Droplets which may enter the switch are channelled out through ports in the switch body.

For IP65 see options below

Dimensions



Panel thickness

L 0.75 to 2.5mm

** For cut-out details on momentary switches call sales

Terminal spacing - Poles 10.5 between centres

Rocker Colour	Lamp Voltage	Legend	Legend Colour	Options	BioCote
B Black	Blank	Blank	Blank	G74 Protective Cover	B BioCote
R Red	2 125V Neon	1223	B Black	Finish Matt is standard. Colour Call sales for custom colours. A full range is available for large orders. Legend printing Select from the examples or call sales for custom legends. Protective cover The 6050 series is a water through design. For a higher level of sealing, a snap on cover is available (add G after body code). This reduces panel thickness by 1mm.  Panel sealing washer W42 is available. This reduces panel thickness by 1.00mm. Covers are not suitable for momentary types. IP Ratings Call the sales for details. Terminal Link P1067 connects the poles of a double pole switch or twin unit. # Mounting orientation may affect IP rating. BioCote Antimicrobial Additive  Moulded components have antimicrobial properties using BioCote silver ion technology. For all options call sales.	
W White	3 250V Neon		W White		
	5 12Vdc LED (P Rocker)				
	6 24Vdc LED (P Rocker)				
	7 12V Filament				
	8 24Vdc Filament				

Examples



C6050AL - - -



C6053AL - - -



C6053PL - - -



C6000A/C6000AL



C6003P/C6003PL



C6003P/C6030AL

1500 Standard & 1300 High Inrush Switches

150A to EN61058-1 and 16A 250Vac



Key Features

- Standard rocker switch
- Non-illuminated
- 150A inrush
- Choice of switching circuits including 3 position
- Choice of bezel styles
- Choice of panel cut outs
- Matching indicator
- Single pole
- Splash resistant option
- BioCote antimicrobial option
- DC LED Illumination Available for "P" Rocker
- Panel cut out 'A' style: 27.3 x 12.3mm

Approvals and specifications

UL 1500 Series 16(4)A 250Vac T125

UL CSA 16A Non Ind 250Vac, (2 posn) 250Vac 1hp, 125Vac 1/2hp, (3 posn) 250Vac 1/2hp, 125Vac 1/4hp
1330 36Vdc 14A
1350 72 Vdc 7A
1500 & 1510 14 Vdc 10A
UL 85°C, file E45221, CSA file LR10990

In house test:
10A 24Vdc—Indicative rating only

1300 series 16(6)A 250Vac T125 5E4 (50,000 Ops.)
150A Inrush to EN61058-1

Terminal	Function	Rocker	Body	Finish	Body Colour	Rocker Colour
C 6.3 x 0.8	Standard 1500 ON - OFF	A Softline Matt	Panel cut-out Cut-outs must be punched in the direction of insertion A 12.2/12.3 27.2/27.3 Gloss or Matt	M Matt	B Black	Un-Lit
H 4.8 x 0.8*	1501 HP rating N/A ON - OFF (momentary ON)	B Splash resistant (with Arcshield) Matt	B 11.0/11.1 30.0/30.1 Matt only	G Gloss	R Red	B Black
K 2.8 x 0.8*	1502 HP rating N/A ON - OFF (momentary OFF)	H Slotted (for custom Adaptors) not momentary	B 11.0/11.1 30.0/30.1 Matt only	Applies to both Rocker & Body	R Red	R Red
T 2.8 x 0.8*	1510 µ HP rating N/A ON - ON	V Curved Matt or gloss	L 11.0/11.1 30.0/30.1 Matt only		W White	W White
U 2.8 x 0.8*	1511 µ HP rating N/A ON - ON (momentary 1 side)	W Splash resistant (with Arcshield) Matt	Q 11.5/11.6 28.2/28.3 Gloss or matt			Lit
X 2.8 x 0.8*	1520 µ 125V & 250V 1/2 HP H terminal rated T100 only ON - OFF - ON	X Two colour Matt ON - OFF only (not momentary)	R 14.0/14.1 28.5/28.6 Matt only			A Amber
U 2.8 x 0.8*	1521 µ HP rating N/A H terminal rated T100 only ON - OFF - ON (momentary 1 side)	F Flat lens Gloss (0430 only)	T 11.5/11.6 28.2/28.3 Matt only			C Clear
U 2.8 x 0.8*	1522 µ HP rating N/A H terminal rated T100 only ON - OFF - ON (momentary 2 sides)	A Softline lens Matt (0430 only) as F but with raised profile				G Green
X 2.8 x 0.8*	0430 HP rating N/A H terminal rated T100 only ON - OFF					R Red
X 2.8 x 0.8*	High Inrush 1300 ON - OFF					

Dimensions


UL CSA 20A 250Vac 1hp, 125Vac 1/2hp
UL 85°C, file E45221, CSA file LR10990

In house test:

20A 24Vdc — Indicative rating only

BioCote antimicrobial additive. Independently verified to ISO22196:2007.

3mm contact gap except if marked μ .



Panel thickness

A,Q 0.75 to 3.3mm
L,B,T 0.75 to 2.5mm
R 0.75 to 3.0mm


* For cut-out details on momentary switches call sales

Splash Resistance

1500 W and B splash resistant options


Feather edge seals and a close fitting collar protect current carrying parts from moisture.

B option has Hytrel collar/seals for enhanced protection.



1300 High inrush, positive break switching

The 1300 series mechanism ensures contact welds formed at switch-on are positively separated by the plunger tube acting directly on the step in the moving contact.

Lamp Voltage	Insert Colour	Legend	Legend Colour	Options	Biocote
Blank	Blank	Blank	Blank	Finish Matt is standard. Colour Call sales for custom colours. A full range is available for large orders. Legend printing Select from the examples or call sales for custom legends. Lamp voltage Call sales for details. Blanking plates A0434 - - Dummy units to fill unused panel holes. Protective cover Snaps on to A, L, Q or T bodies (add G after body code in cat no.), this reduces panel thickness by 1mm.  Panel sealing washer W46 is available for the same body sizes, this reduces panel thickness by a further 0.8mm. Covers are not suitable for momentary types. BioCote Antimicrobial Additive Moulded components have antimicrobial properties using BioCote silver ion technology. For all options call sales.	B BioCote
2 125V Neon	R Red	602A	B Black		
3 250V Neon	W White		W White		
7 12V Filament					
8 24Vdc Filament					

Examples



C1500AR ---
T1500AR ---



C1500AL ---
T1500AL ---



C1500XL ---
T1500XL ---



C1510AL ---
T1510AL ---




C1520AL ---
T1520AL ---



C0430AL ---
T0430AL ---

5500 Lit Rocker Series

10A 250Vac



Key Features

- Standard rocker switch
- Illuminated
- Choice of switching circuits
- Choice of bezel styles
- Choice of panel cut outs
- Matching indicator
- Single pole
- Splash resistant option
- Panel cut out 'A' style:

Approvals and specifications

16(4)A 250Vac T85
10(3)A 250Vac T100, (12A 250Vac T125 for P rocker only)

UL CSA 15A 250Vac, CSA 16A Non Ind 250Vac
UL CSA 250Vac 1hp, 125Vac 1/2hp
UL 85°C, file E45221, CSA file LR10990

μ contact gap.


For Twin units repeat the order details for both the left and right sides.

Terminal	Function	Rocker	Body	Body Colour	Rocker Colour
C 6.3 x 0.8	Approvals & ratings vary with function ON OFF Switches - ON when pressed over terminal 3 	A Softline (Matt only) 	A Panel Cut - outs B L Q R T 	B Black	Un-Lit B Black R Red W White Lit A Amber C Clear G Green R Red
H 4.8 x 0.8	5500 μ ON - OFF Single pole	P Lit window (Matt only) 		W White	
T Solder	5503 μ ON - OFF Lit Switched neutral				
	5508 μ ON - OFF Unswitched neutral				

Dimensions

Panel thickness


A, Q	0.75 to 3.3mm
L, B, T	0.75 to 2.5mm
R	0.75 to 3.0mm



Twin units

Two single switches or a switch and an indicator light can be assembled side by side in one double pole body.

For 5500 range panel cut-out details (L, B and T) call sales.



Terminal spacing -
Poles 10.8 between centres (twin units)

For twin units the first set of order format details refer to the left hand unit, when looking at the front of the assembly.
(This has terminal numbers 1, 2 & 3)

Lamp Voltage	Legend	Legend Colour	Options
Blank	Blank	Blank	Finish Matt is standard. Colour Call factory for custom colours. A full range is available for large orders. Legend printing Select from the examples or call factory for custom legends. Lamp voltage Call factory for details. Blanking plate A0434 - - (SP) A0494 - - (DP) Dummy units to fill unused panel holes. Protective cover Snaps on to A, L, Q or T bodies (add G after body in cat no.), this reduces panel thickness by 1.00mm.  Panel sealing washers W46 (Single Pole) and W42 (Double Pole) are available for these body types, this reduces panel thickness by 2mm. For all options call the factory.
2 125V Neon	602A	B Black	
3 250V Neon		W White	
5 12Vdc LED (P Rocker)			
6 24Vdc LED (P Rocker)			
7 12V Filament			
8 24Vdc Filament			

Examples



C5503AL - - -



C5500AL - - -



C5503PL - - -



C5503A/
C5430AL



C5503A/C5503AL



C5503P/C5503PL

1500 Twin Units Switches and Indicators

16A 250Vac



Key Features

- Twin unit rocker switch
- Choice of switching circuits including 3 position
- Push-on, solder and PCB terminals
- Choice of bezel styles
- Choice of panel cut outs
- Matching indicator
- Single pole switches
- Splash resistant option
- Panel cut out 'A' style: 27.2 x 22.3mm

Approvals and Specifications

16(4)A 250Vac T125


UL CSA 16A 250Vac
UL CSA (2 posn) 250Vac 1hp, 125Vac
1/2hp, (3 posn) 250 Vac
1/2hp, 125Vac 1/4hp
UL 85°C, file E45221, CSA file LR10990

For versions with High Inrush or for 50,000 operations,
3mm contact gap except where marked μ .

Terminal	Function	Rocker	Body		Finish	Body Colour	Rocker Colour
C 6.3 x 0.8	Approvals & ratings vary with function ON OFF Switches - ON when pressed over terminal 1 or 4 	A Softline (Matt only) 	A Panel Cut - outs 	Bezel 	M Matt	B Black	Un-Lit B Black
H 4.8 x 0.8	1500 ON - OFF	B Softline (Matt only) 	B 		G Gloss	W White	R Red
T 02.1 Solder	1510 μ ON - ON	W Softline (Matt only) 	L 		Applies to both Rocker & Body		W White
1520 μ ON - OFF - ON			Q 				Lit
K 2.0 9.1 1.2	0430 Indicator	X Softline (Matt only) 	R 				A Amber
X 4.0 9.1		A Softline (Matt only) 	T 				C Clear
							G Green
							R Red

Dimensions


Panel thickness
A,Q 0.75 to 3.3mm
L,B,T 0.75 to 2.5mm
R 0.75 to 3.0mm



Call sales for terminal spacing details


Twin units

Two single switches or a switch and an indicator light can be assembled side by side in one double pole body.



For twin units the first set of order format details refer to the left hand unit, when looking at the front of the assembly.
 (This has terminal numbers 1, 2 & 3)

Splash Resistant



Feather edge seals and a close fitting collar protect current carrying parts from moisture.

B option has Hytrel collar/seals for enhanced protection.

Insert Colour	Lamp Voltage	Legend	Legend Colour	Options	Biocote
Blank	Blank	Blank	Blank	Finish Matt is standard.	B Biocote
R Red	2 125V Neon	602A	B Black	Colour Call factory for custom colours. A full range is available for large orders.	
W White	3 250V Neon		W White	Legend printing Select from the examples or call factory for custom legends.	
	5 12Vdc LED (P Rocker)			Lamp voltage Call factory for details.	
	6 24Vdc LED (P Rocker)				
	7 12V Filament				
	8 24Vdc Filament				

Examples



C1500A/C1500AL



C1500A/C0430AL



C1500X/C1500XL



C1520A/C1510AL



C1500A/C1520AL



C0430A/C0430AL

1550 Standard and 1350 High Inrush

150A to EN61058-1 and 16A 250Vac



Key Features

- Standard rocker switch
- 1350/53 high inrush
- Choice of switching circuits including 3 position
- Push-on, solder and PCB terminals
- Choice of bezel styles
- Choice of panel cut outs
- Matching indicator
- Double pole
- Splash resistant option
- BioCote antimicrobial option
- Panel cut out 'A' style: 27.2 x 22.3mm

Approvals and specifications

1550 Series 16(4)A 250Vac T125

UL CSA 16A 250Vac, (2 posn) 250Vac 1hp, 125Vac 1/2hp, 1350 72 Vdc 7A
(3 posn) 250 Vac 1/2hp, 125Vac 1/4hp.
UL 85°C, file E45221, CSA file LR10990.

In house test:

10A 24Vdc—Indicative rating only

1350 series 16(4)A 250Vac T85 1E4 (10,000 Ops.)
1330 series 16(6)A 250Vac T125 5E4 (50,000 Ops.)
150A Inrush to EN61058-1.

Terminal	Function		Rocker	Body
C 	Standard 1550 	1487 μ In-house tested to 10(3) A 250Vac (B rocker only)	A Softline Matt 	Panel cut-out Bezel Cut-outs must be punched in the direction of insertion
H 	1551 HP rating N/A 	0480 X terminal N/A	B Splash resistant Softline 	A
K 	1552 HP rating N/A 	High Inrush 1350 Not W, X or B rocker	V Curved 	B
T 	1553 Not W, X or B rocker 	1353 Not W, X or B rocker	W Splash resistant Curved 	L
U 	1560 μ 		P Lit window Matt 	Q
X 	1561 μ HP rating N/A 		X Two colour Matt 	R
Y 	1562 μ In house tests only 		R Round 	T
Z 	1570 μ 125V & 250V 1/2 HP H terminal rated T100 only H terminal rated T100 only		F Flat Lens Gloss (0480) 	R
AA 	1571 μ HP rating N/A H terminal rated T100 only 		A Softline lens Matt (0480 only) as F but with raised profile 	T
BB 	1572 μ HP rating N/A H terminal rated T100 only 			
CC 	1484 μ In-house tested to 10(3) A 250Vac (B rocker only)			

Approvals and specifications (continued)

UL CSA 20A 250Vac 1hp, 125Vac 1/2hp.
UL 72Vdc 7A, 36Vdc 14A.
UL 85°C, file E45221, CSA file LR10990.


In house test:
20A 24Vdc—Indicative rating only

Splash Resistance




1300 High inrush, positive break switching
The 1300 series mechanism ensures contact welds formed at switch-on are positively separated by the plunger tube acting directly on the step in the moving contact.

Dimensions



Panel thickness
A,Q 0.75 to 3.3mm
L,B,T 0.75 to 2.5mm
R 0.75 to 3.0mm

* For cut-out details on momentary switches call sales

Finish	Body Colour	Rocker Colour	Insert Colour	Lamp Voltage	Legend	Legend Colour	Options
M Matt	B Black	Un-Lit B Black R Red W White Lit A Amber G Green C Clear R Red	Blank R Red W White	Blank 2 125V Neon 3 250V Neon 5 12Vdc LED (P Rocker) 6 24Vdc LED (P Rocker) 7 12V Filament 8 24Vdc Filament	Blank 602A	Blank B Black W White	Finish Matt is standard. Colour Call sales for custom colours. A full range is available for large orders. Legend printing Select from the examples or call sales for custom legends. Lamp voltage Call sales for details. Blanking plates A0494 Dummy units to fill unused panel holes. Protective cover Snaps on to A, L, Q or T bodies (add G after body in cat no). This reduces panel thickness by 1mm. 
Examples							

Examples



□ C1350AL ---



□ C1550XL ---



□ C1553PL ---



□ C1553RA ---
Shown with M614
bezel cover



Optional snap-in
M441 barrier




C1553AA with M616
guard Cut-out
22.0/22.1 x 29.4/29.5
Guard accepts "A"
body only



□ C0480RA ---
Shown with
M614 bezel
cover



□ C0480AL ---



Panel sealing washer W42 is available for the above body sizes. This reduces panel thickness by a further 1.00mm.
Covers are not suitable for momentary types.

BioCote Antimicrobial Additive

Moulded components have antimicrobial properties using BioCote silver ion technology.

For all options call sales.

1550 Standard & 1350 High Inrush Switches

150A to EN61058-1 and 16A 250Vac/250Vdc



Key Features

- Standard rocker switch
- 1350/53 high inrush
- Choice of switching circuits including 3 position
- Push-on, solder and PCB terminals
- Choice of bezel styles
- Choice of panel cut outs
- Matching indicator
- Double pole
- Option with guard & cover
- DC LED Illumination Available for "P" Rocker
- Bezel size 'G' style 32.0 x 25.0

Approvals and specifications

1550 Series 16(4)A 250Vac T125

UL CSA 16A 250Vac, (2 posn) 250Vac 1hp, 125Vac 1/2hp, (3 posn) 250 Vac 1/2hp, 125Vac 1/4hp. UL 85°C, file E45221, CSA file LR10990.

In house test:
10A 24Vdc—Indicative rating only

1350 Series

UL CSA 20A 250Vac 1hp, 125Vac 1/2hp. UL 72Vdc 7A, 36Vdc 14A, UL 85°C, file E45221, CSA file LR10990.

Terminal	Function	Rocker	Body	Finish	Body Colour	Rocker Colour
C 6.3 x 0.8	Standard 1550 1551 HP rating N/A 1552 HP rating N/A 1553 Not W, X or B rocker 1560 μ 1561 μ HP rating N/A 1562 μ In house tests only 1570 μ 125V & 250V 1/2 HP H terminal rated T100 only 1571 μ HP rating N/A H terminal rated T100 only 1572 μ HP rating N/A H terminal rated T100 only High Inrush 1350 Not W, X or B rocker 1353 Not W, X or B rocker PCB 0.8Sq* *Contact sales for details on 1350 series	 ON - OFF ON - OFF (momentary ON) ON - OFF (momentary OFF) ON - OFF Lit ON - ON ON - ON (Momentary 1 Side) ON - ON 2 Circuit ON - OFF - ON ON - OFF - ON (momentary 1 side) ON - OFF - ON (momentary 2 sides) ON - OFF ON - OFF Lit	A Softline Matt Panel cut-out Bezel Cut-outs must be punched in the direction of insertion B 22.1/22.2 x 30.0/30.1 Matt only L 22.1/22.2 x 28.2/28.3 Matt only V Curved Matt or Gloss Gloss only Lit (not momentary) P Lit window Matt Lit (not momentary)	M Matt G Gloss Applies to both Rocker & Body	B Black W White	Un-Lit B Black R Red W White Lit A Amber G Green C Clear R Red

Splash Resistance



In house test:

20A 24Vdc—Indicative rating only

BioCote antimicrobial additive. Independently verified to ISO22196:2007.


3mm contact gap except if marked μ .



1350 High inrush, positive break switching

The 1350 series mechanism ensures contact welds formed at switch-on are positively separated by the plunger tube acting directly on the step in the moving contact.

Dimensions



Panel thickness

G, H 0.75 to 2.5mm

Terminal spacing - Poles 10.2 between centres

* For cut-out details on momentary switches call sales

Insert Colour	Lamp Voltage	Legend	Legend Colour	Options	Biocote
Blank	Blank	Blank	Blank	Finish Matt is standard.	B Biocote
R Red	2 125V Neon	602A	B Black	Colour Call sales for custom colours. A full range is available for large orders.	
W White	3 250V Neon		W White	Legend printing Select from the examples or call sales for custom legends.	
	5 12Vdc LED (P Rocker)			Lamp voltage Call sales for details.	
	6 24Vdc LED (P Rocker)			BioCote Antimicrobial Additive 	
	7 12V Filament			Moulded components have antimicrobial properties using BioCote silver ion technology.	
	8 24Vdc Filament				

Examples



C1553AH - - -



C1550AH - - -

R13 Round Rocker Switches

10A 250Vac



Key Features

- ⬢ Miniature round rocker switch
- ⬢ Ratings up to 10A, 250Vac
- ⬢ Single & double pole
- ⬢ Illuminated & nonilluminated, neon and LED
- ⬢ Choice of actuators
- ⬢ Matching indicator
- ⬢ Panel cut out: 20.2 dia.

Approvals and specifications

⚡ SP 10(4)A 250Vac T85 1E4

⚡ DP 10(4)A 250Vac T85 1E4

UL CSA SP 16A 125Vac & 10A 250Vac
UL CSA DP 16A 125Vac, 10A 250Vac, 10A 28Vdc
UL 85°C, file E67774(S), CSA file LR45128


RoHS compliant

Single pole has μ contact gap.


Special products

Are made to order and can be supplied with a range of body and rocker / lens colours, print & lamp voltage.


Dimensions



Snap fixing into panel thickness up to 3.0




Snap fixing into 2.0 to 3.0mm panels




Snap fixing into 0.7 to 3.0mm panels

Single Pole



Double Pole



Protective cover L188



Snap on to bodies (not R13 211 or R13 112LP), this reduces maximum acceptable panel thickness to 2.4mm.

Examples



⚡ R13 112B NAA



⚡ R13 112A AAA



⚡ R13 112A2 ---

R13 / 112 / A / B / B / 3 / 2 / 602A / W / L188

Series

Type

Function

Body Colour

Rocker Colour

Insert Colour

Lamp Voltage

Legend

Legend Colour

Legend Colour

Product details




1 2
SP ON - OFF μ
Cat no.
R13 112A AAA



1 2 3
SP ON - OFF μ
Lit 230V
Cat no.
R13 112B NAC



1 2
SP ON - OFF μ
Bright colour ON signal
Cat no.
R13 112A2 - -




1 2
SP ON - OFF μ
Cat no.
R13 112A AAB



1 2 3
SP ON - ON μ
Cat no.
R13 112C AAA



1 2 3
SP ON - OFF μ
Lit Window
Cat no.
R13 112B2 - -




1 2 3
SP ON - OFF μ
Lit 230V
Cat no.
R13 112B NAA



1 2 3
SP ON - OFF - ON μ
Cat no.
R13 112D AAA



12 3- 3+
SP ON - OFF μ
Paddle tip has red LED
Cat no.
R13 112LP - -




1 2 3
SP ON - OFF μ
Lit 230V
Cat no.
R13 112B NAB



SP ON - OFF μ
(Momentary ON)
Cat no.
R13 208F AAA*



1 3
Indicator light
Cat no.
R9 92B - - -



DP ON - OFF
Cat no.
R13 244A AAA



DP ON - OFF
Lit 230V
Cat no.
R13 244B NAA