




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A3	ECR-16-004045	17MAR2016	KD	RR
	A4	ECR-16-010013	19JUL2016	KD	RR
	A5	ECR-16-013486	22SEP2016	KD	RR
	A6	ECR-17-008121	07JUN2017	IZ	RR



- 1 PRELIMINARY - NOT RELEASED FOR PRODUCTION
- 2 ONLY FOR 3-927827-1 & 3-927827-2, DIMENSIONS HAVE TO FOLLOW SHEET 2
- INSULATION RANGE: $\varnothing 2.0 - 2.7$
- INSULATION BARREL DIMENSION
- 3 ONLY FOR 3-964324-1 DIMENSIONS HAVE TO FOLLOW SHEET 3
- INSULATION RANGE: $\varnothing 1.4 - 2.1$
- INSULATION BARREL DIMENSION




2.3 ±0.15	PRESILVERED	CuFe2	3-927831-5	A
2.3 ±0.15	PRESILVERED	CuSn4	3-927831-4	A
2.3 ±0.15	PRETINNED	CuSn4	3-927831-2	A
2.3 ±0.15	PRETINNED	CuFe2	3-927831-1	A
2.5	PRETINNED	CuFe2	2825197-1	A
A	FINISH	MATERIAL	PN	REV

INSUL. RANGE $\varnothing 1.4 - 2.1$ mm	WIRE RANGE $\varnothing 0.5 - 1.0$ mm ²
--	---


THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN SUDHAKAR N S 27MAR2015	TE Connectivity		
DIMENSIONS: mm		CHK L. FEDERICO 31MAR2015			
	TOLERANCES UNLESS OTHERWISE SPECIFIED: ±0.2		NAME STANDARD-POWER-TIMER CONTACT		
	0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±		- -		
	FINISH		SIZE A3		
	MATERIAL		CAGE CODE -		
-		APVD R. RICCARDO 31MAR2015	DRAWING NO C-2825197		
-		PRODUCT SPEC 108-18025	RESTRICTED TO -		
-		APPLICATION SPEC 114-18037	SCALE 5:1		
-		WEIGHT -	SHEET 1 OF 3		
-		Customer Drawing	REV A6		

ONLY FOR 3-927827-1 & 3-927827-2
OTHERS DIMENSION SEE SHEET 1


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-



B - B




A - A







2.3 ±0.15	PRETINNED	CuSn4	2 3-927827-2	A
2.3 ±0.15	PRETINNED	CuFe2	2 3-927827-1	A
A	FINISH	MATERIAL	PN	REV

INSUL. RANGE Ø2.0-2.7 mm	WIRE RANGE Ø0.5-1.0 mm ²
-----------------------------	--

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN SUDHAKAR N S 27MAR2015	TE Connectivity			
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: ±0.2	CHK L. FEDERICO 31MAR2015	NAME STANDARD-POWER-TIMER CONTACT - -			
	0 PLC ±- 1 PLC ±- 2 PLC ±- 3 PLC ±- 4 PLC ±- ANGLES ±- FINISH	APVD R. RICCARDO 31MAR2015				
		PRODUCT SPEC 108-18025				
MATERIAL - -	-	APPLICATION SPEC 114-18037	SIZE A3	CAGE CODE -	DRAWING NO C-2825197	RESTRICTED TO -
		WEIGHT -				
Customer Drawing			SCALE 5:1	SHEET 2 OF 3	REV A6	

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

ONLY FOR 3-964324-1
OTHERS DIMENSION SEE SHEET 1



2.3 ±0.15	PRETINNED	CuFe2	3 3-964324-1	A
A	FINISH	MATERIAL	PN	REV

INSUL. RANGE Ø 1.4-2.1 mm	WIRE RANGE Ø 0.5-1.0 mm2
------------------------------	-----------------------------

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN SUDHAKAR N S 27MAR2015	TE TE Connectivity STANDARD-POWER-TIMER CONTACT		
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: ±0.2	CHK L. FEDERICO 31MAR2015			
	0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±	APVD R. RICCARDO 31MAR2015			
		PRODUCT SPEC 108-18025			
		APPLICATION SPEC 114-18037	NAME -		
		WEIGHT -	SIZE A3	CAGE CODE -	DRAWING NO C-2825197
MATERIAL -	FINISH -	Customer Drawing			RESTRICTED TO -
		SCALE 5:1			SHEET 3 OF 3
					REV A6