



PHYSICAL DIMENSIONS:

A	6.30	[.248]	±	0.10	[.004]
B	11.38	[.448]	±	0.18	[.007]
C	9.32	[.367]	±	0.18	[.007]
D	7.62	[.300]	±	0.10	[.004]
E	2.54	[.100]	±	0.13	[.005]
T ₁	3.43	[.135]	±	0.25	[.010]
T ₂	0.64	[.025]	±		TYP.


Z vs. FREQUENCY (C,O,N)



Z, R, XL vs. FREQUENCY



CM2545X171B-10




ELECTRICAL CHARACTERISTICS:

Z @ 100MHz (Ω)	DCR (Ω)	Rated Current
Nominal	170	
Minimum	128	
Maximum	212	0.01 10,000 mA


NOTES: UNLESS OTHERWISE SPECIFIED

1. BULK PACKED, 1260 per CASE.
2. COMPONENTS SHOULD BE ADEQUATELY PREHEATED BEFORE SOLDERING.
3. TERMINATION FINISH IS 100% TIN.
4. THIS PART HAS NO PIN POLARITY.
5. OPERATION TEMPERATURE (INCLUDING SELF-HEATING): -40 ~ +125°C.

EQUIVALENT CIRCUIT



HOLE PATTERN FOR WAVE SOLDERING



RoHS

UNCONTROLLED
DOCUMENT

DIMENSIONS ARE IN mm [INCHES]				This print is the property of Laird Tech. and is loaned in confidence subject to return upon request and with the understanding that no copies shall be made without the written consent of Laird Tech. All rights to design or invention are reserved.			
D	ADD NOTE 5	08/30/12	QU				
C	UPDATE COMPANY LOGO UPDATE ROHS SYMBOL AND KAPTON LABEL ADD EC	11/05/08	JRK				
B	UPDATE COMPANY LOGO	05/17/07	JRK				
A	ORIGINAL DRAFT	5/26/04	JRK				
REV	DESCRIPTION	DATE					
				PROJECT/PART NUMBER:	CM2545X171B-10	REV	D
				DATE:	5/26/04	SCALE:	NTS
				CAD #	CM2545X171B-10-D-1	TOOL #	H0249-600
				DRAWN BY: JRK			
				SHEET: 1 of 2			