







- NOTES:
1. ALL DIMENSIONS IN MM [INCH]
 2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
 3. TERMINAL NUMBERS FOR REF ONLY
 4. CONTACT RATING: CURRENT: 100mA
VOLTAGE: 30 VDC
 5. OPERATING LIFE: 50,000 MAKE-AND-BREAK CYCLES
 6. INSULATION RESISTANCE: 500VDC, 100 Mega-OHM, MIN.
 7. OPERATING FORCE: 250 ± 100 GRAMS
 8. OPERATING TEMP.: -20°C to 70°C
 - ▲9. TRAVEL: MOMENTARY
1.50 ± 0.3mm FULL TRAVEL
 10. CONTACT RESISTANCE: 50 Milli-OHM, MAX.
 11. ▲ DENOTES CRITICAL PARAMETER.
 12. 2002/95/EC (ROHS) COMPLIANT
 - ▲13. LED: NONE



E-SWITCH™

TITLE LP40A1PBATN

B	19603	DRAWING UPDATE	1/19/11	BGL
A	18993	Release For Production	4/19/10	BLR
REV	PCR NO	DESCRIPTION	DATE	BY
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED				

SCALE	2 = 1	DATE	4/19/2010	DR	BLR	DWG	B240035	REV	B
-------	-------	------	-----------	----	-----	-----	---------	-----	---