


PGA Sockets — Patterns (Continued)


23 x 23
591 Positions
interstitial



Style	Page No. ¹	Solder Tail Length	Socket No.
TAZ	115	.140 3.56	382585-3


¹ Phosphor bronze contacts.

25 x 25
401 Positions



Style	Page No. ¹	Solder Tail Length	Socket No.
TAZ	115	.140 3.56	382585-8
TAZ	115	.170 4.32	382585-9

26 x 24
387 Positions
Pentium™ Pro




Style	Page No. ¹	Solder Tail Length	Socket No.
SLZ ² 107		.090 2.29	916680-2 ³
SLZ ² 107		.110 3.56	916680-3 ³
SLZ ² 107		.080 2.03	916738-1 ⁴
SLZ ² 107		.090 2.29	916738-2 ⁴
SLZ ² 107		.110 2.79	916738-3 ⁴

¹ Molded Socket 8


⁴ Same as 915679 series

24 x 24
431 Positions
Digital 21064



Style	Page No. ¹	Solder Tail Length	Socket No.
SLZ ² 107		.110 2.79	916603-1
SLZ ² 107		.140 3.56	916603-2
TAZ	115	.170 4.32	382585-2
HAZ ³ 122		.140 3.56	382876-7

25 x 25
1201 Positions
Interstitial



Style	Page No. ¹	Solder Tail Length	Socket No.
HAZ	122	.170 4.32	382870-1

Note:

Consult AMP customer drawings for actual orientation in socket.

Legend:

SLZ — Single Lever ZIF
TAZ — Tool Actuated ZIF
HAZ — Handle Actuated ZIF
SAZ — Screwdriver Actuated ZIF

¹ Refer to these pages for product information.

² Open center.

³ Heat sink compatible.

⁴ Ivory.

⁵ Rotate pattern clockwise 90°.

⁶ .000010 [0.00025] thick gold over nickel on contacts.

⁷ .000015 [0.00038] thick gold over nickel on solder tails.

⁸ Rotate pattern clockwise 180°.

⁹ .000030 [0.00076] thick gold over nickel on solder tails.

¹⁰ .000015 [0.00038] thick gold over nickel on contacts.

¹¹ Red ink stamping on housing for visual aid during activation and deactivation.