

Customer Information Sheet

DRAWING No.: M20-E06XXXX

SHEET 2 OF 2


IF IN DOUBT - ASK

©

NOT TO SCALE

THIRD ANGLE PROJECTION

ALL DIMENSIONS IN mm



PART No.	No. OF CONTACTS	DIM 'A'	DIM 'B'
M20-E0602XX	2	5.08	2.54
M20-E0603XX	3	7.62	5.08
M20-E0604XX	4	10.16	7.62
M20-E0605XX	5	12.70	10.16
M20-E0606XX	6	15.24	12.70
M20-E0608XX	8	20.32	17.78
M20-E0610XX	10	25.40	22.86

SPECIFICATIONS:**MATERIAL:**MOULDING = 30% GLASS-FILLED PA6T,
UL94V-0, BLACK

CONTACT = BRASS

FINISH:**CONTACT:**

45 = GOLD OVER NICKEL

46 = 100% TIN OVER NICKEL

ELECTRICAL:

CURRENT RATING = 3A

CONTACT RESISTANCE:

INITIAL = 20mΩ MAX

AFTER CONDITIONING = 30mΩ MAX

INSULATION RESISTANCE = 1,000MΩ MIN

DIELECTRIC STRENGTH = 1,000V AC / 1 MINUTE

MECHANICAL:


DURABILITY = 300 OPERATIONS

ENVIRONMENTAL:

TEMPERATURE RANGE = -40°C TO +105°C

PACKING:

BAG

Asia only**NOTES:**1. RECOMMENDED PCB HOLE SIZE = $\varnothing 1.02 \pm 0.05$ mm.

ORDER CODE:

M20-E06XXXXNo. OF CONTACTS PER ROW —
02 TO 06, 08, 10

FINISH —

45 = GOLD

46 = 100% TIN

WJB	I	12.02.08	----
NAME	ISS.	DATE	C/NOTE
APPROVED: R. ADDE			
CHECKED: M. G. PLESTED			
DRAWN: W. J. BOURNE			
CUSTOMER REF.:			
ASSEMBLY DRG:			

HARWINHARWIN INC
U.S.A.
TEL: 603 893 5376
FAX: 603 893 5396
mis@harwin.comHARWIN PLC
Europe (U.K.)
TEL: 023 9231 4545
FAX: 023 9231 4590
mis@harwin.co.ukHARWIN PTE
Asia (Singapore)
TEL: +65 6779 4909
FAX: +65 6779 3868
mis@harwin.com.sgTHIS DRAWING AND ANY
INFORMATION OR DESCRIPTIVE
MATTER SET OUT HEREON ARE
CONFIDENTIAL AND COPYRIGHT
PROPERTY OF THE HARWIN
GROUP AND MUST NOT BE
DISCLOSED, LOANED, COPIED
OR USED FOR MANUFACTURING,
TENDERING OR FOR ANY
OTHER PURPOSE WITHOUT
THEIR WRITTEN PERMISSION.**TOLERANCES**X. = ± 1 mmX.X = ± 0.25 mmX.XX = ± 0.10 mmX.XXX = ± 0.01 mmANGLES = $\pm 5^\circ$

UNLESS STATED

MATERIAL:

SEE ABOVE

FINISH: SEE ABOVE

S/AREA: mm²**TITLE:**2.54mm PITCH SIL VERTICAL
PC TAIL PIN HEADER

DRAWING NUMBER:

M20-E06XXXXSHT
2
OF
2