





(B2)	OBSOLETE	19	24.13	39	49.53	//	77.47	25.93	51.33	79.27	82.71	90.09	0.76µm	120		2-179540-5
(B2)	OBSOLETE	//	//	//	//	49	62.23	//	//	64.03	67.47	74.85	0.76µm	100		2-179540-4
		//	//	//	//	39	49.53	//	//	51.33	54.77	62.15	0.76µm	80	4	2-179540-3
		//	//	//	//	29	36.83	//	//	38.63	42.07	49.45	0.76µm	60		2-179540-2
		//	//	//	//	19	24.13	//	//	25.93	29.37	36.75	0.76µm	40	3	2-179540-1
		19	24.13	39	49.53	//	77.47	25.93	51.33	79.27	82.71	90.09	0.3µm	120		179540-5
		//	//	//	//	49	62.23	//	//	64.03	67.47	74.85	0.3µm	100		179540-4
		//	//	//	//	39	49.53	//	//	51.33	54.77	62.15	0.3µm	80		179540-3
(B2)	OBSOLETE	//	//	//	//	29	36.83	//	//	38.63	42.07	49.45	0.3µm	60		179540-2
(B2)	OBSOLETE	//	//	//	//	19	24.13	//	//	25.93	29.37	36.75	0.3µm	40		179540-1
		a	A	b	B	c	C	D	E	F	G	H	THK OF GOLD	Pos.		P/N

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN H.KODOMA 27MAY94		 TE Connectivity			
		CHK Y.FUJIURA 28MAY94					
DIMENSIONS: mm 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 0.2 1 PLC ± 0.25 2 PLC ± 0.3 3 PLC ± — 4 PLC ± — ANGLES ± ± 3°		NAME AMP FH CONNECTOR PLUG (VERTICAL) (HIGH TEMP TYPE)			
MATERIAL		PRODUCT SPEC — APPLICATION SPEC — WEIGHT —				SIZE A2	CAGE CODE 00779
		FINISH — 		SCALE NTS		SHEET 1 of 1	REV R2
CUSTOMER DRAWING							