




SECT. G-G



SECT. H-H



黄銅 BRASS (t=0.203)	部分金メッキ : 0.76 μm MIN. SELECTIVE GOLD : 0.76 μm MIN. 部分半田メッキ : 2 μm MIN. SELECTIVE TIN-LEAD : 2 μm MIN. ニッケルメッキ (下地) : 1.27 μm MIN. NICKEL : 1.27 μm MIN.	0.6	2.3	2.3	0.4	1.65	1.8	Ø 0.9-1.8	#22-28	39-00-0086	5556 GS2L	バラ状 LOOSE
		0.9	4.5	3.6	0.5	2.3	1.9	Ø 1.3-3.1	#18-24	39-00-0055	5556 GS	バラ状 LOOSE
MATERIAL	メッキ・FINISH	F	E	D	C	B	A	被覆外形 INS. RANGE	適用電線 WIRE RANGE	EDP NO.	ENG. NO.	端子形状 FORM

注記
NOTES.

- 適合ハウジング : 5557 シリーズ
APPLICABLE HOUSING : 5557 SERIES.
- 嵌合相手 : 5558, 5566, 5569 シリーズ
MATES WITH TERMINAL : 5558 , 5566 , 5569 SERIES.
- 適用電線が #22-28 の製品のセレーション数は 1 とする。
THE NUMBER OF SERRATIONS TO BE ONE
FOR WIRE RANGE #22-28.

REVISED EC NO: J2005-1103 DRAWN:MMDA CHKD:KTOYODA APPR:NUKITA	DESCRIPTION 2004/10/20 2004/10/20 2004/10/22	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 10:1	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION	
		10 UNDER	±0.2	DRAWN BY H. HIRAMO	DATE 1991/05/18	TITLE NEW MINI FIT CONN CRIMP REC			
		10 OVER 30 UNDER	±0.25	CHECKED BY M. FUKUSI	DATE 1998/11/09				
		30 OVER	±0.3	APPROVED BY M. ENOMOT	DATE 1998/11/09	 MOLEX INCORPORATED			
		ANGULAR ±3 °	MATERIAL NO.		DOCUMENT NO.				
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE A3		SEE CHART SD-5556GS** 1 OF 1			
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									