



PRODUCT NUMBER

20020035-XXXXXXLF

20020035-□□□□B0□□LF

PITCH

G: 5.00 mm
H: 5.08 mm

POLES

02: 2 POLES
03: 3 POLES
.....
24: 24 POLES

LF : DENOTED RoHS COMPATIBLE

1 : STANDARD PRODUCT
W/ BOX PACKING

PROPERTY TABLE

PROPERTY TABLE					
FCI SERIES NAME			35-500	35-508	
PITCH (mm)			5.00	5.08	
VOLTAGE RATING (VAC)			300	300	
CURRENT RATING (A)			10	10	
APPLICABLE WIRE RANGE (AWG)		1-WIRE	12~26	12~26	
		2-WIRE	NA	NA	
WIRE CROSS SECTION (mm ²)		SOLID	1-WIRE	2.5	2.5
			2-WIRE	NA	NA
		STRANDED	1-WIRE	2.5	2.5
			2-WIRE	NA	NA
OPENING CONTACT HOUSING(mm ²)			2.4x3.0	2.2x3.0	
WIRE STRIP LENGTH(mm)			8~9	8~9	
WITHSTANDING VOLTAGE (kV)			1.6	1.6	
OPERATING TEMP. (°C)			-40~+115	-40~+115	
POLES AVAILABLE			02~24	02~24	
SAFETY CERTIFICATE					


HOUSING CODE

CODE	COLOR	AVAILABILITY
1	GREEN(RAL 6018/T)	STANDARD
2	BLACK	ON REQUEST ONLY
3	GREY(RAL 7004/P)	ON REQUEST ONLY
4	BLUE(RAL 5015/A)	ON REQUEST ONLY




NOTES:

1. MATERIALS


- 1-1 HOUSING: THERMALPLASTIC RESIN, UL 94V-0 RATED.
- 1-2 INSULATING LEVER: THERMALPLASTIC RESIN, UL 94V-0 RATED.
- 1-3 WIRE GUARD : STAINLESS STEEL.
- 1-4 TERMINAL: COPPER ALLOY, TIN PLATED.
- 1-5 SCREW: STEEL, ZINC PLATED.
2. PRODUCT SPECIFICATION REFER TO FCI GS-12-625.
3. PRODUCT PACKING SPECIFICATION REFER TO FCI GS-14-1394.
4. FCI, SAFETY CERTIFICATE LOGO AND SERIES NAME TO BE SHOWN ON PRODUCT SURFACE.
5. THE PRODUCTS WHERE THE PART NUMBER END IN "LF" MEET THE EUROPEAN UNION DIRECTIVE AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.

mat'l. code				surface ASME Y14.5 ✓		tolerance ASME Y14.5		projection 		product family TERMINAL BLOCK						
ltr	ecn no	dr	date	tolerances unless otherwise specified						title						
A	T11-0004	WL	011811	angles	lineal	X.±0.5			TERMINAL BLOCK							
B	T-005306	WL	082311			X.X±0.3			PLUGGABLE SIGNAL PLUG, DOWNSIDE CONTACT							
						X'±1"			W/FLANGE							
						X.XX±0.1		scale		dwg no						
				dr	WENDY CHEN		113010				sheet 1 of 3				size	
				engr	JASON HSU		113010				20020035				A4	
				chr	JASON HSU		113010									
				appd	JASON HSU		113010									
sheet index	revision sheet	B	B	B						type						CUSTOMER Drawing
		1	2	3												

PRODUCT NUMBER	SERIES NAME	PITCH
20020035-GXXXXXXLF	35-500	5.00 mm



SECTION A-A




N = Number of poles
 DIM. L = $(N \times 5.00 [.197]) + 0.6 [.024]$
 DIM. P = $(N - 1) \times 5.00 [.197]$
 DIM. T = $(N \times 5.00 [.197]) + 10.02 [.394]$
 DIM. K = $(N + 1) \times 5.00 [.197]$

POLES	DIM. L & P	DIM. T & K
2-6p	$\pm 0.15 [.006]$	$\pm 0.15 [.006]$
7-12p	$\pm 0.20 [.008]$	$\pm 0.25 [.010]$
13-18p	$\pm 0.25 [.010]$	$\pm 0.30 [.012]$
19-24p	$\pm 0.30 [.012]$	$\pm 0.40 [.016]$

mat'l. code				surface ASME Y14.5 ✓	tolerance ASME Y14.5	projection MM [INCH]	product family TERMINAL BLOCK
ltr	ecn no	dr	date	tolerances unless otherwise specified			title
B				angles X°±1°	X.X±0.5 X.X±0.3 X.XX±0.1	scale	TERMINAL BLOCK PLUGGABLE SIGNAL PLUG, DOWNSIDE CONTACT W/FLANGE
		dr	WENDY CHEN	113010			sheet 2 of 3
		enr	JASON HSU	113010			size
		chr	JASON HSU	113010			A4
		appd	JASON HSU	113010			type
sheet index	revision sheet						CUSTOMER Drawing

PRODUCT NUMBER	SERIES NAME	PITCH
20020035-HXXXXXXLF	35-508	5.08 mm



N = Number of poles
 DIM. L = $(N \times 5.08 [.200]) + 0.5 [.020]$
 DIM. P = $(N - 1) \times 5.08 [.200]$
 DIM. T = $(N \times 5.08 [.200]) + 0.16 [.400]$
 DIM. K = $(N + 1) \times 5.08 [.200]$

POLES	DIM. L & P	DIM. T & K
2-6p	$\pm 0.15 [.006]$	$\pm 0.15 [.006]$
7-12p	$\pm 0.20 [.008]$	$\pm 0.25 [.010]$
13-18p	$\pm 0.25 [.010]$	$\pm 0.30 [.012]$
19-24p	$\pm 0.30 [.012]$	$\pm 0.40 [.016]$

mat'l. code				surface ASME Y14.5 ✓	tolerance ASME Y14.5	projection MM [INCH]	product family TERMINAL BLOCK
ltr	ecn no	dr	date	tolerances unless otherwise specified			title
B				angles X°±1°	X.±0.5 X.X±0.3 X.XX±0.1	scale	TERMINAL BLOCK PLUGGABLE SIGNAL PLUG, DOWNSIDE CONTACT W/FLANGE
		dr	WENDY CHEN	113010			dwg no
		enr	JASON HSU	113010			sheet 3 of 3
		chr	JASON HSU	113010			size
		appd	JASON HSU	113010			A4
sheet index	revision sheet						type
							CUSTOMER Drawing