

Paired
Overall Beldfoil® Shield

Audio, Control, and Instrumentation Cables

Description UL AWM Style	Trade No. UL NEC C(UL) CEC Type	No. of Pairs	Standard Lengths		Std. Unit Lbs. ea.	Insulation Thickness		Jacket Thickness		Nominal O.D.		Nominal Capacitance			
			ft.	m		Inch	mm	Inch	mm	Inch	mm	* pF/ ft.	* pF/ m	** pF/ ft.	** pF/ m

22 Gage
Solid Conductors
PVC Insulated

Product Description
Tinned copper, PVC insulated, twisted pairs. Overall Beldfoil aluminum-polyester shield. 22 AWG stranded tinned copper drain wire. Chrome PVC jacket. Color code chart No. 3, Technical Information Section.

Shorting Fold Beldfoil 100% Shield Coverage 2464 300V 80°C See Attenuation, Rise Time and Bit Rate data for this series on page 91.	9302 NEC CMG CEC CMG	2	100 U-500 500 U-1000 1000	30.5 U-152.4 152.4 U-304.8 304.8	3.4 15.8 15.6 29.1 30.1	.013	.33	.032	.81	.244	6.20	35	115	50	164
	9305 NEC CMG CEC CMG	4	100 U-500 500 U-1000 1000	30.5 U-152.4 152.4 U-304.8 304.8	4.8 22.4 23.2 43.8 43.6	.013	.33	.032	.81	.265	6.73	35	115	50	164
	9306 NEC CMG CEC CMG	6	100 500 1000	30.5 152.4 304.8	6.9 31.4 64.0	.013	.33	.032	.81	.315	8.00	35	115	50	164
	9309 NEC CMG CEC CMG	9	100 500 1000	30.5 152.4 304.8	9.4 47.2 91.9	.013	.33	.033	.84	.363	9.22	35	115	50	164
	9315 NEC CMG CEC CMG	15	100 500 1000	30.5 152.4 304.8	14.7 71.8 139.1	.013	.33	.037	.94	.449	11.41	35	115	50	164
	9319 NEC CMG CEC CMG	19	100 500 1000	30.5 152.4 304.8	17.6 86.5 169.0	.013	.33	.040	1.02	.495	12.57	35	115	50	164
	9327 NEC CMG CEC CMG	27	100 500 1000	30.5 152.4 304.8	24.3 119.9 237.4	.013	.33	.045	1.14	.615	15.62	35	115	50	164
Beldfoil 100% Shield Coverage 60°C	8751 NEC CMG CEC CMG	51	250 ^{sq} 500 ^{sq} 1000 ^{sq} 1500 ^{sq}	76.2 152.4 304.8 457.2	96.0 189.2 384.4 609.3	.010	.25	.050	1.27	.710	18.03	30	98	42.8	140
	Product Description: Tinned copper, PVC insulated, twisted pairs. Beldfoil aluminum-polyester shield. 22 AWG stranded tinned copper drain wire. Chrome PVC jacket. Suggested working voltage: 300V RMS. For 38 pair polypropylene version, see 8752. Color code: Request Technical Bulletin T/8-4.														
Shorting Fold Beldfoil 100% Shield Coverage 60°C	9753 NEC CMG CEC CMG	102	250 ^{sq} 500 ^{sq} 1000 ^{sq}	76.2 152.4 304.8	215.3 438.7 879.3	.010	.25	.085	2.16	1.120	28.45	32	105	40	131
	Product Description: Tinned copper, PVC insulated, twisted pairs. Beldfoil aluminum-polyester shield. 22 AWG stranded tinned copper drain wire. Chrome PVC jacket. Suggested working voltage: 300V RMS. Color code: Request Technical Bulletin T/8-4.														

* Capacitance between conductors.
 ** Capacitance between one conductor and other conductors connected to shield.
 sq Spools are one piece, but length may vary -0 +20% from length shown.