

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AD	00		G	REVISED PER ECO-14-000068	23APR2014	NK	MM

- 1



ASSEMBLY MAY BE BROKEN TO THE DESIRED NUMBER OF POSITIONS.
- 2

THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND HOUSING
- 3

POINT OF MEASUREMENT FOR PLATING THICKNESS
- 4


BREAKAWAY NOTCH ANGLE CAN BE ORIENTED TO THE RIGHT (AS SHOWN) OR TO THE LEFT
- 5

OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



RECOMMENDED HOLE LAYOUT

	OBSOLETE	3.984	3.900	39	40	4-103148-0
		3.884	3.800	38	39	3-103148-9
		3.784	3.700	37	38	3-103148-8
		3.684	3.600	36	37	3-103148-7
SUPERSEDED BY 8-146304-6		3.584	3.500	35	36	3-103148-6
	OBSOLETE	3.484	3.400	34	35	3-103148-5
		3.384	3.300	33	34	3-103148-4
		3.284	3.200	32	33	3-103148-3
		3.184	3.100	31	32	3-103148-2
		3.084	3.000	30	31	3-103148-1
		2.984	2.900	29	30	3-103148-0
		2.884	2.800	28	29	2-103148-9
		2.784	2.700	27	28	2-103148-8
		2.684	2.600	26	27	2-103148-7
		2.584	2.500	25	26	2-103148-6
SUPERSEDED BY 7-146304-5		2.484	2.400	24	25	2-103148-5
	OBSOLETE	2.384	2.300	23	24	2-103148-4
		2.284	2.200	22	23	2-103148-3
		2.184	2.100	21	22	2-103148-2
		2.084	2.000	20	21	2-103148-1
		1.984	1.900	19	20	2-103148-0
		1.884	1.800	18	19	1-103148-9
		1.784	1.700	17	18	1-103148-8
		1.684	1.600	16	17	1-103148-7
	OBSOLETE	1.584	1.500	15	16	1-103148-6
		1.484	1.400	14	15	1-103148-5
		1.384	1.300	13	14	1-103148-4
		1.284	1.200	12	13	1-103148-3
SUPERSEDED BY 6-146304-2		1.184	1.100	11	12	1-103148-2
	OBSOLETE	1.084	1.000	10	11	1-103148-1
		.984	.900	9	10	1-103148-0
SUPERSEDED BY 5-146304-9		.884	.800	8	9	103148-9
	OBSOLETE	.784	.700	7	8	103148-8
		.684	.600	6	7	103148-7
		.584	.500	5	6	103148-6
		.484	.400	4	5	103148-5
	OBSOLETE	.384	.300	3	4	103148-4
		.284	.200	2	3	103148-3
		.184	.100	1	2	103148-2
	OBSOLETE	.084	—	—	1	103148-1
		C	B	A	NO OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN H MOLL 23OCT87		 TE Connectivity					
DIMENSIONS: INCHES		CHK T. CLARK 23OCT87							
		APVD T. CLARK 29OCT87		NAME HEADER ASSY, MOD II, BREAKAWAY, SINGLE ROW, .100CL, RIGHT ANGLE, WITH .025 SQ POSTS					
		PRODUCT SPEC —							
		APPLICATION SPEC —							
MATERIAL HOUSING: FLAME RETARDANT THERMOPLASTIC; COLOR-BLACK POSTS: COPPER ALLOY		FINISH : POSTS .000030 GOLD ON CONTACT AREA, .000100-.000200 MATTE TIN-LEAD ON SOLDER TAIL, ALL OVER .000050 NICKEL		WEIGHT —		A2 00779 C=103148		—	
CUSTOMER DRAWING				SCALE 4:1		SHEET 1 of 1		REV G	