




PANDUIT * PART NO.	NOMINAL BUNDLE DIAMETER	MAXIMUM RECOMMENDED BUNDLE DIAMETER	DIMENSIONS			WEIGHT lbs / 100 (g) / ft.
			"A" (Ref.)	"B" (Ref.)	"C"	
PW38_----	0.38 (9.65)	0.43 (10.92)	0.36 (9.14)	0.125 (3.18)	0.030 (0.76)	1.68 (762.0)
PW50_----	0.50 (12.70)	0.55 (13.97)	0.47 (11.94)		0.032 (0.81)	2.01 (910.00)
PW75_----	0.75 (19.05)	0.81 (20.57)	0.72 (18.29)		0.035 (0.89)	2.87 (1301.81)
PW100_----	1.00 (25.40)	1.125 (28.58)	0.81 (20.57)		0.040 (1.02)	4.47 (2027.6)
PW150_----	1.50 (38.10)	1.625 (41.28)	1.125 (28.58)		0.042 (1.07)	7.65 (3469.9)

1. SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE.
NO SPLICES ALLOWED.
2. DIMENSION "A" IS STATIC INSIDE DIAMETER.
DIMENSION "B" IS WIDTH OF BREAKOUT SLOTS.
DIMENSION "C" IS WALL THICKNESS.
3. NON FLAME RETARDANT PAN-WRAP IS OFFERED IN THE FOLLOWING COLORS:

PW75F - C20

Q	-	25	feet	(7.62	meters)
L	-	50	feet	(15.24	meters)
C	-	100	feet	(30.48	meters)
T	-	200	feet	(60.96	meters)
TL	-	250	feet	(76.20	meters)

F - POLYETHYLENE



CAD FILENAME/LAYERS

PANDUIT

CORP.

PAN-WRAP
(PW___F-___)

DRAWN BY JAD

DATE 11/5/04

SCALE NONE

DRAWING NO.

GB2508BH

DWG
A
SIZE

01A	6/17/09	JAD		REVISE TO TEAMCENTER NAMING, ADDED PW38, CHANGED NOTE 3	GB2508BH	01A				DATE 11/5/04	SEE NOTE 3	DRAWING NO. GB2508BH	DWG A
REV	DATE	BY	CHK	DESCRIPTION	ECN - R	CUST	SUP		CHK'D 			SIZE	