

## HIGH ISOLATION VOLTAGE SINGLE TRANSISTOR TYPE MULTI PHOTOCOUPLER SERIES

–NEPOC Series–

### DESCRIPTION

- ★ The PS2561A-1 is an optically coupled isolator containing a GaAs light emitting diode and an NPN silicon phototransistor to realize an excellent cost performance.


The PS2561A-1 is in a plastic DIP (Dual In-line Package) and the PS2561AL-1 is lead bending type (Gull-wing) for surface mount.

The PS2561AL1-1 is lead bending L1 type and the PS2561AL2-1 is lead bending L2 type (Gull-wing).

### FEATURES

- ★
  - Lead-free product : Solder plating specification Sn-Bi
  - High isolation voltage (BV = 5 000 Vr.m.s.)
  - Ordering number of taping product: PS2561AL-1-E3, E4, F3, F4  
: PS2561AL2-1-E3, E4
- Safety standards
  - UL, BSI, CSA, NEMKO, DEMKO, SEMKO, FIMKO, approved
- ★
  - DIN EN60747-5-2 (VDE0884 Part2) approved (option)

### PIN CONNECTION (Top View)




### APPLICATIONS

- Power supply
- Telephone/FAX.
- FA/OA equipment
- Programmable logic controller


The information in this document is subject to change without notice. Before using this document, please confirm that this is the latest version.  
Not all devices/types available in every country. Please check with local NEC Compound Semiconductor Devices representative for availability and additional information.

PACKAGE DIMENSIONS (UNIT : mm)


DIP Type




Long Creepage Distance




Lead Bending Type



Long Creepage Distance (Gull-Wing)



★ MARKING EXAMPLE



★ ORDERING INFORMATION (1/2)

| Part Number      | Package                      | Packing Style         | Safety Standard Approval                                                          | Solder plating Specification | Application Part Number <sup>*1</sup> |                              |
|------------------|------------------------------|-----------------------|-----------------------------------------------------------------------------------|------------------------------|---------------------------------------|------------------------------|
| PS2561A-1        | 4-pin DIP                    | Magazine case 100 pcs | Standard products<br>(UL, CSA, BSI,<br>NEMKO, DEMKO,<br>SEMKO, FIMKO<br>approved) | Sn-Pb                        | PS2561A-1                             |                              |
| PS2561AL-1       |                              |                       |                                                                                   |                              |                                       |                              |
| PS2561AL1-1      |                              |                       |                                                                                   |                              |                                       |                              |
| PS2561AL2-1      |                              |                       |                                                                                   |                              |                                       |                              |
| PS2561AL-1-E3    |                              |                       |                                                                                   |                              |                                       |                              |
| PS2561AL-1-E4    |                              |                       |                                                                                   |                              |                                       |                              |
| PS2561AL2-1-E3   |                              |                       |                                                                                   |                              |                                       |                              |
| PS2561AL2-1-E4   |                              |                       |                                                                                   |                              |                                       |                              |
| PS2561AL-1-F3    |                              |                       |                                                                                   |                              |                                       |                              |
| PS2561AL-1-F4    |                              |                       |                                                                                   |                              |                                       |                              |
| PS2561A-1-V      |                              | Magazine case 100 pcs | DIN EN60747-5-2<br>(VDE0884 Part2)<br>Approved products<br>(option)               |                              |                                       |                              |
| PS2561AL-1-V     |                              |                       |                                                                                   |                              |                                       |                              |
| PS2561AL1-1-V    |                              |                       |                                                                                   |                              |                                       |                              |
| PS2561AL2-1-V    |                              |                       |                                                                                   |                              |                                       |                              |
| PS2561AL-1-V-E3  |                              |                       |                                                                                   |                              |                                       | Embossed Tape 1 000 pcs/reel |
| PS2561AL-1-V-E4  |                              |                       |                                                                                   |                              |                                       |                              |
| PS2561AL2-1-V-E3 |                              |                       |                                                                                   |                              |                                       | Embossed Tape 1 000 pcs/reel |
| PS2561AL2-1-V-E4 |                              |                       |                                                                                   |                              |                                       |                              |
| PS2561AL-1-V-F3  |                              |                       |                                                                                   |                              |                                       | Embossed Tape 2 000 pcs/reel |
| PS2561AL-1-V-F4  |                              |                       |                                                                                   |                              |                                       |                              |
| PS2561A-1-A      |                              | Magazine case 100 pcs | Standard products<br>(UL, CSA, BSI,<br>NEMKO, DEMKO,<br>SEMKO, FIMKO<br>approved) | Sn-Bi                        |                                       |                              |
| PS2561AL-1-A     |                              |                       |                                                                                   |                              |                                       |                              |
| PS2561AL1-1-A    |                              |                       |                                                                                   |                              |                                       |                              |
| PS2561AL2-1-A    |                              |                       |                                                                                   |                              |                                       |                              |
| PS2561AL-1-E3-A  | Embossed Tape 1 000 pcs/reel |                       |                                                                                   |                              |                                       |                              |
| PS2561AL-1-E4-A  |                              |                       |                                                                                   |                              |                                       |                              |
| PS2561AL2-1-E3-A | Embossed Tape 1 000 pcs/reel |                       |                                                                                   |                              |                                       |                              |
| PS2561AL2-1-E4-A |                              |                       |                                                                                   |                              |                                       |                              |
| PS2561AL-1-F3-A  | Embossed Tape 2 000 pcs/reel |                       |                                                                                   |                              |                                       |                              |
| PS2561AL-1-F4-A  |                              |                       |                                                                                   |                              |                                       |                              |

\*1 For the application of the Safety Standard, following part number should be used.

★ ORDERING INFORMATION (2/2)

| Part Number        | Package   | Packing Style                | Safety Standard Approval                                            | Solder plating Specification | Application Part Number <sup>*1</sup> |
|--------------------|-----------|------------------------------|---------------------------------------------------------------------|------------------------------|---------------------------------------|
| PS2561A-1-V-A      | 4-pin DIP | Magazine case 100 pcs        | DIN EN60747-5-2<br>(VDE0884 Part2)<br>Approved products<br>(option) | Sn-Bi                        | PS2561A-1                             |
| PS2561AL-1-V-A     |           |                              |                                                                     |                              |                                       |
| PS2561AL1-1-V-A    |           |                              |                                                                     |                              |                                       |
| PS2561AL2-1-V-A    |           |                              |                                                                     |                              |                                       |
| PS2561AL-1-V-E3-A  |           | Embossed Tape 1 000 pcs/reel |                                                                     |                              |                                       |
| PS2561AL-1-V-E4-A  |           |                              |                                                                     |                              |                                       |
| PS2561AL2-1-V-E3-A |           | Embossed Tape 1 000 pcs/reel |                                                                     |                              |                                       |
| PS2561AL2-1-V-E4-A |           |                              |                                                                     |                              |                                       |
| PS2561AL-1-V-F3-A  |           | Embossed Tape 2 000 pcs/reel |                                                                     |                              |                                       |
| PS2561AL-1-V-F4-A  |           |                              |                                                                     |                              |                                       |

\*1 For the application of the Safety Standard, following part number should be used.

**ABSOLUTE MAXIMUM RATINGS (T<sub>A</sub> = 25°C, unless otherwise specified)**

| Parameter                       |                                    | Symbol              | Ratings     | Unit    |
|---------------------------------|------------------------------------|---------------------|-------------|---------|
| Diode                           | Reverse Voltage                    | V <sub>R</sub>      | 6           | V       |
|                                 | Forward Current (DC)               | I <sub>F</sub>      | 30          | mA      |
|                                 | Power Dissipation Derating         | ΔP <sub>D</sub> /°C | 1.5         | mW/°C   |
|                                 | Power Dissipation                  | P <sub>D</sub>      | 150         | mW      |
|                                 | Peak Forward Current <sup>*1</sup> | I <sub>FP</sub>     | 0.5         | A       |
| Transistor                      | Collector to Emitter Voltage       | V <sub>CEO</sub>    | 70          | V       |
|                                 | Emitter to Collector Voltage       | V <sub>ECO</sub>    | 5           | V       |
|                                 | Collector Current                  | I <sub>C</sub>      | 30          | mA      |
|                                 | Power Dissipation Delay            | ΔP <sub>C</sub> /°C | 1.5         | mW/°C   |
|                                 | Power Dissipation                  | P <sub>C</sub>      | 150         | mW      |
| Isolation Voltage <sup>*2</sup> |                                    | BV                  | 5 000       | Vr.m.s. |
| Operating Ambient Temperature   |                                    | T <sub>A</sub>      | –55 to +100 | °C      |
| Storage Temperature             |                                    | T <sub>stg</sub>    | –55 to +150 | °C      |

**\*1** PW = 100 μs, Duty Cycle = 1%

**\*2** AC voltage for 1 minute at T<sub>A</sub> = 25°C, RH = 60% between input and output


ELECTRICAL CHARACTERISTICS (T<sub>A</sub> = 25°C)

| Parameter  |                                                                        | Symbol               | Conditions                                                            | MIN.             | TYP. | MAX. | Unit |
|------------|------------------------------------------------------------------------|----------------------|-----------------------------------------------------------------------|------------------|------|------|------|
| Diode      | Forward Voltage                                                        | V <sub>F</sub>       | I <sub>F</sub> = 10 mA                                                |                  | 1.2  | 1.4  | V    |
|            | Reverse Current                                                        | I <sub>R</sub>       | V <sub>R</sub> = 5 V                                                  |                  |      | 5    | μA   |
|            | Terminal Capacitance                                                   | C <sub>t</sub>       | V = 0 V, f = 1.0 MHz                                                  |                  | 10   |      | pF   |
| Transistor | Collector to Emitter Dark Current                                      | I <sub>CEO</sub>     | V <sub>CE</sub> = 70 V, I <sub>F</sub> = 0 mA                         |                  |      | 100  | nA   |
| Coupled    | Current Transfer Ratio (I <sub>c</sub> /I <sub>F</sub> ) <sup>*1</sup> | CTR                  | I <sub>F</sub> = 5 mA, V <sub>CE</sub> = 5 V                          | 50               |      | 300  | %    |
|            | Collector Saturation Voltage                                           | V <sub>CE(sat)</sub> | I <sub>F</sub> = 10 mA, I <sub>c</sub> = 2 mA                         |                  | 0.13 | 0.3  | V    |
|            | Isolation Resistance                                                   | R <sub>I-O</sub>     | V <sub>I-O</sub> = 1.0 kV <sub>DC</sub>                               | 10 <sup>11</sup> |      |      | Ω    |
|            | Isolation Capacitance                                                  | C <sub>I-O</sub>     | V = 0 V, f = 1.0 MHz                                                  |                  | 0.4  |      | pF   |
|            | Rise Time <sup>*2</sup>                                                | t <sub>r</sub>       | V <sub>CC</sub> = 10 V, I <sub>c</sub> = 2 mA, R <sub>L</sub> = 100 Ω |                  | 5    |      | μs   |
|            | Fall Time <sup>*2</sup>                                                | t <sub>f</sub>       |                                                                       |                  | 7    |      |      |







\*1 CTR rank

- N : 50 to 300 (%)
- H : 80 to 160 (%)
- Q : 100 to 200 (%)
- W : 130 to 260 (%)

\*2 Test circuit for switching time




**TYPICAL CHARACTERISTICS ( $T_A = 25^\circ\text{C}$ , unless otherwise specified)**




**Remark** The graphs indicate nominal characteristics.


NORMALIZED CURRENT TRANSFER RATIO vs. AMBIENT TEMPERATURE




CURRENT TRANSFER RATIO vs. FORWARD CURRENT




SWITCHING TIME vs. LOAD RESISTANCE




SWITCHING TIME vs. LOAD RESISTANCE



FREQUENCY RESPONSE




LONG TERM CTR DEGRADATION



**Remark** The graphs indicate nominal characteristics.

TAPING SPECIFICATIONS (UNIT : mm)


Outline and Dimensions (Tape)




Tape Direction

PS2561AL-1-E3

PS2561AL-1-E4




Outline and Dimensions (Reel)




Packing: 1 000 pcs/reel


# Outline and Dimensions (Tape)



## Tape Direction




# Outline and Dimensions (Reel)




★


### Outline and Dimensions (Tape)



### Tape Direction



### Outline and Dimensions (Reel)




## NOTES ON HANDLING

### 1. Recommended soldering conditions

#### (1) Infrared reflow soldering

- Peak reflow temperature 260°C or below (package surface temperature)
- Time of peak reflow temperature 10 seconds or less
- Time of temperature higher than 220°C 60 seconds or less
- Time to preheat temperature from 120 to 180°C 120±30 s
- Number of reflows Three
- Flux Rosin flux containing small amount of chlorine (The flux with a maximum chlorine content of 0.2 Wt% is recommended.)

Recommended Temperature Profile of Infrared Reflow



#### (2) Wave soldering

- Temperature 260°C or below (molten solder temperature)
- Time 10 seconds or less
- Preheating conditions 120°C or below (package surface temperature)
- Number of times One (Allowed to be dipped in solder including plastic mold portion.)
- Flux Rosin flux containing small amount of chlorine (The flux with a maximum chlorine content of 0.2 Wt% is recommended.)

#### ★ (3) Soldering by soldering iron

- Peak temperature (lead part temperature) 350°C or below
- Time (each pins) 3 seconds or less
- Flux Rosin flux containing small amount of chlorine (The flux with a maximum chlorine content of 0.2 Wt% is recommended.)

(a) Soldering of leads should be made at the point 1.5 to 2.0 mm from the root of the lead.

(b) Please be sure that the temperature of the package would not be heated over 100°C.

**(4) Cautions**

- Fluxes

Avoid removing the residual flux with freon-based and chlorine-based cleaning solvent.

★ **2. Cautions regarding noise**

Be aware that when voltage is applied suddenly between the photocoupler's input and output or between collector-emitters at startup, the output side may enter the on state, even if the voltage is within the absolute maximum ratings.

**USAGE CAUTIONS**

1. Protect against static electricity when handling.
2. Avoid storage at a high temperature and high humidity.

- **The information in this document is current as of May, 2004. The information is subject to change without notice. For actual design-in, refer to the latest publications of NEC's data sheets or data books, etc., for the most up-to-date specifications of NEC semiconductor products. Not all products and/or types are available in every country. Please check with an NEC sales representative for availability and additional information.**
- No part of this document may be copied or reproduced in any form or by any means without prior written consent of NEC. NEC assumes no responsibility for any errors that may appear in this document.
- NEC does not assume any liability for infringement of patents, copyrights or other intellectual property rights of third parties by or arising from the use of NEC semiconductor products listed in this document or any other liability arising from the use of such products. No license, express, implied or otherwise, is granted under any patents, copyrights or other intellectual property rights of NEC or others.
- Descriptions of circuits, software and other related information in this document are provided for illustrative purposes in semiconductor product operation and application examples. The incorporation of these circuits, software and information in the design of customer's equipment shall be done under the full responsibility of customer. NEC assumes no responsibility for any losses incurred by customers or third parties arising from the use of these circuits, software and information.
- While NEC endeavours to enhance the quality, reliability and safety of NEC semiconductor products, customers agree and acknowledge that the possibility of defects thereof cannot be eliminated entirely. To minimize risks of damage to property or injury (including death) to persons arising from defects in NEC semiconductor products, customers must incorporate sufficient safety measures in their design, such as redundancy, fire-containment, and anti-failure features.
- NEC semiconductor products are classified into the following three quality grades:  
 "Standard", "Special" and "Specific". The "Specific" quality grade applies only to semiconductor products developed based on a customer-designated "quality assurance program" for a specific application. The recommended applications of a semiconductor product depend on its quality grade, as indicated below. Customers must check the quality grade of each semiconductor product before using it in a particular application.  
 "Standard": Computers, office equipment, communications equipment, test and measurement equipment, audio and visual equipment, home electronic appliances, machine tools, personal electronic equipment and industrial robots  
 "Special": Transportation equipment (automobiles, trains, ships, etc.), traffic control systems, anti-disaster systems, anti-crime systems, safety equipment and medical equipment (not specifically designed for life support)  
 "Specific": Aircraft, aerospace equipment, submersible repeaters, nuclear reactor control systems, life support systems and medical equipment for life support, etc.  
 The quality grade of NEC semiconductor products is "Standard" unless otherwise expressly specified in NEC's data sheets or data books, etc. If customers wish to use NEC semiconductor products in applications not intended by NEC, they must contact an NEC sales representative in advance to determine NEC's willingness to support a given application.  
 (Note)  
 (1) "NEC" as used in this statement means NEC Corporation, NEC Compound Semiconductor Devices, Ltd. and also includes its majority-owned subsidiaries.  
 (2) "NEC semiconductor products" means any semiconductor product developed or manufactured by or for NEC (as defined above).

M8E 00.4-0110

|                    |               |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                     |
|--------------------|---------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <div>Caution</div> | GaAs Products | <p>This product uses gallium arsenide (GaAs).<br/>GaAs vapor and powder are hazardous to human health if inhaled or ingested, so please observe the following points.</p> <ul style="list-style-type: none"> <li>• Follow related laws and ordinances when disposing of the product. If there are no applicable laws and/or ordinances, dispose of the product as recommended below. <ol style="list-style-type: none"> <li>1. Commission a disposal company able to (with a license to) collect, transport and dispose of materials that contain arsenic and other such industrial waste materials.</li> <li>2. Exclude the product from general industrial waste and household garbage, and ensure that the product is controlled (as industrial waste subject to special control) up until final disposal.</li> </ol> </li> <li>• Do not burn, destroy, cut, crush, or chemically dissolve the product.</li> <li>• Do not lick the product or in any way allow it to enter the mouth.</li> </ul> |
|--------------------|---------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

► For further information, please contact

**NEC Compound Semiconductor Devices, Ltd.**    <http://www.ncsd.necel.com/>

E-mail: [salesinfo@ml.ncsd.necel.com](mailto:salesinfo@ml.ncsd.necel.com) (sales and general)

[techinfo@ml.ncsd.necel.com](mailto:techinfo@ml.ncsd.necel.com) (technical)

5th Sales Group, Sales Division    TEL: +81-44-435-1588    FAX: +81-44-435-1579

**NEC Compound Semiconductor Devices Hong Kong Limited**

E-mail: [ncsd-hk@elhk.nec.com.hk](mailto:ncsd-hk@elhk.nec.com.hk) (sales, technical and general)

Hong Kong Head Office    TEL: +852-3107-7303    FAX: +852-3107-7309

Taipei Branch Office    TEL: +886-2-8712-0478    FAX: +886-2-2545-3859

Korea Branch Office    TEL: +82-2-558-2120    FAX: +82-2-558-5209

**NEC Electronics (Europe) GmbH**    <http://www.ee.nec.de/>

TEL: +49-211-6503-0    FAX: +49-211-6503-1327

**California Eastern Laboratories, Inc.**    <http://www.cel.com/>

TEL: +1-408-988-3500    FAX: +1-408-988-0279