

1829A Coax - Series 6

 For more Information
 please call

1-800-Belden1

**General Description:**

Series 6, 18 AWG solid .040" bare copper-covered steel conductor, gas-injected foam polyethylene insulation, Duobond® II + aluminum braid shield (60% coverage), PVC jacket (black, gray, white or neutral).

Physical Characteristics (Overall)**Conductor**

AWG:

# Coax	AWG	Stranding	Conductor Material	Dia. (mm)
1	18	Solid	BCCS - Bare Copper Covered Steel	1.016

Total Number of Conductors: 1

Insulation

Insulation Material:

Insulation Material	Dia. (mm)
Gas-injected FPE - Foam Polyethylene	4.572

Outer Shield

Outer Shield Material:

Layer #	Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
1	Bonded Duofoil®	Tape	Bonded Aluminum Foil-Polyester Tape-Aluminum Foil	100
2		Braid	AL - Aluminum	60

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
PVC - Polyvinyl Chloride

Overall Cable

Overall Nominal Diameter: 6.858 mm

Mechanical Characteristics (Overall)

Operating Temperature Range:	-40°C To +80°C
Bulk Cable Weight:	40.181 Kg/Km
Max. Recommended Pulling Tension:	560.473 N
Min. Bend Radius/Minor Axis:	69.850 mm

Applicable Specifications and Agency Compliance (Overall)**Applicable Standards & Environmental Programs**

NEC/(UL) Specification:	CATV, CM
CEC/C(UL) Specification:	CM
EU Directive 2011/65/EU (ROHS II):	Yes
EU CE Mark:	No
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2004

EU Directive 2002/96/EC (WEEE):	Yes
---------------------------------	-----

EU Directive 2003/11/EC (BFR):	Yes
--------------------------------	-----

CA Prop 65 (CJ for Wire & Cable):	Yes
-----------------------------------	-----

MII Order #39 (China RoHS):	Yes
-----------------------------	-----

Series Type:	Series 6
--------------	----------

Flame Test

UL Flame Test:	UL1685 UL Loading
----------------	-------------------

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Electrical Characteristics (Overall)**Nom. Characteristic Impedance:**

Impedance (Ohm)

75.000

Nom. Inductance:

Inductance (μH/m)

0.318257

Nom. Capacitance Conductor to Shield:

Capacitance (pF/m)

53.1522

Nominal Velocity of Propagation:

VP (%)

83

Nominal Delay:

Delay (ns/m)

3.9372

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)

91.868

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/km)

29.529

Nom. Attenuation:

Freq. (MHz)	Attenuation (dB/100m)
-------------	-----------------------

5	1.6405
---	--------

55	4.5934
----	--------

211	8.5306
-----	--------

500	13.4521
-----	---------

750	16.7331
-----	---------

862	18.0455
-----	---------

1000	19.686
------	--------

1450	25.5918
------	---------

1800	28.2166
------	---------

2250	32.1538
------	---------

3000	37.0753
------	---------

Max. Attenuation:

Freq. (MHz)	Attenuation (dB/100m)
-------------	-----------------------

5	2.19827
---	---------

55	5.2496
----	--------

211	9.41647
-----	---------

500	14.6989
-----	---------

750	18.3408
-----	---------

862	19.6204
-----	---------

1000	21.4577
1450	26.248
1800	28.8728
2250	32.81
3000	39.0439

Max. Operating Voltage - UL:

Voltage
350 V RMS

Minimum Structural Return Loss:

Start Freq. (MHz)	Stop Freq. (MHz)	Min. SRL (dB)
950	2250	15
2250	3000	10

Sweep Test

Sweep Testing: 950 MHz - 3 GHz

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
1829A Q5HU1000	305 MT	13.154 KG	WHITE, NEUTRAL	Z	#18 GIFHDLDP SH FR PVC
1829A Q5H1000	305 MT	13.608 KG	WHITE, NEUTRAL	Z	#18 GIFHDLDP SH FR PVC
1829A 008U1000	305 MT	13.154 KG	GRAY	Z	#18 GIFHDLDP SH FR PVC
1829A 0081000	305 MT	13.608 KG	GRAY	Z	#18 GIFHDLDP SH FR PVC
1829A 009U1000	305 MT	13.154 KG	WHITE	Z	#18 GIFHDLDP SH FR PVC
1829A 0091000	305 MT	13.608 KG	WHITE	Z	#18 GIFHDLDP SH FR PVC
1829A 010U1000	305 MT	13.154 KG	BLACK		#18 GIFHDLDP SH FR PVC
1829A 0101000	305 MT	13.608 KG	BLACK	C	#18 GIFHDLDP SH FR PVC

Notes:

C = CRATE REEL PUT-UP.

Z = FINAL PUT-UP LENGTH MAY VARY (+ OR -) 10% FOR SPOOLS OR REELS AND(+ OR -) 5% FOR UNREEL CARTONS FROM LENGTH SHOWN.

Revision Number: 6 Revision Date: 08-10-2012

© 2013 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.