





REV F - 2006-04-17






FIG. 1

www.fciconnect.com			surface ☒		tolerance std		projection		MM	
			TOLERANCES UNLESS OTHERWISE SPECIFIED							
Dr	Jason Hsu	1/11/11	ANGULAR	LINEAR	0.X	± 0.25	size A4	Scale N/A		
Eng	Jason Hsu	1/11/11			0.XX	± 0.15				
Chr	S Alosius	5/21/15			0.XXX	± 0.10				
Appr	Biju K Paul	5/21/15	Product family				ECN ELX-I-20939			
			title PLCC SMT Socket				dwg no 69802		Rev. AG	
catalog no			-				CUSTOMER		sheet 1 of 5	

TABLE I

NO. OF CONTACTS	DIM. A ±0.20	DIM. B ±0.20	DIM. C ±0.20	DIM. D ±0.20	DIM. E MAX.	DIM. F ±0.10	DIM. G ±0.10	DIM. H ±0.20	DIM. I ±0.20	DIM. J ±0.20
32	7.62	17.78	22.50	10.16	20.32	11.02	13.56	17.78	11.94	14.48
44	12.70	22.86	27.50	12.70	22.86	16.10	16.10	20.32	17.02	

TABLE II

PART NO.	WITH POLARIZING PEGS	PACKAGING BY PVC TUBE	PACKAGING BY TAPE & REEL	MCK PART NO.
69802-0XXLF	✓	✓		PLCC-XXP-T-SMT-P-LF
69802-1XXLF		✓		PLCC-XXP-T-SMT-LF
69802-4XXLF			✓	PLCC-XXP-T-SMT-TR-LF

NOTE:

ORDERING DATA: 69802 - X XX LF

LEAD FREE
 NO OF CONTACTS
 SEE TABLE II



Copyright FCI.

www.fciconnect.com			surface - ✓		tolerance std		projection		MM	
			TOLERANCES UNLESS OTHERWISE SPECIFIED							
Dr	Jason Hsu	1/11/11	ANGULAR	LINEAR	0.X	± 0.25	size A4	Scale N/A		
Eng	Jason Hsu	1/11/11			0.XX	± 0.15				
Chr	S Alosius	5/21/15			0.XXX	± 0.10				
			0° ±5°				ECN		ELX-1-20939	
Appr	BiJu K Paul	5/21/15	Product family					Spec ref		
			title PLCC SMT Socket			dwg no 69802		Rev A0		
catalog no			-			CUSTOMER			sheet 2 of 5	

REV F - 2005-04-17

NOTES:

1. MATERIAL:

1-1 HOUSING : PPS GB8411,UL94V-0 COLOR IN BROWN.
 PLATING : 150u" LEAD FREE TIN MIN. OVER 40u" NICKEL MIN.
 CONTACT : PHOSPHOR BRONZE C5212RH.

2. THE "FCI" LOGO IS LOCATED AS SHOWN.

3. RECOMMEND PCB LAYOUT IS SHOWN IN FIG.1.

4. COPLANARITY REQUIREMENT;

A. CONTACT MUST BE BELOW HOUSING BOTTOM SURFACE WITHIN 0.23MM.
 B. CONTACT SEATING LINE MUST BE WITHIN 0.102MM.

5. THE POSITION OF PIN#1 IN THE CENTER PAD IS AS SHOWN.

6. THE PACKAGING INFORMATION SHOWS ON SHEET 4 &5.

7. PRODUCT SPECIFICATION; GES-12-158.

8. MANUFACTURING PROCESS COMPATIBILITY: THE HOUSING WILL WITHSTAND EXPOSURE
 TO 245°C PEAK TEMPERATURE FOR 5 SECOND IN A IR REFLOW APPLICATION.



Copyright FCI.

www.fciconnect.com			surface 		tolerance std		projection 			
			TOLERANCES UNLESS OTHERWISE SPECIFIED							
Dr	Jason Hsu	1/11/11	ANGULAR	LINEAR	0.X	± 0.25	size A4	Scale N/A		
Eng	Jason Hsu	1/11/11			0.XX	± 0.15				
Chr	S Alosius	5/21/15			0.XXX	± 0.10				
Appr	Biju K Paul	5/21/15	0° ±5°				ECN		ELX-I-20939	
			Product family				Spec ref			
			title PLCC SMT Socket			dwg no 69802			Rev. AG	
			catalog no -			CUSTOMER			sheet 3 of 5	

REV F - 2005-04-17



Copyright FCI.





TABLE III

NO. OF PIN.	WIDTH	PITCH	PCS/REEL	REEL/CARTON	TOTAL (PCS)
32P	32.0	24.00	390	10	3900
44P	44.0	32.00	250	8	2000



*REEL DIAMETER: $\varnothing 13$ in"

www.fciconnect.com			surface 		tolerance std		projection 				
			TOLERANCES UNLESS OTHERWISE SPECIFIED								
Dr	Jason Hsu	1/11/11	ANGULAR	LINEAR	0.X	± 0.25	size	A4	Scale N/A		
Eng	Jason Hsu	1/11/11			0.XX	± 0.15					
Chr	S Alosius	5/21/15			0.XXX	± 0.10					
Appr	Biju K Paul	5/21/15	0° ±5°				ECN		ELX-I-20939		
			Product family					Spec ref			
			title			PLCC SMT Socket			dwg no		Rev. AG
			catalog no			-			CUSTOMER		
									sheet 4 of 5		

REV F - 2005-04-17

TABLE IV

A / P PART NO.	69802-X32X	69802-X44X
DESCRIPTION	32P	44P
PCS / TUBE	28	25
PCS / INNER BOX	728	500
INNER BOX / CARTON (WITH SOCKET)	10	10
INNER BOX / CARTON (W / O SOCKET)	0	0
TOTAL (PCS)	7280	5000
N.W.	10.0 KG	8.5 KG
G.W.	18.0 KG	17.0 KG



www.fciconnect.com			surface - ✓	tolerance std	projection	MM	
			TOLERANCES UNLESS OTHERWISE SPECIFIED		⊕-□	↔	
Dr	Jason Hsu	1/11/11	ANGULAR	LINEAR	0.X	± 0.25	size A4
Eng	Jason Hsu	1/11/11			0.XX	± 0.15	
Chr	S Alosius	5/21/15	0° ±5°		0.XXX	± 0.10	ECN ELX-1-20939
Appr	BiJu K Paul	5/21/15	Product family			Spec ref	
title PLCC SMT Socket			dwg no 69802			Rev. AG	
catalog no -			CUSTOMER			sheet 5 of 5	