


HV RAD-LDD Indust X7R HV, Ceramic, 3300 pF, 20%, 3,000 V, X7R, Commercial, High Voltage, Lead Spacing = 5.59mm



General Information	
Supplier:	KEMET
Series:	HV RAD-LDD Indust X7R HV
Style:	Radial
Description:	Commercial, High Voltage
Features:	Commercial
RoHS:	Yes
Termination:	Nickel
Failure Rate:	N/A

Dimensions	
L	8.13mm MAX
H	7.11mm MAX
T	6.35mm MAX
S	5.59mm +/-0.76mm
LL	31.75mm MIN
F	0.635mm +/-0.102/-0.051mm

Specifications	
Capacitance:	3300 pF
Capacitance Tolerance:	20%
Voltage DC:	3000 VDC
Dielectric Withstanding Voltage:	4,500 V
Temperature Range:	-55/+125C
Temperature Coefficient:	X7R
Dissipation Factor:	2.5%
Insulation Resistance:	100 GOhms

Packaging Specifications	
Packaging:	Bulk, Bag
Packaging Quantity:	1

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.