

# SCREW AND TERMINAL ASSEMBLY

PTXXX-XX-XX

ENTER 1 FOR A1000 SERIES  
DO NOT ENTER DIGIT WHEN  
ASSY.IS FOR A2000 OR  
A3000 SERIES.

## TERMINAL OPTIONS

| OPTION CODE | DESCRIPTION        |
|-------------|--------------------|
| NC          | P.C.TAIL (NO COIN) |

## TERMINAL OPTIONS 1000 SERIES

| OPTION CODE | DESCRIPTION         |
|-------------|---------------------|
| 01          | HANDWIRED           |
| 02          | P.C.TAIL            |
| 03          | NON FEED-THRU & MT. |
| 04          | SHORT WIRE WRAP     |
| 07          | EXTENDED WIRE WRAP  |
| 08          | P.C. TAIL (NO COIN) |

## TERMINAL OPTIONS 2000/3000 SERIES

| OPTION CODE | DESCRIPTION          |
|-------------|----------------------|
| 01          | SOLDER TAIL          |
| 02          | P.C.TAIL             |
| 04          | WIRE WRAP            |
| 05          | EXTENDED SOLDER TAIL |
| 06          | SHORT SOLDER TAIL    |
| 07          | EXTENDED WIRE WRAP   |
| 09          | .250 WIDE Q.C.       |
| 10          | .187 WIDE Q.C.       |
| 11          | .110 WIDE Q.C.       |
| 19          | EXTENDED .250 W Q.C. |

## METRIC

|    |                      |
|----|----------------------|
| 71 | SOLDER TAIL          |
| 72 | P.C.TAIL             |
| 74 | WIRE WRAP            |
| 75 | EXTENDED SOLDER TAIL |
| 77 | EXTENDED WIRE WRAP   |
| 79 | .250 WIDE Q.C.       |
| 80 | .187 WIDE Q.C.       |
| 81 | .110 WIDE Q.C.       |
| 89 | EXTENDED .250 W Q.C. |

## SCREW OPTIONS 1000 SERIES


| OPTION CODE | DESCRIPTION          |
|-------------|----------------------|
| 00          | NO SCREWS            |
| 02          | #6-32 PHILSLOT       |
| 03          | #6-32 PH/SL P.H. S/S |
| 04          | #6-32 PHILSLOT BRASS |
| 07          | #6-32 SEMS PH/SL STL |

## SCREW OPTIONS 2000/3000 SERIES

| OPTION CODE | DESCRIPTION              |
|-------------|--------------------------|
| 00          | NO SCREWS                |
| 01          | #6-32 SLT.HX/HD GRN.GRD. |
| 02          | #6-32 PHILSLOT           |
| 07          | #6-32 SEMS PHILSLOT      |
| 04          | #6-32 PHILSLOT BRASS     |
| 09          | #6-32 SEMS PHILSLOT BRAS |

## METRIC

M3.5 X 6 METRIC THD.B.H.



DETAIL FOR 2000/3000  
SERIES TERMINALS

### NOTES:

- UNP (AT THE END OF THE PART #) = UNPACKED

PART NO. PTXXX-XX-XX

METRIC(mm)[ENGLISH(in)]

THIS IS A CAD DRAWING — DO NOT  
MANUALLY REVISE

| TOLERANCES<br>UNLESS OTHERWISE SPECIFIED |                 | THIRD ANGLE PROJECTION                      |
|------------------------------------------|-----------------|---------------------------------------------|
| METRIC TOL                               | ENGLISH TOL     |                                             |
| 1 PL DEC.=±.25                           | 2 PL DEC.=±.01  | ANGULAR TOL= ±2°<br>FRACTION TOL= ± 1/64 IN |
| 2 PL DEC.=±.13                           | 3 PL DEC.=±.005 |                                             |

**COPYRIGHT** — Cooper Industries, Inc.  
This is an unpublished work. The disclosure of this work is limited to a select personnel.  
Further dissemination or disclosure to the public is PROHIBITED. This unpublished work  
is protected by Federal Copyright law and all rights thereunder are reserved by Cooper  
Industries, Inc.

**CONFIDENTIAL** — The information contained in this document is the property of  
Cooper Industries, Inc. It is not for public disclosure. Possession of the information does  
not convey any right to loan, sell or disclose the information. Unauthorized reproduction  
or use of the information is prohibited. This document is to be returned to Cooper  
Industries, Inc. upon completion of the purposes for which it is loaned or upon request.  
MATERIAL

FINISH USED ON

**COOPER** Bussmann Circuit Components  
7300 W. Wilson Ave. Chicago, IL 60656

TITLE  
SCREW & TERMINAL ASSY.

DRAWN BY RF ENG. / APPR. R.MAROS DATE 7/11/95 SCALE 1:1

PART NO. PTXXX-XX-XX

SHEET 1 of 1

F/N: 00022095

B-SEC: REV 12/85