


3M™ WIREMOUNT SOCKET, 3000 SERIES
.100" X .100" FOR .050" PITCH CABLE, (OPTIONAL PLASTIC OR METAL STRAIN RELIEF)



- * INDUSTRY STANDARD IDC SOCKET.
- * POSITIVE LOCKING METAL "J" CLIPS PROVIDE HIGH COVER RETENTION.
- * MATES WITH 3M HEADERS, PLUGS AND PIN STRIPS FOR QUICK CONNECT/DISCONNECT CAPABILITY.
- * OPEN OR CLOSED END COVERS AVAILABLE.
- * ACCEPTS FLAT CABLE OR DISCRETE WIRE.
- * MILITARY POLARIZATION, WITH OR WITHOUT CENTER BUMP.
- * TRANSFER ADHESIVE ON COVERS PROVIDES PRECISION ALIGNMENT BETWEEN CONNECTOR AND CABLES RESULTING IN HIGH YIELD TERMINATIONS.
- * AVAILABILITY OF PULL TAB TO FACILITATE PROPER UNPLUGGING.
- * AVAILABILITY OF 2 TYPES OF STRAIN RELIEF (STANDARD AND LOW PROFILE) TO ISOLATE THE IDC INTERFACE.
- * SET THE STANDARD FOR MIL SPEC AND IEC STANDARDIZATION.
- * AVAILABILITY OF MILITARY AND CENTER BUMP POLARIZATION.

2 PHYSICAL :

INSULATION: GLASS FILLED POLYESTER (PBT)
MATERIAL: UL94V-0
FLAMMABILITY: COLOR: GRAY
CONTACT: COPPER ALLOY
MATERIAL: J-CLIP: STAINLESS STEEL
PLATING: UNDER PLATING AND U-SLOT: 100μ" [2.54μm] AVG. NICKEL-OVERALL
WIPING AREA: 30μ" [0.76μm] AVG. GOLD
WIRE ACCOMMODATION: 26 AND 28 AWG SOLID AND STRANDED
MARKINGS: 3M LOGO, PART IDENTIFICATION NUMBER, ORIENTATION TRIANGLE

2 ELECTRICAL :

CURRENT RATING:

	1 LINE	6 ADJACENT LINES	ALL LINES
28 AWG	4.50	1.75	1.00
26 AWG	4.75	2.00	1.00

RATING CONDITIONS: EIA-364-070 METHOD 2, 30°C MAXIMUM TEMPERATURE RISE, 20% DERATED. REFERENCE APPROPRIATE 3M PRODUCT SPECIFICATION FOR CURRENT DERATING CURVES.

INSULATION RESISTANCE: >1 X 10⁹Ω AT 500 V_{DC}
WITHSTANDING VOLTAGE: 1,000V_{RMS} AT SEA LEVEL

2 ENVIRONMENTAL :

TEMPERATURE RATING: -55°C TO +105°

ORDERING INFORMATION
SOCKETS

XXXX-XXXX

SOCKET SERIES:
(SEE TABLE 1)

STRAIN RELIEF:
00 = NO STRAIN RELIEF
XX = CONTACT QUANTITY FOR
PLASTIC STRAIN RELIEF
10 THRU 60 POSITION
(I.E. 50 FOR A 50 POS)
05 = PLASTIC STRAIN RELIEF
6 AND 8 POSITION
06 = METAL STRAIN RELIEF
10 THRU 60 POSITION

POLARIZATION:
0 = MILITARY (DUAL SLOT)
6 = CENTER BUMP AND MILITARY

COVER:
6 = OPEN END
(FOR DAISY CHANING OR BUSSING)
7 = CLOSED END
(FOR END CABLE TERMINATION)
(10 TO 60 POSITION ONLY)

3M ELECTRONICS MATERIALS SOLUTIONS DIVISION
INTERCONNECT SOLUTIONS
<http://www.3M.com/interconnect>

3M IS A TRADEMARK OF 3M COMPANY.
FOR TECHNICAL, SALES OR ORDERING
INFORMATION CALL 800-225-5373

UL
UL FILE NO: E68080

(ORDER SEPARATELY)
SEE TS-0720

ORDERING INFORMATION
STRAIN RELIEF

3448-X0XX

TYPE:
2 = METAL, LOW PROFILE
10 THRU 60 POSITION
(SEE NOTE 3)
3 = PLASTIC

XX = CONTACT QUANTITY
SEE TABLE 1
(I.E. 50 FOR A
50 POSITION STRAIN
RELIEF)

ORDERING INFORMATION
KEYING PLUG

3435-0000

ORDERING INFORMATION
PULL TABS

3490-X


NOTE:
ASSEMBLY TOOLS:
3M PRESS (OR EQUIVALENT): 3640
3M LOCATOR PLATE: 3443-94
3M PLATTN: 3442-9

- NOTES
1. REGULATORY INFORMATION:
VISIT 3M.com/regs
 2. UNLESS OTHERWISE NOTED,
REFERENCES TO INDUSTRY
SPECIFICATIONS ARE INTENDED
TO INDICATE SUBSTANTIAL
COMPLIANCE TO THE MATERIAL
ELEMENTS OF THE SPECIFICATION.
SUCH REFERENCES SHOULD NOT BE
CONSTRUED AS A GUARANTEE OF
COMPLIANCE TO ALL REQUIREMENTS
IN A GIVEN SPECIFICATION.
 3. THIS POLARIZING GROOVE IS
NON-EXISTENT ON 3863, 3868,
3385 AND 3473 SERIES.
 4. THIS POLARIZING GROOVE IS
NON-EXISTENT ON 3863 SERIES
FOR POLARIZATION OPTION 6.
 5. THE LOW PROFILE STRAIN RELIEF
CAN BE USED WITH THE 4600 SERIES
PLUG AND .100 X .100 HEADERS
WITH EJECTOR LATCHES. THE LATCHES
WILL ONLY FUNCTION AS AN EJECTOR.
 6. TAPERED PIN TIP CONFIGURATION
RECOMMENDED.
 7. DIMENSION MEASURED AT TIP OF
PINS.



DIMENSIONS: INCHES [MM]
[MM] IS REF. ONLY

DESIGN REFERENCE	NEXT ASSEMBLY	REV	ECO	ISSUE DATE AND DESCRIPTION	DRFT	CHKD
XXXX	XXXX	ECO	ECO	DATE JUN 21, 2021	DATE	DATE
DIVISION	DIVISION CODE	DRFT	CHKD	DATE JUN 21, 2021	DATE	DATE
DO NOT SCALE DRAWING	SCALE 4/1	TOLERANCES EXCEPT AS NOTED	INCHES .00 ± .01 .000 ± .005 .0000 ± .0002	MILLIMETERS 0 ± .00 ± .000 ± .000	MARKED ONLY	ANGLES ±
THIRD ANGLE PROJECTION	INTERPRET PER ASME Y14.5 - 2018	MAX SURFACE ROUGHNESS	0.00 ± .000 ± .000	MIN SURFACES	0.00 ± .000 ± .000	0.00 ± .000 ± .000
3M	3M Center St. Paul, MN 55144	© 3M COPYRIGHT 2021	This document and the information it contains are 3M property and may not be reproduced or further distributed without 3M permission, or used or disclosed other than for 3M authorized purposes. All rights reserved.	TITLE	WIREMOUNT SOCKET, .100" X .100", .050" PITCH CABLE	CAGE NUMBER
MODEL	3000	SIZE	DRAWING NO.	REV.	78-5100-0718-6	G
LISTS	YES	NO	SHT 1 OF 4			

3M™ WIREMOUNT SOCKET, 3000 SERIES
.100" X .100" FOR .050" PITCH CABLE, (OPTIONAL PLASTIC OR METAL STRAIN RELIEF)





COVER ASSEMBLY




CONTACT QTY.	SOCKET SERIES	DIM. "A"	DIM. "B"
06	3863	0.48 [12.2]	0.34 [8.6]
08	3868	0.58 [14.7]	0.44 [11.2]
10	3473	0.68 [17.3]	0.54 [13.7]
14	3385	0.88 [22.4]	0.74 [18.8]
16	3452	0.98 [24.9]	0.84 [21.3]
20	3421	1.18 [30.0]	1.04 [26.4]
24	3626	1.38 [35.1]	1.24 [31.5]
26	3399	1.48 [37.6]	1.34 [34.0]
30	3419	1.68 [42.7]	1.54 [39.1]
34	3414	1.88 [47.8]	1.74 [44.2]
36	9436	1.98 [50.3]	1.84 [46.7]
40	3417	2.18 [55.4]	2.04 [51.8]
44	9444	2.38 [60.5]	2.24 [56.9]
50	3425	2.68 [68.1]	2.54 [64.5]
60	3334	3.18 [80.8]	3.04 [77.2]

G		97305		JUN 21, 2021		JNC		SKN	
REVISED AND REDRAWN									
REV		ECO		ISSUE DATE AND DESCRIPTION		DRFT		CHKD	
REV		ECO		DATE		MFG		DATE	
CHKD		CHKD		DATE		APPL		DATE	
				JUN 21, 2021		S. NEU		JUN 22, 2021	
DIVISION		DIVISION CODE							
		EMSD							
DO NOT SCALE DRAWING		SCALE		TOLERANCES EXCEPT AS NOTED					
		6 1							
THIRD ANGLE PROJECTION		INCHES		TITLE					
		.0000 ± .0002		WIRE MOUNT SOCKET, .100" X .100", .050" PITCH CABLE					
INTERPRET PER ASME Y14.5 2018		MILLIMETERS		CAGE NUMBER					
		.0000 ± .0002		SIZE					
MAX. SURFACE ROUGHNESS		.0000 ± .0002		DRAWING NO.					
		.0000 ± .0002		D					
ALL SURFACES		.0000 ± .0002		5100-0718-6					
MARKED ONLY		.0000 ± .0002		REV. C					
		.0000 ± .0002		MODEL					
		.0000 ± .0002		3000					
		.0000 ± .0002		DET. LISTS					
		.0000 ± .0002		YES ☒ NO					
		.0000 ± .0002		SHT 2 OF 4					


3M™ WIREMOUNT SOCKET, 3000 SERIES
.100" X .100" FOR .050" PITCH CABLE, (OPTIONAL PLASTIC OR METAL STRAIN RELIEF)




RECOMMENDED PIN PATTERN FOR STACKED CONFIGURATIONS



ASSEMBLED HEIGHT
WITH METAL PROFILE
STRAIN RELIEF



ASSEMBLED HEIGHT
WITHOUT STRAIN RELIEF



ASSEMBLED HEIGHT
WITH PLASTIC
STRAIN RELIEF

G		97305		JUN 21, 2021		JNC		SAN	
REVISED AND REDRAWN									
DESIGN REFERENCE		NEXT ASSEMBLY		ISSUE DATE AND DESCRIPTION		DRFT		CHKD	
MODIFY CODES				DATE JUN 21, 2021		MFG		DATE	
				CHKD		DATE		APPROV. S. NEW	
								DATE JUN 22, 2021	
DIVISION		DIVISION CODE EMSD		© 3M COPYRIGHT 2021					
DO NOT SCALE DRAWING		SCALE 6/1		TOLERANCES EXCEPT AS NOTED		 St. Paul, MN 55144 This document and the information it contains are 3M property and may not be reproduced or further distributed without 3M permission, or used or disclosed otherwise than for 3M authorized purposes. All rights reserved.			
 THIRD ANGLE PROJECTION		INCHES .0 ± .01 .00 ± .005 .0000 ± .0002		TITLE WIREMOUNT SOCKET, .100" X .100", .050" PITCH CABLE					
INTERPRET PER ASME Y14.5 - 2018 MAX. SURFACE ROUGHNESS ALL SURFACES ✓ MARKED ONLY		MILLIMETERS 0 ± .0 ± .00 ± .000 ±		CAGE NUMBER SIZE D		DRAWING NO. 578-5100-0718-6		REV. G	
		ANGLES ±		MODEL 3000		DET. Lists ☐ YES ☒ NO		SHT 3 OF 4	

3M™ WIREMOUNT SOCKET, 3000 SERIES

.100" X .100" FOR .050" PITCH CABLE, (OPTIONAL PLASTIC OR METAL STRAIN RELIEF)

Regulatory: For regulatory information about this product, visit 3M.com/regs or contact your 3M representative.

Technical Information: The technical information, recommendations and other statements contained in this document are based upon tests or experience that 3M believes are reliable, but the accuracy or completeness of such information is not guaranteed.

Product Use: Many factors beyond 3M's control and uniquely within user's control can affect the use and performance of a 3M product in a particular application. Given the variety of factors that can affect the use and performance of a 3M product, user is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application.

Warranty, Limited Remedy, and Disclaimer: Unless an additional warranty is specifically stated on the applicable 3M product packaging or product literature, 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OR TRADE. If the 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability: Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.

3M Company
Electronics Materials Solutions Division
13011 McCallen Pass, Bldg. C
Austin, TX 78753-5380
1-800-225-5373
www.3M.com/interconnect

G		97305		JUN 21, 2021		JNC		SKN	
REVISED AND REDRAWN									
ISSUE DATE AND DESCRIPTION		DRFT		CHKD					
CAST		TIG LONE		MFG		DATE		DATE	
JUN 21, 2021		JUN 21, 2021		S. NEU		JUN 22, 2021			
DIVISION		DIVISION CODE							
EWSO									
DO NOT SCALE DRAWING		SCALE B 1		TOLERANCES EXCEPT AS NOTED					
		INCHES .0 .00 ± .01 .000 ± .005 .0000 ± .0002		TITLE WIREMOUNT SOCKET 100" X 100" .050" PITCH CABLE					
THIRD ANGLE PROJECTION		MILLIMETERS 0 .00 ± .00 ± .000 ±		CASE NUMBER SIZE DRAWING NO.		REV. 6			
INTERPRET PER ASME Y14.5 - 2018		MAX SURFACE ROUGHNESS ALL SURFACES MARKED ONLY		MODEL 3000		DET. YES NO SHT 4 OF 6			
		ANGLES ±							