



# 319-001

## EMI/RFI Shield Sock Shrink Boot Adapter




### with Optional Shrink Boot

### Low Profile - Rotatable Coupling

## CONNECTOR DESIGNATORS A-F-H-L-S ROTATABLE COUPLING



**STYLE 2  
(STRAIGHT)**  
See Note 5)




**STYLE 2  
(45° & 90°)**  
See Note 5)

**-445**

Now Available  
with the "NESTOR"

Glenair's Non-Detent,  
Spring-Loaded, Self-  
Locking Coupling.

Add "-445" to Specify  
This AS85049 Style "N"  
Coupling Interface.



**319-001**  
**EMI/RFI Shield Sock Shrink Boot Adapter**  
 with Optional Shrink Boot  
 Low Profile - Rotatable Coupling



319

See inside back cover fold-out or pages 13 and 14 for unabridged Tables I and II.

**TABLE III: DIMENSIONS**

| Shell Size<br>Conn. Desig. |    | E     |        | F     |        | G     |        | H     |        |
|----------------------------|----|-------|--------|-------|--------|-------|--------|-------|--------|
| A-F-L-S                    | H  | Max   |        | Max   |        | Max   |        | Max   |        |
| 08                         | 09 | .457  | (11.6) | 1.710 | (43.4) | .500  | (12.7) | 1.730 | (43.9) |
| 10                         | 11 | .520  | (13.2) | 1.770 | (45.0) | .595  | (15.1) | 1.850 | (47.0) |
| 12                         | 13 | .582  | (14.8) | 1.830 | (46.5) | .610  | (15.5) | 1.870 | (47.5) |
| 14                         | 15 | .645  | (16.4) | 1.920 | (48.8) | .700  | (17.8) | 1.940 | (49.3) |
| 16                         | 17 | .738  | (18.7) | 2.030 | (51.6) | .885  | (22.5) | 2.030 | (51.6) |
| 18                         | 19 | .926  | (23.5) | 2.220 | (56.4) | .975  | (24.8) | 2.200 | (55.9) |
| 20                         | 21 | .926  | (23.5) | 2.220 | (56.4) | .975  | (24.8) | 2.200 | (55.9) |
| 22                         | 23 | 1.020 | (25.9) | 2.370 | (60.2) | 1.125 | (28.6) | 2.310 | (58.7) |
| 24                         | 25 | 1.020 | (25.9) | 2.370 | (60.2) | 1.125 | (28.6) | 2.310 | (58.7) |
| 28                         |    | 1.145 | (29.1) | 2.420 | (61.5) | 1.225 | (31.1) | 2.480 | (63.0) |
| 32                         |    | 1.207 | (30.7) | 2.520 | (64.0) | 1.575 | (40.0) | 2.730 | (69.3) |
| 36                         |    | 1.238 | (31.4) | 2.610 | (66.3) | 1.775 | (45.1) | 2.730 | (69.3) |

**TABLE IV: CABLE ENTRY/SHRINK BOOT**

| Dash No. | Cable Entry  | Shrink Boot * |
|----------|--------------|---------------|
| 01       | .188 (4.8)   | n/a           |
| 02       | .250 (6.4)   | n/a           |
| 03       | .312 (7.9)   | 770-001S103   |
| 04       | .375 (9.5)   | 770-001S103   |
| 05       | .438 (11.1)  | 770-001S103   |
| 06       | .500 (12.7)  | 770-001S104   |
| 07       | .562 (14.3)  | 770-001S104   |
| 08       | .625 (15.9)  | 770-001S104   |
| 09       | .688 (17.5)  | 770-001S105   |
| 10       | .750 (19.1)  | 770-001S105   |
| 11       | .812 (20.6)  | 770-001S105   |
| 12       | .875 (22.2)  | 770-001S106   |
| 13       | .938 (23.8)  | 770-001S106   |
| 14       | 1.000 (25.4) | 770-001S106   |
| 15       | 1.250 (31.8) | 770-001S107   |
| 16       | 1.500 (38.1) | 770-001S108   |
| 17       | 1.750 (44.5) | n/a           |
| 18       | 2.000 (50.8) | n/a           |
| 19       | 1.125 (28.6) | n/a           |
| 20       | 1.375 (34.9) | n/a           |
| 21       | 1.625 (41.3) | n/a           |
| 22       | 1.062 (27.0) | n/a           |
| 23       | 1.188 (30.2) | n/a           |
| 24       | 1.875 (47.6) | n/a           |

1. Cable Entry or range is defined as the accommodation range for the wire bundle or cable. Dimensions shown are not intended for inspection criteria.
2. See Shrink Boot Reference Information (page 40).
3. Metric dimensions (mm) are indicated in parentheses.
4. O-Ring not supplied with Connector Designator A.
5. When maximum entry (page 21) is exceeded, Style 2 will be supplied. Dimensions E, F, G, & H will not apply. Please consult factory.

**TABLE II - STANDARD FINISHES**

| GLENAIR                                                                      |                                                   |
|------------------------------------------------------------------------------|---------------------------------------------------|
| SYMBOL                                                                       | FINISH                                            |
| B                                                                            | Cadmium Plate, Olive Drab                         |
| M                                                                            | Electroless Nickel                                |
| NF                                                                           | Cadmium Plate, Olive Drab Over Electroless Nickel |
| See Back Cover for Complete Finish Information and Additional Finish Options |                                                   |