




Suitable for use in high temperature applications up to 600°C (1112°F). Applications include hot melt glue guns, furnaces, heaters, process equipment and machinery. Terminal blocks are offered with mounting holes for panel mounting or free floating applications.


CB4


Available in 1-3 poles.

CB6


Available in 1-3 poles.

CB16














Available in 2-3 poles.

- Compact, space saving
- Tubular screw clamp
- Free float or panel mount
- Temperature range:
-40°C (-40°F) to
600°C (1112°F)
- Standard color: white
- Material
Housing: Steatite
Clamp: Brass
Screws: Zinc plated steel

New CB6/4H



Insulation Material	Ceramic			Ceramic			Ceramic		
Approvals	  			  			  		
Wire Range	24-12 AWG	.5-2.5mm ²	24-12 AWG	24-12 AWG	.5-2.5mm ²	24-12 AWG	24-12 AWG	.5-2.5mm ²	24-12 AWG
Voltage Rating	600V	800 V	300V	600V	800 V	300V	600V	800 V	300V
Current Rating	30 A	24 A	20 A	40 A	32 A	30 A	76 A	57 A	65 A
Torque	7 lb-in.	.4 Nm	6 lb-in.	7 lb-in.	.5 Nm	6 lb-in.	14 lb-in.	1.2 Nm	12 lb-in.
No. of Poles	Cat. No.	Std. Pk.		Cat. No.	Std. Pk.		Cat. No.	Std. Pk.	
1 (free floating)	CB4/1	50		CB6/1	50				
2 (free floating)	CB4/2	50							
2 (with mounting holes)	CB4/2H	50		CB6/2H	50		CB16/2H	50	
3 (free floating)	CB4/3	50							
3 (with mounting holes)	CB4/3H	50		CB6/3H	50		CB16/3H	50	
4 (with mounting hole)	—	—		CB6/4H	50		—	—	

Design A

Design B

Design C

Design D

Design E

Design F


Type Cat. No.	Design Type	No. of Poles	Stripping Length	P	a	b	w	h	d1	d2	Fixing Screw
CB4/1	A	1	6	11	-	-	23	18.5	-	-	-
CB4/2	B	2	6	18	7.3	-	23	18.5	-	-	-
CB4/2H	C	2	6	24	13	14.6	23	18.5	6	3.5	M3 x 16
CB4/3	D	3	6	25	7.3	-	23	18.5	-	-	-
CB4/3H	E	3	6	36	13	13	23	18.5	6	3.5	M3 x 16
CB6/1	A	1	6	12	-	-	25.5	19.5	-	-	-
CB6/2H	C	2	6	26	15	12.6	25.5	19.5	6	3.5	M3 x 16
CB6/3H	E	3	6	41	15	15	25.5	19.5	6	3.5	M3 x 16
CB16/2H	C	2	8.5	31	17	16.5	28	23.2	6	3.5	M3 x 20
CB16/3H	E	3	8.5	48	17	17	28	23.2	6	3.5	M3 x 20
CB6/4H	F	4	6	39	8	-	20	16	6	3.5	M3 x 16

Note: All dimensions are shown in mm, to convert to inches please divide by 25.4.