






DRAWING MADE IN THIRD ANGLE PROJECTION

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION, 19
© COPYRIGHT 19 BY AMP INCORPORATED, HARRISBURG, PA. ALL INTERNATIONAL RIGHTS
RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENTS AND/OR PATENTS PENDING.



- 1 GOLD PLATING IS NOT REQUIRED IN THIS AREA.
- 2 CUT-OUTS ON THE BOX ARE AT MANUFACTURERS OPTION.
- 3 THIS TERMINAL IS REELED FOR THE STANDARD APPLICATOR.
- 4 THIS TERMINAL IS REELED FOR THE MINI APPLICATOR.
- 5 .000015 GOLD ON THE CONTACT AREA, GOLD FLASH ON THE REMAINDER ALL OVER .000050 NICKEL.
- 6 .000030 GOLD OVER .000050 NICKEL.
- 7 .000030 GOLD ON THE CONTACT AREA, GOLD FLASH ON THE REMAINDER ALL OVER .000050 NICKEL.
- 8 .000100-.000200 BRIGHT TIN-LEAD OVER .000050 NICKEL.
- 9 POINT OF MEASUREMENT FOR PLATING THICKNESS (INSIDE BEAMS).
- 10 OBSOLETE PART NUMBER.



REVISIONS									
REV	LOC	DIST	P	F	ZONE	LTR	DESCRIPTION	DATE	APPROVED
E							REVISED AND REDRAWN ECN 893	-	
F							REVISED ECN 950	LM 2-7-86	JLG
F1							REVISED ECN 1041	5-1-86	
F2							OBSOLETE ECN 1821	LDR 2-22-88	JLG
G							REV ECN AR2029 AR2120	OK 9-27-88	JLG
H							REV PER ECN AR2491	JPG 6-8-89	
J							REV LOC & DIST AD-4171	3-90	BF

3	4	8	10	-4	1	10	-1
3	4	8	10	-4	1	10	-0
4	4	7	87045-3		86491-6		
4	6	7	87045-2		86491-4		
4	3	6	87045-2		10	-3	
4	5	6	87045-1		86491-2		
4	5	5	87045-1		10	-1	
REMARKS	FINISH	LOOSE PIECE PART NUMBER	PART NUMBER				

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ON: 2 PL DEC $\pm$ - 3 PL DEC $\pm$.005 ANGLES $\pm$ - MATERIAL: BERYLLIUM COPPER, .008 THICK FINISH: SEE TABLE		DR 12-10-85 L.D. RINGLEY	AMP AMP INCORPORATED Harrisburg, Pa. 17105 NAME CONTACT, MOD IV 1/2, RECEPTACLE, CRIMP SNAP-IN			
		CHK 12-16-85 J.L. GESFORD				
		APPD 12-16-85 J.L. GESFORD				
		APPD 12-16-85 CLIFFORD LINDGREN				
		PRODUCT SPEC 108-25,021	SIZE C	FSCM NO 00779	DRAWING NO 86491	
		APPLICATION SPEC 114-25,003	SCALE NTS			SHEET 1 - 1
		WEIGHT -				