

10

9

8

7

6



5

4





3

2

1



RECOMMENDED P.C.B HOLE LAYOUT



REVISION OF DRAWING MAY BE
CHANGED DURING FINAL RELEASED
FOR PRODUCTION.

ib_frame_A3_P_AM_T
Rev. G 2012/01/11

9

8

7

6

5

4

3

2

1

NOTES:

1. MATERIAL:

HSG: LCP, GLASS-FILLED, UL94V-0,

COLOR: BLACK

PIN: 0.64MM SQ PIN, COPPER ALLOY

2. PLATING TYPE:

(1) : 0.0254 μ m GOLD FLASH OVER1.25 μ m MIN. NICKEL OVERALL.(2) : 0.025 μ m MIN. GOLD PLATE ON CONTACT AND1.88 μ m MIN. TIN ON SOLDER TAIL OVER1.25 μ m MIN. NICKEL OVERALL.(3) : 0.25 μ m MIN. GOLD PLATE ON CONTACT AND1.88 μ m MIN. TIN ON SOLDER TAIL OVER1.25 μ m MIN. NICKEL OVERALL.(4) : 0.38 μ m MIN. GOLD PLATE ON CONTACT AND1.88 μ m MIN. TIN ON SOLDER TAIL OVER1.25 μ m MIN. NICKEL OVERALL.(5) : 0.75 μ m MIN. GOLD PLATE ON CONTACT AND1.88 μ m MIN. TIN ON SOLDER TAIL OVER1.25 μ m MIN. NICKEL OVERALL(6) : 2.50 μ m MIN. TIN OVER 1.25 μ m MIN. NICKEL OVERALL.(7) : 0.38 μ m MIN. GOLD PLATE ON CONTACT AND2.50 μ m MIN. TIN ON SOLDER TAIL OVER1.25 μ m MIN. NICKEL OVERALL.(8) : 0.38 μ m MIN. GOLD PLATE ON CONTACT AND0.05 μ m MIN. GOLD FLASH ON SOLDER TAIL OVER1.25 μ m MIN. NICKEL OVERALL.(9) : 0.05 - 0.25 μ m MIN. GOLD FLASH OVER1.25 μ m MIN. NICKEL OVERALL.

3. PIN PUSHOUT FORCE: 1KG MIN IN EITHER DIRECTION

4. THE ABOVE 14 CKT IS FOR ILLUSTRATION PURPOSE ONLY.

5. FOR PACKAGING OPTION PLEASE REFER TO THE TABLE.

6. RECOMMENDED PCB THICKNESS 1.60MM.

7. PRODUCT SPECIFICATION: PS-87920-019

8. WAFER TO BE FLAT WITHIN 0.003mm/mm

9. IRREGULAR CIRCUIT CUTOFF WITHIN BREAKAWAY SECTION

IS PERMISSIBLE. CUTTING OR CHIPPING OF THE MAIN

BODY IS NOT ACCEPTABLE.

10. PARTS ARE NOT STACKABLE ON 2.54 CENTER

11. CAP TO BE PLACED AS CENTRAL OF PART AS POSSIBLE

WITH THE TOP SURFACE FLAT FOR PICK AND PLACE.

12. PACKAGING SPECIFICATION:

TRAY: PK-89990-489

BULK: PK-89990-491

SHT 7, +879140847
EC NO: S2014-0048
2013/07/11
DRWNATSEE
CHKD:SKANG
2013/07/11
APPR:MLONG
2013/10/09

QUALITY
SYMBOLS
 $\nabla_A=0$
 $\nabla_C=0$
 $\nabla_P=0$

GENERAL TOLERANCES
(UNLESS SPECIFIED)

	mm	INCH
4 PLACES	± ---	± ---
3 PLACES	± ---	± ---
2 PLACES	± 0.20	± ---
1 PLACE	± ---	± ---
0 PLACE	±	±

ANGULAR ± 3 °
DRAFT WHERE APPLICABLE
MUST REMAIN
WITHIN DIMENSIONS

DIMENSION STYLE
MM ONLY

DRAWN BY	DATE
KCHO	2004/11/05
CHECKED BY	DATE
PTLIM	2004/12/08
APPROVED BY	DATE
MLONG	2010/09/06

MATERIAL NO.
SEE TABLE

SCALE
NTS

THIRD ANGLE
PROJECTION

DESIGN UNITS
METRIC

2.54MM PITCH
DUAL ROW HEADER
SINGLE WAFER, T/H

molex

DOCUMENT NO.
SD-87914-013

SHEET NO.
1 OF 45

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX
INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

	10		9		8		7		6		5		4		3		2		1																																																																												
	PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION																																																																																						
									A	B	F	M	P																																																																																		
F	87914-0211	-----	-----	-----	-----	2	----	1	2.54	----	10.92	5.84	2.79	F																																																																																	
	87914-0221	-----	-----	-----	-----	2	----	1	2.54	----	12.25	7.00	2.96																																																																																		
	87914-0231	-----	-----	-----	-----	2	----	1	2.54	----	13.38	6.09	5.00																																																																																		
	87914-0212	-----	-----	-----	-----	2	----	2	2.54	----	10.92	5.84	2.79	E																																																																																	
	87914-0222	-----	-----	-----	-----	2	----	2	2.54	----	12.25	7.00	2.96																																																																																		
	87914-0232	-----	-----	-----	-----	2	----	2	2.54	----	13.38	6.09	5.00																																																																																		
E	87914-0213	-----	-----	-----	-----	2	----	3	2.54	----	10.92	5.84	2.79	E																																																																																	
	87914-0223	-----	-----	-----	-----	2	----	3	2.54	----	12.25	7.00	2.96																																																																																		
	87914-0233	-----	-----	-----	-----	2	----	3	2.54	----	13.38	6.09	5.00																																																																																		
	87914-0214	-----	-----	-----	-----	2	----	4	2.54	----	10.92	5.84	2.79	D																																																																																	
	87914-0224	-----	-----	-----	-----	2	----	4	2.54	----	12.25	7.00	2.96																																																																																		
	87914-0234	-----	-----	-----	-----	2	----	4	2.54	----	13.38	6.09	5.00																																																																																		
D	87914-0215	-----	-----	-----	-----	2	----	5	2.54	----	10.92	5.84	2.79	D																																																																																	
	87914-0225	-----	-----	-----	-----	2	----	5	2.54	----	12.25	7.00	2.96																																																																																		
	87914-0235	-----	-----	-----	-----	2	----	5	2.54	----	13.38	6.09	5.00																																																																																		
	87914-0216	-----	-----	-----	-----	2	----	6	2.54	----	10.92	5.84	2.79	C																																																																																	
	87914-0226	-----	-----	-----	-----	2	----	6	2.54	----	12.25	7.00	2.96																																																																																		
	87914-0236	-----	-----	-----	-----	2	----	6	2.54	----	13.38	6.09	5.00																																																																																		
C														C																																																																																	
														B																																																																																	
B														B																																																																																	
A														A																																																																																	
<table><tr><td rowspan="4">SHT 7. +879140847 EC NO: S2014-0048 2013/07/11 DRW:NATSEE CHKD:SKANG 2013/07/11 APPR:MLONG 2013/10/09</td><td rowspan="4">DESCRIPTION</td><td rowspan="4">REV</td><td rowspan="4">QUALITY SYMBOLS </td><td colspan="3">GENERAL TOLERANCES (UNLESS SPECIFIED)</td><td colspan="2">DIMENSION STYLE MM ONLY</td><td>SCALE NTS</td><td>DESIGN UNITS METRIC</td><td colspan="2">THIRD ANGLE PROJECTION</td></tr><tr><td></td><td>mm</td><td>INCH</td><td>DRAWN BY KCHO</td><td>DATE 2004/11/05</td><td colspan="4" rowspan="2">2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H</td></tr><tr><td></td><td></td><td></td><td>CHECKED BY PTLIM</td><td>DATE 2004/12/08</td></tr><tr><td></td><td></td><td></td><td></td><td></td><td>APPROVED BY MLONG</td><td>DATE 2010/09/06</td><td colspan="4" rowspan="2">molex</td></tr><tr><td></td><td></td><td></td><td></td><td></td><td>MATERIAL NO.</td><td></td></tr><tr><td></td><td></td><td></td><td></td><td></td><td colspan="2">SEE TABLE</td><td colspan="2">DOCUMENT NO. SD-87914-013</td><td colspan="2">SHEET NO. 2 OF 45</td></tr><tr><td colspan="3">D14</td><td></td><td colspan="3">DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS</td><td>SIZE A3</td><td colspan="12">THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION</td></tr></table>																				SHT 7. +879140847 EC NO: S2014-0048 2013/07/11 DRW:NATSEE CHKD:SKANG 2013/07/11 APPR:MLONG 2013/10/09	DESCRIPTION	REV	QUALITY SYMBOLS 	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION			mm	INCH	DRAWN BY KCHO	DATE 2004/11/05	2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H							CHECKED BY PTLIM	DATE 2004/12/08						APPROVED BY MLONG	DATE 2010/09/06	molex									MATERIAL NO.							SEE TABLE		DOCUMENT NO. SD-87914-013		SHEET NO. 2 OF 45		D14				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION											
SHT 7. +879140847 EC NO: S2014-0048 2013/07/11 DRW:NATSEE CHKD:SKANG 2013/07/11 APPR:MLONG 2013/10/09	DESCRIPTION	REV	QUALITY SYMBOLS 	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION																																																																																				
					mm	INCH	DRAWN BY KCHO	DATE 2004/11/05	2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H																																																																																						
							CHECKED BY PTLIM	DATE 2004/12/08																																																																																							
									APPROVED BY MLONG	DATE 2010/09/06	molex																																																																																				
					MATERIAL NO.																																																																																										
					SEE TABLE		DOCUMENT NO. SD-87914-013		SHEET NO. 2 OF 45																																																																																						
D14				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																																																																																							
fb_frame_A3_P_AM_T Rev. G 2012/01/11	9		8		7		6		5		4		3		2		1																																																																														

[illegible]

[illegible]

[illegible]

[illegible]

	10		9		8		7		6		5		4		3		2		1		
	PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	PART NO. FOR BULK PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION											
										A	B	F	M	P	G						
F	87914-1011	-----	-----	-----	-----	-----	10	-----	1	12.70	10.16	10.92	5.84	2.79	----					F	
	87914-1021	-----	-----	-----	-----	-----	10	-----	1	12.70	10.16	12.25	7.00	2.96	----						
	87914-1031	-----	-----	-----	-----	-----	10	-----	1	12.70	10.16	13.38	6.09	5.00	----						
	87914-1012	-----	-----	-----	-----	-----	10	-----	2	12.70	10.16	10.92	5.84	2.79	----					E	
	87914-1022	-----	-----	-----	-----	-----	10	-----	2	12.70	10.16	12.25	7.00	2.96	----						
	87914-1032	-----	-----	-----	-----	-----	10	-----	2	12.70	10.16	13.38	6.09	5.00	----						
E	87914-1013	-----	-----	-----	-----	-----	10	-----	3	12.70	10.16	10.92	5.84	2.79	----					E	
	87914-1023	-----	-----	-----	-----	-----	10	-----	3	12.70	10.16	12.25	7.00	2.96	----						
	87914-1033	-----	-----	-----	-----	-----	10	-----	3	12.70	10.16	13.38	6.09	5.00	----						
	87914-1014	-----	-----	-----	-----	-----	10	-----	4	12.70	10.16	10.92	5.84	2.79	----					D	
	87914-1024	-----	-----	-----	-----	-----	10	-----	4	12.70	10.16	12.25	7.00	2.96	----						
	87914-1034	-----	-----	-----	-----	-----	10	-----	4	12.70	10.16	13.38	6.09	5.00	----						
D	87914-1015	-----	-----	-----	-----	-----	10	-----	5	12.70	10.16	10.92	5.84	2.79	----					D	
	87914-1025	-----	-----	-----	-----	-----	10	-----	5	12.70	10.16	12.25	7.00	2.96	----						
	87914-1035	-----	-----	-----	-----	-----	10	-----	5	12.70	10.16	13.38	6.09	5.00	----						
	87914-1016	-----	-----	-----	-----	-----	10	-----	6	12.70	10.16	10.92	5.84	2.79	----					C	
	87914-1026	-----	-----	-----	-----	-----	10	-----	6	12.70	10.16	12.25	7.00	2.96	----						
	87914-1036	-----	-----	-----	-----	-----	10	-----	6	12.70	10.16	13.38	6.09	5.00	----						
C	87914-0001	-----	-----	-----	-----	-----	10	-----	7	12.70	10.16	12.07	5.97	3.81	----					C	
	-----	-----	-----	-----	-----	87914-1037	10	9	4	12.70	10.16	10.92	5.84	2.79	----						
																				B	
B																				B	

A	SHT 7. +879140847 EC NO: S2014-0048 DRW:ATSEE 2013/07/11 CHKD:SKANG 2013/07/11 APPR:MLONG 2013/10/09	REV	DESCRIPTION	QUALITY SYMBOLS F_A=0 F_G=0 F_P=0	GENERAL TOLERANCES (UNLESS SPECIFIED) <table><tr><th></th><th>mm</th><th>INCH</th></tr><tr><td>4 PLACES</td><td>± ---</td><td>± ---</td></tr><tr><td>3 PLACES</td><td>± ---</td><td>± ---</td></tr><tr><td>2 PLACES</td><td>± 0.20</td><td>± ---</td></tr><tr><td>1 PLACE</td><td>± ---</td><td>± ---</td></tr><tr><td>0 PLACE</td><td>±</td><td>±</td></tr></table>			mm	INCH	4 PLACES	± ---	± ---	3 PLACES	± ---	± ---	2 PLACES	± 0.20	± ---	1 PLACE	± ---	± ---	0 PLACE	±	±	DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION	
								mm	INCH																					
							4 PLACES	± ---	± ---																					
							3 PLACES	± ---	± ---																					
							2 PLACES	± 0.20	± ---																					
							1 PLACE	± ---	± ---																					
							0 PLACE	±	±																					
							DRAWN BY KCHO		DATE 2004/11/05		2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H																			
							CHECKED BY PTLIM		DATE 2004/12/08																					
							APPROVED BY MLONG		DATE 2010/09/06		molex																			
MATERIAL NO.		DOCUMENT NO.		SHEET NO.																										
SEE TABLE		SD-87914-013		8 OF 45																										
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																												

10		9		8		7		6		5		4		3		2		1	
F	PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION					F					
	A	B	F	M	P														
E	87914-1211	-----	-----	-----	-----	12	-----	1	15.24	12.70	10.92	5.84	2.79	E					
	-----	87914-1291	-----	-----	-----	12	-----	9	15.24	12.70	10.92	5.84	2.79						
	87914-1221	-----	-----	-----	-----	12	-----	1	15.24	12.70	12.25	7.00	2.96						
	87914-1231	-----	-----	-----	-----	12	-----	1	15.24	12.70	13.38	6.09	5.00						
	87914-1212	-----	-----	-----	-----	12	-----	2	15.24	12.70	10.92	5.84	2.79						
	87914-1222	-----	-----	-----	-----	12	-----	2	15.24	12.70	12.25	7.00	2.96						
D	87914-1232	-----	-----	-----	-----	12	-----	2	15.24	12.70	13.38	6.09	5.00	D					
	87914-1213	-----	-----	-----	-----	12	-----	3	15.24	12.70	10.92	5.84	2.79						
	87914-1223	-----	-----	-----	-----	12	-----	3	15.24	12.70	12.25	7.00	2.96						
	87914-1233	-----	-----	-----	-----	12	-----	3	15.24	12.70	13.38	6.09	5.00						
	87914-1214	-----	-----	-----	-----	12	-----	4	15.24	12.70	10.92	5.84	2.79						
	87914-1224	-----	-----	-----	-----	12	-----	4	15.24	12.70	12.25	7.00	2.96						
C	87914-1234	-----	-----	-----	-----	12	-----	4	15.24	12.70	13.38	6.09	5.00	C					
	87914-1215	-----	-----	-----	-----	12	-----	5	15.24	12.70	10.92	5.84	2.79						
	87914-1225	-----	-----	-----	-----	12	-----	5	15.24	12.70	12.25	7.00	2.96						
	87914-1235	-----	-----	-----	-----	12	-----	5	15.24	12.70	13.38	6.09	5.00						
	87914-1216	-----	-----	-----	-----	12	-----	6	15.24	12.70	10.92	5.84	2.79						
	87914-1226	-----	-----	-----	-----	12	-----	6	15.24	12.70	12.25	7.00	2.96						
B	87914-1236	-----	-----	-----	-----	12	-----	6	15.24	12.70	13.38	6.09	5.00	B					
A															A				

10		9		8		7		6		5		4		3		2		1	
PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION											
								A	B	F	M	P							
F	87914-1251	-----	-----	-----	-----	12	-----	1	15.24	12.70	18.40	13.08	3.03						
	87914-1252	-----	-----	-----	-----	12	-----	2	15.24	12.70	18.40	13.08	3.03						
	87914-1253	-----	-----	-----	-----	12	-----	3	15.24	12.70	18.40	13.08	3.03						
	87914-1254	-----	-----	-----	-----	12	-----	4	15.24	12.70	18.40	13.08	3.03						
	87914-1255	-----	-----	-----	-----	12	-----	5	15.24	12.70	18.40	13.08	3.03						
	87914-1256	-----	-----	-----	-----	12	-----	6	15.24	12.70	18.40	13.08	3.03						
E	87914-1241	-----	-----	-----	-----	12	-----	1	15.24	12.70	12.50	6.95	3.26						
	87914-1242	-----	-----	-----	-----	12	-----	2	15.24	12.70	12.50	6.95	3.26						
	87914-1243	-----	-----	-----	-----	12	-----	3	15.24	12.70	12.50	6.95	3.26						
	87914-1244	-----	-----	-----	-----	12	-----	4	15.24	12.70	12.50	6.95	3.26						
	87914-1245	-----	-----	-----	-----	12	-----	5	15.24	12.70	12.50	6.95	3.26						
	87914-1246	-----	-----	-----	-----	12	-----	6	15.24	12.70	29.26	23.32	3.65						
D																			
C																			
B																			
A																			
fb_frame_A3_P_AM_T Rev. G 2012/01/11		9	8	7	6	5	4	3	2	1									

SHT 7, +879140847 EC NO: S2014-0048 DRWN:ATSEE 2013/07/11 CHKD:SKANG 2013/07/11 APPR:MLONG 2013/10/09	DESCRIPTION REV	QUALITY SYMBOLS F=0 F=0 F=0	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION			
			4 PLACES 3 PLACES 2 PLACES 1 PLACE 0 PLACE	mm	INCH	DRAWN BY KCHO	DATE 2004/11/05	TITLE 2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H					
				± ---	± ---	CHECKED BY PTL IM	DATE 2004/12/08						
				± 0.20	± ---	APPROVED BY MLONG	DATE 2010/09/06						
				± ---	± ---	MATERIAL NO.	DOCUMENT NO.						
				±	±	SEE TABLE			SD-87914-013				
			ANGULAR ± 3 °			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION			SHEET NO. 10 OF 45	

tb_frame_A3_P_AM_T
Rev. G 2012/01/11

	10		9		8		7		6		5		4		3		2		1																																												
	PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION																																																						
									A	B	F	M	P																																																		
F	87914-1441	-----	-----	-----	-----	14	-----	1	17.78	15.24	13.42	8.08	3.05																																																		
	87914-1442	-----	-----	-----	-----	14	-----	2	17.78	15.24	13.42	8.08	3.05																																																		
	87914-1443	-----	-----	-----	-----	14	-----	3	17.78	15.24	13.42	8.08	3.05																																																		
	87914-1444	-----	-----	-----	-----	14	-----	4	17.78	15.24	13.42	8.08	3.05																																																		
	87914-1445	-----	-----	-----	-----	14	-----	5	17.78	15.24	13.42	8.08	3.05																																																		
E																																																															
D																																																															
C																																																															
B																																																															
A																																																															
<table><tr><td rowspan="10">SHT 7, +879140847 EC NO: S2014-0048 DRWN:ATSEE 2013/07/11 CHKD:SKANG 2013/07/11 APPR:MLONG 2013/10/09 D14</td><td rowspan="10">QUALITY SYMBOLS =0 =0 =0</td><td colspan="3">GENERAL TOLERANCES (UNLESS SPECIFIED)</td><td colspan="2">DIMENSION STYLE MM ONLY</td><td>SCALE NTS</td><td>DESIGN UNITS METRIC</td><td colspan="2">THIRD ANGLE PROJECTION</td></tr><tr><td rowspan="5">4 PLACES 3 PLACES 2 PLACES 1 PLACE 0 PLACE</td><td>mm</td><td>INCH</td><td>DRAWN BY KCHO</td><td>DATE 2004/11/05</td><td colspan="2" rowspan="5">TITLE 2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H molex</td></tr><tr><td>± ---</td><td>± ---</td><td>CHECKED BY PTLIM</td><td>DATE 2004/12/08</td></tr><tr><td>± 0.20</td><td>± ---</td><td>APPROVED BY MLONG</td><td>DATE 2010/09/06</td></tr><tr><td>± ---</td><td>± ---</td><td>MATERIAL NO.</td><td>DOCUMENT NO. SD-87914-013</td></tr><tr><td>±</td><td>±</td><td colspan="2">SHEET NO. 12 OF 45</td></tr><tr><td colspan="3">DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS</td><td>SIZE A3</td><td colspan="5">THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION</td></tr></table>																					SHT 7, +879140847 EC NO: S2014-0048 DRWN:ATSEE 2013/07/11 CHKD:SKANG 2013/07/11 APPR:MLONG 2013/10/09 D14	QUALITY SYMBOLS =0 =0 =0	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		4 PLACES 3 PLACES 2 PLACES 1 PLACE 0 PLACE	mm	INCH	DRAWN BY KCHO	DATE 2004/11/05	TITLE 2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H molex		± ---	± ---	CHECKED BY PTLIM	DATE 2004/12/08	± 0.20	± ---	APPROVED BY MLONG	DATE 2010/09/06	± ---	± ---	MATERIAL NO.	DOCUMENT NO. SD-87914-013	±	±	SHEET NO. 12 OF 45		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				
SHT 7, +879140847 EC NO: S2014-0048 DRWN:ATSEE 2013/07/11 CHKD:SKANG 2013/07/11 APPR:MLONG 2013/10/09 D14	QUALITY SYMBOLS =0 =0 =0	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION																																																						
		4 PLACES 3 PLACES 2 PLACES 1 PLACE 0 PLACE	mm	INCH	DRAWN BY KCHO	DATE 2004/11/05	TITLE 2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H molex																																																								
			± ---	± ---	CHECKED BY PTLIM	DATE 2004/12/08																																																									
			± 0.20	± ---	APPROVED BY MLONG	DATE 2010/09/06																																																									
			± ---	± ---	MATERIAL NO.	DOCUMENT NO. SD-87914-013																																																									
			±	±	SHEET NO. 12 OF 45																																																										
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																																																									

fb_frame_A3_P_AM_T
Rev. G 2012/01/11

9

8

7

6

5

4

3

2

1

10		9		8		7		6		5		4		3		2		1																																																																									
PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION																																																																																			
								A	B	F	M	P																																																																															
F	87914-1811	-----	-----	-----	-----	18	-----	1	22.86	20.32	10.92	5.84	2.79																																																																														
	87914-1821	-----	-----	-----	-----	18	-----	1	22.86	20.32	12.25	7.00	2.96																																																																														
	87914-1831	-----	-----	-----	-----	18	-----	1	22.86	20.32	13.38	6.09	5.00																																																																														
	87914-1812	-----	-----	-----	-----	18	-----	2	22.86	20.32	10.92	5.84	2.79																																																																														
	87914-1822	-----	-----	-----	-----	18	-----	2	22.86	20.32	12.25	7.00	2.96																																																																														
	87914-1832	-----	-----	-----	-----	18	-----	2	22.86	20.32	13.38	6.09	5.00																																																																														
E	87914-1813	-----	-----	-----	-----	18	-----	3	22.86	20.32	10.92	5.84	2.79																																																																														
	87914-1823	-----	-----	-----	-----	18	-----	3	22.86	20.32	12.25	7.00	2.96																																																																														
	87914-1833	-----	-----	-----	-----	18	-----	3	22.86	20.32	13.38	6.09	5.00																																																																														
	87914-1814	-----	-----	-----	-----	18	-----	4	22.86	20.32	10.92	5.84	2.79																																																																														
	87914-1824	-----	-----	-----	-----	18	-----	4	22.86	20.32	12.25	7.00	2.96																																																																														
	87914-1834	-----	-----	-----	-----	18	-----	4	22.86	20.32	13.38	6.09	5.00																																																																														
D	87914-1815	-----	-----	-----	-----	18	-----	5	22.86	20.32	10.92	5.84	2.79																																																																														
	87914-1825	-----	-----	-----	-----	18	-----	5	22.86	20.32	12.25	7.00	2.96																																																																														
	87914-1835	-----	-----	-----	-----	18	-----	5	22.86	20.32	13.38	6.09	5.00																																																																														
	87914-1816	-----	-----	-----	-----	18	-----	6	22.86	20.32	10.92	5.84	2.79																																																																														
	87914-1826	-----	-----	-----	-----	18	-----	6	22.86	20.32	12.25	7.00	2.96																																																																														
	87914-1836	-----	-----	-----	-----	18	-----	6	22.86	20.32	13.38	6.09	5.00																																																																														
C																																																																																											
B																																																																																											
A																																																																																											
<table><tr><td rowspan="4">SHT 7, +879140847 EC NO: SZ014-0048 DRWN:ATSE 2013/07/11 CHKD:SKANG 2013/07/11 APPR:MLONG 2013/10/09</td><td rowspan="4">QUALITY SYMBOLS </td><td rowspan="4">GENERAL TOLERANCES (UNLESS SPECIFIED) <table><tr><td></td><td>mm</td><td>INCH</td></tr><tr><td>4 PLACES</td><td>± ---</td><td>± ---</td></tr><tr><td>3 PLACES</td><td>± ---</td><td>± ---</td></tr><tr><td>2 PLACES</td><td>± 0.20</td><td>± ---</td></tr><tr><td>1 PLACE</td><td>± ---</td><td>± ---</td></tr><tr><td>0 PLACE</td><td>±</td><td>±</td></tr></table></td><td colspan="2">DIMENSION STYLE MM ONLY</td><td>SCALE NTS</td><td>DESIGN UNITS METRIC</td><td rowspan="4"> THIRD ANGLE PROJECTION</td></tr><tr><td colspan="2">DRAWN BY KCHO</td><td>DATE 2004/11/05</td><td colspan="3" rowspan="2">2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H</td></tr><tr><td colspan="2">CHECKED BY PTL IM</td><td>DATE 2004/12/08</td></tr><tr><td colspan="2">APPROVED BY MLONG</td><td>DATE 2010/09/06</td><td colspan="3">molex</td></tr><tr><td colspan="2">MATERIAL NO.</td><td colspan="3">DOCUMENT NO.</td><td colspan="2">SHEET NO.</td></tr><tr><td colspan="2">SEE TABLE</td><td colspan="3">SD-87914-013</td><td colspan="2">14 OF 45</td></tr><tr><td colspan="2">DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS</td><td colspan="16">THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION</td></tr></table>																			SHT 7, +879140847 EC NO: SZ014-0048 DRWN:ATSE 2013/07/11 CHKD:SKANG 2013/07/11 APPR:MLONG 2013/10/09	QUALITY SYMBOLS 	GENERAL TOLERANCES (UNLESS SPECIFIED) <table><tr><td></td><td>mm</td><td>INCH</td></tr><tr><td>4 PLACES</td><td>± ---</td><td>± ---</td></tr><tr><td>3 PLACES</td><td>± ---</td><td>± ---</td></tr><tr><td>2 PLACES</td><td>± 0.20</td><td>± ---</td></tr><tr><td>1 PLACE</td><td>± ---</td><td>± ---</td></tr><tr><td>0 PLACE</td><td>±</td><td>±</td></tr></table>		mm	INCH	4 PLACES	± ---	± ---	3 PLACES	± ---	± ---	2 PLACES	± 0.20	± ---	1 PLACE	± ---	± ---	0 PLACE	±	±	DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION	DRAWN BY KCHO		DATE 2004/11/05	2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H			CHECKED BY PTL IM		DATE 2004/12/08	APPROVED BY MLONG		DATE 2010/09/06	molex			MATERIAL NO.		DOCUMENT NO.			SHEET NO.		SEE TABLE		SD-87914-013			14 OF 45		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION															
SHT 7, +879140847 EC NO: SZ014-0048 DRWN:ATSE 2013/07/11 CHKD:SKANG 2013/07/11 APPR:MLONG 2013/10/09	QUALITY SYMBOLS 	GENERAL TOLERANCES (UNLESS SPECIFIED) <table><tr><td></td><td>mm</td><td>INCH</td></tr><tr><td>4 PLACES</td><td>± ---</td><td>± ---</td></tr><tr><td>3 PLACES</td><td>± ---</td><td>± ---</td></tr><tr><td>2 PLACES</td><td>± 0.20</td><td>± ---</td></tr><tr><td>1 PLACE</td><td>± ---</td><td>± ---</td></tr><tr><td>0 PLACE</td><td>±</td><td>±</td></tr></table>		mm	INCH	4 PLACES	± ---	± ---	3 PLACES	± ---	± ---	2 PLACES	± 0.20	± ---	1 PLACE	± ---	± ---	0 PLACE				±	±	DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION																																																															
				mm	INCH																																																																																						
			4 PLACES	± ---	± ---																																																																																						
			3 PLACES	± ---	± ---																																																																																						
2 PLACES	± 0.20	± ---																																																																																									
1 PLACE	± ---	± ---																																																																																									
0 PLACE	±	±																																																																																									
DRAWN BY KCHO		DATE 2004/11/05	2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H																																																																																								
CHECKED BY PTL IM		DATE 2004/12/08																																																																																									
APPROVED BY MLONG		DATE 2010/09/06	molex																																																																																								
MATERIAL NO.		DOCUMENT NO.			SHEET NO.																																																																																						
SEE TABLE		SD-87914-013			14 OF 45																																																																																						
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																																																																																									

fb_frame_A3_P_AM_T Rev. G 2012/01/11	9	8	7	6	5	4	3	2	1
---	---	---	---	---	---	---	---	---	---

10		9		8		7		6		5		4		3		2		1	
PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION											
								A	B	F	M	P							
F	87914-2011	-----	-----	-----	-----	20	-----	1	25.40	22.86	10.92	5.84	2.79						
	87914-2021	-----	-----	-----	-----	20	-----	1	25.40	22.86	12.25	7.00	2.96						
	87914-2031	-----	-----	-----	-----	20	-----	1	25.40	22.86	13.38	6.09	5.00						
	87914-2012	-----	-----	-----	-----	20	-----	2	25.40	22.86	10.92	5.84	2.79						
	87914-2022	-----	-----	-----	-----	20	-----	2	25.40	22.86	12.25	7.00	2.96						
	87914-2032	-----	-----	-----	-----	20	-----	2	25.40	22.86	13.38	6.09	5.00						
E	87914-2013	-----	-----	-----	-----	20	-----	3	25.40	22.86	10.92	5.84	2.79						
	87914-2023	-----	-----	-----	-----	20	-----	3	25.40	22.86	12.25	7.00	2.96						
	87914-2033	-----	-----	-----	-----	20	-----	3	25.40	22.86	13.38	6.09	5.00						
	87914-2014	-----	-----	-----	-----	20	-----	4	25.40	22.86	10.92	5.84	2.79						
	87914-2024	-----	-----	-----	-----	20	-----	4	25.40	22.86	12.25	7.00	2.96						
	87914-2034	-----	-----	-----	-----	20	-----	4	25.40	22.86	13.38	6.09	5.00						
D	87914-2015	-----	-----	-----	-----	20	-----	5	25.40	22.86	10.92	5.84	2.79						
	87914-2025	-----	-----	-----	-----	20	-----	5	25.40	22.86	12.25	7.00	2.96						
	87914-2035	-----	-----	-----	-----	20	-----	5	25.40	22.86	13.38	6.09	5.00						
	87914-2016	-----	-----	-----	-----	20	-----	6	25.40	22.86	10.92	5.84	2.79						
	87914-2026	-----	-----	-----	-----	20	-----	6	25.40	22.86	12.25	7.00	2.96						
	87914-2036	-----	-----	-----	-----	20	-----	6	25.40	22.86	13.38	6.09	5.00						
C																			
B																			
A	SHT 7, +879140847 EC NO: S2014-0048 DRWN:ATSEE 2013/07/11 CHKD:SKANG 2013/07/11 APPR:MLONG 2013/10/09 REV D14							QUALITY SYMBOLS F=0 F=0 F=0	GENERAL TOLERANCES (UNLESS SPECIFIED) mm INCH 4 PLACES ± --- ± --- 3 PLACES ± --- ± --- 2 PLACES ± 0.20 ± --- 1 PLACE ± --- ± --- 0 PLACE ± ± ANGULAR ± 3 ° DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			DIMENSION STYLE MM ONLY DRAWN BY DATE KCHO 2004/11/05 CHECKED BY DATE PTL IM 2004/12/08 APPROVED BY DATE MLONG 2010/09/06 MATERIAL NO. SEE TABLE		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION 2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H molex		SHEET NO. 15 OF 45	
	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																		

fb_frame_A3_P_AM_T Rev. G 2012/01/11	9	8	7	6	5	4	3	2	1
---	---	---	---	---	---	---	---	---	---

10		9		8		7		6		5		4		3		2		1		
PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION												
								A	B	F	M	P								
F	87914-2211	-----	-----	-----	-----	22	-----	1	27.94	25.40	10.92	5.84	2.79							F
	87914-2221	-----	-----	-----	-----	22	-----	1	27.94	25.40	12.25	7.00	2.96							
	87914-2231	-----	-----	-----	-----	22	-----	1	27.94	25.40	13.38	6.09	5.00							
	87914-2212	-----	-----	-----	-----	22	-----	2	27.94	25.40	10.92	5.84	2.79							
	87914-2222	-----	-----	-----	-----	22	-----	2	27.94	25.40	12.25	7.00	2.96							
	87914-2232	-----	-----	-----	-----	22	-----	2	27.94	25.40	13.38	6.09	5.00							
E	87914-2213	-----	-----	-----	-----	22	-----	3	27.94	25.40	10.92	5.84	2.79							E
	87914-2223	-----	-----	-----	-----	22	-----	3	27.94	25.40	12.25	7.00	2.96							
	87914-2233	-----	-----	-----	-----	22	-----	3	27.94	25.40	13.38	6.09	5.00							
	87914-2214	-----	-----	-----	-----	22	-----	4	27.94	25.40	10.92	5.84	2.79							
	87914-2224	-----	-----	-----	-----	22	-----	4	27.94	25.40	12.25	7.00	2.96							
	87914-2234	-----	-----	-----	-----	22	-----	4	27.94	25.40	13.38	6.09	5.00							
D	87914-2215	-----	-----	-----	-----	22	-----	5	27.94	25.40	10.92	5.84	2.79							D
	87914-2225	-----	-----	-----	-----	22	-----	5	27.94	25.40	12.25	7.00	2.96							
	87914-2235	-----	-----	-----	-----	22	-----	5	27.94	25.40	13.38	6.09	5.00							
	87914-2216	-----	-----	-----	-----	22	-----	6	27.94	25.40	10.92	5.84	2.79							
	87914-2226	-----	-----	-----	-----	22	-----	6	27.94	25.40	12.25	7.00	2.96							
	87914-2236	-----	-----	-----	-----	22	-----	6	27.94	25.40	13.38	6.09	5.00							
C																				C
B																				B
A	SHT 7, +879140847 EC NO: SZ014-0048 DRWN:ATSE 2013/07/11 CHKD:SKANG 2013/07/11 APPR:MLONG 2013/10/09							QUALITY SYMBOLS		GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE		SCALE		DESIGN UNITS		THIRD ANGLE PROJECTION	
</																				

[illegible]

	10		9		8		7		6		5		4		3		2		1	
	PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION											
									A	B	F	M	P							
F	87914-2811	-----	-----	-----	-----	28	-----	1	35.56	33.02	10.92	5.84	2.79							F
	87914-2821	-----	-----	-----	-----	28	-----	1	35.56	33.02	12.25	7.00	2.96							
	87914-2831	-----	-----	-----	-----	28	-----	1	35.56	33.02	13.38	6.09	5.00							
	87914-2812	-----	-----	-----	-----	28	-----	2	35.56	33.02	10.92	5.84	2.79							E
	87914-2822	-----	-----	-----	-----	28	-----	2	35.56	33.02	12.25	7.00	2.96							
	87914-2832	-----	-----	-----	-----	28	-----	2	35.56	33.02	13.38	6.09	5.00							
E	87914-2813	-----	-----	-----	-----	28	-----	3	35.56	33.02	10.92	5.84	2.79							D
	87914-2823	-----	-----	-----	-----	28	-----	3	35.56	33.02	12.25	7.00	2.96							
	87914-2833	-----	-----	-----	-----	28	-----	3	35.56	33.02	13.38	6.09	5.00							
	87914-2814	-----	-----	-----	-----	28	-----	4	35.56	33.02	10.92	5.84	2.79							C
	87914-2824	-----	-----	-----	-----	28	-----	4	35.56	33.02	12.25	7.00	2.96							
	87914-2834	-----	-----	-----	-----	28	-----	4	35.56	33.02	13.38	6.09	5.00							
D	87914-2815	-----	-----	-----	-----	28	-----	5	35.56	33.02	10.92	5.84	2.79							B
	87914-2825	-----	-----	-----	-----	28	-----	5	35.56	33.02	12.25	7.00	2.96							
	87914-2835	-----	-----	-----	-----	28	-----	5	35.56	33.02	13.38	6.09	5.00							
	87914-2816	-----	-----	-----	-----	28	-----	6	35.56	33.02	10.92	5.84	2.79							A
	87914-2826	-----	-----	-----	-----	28	-----	6	35.56	33.02	12.25	7.00	2.96							
	87914-2836	-----	-----	-----	-----	28	-----	6	35.56	33.02	13.38	6.09	5.00							
C																				
B																				
A								SHT 7, +879140847 EC NO: S2014-0048 DRW:ATSEE 2013/07/11 CHKD:SKANG 2013/07/11 APPR:MLONG 2013/10/09 REV	QUALITY SYMBOLS DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION				2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H molex SD-87914-013 SHEET NO. 19 OF 45
			DRAWN BY DATE		TITLE															
			KCHO 2004/11/05																	
			CHECKED BY DATE																	
			PTLIM 2004/12/08																	
			APPROVED BY DATE																	
			MLONG 2010/09/06																	
			MATERIAL NO.		DOCUMENT NO.															
			SEE TABLE		SD-87914-013															
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION															
		SIZE A3																		

	10		9		8		7		6		5		4		3		2		1											
	PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION																					
									A	B	F	M	P																	
F	87914-3011	-----	-----	-----	-----	30	----	1	38.10	35.56	10.92	5.84	2.79							F										
	87914-3021	-----	-----	-----	-----	30	----	1	38.10	35.56	12.25	7.00	2.96																	
	87914-3031	-----	-----	-----	-----	30	----	1	38.10	35.56	13.38	6.09	5.00																	
	87914-3012	-----	-----	-----	-----	30	----	2	38.10	35.56	10.92	5.84	2.79																	
	87914-3022	-----	-----	-----	-----	30	----	2	38.10	35.56	12.25	7.00	2.96																	
	87914-3032	-----	-----	-----	-----	30	----	2	38.10	35.56	13.38	6.09	5.00																	
E	87914-3013	-----	-----	-----	-----	30	----	3	38.10	35.56	10.92	5.84	2.79							E										
	87914-3023	-----	-----	-----	-----	30	----	3	38.10	35.56	12.25	7.00	2.96																	
	87914-3033	-----	-----	-----	-----	30	----	3	38.10	35.56	13.38	6.09	5.00																	
	87914-3014	-----	-----	-----	-----	30	----	4	38.10	35.56	10.92	5.84	2.79																	
	87914-3024	-----	-----	-----	-----	30	----	4	38.10	35.56	12.25	7.00	2.96																	
	87914-3034	-----	-----	-----	-----	30	----	4	38.10	35.56	13.38	6.09	5.00																	
D	87914-3015	-----	-----	-----	-----	30	----	5	38.10	35.56	10.92	5.84	2.79							D										
	87914-3025	-----	-----	-----	-----	30	----	5	38.10	35.56	12.25	7.00	2.96																	
	87914-3035	-----	-----	-----	-----	30	----	5	38.10	35.56	13.38	6.09	5.00																	
	87914-3016	-----	-----	-----	-----	30	----	6	38.10	35.56	10.92	5.84	2.79																	
	87914-3026	-----	-----	-----	-----	30	----	6	38.10	35.56	12.25	7.00	2.96																	
	87914-3036	-----	-----	-----	-----	30	----	6	38.10	35.56	13.38	6.09	5.00																	
C																				C										
B																				B										
A									SHT 7. +879140847 EC NO: S2014-0048 2013/07/11 DRW:ATSEE CHKD:SKANG 2013/07/11 APPR:MLONG 2013/10/09		QUALITY SYMBOLS F=0 F=0 F=0		GENERAL TOLERANCES (UNLESS SPECIFIED) mm INCH 4 PLACES ± --- ± --- 3 PLACES ± --- ± --- 2 PLACES ± 0.20 ± --- 1 PLACE ± --- ± --- 0 PLACE ± ± ANGULAR ± 3 °		DIMENSION STYLE MM ONLY DRAWN BY DATE KCHO 2004/11/05 CHECKED BY DATE PTLIM 2004/12/08 APPROVED BY DATE MLONG 2010/09/06 MATERIAL NO.		SCALE NTS		DESIGN UNITS METRIC		THIRD ANGLE PROJECTION		2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H		molex		DOCUMENT NO. SD-87914-013		SHEET NO. 20 OF 45	
									D14				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE TABLE															

	10		9		8		7		6		5		4		3		2		1	
F	PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION					F						
	A	B	F	M	P															
	87914-3211	-----	-----	-----	-----	32	-----	1	40.64	38.10	10.92	5.84	2.79							
	87914-3221	-----	-----	-----	-----	32	-----	1	40.64	38.10	12.25	7.00	2.96							
	87914-3231	-----	-----	-----	-----	32	-----	1	40.64	38.10	13.38	6.09	5.00							
	87914-3212	-----	-----	-----	-----	32	-----	2	40.64	38.10	10.92	5.84	2.79							
	87914-3222	-----	-----	-----	-----	32	-----	2	40.64	38.10	12.25	7.00	2.96							
	87914-3232	-----	-----	-----	-----	32	-----	2	40.64	38.10	13.38	6.09	5.00							
E	87914-3213	-----	-----	-----	-----	32	-----	3	40.64	38.10	10.92	5.84	2.79	E						
	87914-3223	-----	-----	-----	-----	32	-----	3	40.64	38.10	12.25	7.00	2.96							
	87914-3233	-----	-----	-----	-----	32	-----	3	40.64	38.10	13.38	6.09	5.00							
	87914-3214	-----	-----	-----	-----	32	-----	4	40.64	38.10	10.92	5.84	2.79							
	87914-3224	-----	-----	-----	-----	32	-----	4	40.64	38.10	12.25	7.00	2.96							
	87914-3234	-----	-----	-----	-----	32	-----	4	40.64	38.10	13.38	6.09	5.00							
D	87914-3215	-----	-----	-----	-----	32	-----	5	40.64	38.10	10.92	5.84	2.79	D						
	87914-3225	-----	-----	-----	-----	32	-----	5	40.64	38.10	12.25	7.00	2.96							
	87914-3235	-----	-----	-----	-----	32	-----	5	40.64	38.10	13.38	6.09	5.00							
	87914-3216	-----	-----	-----	-----	32	-----	6	40.64	38.10	10.92	5.84	2.79							
	87914-3226	-----	-----	-----	-----	32	-----	6	40.64	38.10	12.25	7.00	2.96							
	87914-3236	-----	-----	-----	-----	32	-----	6	40.64	38.10	13.38	6.09	5.00							
C														C						
B														B						

[illegible]

10		9		8		7		6		5		4		3		2		1	
PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION											
								A	B	F	M	P							
F	87914-3611	-----	-----	-----	-----	36	-----	1	45.72	43.18	10.92	5.84	2.79						
	87914-3621	-----	-----	-----	-----	36	-----	1	45.72	43.18	12.25	7.00	2.96						
	87914-3631	-----	-----	-----	-----	36	-----	1	45.72	43.18	13.38	6.09	5.00						
	87914-3612	-----	-----	-----	-----	36	-----	2	45.72	43.18	10.92	5.84	2.79						
	87914-3622	-----	-----	-----	-----	36	-----	2	45.72	43.18	12.25	7.00	2.96						
E	87914-3632	-----	-----	-----	-----	36	-----	2	45.72	43.18	13.38	6.09	5.00						
	87914-3613	-----	-----	-----	-----	36	-----	3	45.72	43.18	10.92	5.84	2.79						
	87914-3623	-----	-----	-----	-----	36	-----	3	45.72	43.18	12.25	7.00	2.96						
D	87914-3633	-----	-----	-----	-----	36	-----	3	45.72	43.18	13.38	6.09	5.00						
	87914-3614	-----	-----	-----	-----	36	-----	4	45.72	43.18	10.92	5.84	2.79						
	87914-3624	-----	-----	-----	-----	36	-----	4	45.72	43.18	12.25	7.00	2.96						
	87914-3634	-----	-----	-----	-----	36	-----	4	45.72	43.18	13.38	6.09	5.00						
	87914-3615	-----	-----	-----	-----	36	-----	5	45.72	43.18	10.92	5.84	2.79						
C	87914-3625	-----	-----	-----	-----	36	-----	5	45.72	43.18	12.25	7.00	2.96						
	87914-3635	-----	-----	-----	-----	36	-----	5	45.72	43.18	13.38	6.09	5.00						
	87914-3616	-----	-----	-----	-----	36	-----	6	45.72	43.18	10.92	5.84	2.79						
	87914-3626	-----	-----	-----	-----	36	-----	6	45.72	43.18	12.25	7.00	2.96						
	87914-3636	-----	-----	-----	-----	36	-----	6	45.72	43.18	13.38	6.09	5.00						
B	87914-3637	-----	-----	-----	-----	36	-----	6	45.72	43.18	12.10	7.01	2.60						
A																			

SHT 7. +879140847 EC NO: S2014-0048 DRW:ATSEE 2013/07/11 CHKD:SKANG 2013/07/11 APPR:MLONG 2013/10/09 D14	QUALITY SYMBOLS 	DESCRIPTION REV	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION			
				mm	INCH	DRAWN BY KCHO	DATE 2004/11/05	2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H molex				
			4 PLACES	± ---	± ---	CHECKED BY	DATE 2004/12/08					
			3 PLACES	± ---	± ---	PTL IM	DATE 2010/09/06					
			2 PLACES	± 0.20	± ---	APPROVED BY						
			1 PLACE	± ---	± ---	MATERIAL NO.	DOCUMENT NO.					
			0 PLACE	±	±	SEE TABLE		SD-87914-013		SHEET NO. 23 OF 45		
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					

fb_frame_A3_P_AM_T Rev. G 2012/01/11		9	8	7	6	5	4	3	2	1
---	--	---	---	---	---	---	---	---	---	---

10		9		8		7		6		5		4		3		2		1	
F	PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION					F					
	A	B	F	M	P														
	87914-3811	-----	-----	-----	-----	38	-----	1	48.26	45.72	10.92	5.84	2.79						
	87914-3821	-----	-----	-----	-----	38	-----	1	48.26	45.72	12.25	7.00	2.96						
	87914-3831	-----	-----	-----	-----	38	-----	1	48.26	45.72	13.38	6.09	5.00						
	87914-3812	-----	-----	-----	-----	38	-----	2	48.26	45.72	10.92	5.84	2.79						
	87914-3822	-----	-----	-----	-----	38	-----	2	48.26	45.72	12.25	7.00	2.96						
	87914-3832	-----	-----	-----	-----	38	-----	2	48.26	45.72	13.38	6.09	5.00						
E	87914-3813	-----	-----	-----	-----	38	-----	3	48.26	45.72	10.92	5.84	2.79	E					
	87914-3823	-----	-----	-----	-----	38	-----	3	48.26	45.72	12.25	7.00	2.96						
	87914-3833	-----	-----	-----	-----	38	-----	3	48.26	45.72	13.38	6.09	5.00						
	87914-3814	-----	-----	-----	-----	38	-----	4	48.26	45.72	10.92	5.84	2.79						
	87914-3824	-----	-----	-----	-----	38	-----	4	48.26	45.72	12.25	7.00	2.96						
	87914-3834	-----	-----	-----	-----	38	-----	4	48.26	45.72	13.38	6.09	5.00						
D	87914-3815	-----	-----	-----	-----	38	-----	5	48.26	45.72	10.92	5.84	2.79	D					
	87914-3825	-----	-----	-----	-----	38	-----	5	48.26	45.72	12.25	7.00	2.96						
	87914-3835	-----	-----	-----	-----	38	-----	5	48.26	45.72	13.38	6.09	5.00						
	87914-3816	-----	-----	-----	-----	38	-----	6	48.26	45.72	10.92	5.84	2.79						
	87914-3826	-----	-----	-----	-----	38	-----	6	48.26	45.72	12.25	7.00	2.96						
	87914-3836	-----	-----	-----	-----	38	-----	6	48.26	45.72	13.38	6.09	5.00						
C														C					
B														B					

	10		9		8		7		6		5		4		3		2		1		
	PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION												
									A	B	F	M	P								
F	87914-4011	-----	-----	-----	-----	40	-----	1	50.80	48.26	10.92	5.84	2.79								
	87914-4021	-----	-----	-----	-----	40	-----	1	50.80	48.26	12.25	7.00	2.96								
	87914-4031	-----	-----	-----	-----	40	-----	1	50.80	48.26	13.38	6.09	5.00								
	87914-4012	-----	-----	-----	-----	40	-----	2	50.80	48.26	10.92	5.84	2.79								
	87914-4022	-----	-----	-----	-----	40	-----	2	50.80	48.26	12.25	7.00	2.96								
	87914-4032	-----	-----	-----	-----	40	-----	2	50.80	48.26	13.38	6.09	5.00								
E	87914-4013	-----	-----	-----	-----	40	-----	3	50.80	48.26	10.92	5.84	2.79								
	87914-4023	-----	-----	-----	-----	40	-----	3	50.80	48.26	12.25	7.00	2.96								
	87914-4033	-----	-----	-----	-----	40	-----	3	50.80	48.26	13.38	6.09	5.00								
	87914-4014	-----	-----	-----	-----	40	-----	4	50.80	48.26	10.92	5.84	2.79								
	87914-4024	-----	-----	-----	-----	40	-----	4	50.80	48.26	12.25	7.00	2.96								
	87914-4034	-----	-----	-----	-----	40	-----	4	50.80	48.26	13.38	6.09	5.00								
D	87914-4015	-----	-----	-----	-----	40	-----	5	50.80	48.26	10.92	5.84	2.79								
	87914-4025	-----	-----	-----	-----	40	-----	5	50.80	48.26	12.25	7.00	2.96								
	87914-4035	-----	-----	-----	-----	40	-----	5	50.80	48.26	13.38	6.09	5.00								
	87914-4016	-----	-----	-----	-----	40	-----	6	50.80	48.26	10.92	5.84	2.79								
	87914-4026	-----	-----	-----	-----	40	-----	6	50.80	48.26	12.25	7.00	2.96								
	87914-4036	-----	-----	-----	-----	40	-----	6	50.80	48.26	13.38	6.09	5.00								
C																					
B																					
A																					

10		9		8		7		6		5		4		3		2		1				
PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION														
								A	B	F	M	P										
F	87914-4211	-----	-----	-----	-----	42	-----	1	53.34	50.80	10.92	5.84	2.79									
	87914-4221	-----	-----	-----	-----	42	-----	1	53.34	50.80	12.25	7.00	2.96									
	87914-4212	-----	-----	-----	-----	42	-----	2	53.34	50.80	10.92	5.84	2.79									
	87914-4222	-----	-----	-----	-----	42	-----	2	53.34	50.80	12.25	7.00	2.96									
	87914-4213	-----	-----	-----	-----	42	-----	3	53.34	50.80	10.92	5.84	2.79									
	87914-4223	-----	-----	-----	-----	42	-----	3	53.34	50.80	12.25	7.00	2.96									
E	87914-4214	-----	-----	-----	-----	42	-----	4	53.34	50.80	10.92	5.84	2.79									
	87914-4224	-----	-----	-----	-----	42	-----	4	53.34	50.80	12.25	7.00	2.96									
	87914-4215	-----	-----	-----	-----	42	-----	5	53.34	50.80	10.92	5.84	2.79									
	87914-4225	-----	-----	-----	-----	42	-----	5	53.34	50.80	12.25	7.00	2.96									
D	87914-4216	-----	-----	-----	-----	42	-----	6	53.34	50.80	10.92	5.84	2.79									
	87914-4226	-----	-----	-----	-----	42	-----	6	53.34	50.80	12.25	7.00	2.96									
C																						
B																						
A	SHT 7, +879140847		EC NO: SZ014-0048		2013/07/11		2013/07/11		2013/10/09		QUALITY SYMBOLS		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE		DESIGN UNITS		THIRD ANGLE PROJECTION	
	DRWN:ATSEE		CHKD:SKANG		APPR:MLONG		REV		DESCRIPTION		F=0		4 PLACES		mm		INCH		DRAWN BY		DATE	
	F=0		F=0		F=0		F=0		F=0		3 PLACES		±---		±---		±---		KCHO		2004/11/05	
	F=0		F=0		F=0		F=0		F=0		2 PLACES		±0.20		±---		±---		PTLIM		2004/12/08	
	F=0		F=0		F=0		F=0		F=0		1 PLACE		±---		±---		±---		APPROVED BY		DATE	
	F=0		F=0		F=0		F=0		F=0		0 PLACE		±		±		±		MLONG		2010/09/06	
	F=0		F=0		F=0		F=0		F=0		ANGULAR ± 3 °		MATERIAL NO.		DOCUMENT NO.		2.54MM PITCH				SHEET NO.	
	F=0		F=0		F=0		F=0		F=0		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE TABLE		SD-87914-013		molex				26 OF 45	
	F=0		F=0		F=0		F=0		F=0		SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									
	F=0		F=0		F=0		F=0		F=0													

fb_frame_A3_P_AM_T
Rev. G 2012/01/11

9

8

7

6

5

4

3

2

1

	10		9	8		7		6	5		4		3		2		1		
F	PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION										
									A	B	F	M	P						
	87914-4411	-----	-----	-----	-----	44	-----	1	55.88	53.34	10.92	5.84	2.79						
	87914-4421	-----	-----	-----	-----	44	-----	1	55.88	53.34	12.25	7.00	2.96						
	87914-4412	-----	-----	-----	-----	44	-----	2	55.88	53.34	10.92	5.84	2.79						
	87914-4422	-----	-----	-----	-----	44	-----	2	55.88	53.34	12.25	7.00	2.96						
	87914-4413	-----	-----	-----	-----	44	-----	3	55.88	53.34	10.92	5.84	2.79						
	87914-4423	-----	-----	-----	-----	44	-----	3	55.88	53.34	12.25	7.00	2.96						
E	87914-4414	-----	-----	-----	-----	44	-----	4	55.88	53.34	10.92	5.84	2.79						
	87914-4424	-----	-----	-----	-----	44	-----	4	55.88	53.34	12.25	7.00	2.96						
	87914-4415	-----	-----	-----	-----	44	-----	5	55.88	53.34	10.92	5.84	2.79						
	87914-4425	-----	-----	-----	-----	44	-----	5	55.88	53.34	12.25	7.00	2.96						
	87914-4416	-----	-----	-----	-----	44	-----	6	55.88	53.34	10.92	5.84	2.79						
	87914-4426	-----	-----	-----	-----	44	-----	6	55.88	53.34	12.25	7.00	2.96						
D																			
C																			
B																			

10		9		8		7		6		5		4		3		2		1	
PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION											
								A	B	F	M	P							
F	87914-4611	-----	-----	-----	-----	46	-----	1	58.42	55.88	10.92	5.84	2.79						
	87914-4621	-----	-----	-----	-----	46	-----	1	58.42	55.88	12.25	7.00	2.96						
	87914-4612	-----	-----	-----	-----	46	-----	2	58.42	55.88	10.92	5.84	2.79						
	87914-4622	-----	-----	-----	-----	46	-----	2	58.42	55.88	12.25	7.00	2.96						
	87914-4613	-----	-----	-----	-----	46	-----	3	58.42	55.88	10.92	5.84	2.79						
	87914-4623	-----	-----	-----	-----	46	-----	3	58.42	55.88	12.25	7.00	2.96						
E	87914-4614	-----	-----	-----	-----	46	-----	4	58.42	55.88	10.92	5.84	2.79						
	87914-4624	-----	-----	-----	-----	46	-----	4	58.42	55.88	12.25	7.00	2.96						
	87914-4615	-----	-----	-----	-----	46	-----	5	58.42	55.88	10.92	5.84	2.79						
	87914-4625	-----	-----	-----	-----	46	-----	5	58.42	55.88	12.25	7.00	2.96						
	87914-4616	-----	-----	-----	-----	46	-----	6	58.42	55.88	10.92	5.84	2.79						
	87914-4626	-----	-----	-----	-----	46	-----	6	58.42	55.88	12.25	7.00	2.96						
D																			
C																			
B																			
A	fb_frame_A3_P_AM_T Rev. G 2012/01/11		9	8	7	6	5	4	3	2	1								
	SHT 7, +879140847 EC NO: SZ014-0048 DRWN:ATSE 2013/07/11 CHKD:SKANG 2013/07/11 APPR:MLONG 2013/10/09		DESCRIPTION REV		QUALITY SYMBOLS F=0 F=0 F=0	GENERAL TOLERANCES (UNLESS SPECIFIED) mm INCH 4 PLACES ± --- ± --- 3 PLACES ± --- ± --- 2 PLACES ± 0.20 ± --- 1 PLACE ± --- ± --- 0 PLACE ± ± ANGULAR ± 3 ° DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		DIMENSION STYLE MM ONLY DRAWN BY DATE KCHO 2004/11/05 CHECKED BY DATE PTL IM 2004/12/08 APPROVED BY DATE MLONG 2010/09/06 MATERIAL NO. SEE TABLE		SCALE NTS TITLE 2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H		DESIGN UNITS METRIC THIRD ANGLE PROJECTION		DOCUMENT NO. SD-87914-013		SHEET NO. 28 OF 45			
	D14							SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									

	10		9		8		7		6		5		4		3		2		1																																																									
	PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION																																																																			
									A	B	F	M	P																																																															
F	87914-4811	-----	-----	-----	-----	48	----	1	60.96	58.42	10.92	5.84	2.79																																																															
	87914-4821	-----	-----	-----	-----	48	----	1	60.96	58.42	12.25	7.00	2.96																																																															
	87914-4812	-----	-----	-----	-----	48	----	2	60.96	58.42	10.92	5.84	2.79																																																															
	87914-4822	-----	-----	-----	-----	48	----	2	60.96	58.42	12.25	7.00	2.96																																																															
	87914-4813	-----	-----	-----	-----	48	----	3	60.96	58.42	10.92	5.84	2.79																																																															
E	87914-4823	-----	-----	-----	-----	48	----	3	60.96	58.42	12.25	7.00	2.96																																																															
	87914-4814	-----	-----	-----	-----	48	----	4	60.96	58.42	10.92	5.84	2.79																																																															
	87914-4824	-----	-----	-----	-----	48	----	4	60.96	58.42	12.25	7.00	2.96																																																															
	87914-4815	-----	-----	-----	-----	48	----	5	60.96	58.42	10.92	5.84	2.79																																																															
	87914-4825	-----	-----	-----	-----	48	----	5	60.96	58.42	12.25	7.00	2.96																																																															
D	87914-4816	-----	-----	-----	-----	48	----	6	60.96	58.42	10.92	5.84	2.79																																																															
	87914-4826	-----	-----	-----	-----	48	----	6	60.96	58.42	12.25	7.00	2.96																																																															
C																																																																												
B																																																																												
A																																																																												
										<table><tr><td rowspan="6">SHT 7. +879140847 EC NO: S2014-0048 DRWN:ATSEE 2013/07/11 CHKD:SKANG 2013/07/11 APPR:MLONG 2013/10/09</td><td rowspan="8">DESCRIPTION REV</td><td colspan="2">QUALITY SYMBOLS</td><td colspan="3">GENERAL TOLERANCES (UNLESS SPECIFIED)</td><td colspan="2">DIMENSION STYLE MM ONLY</td><td>SCALE NTS</td><td>DESIGN UNITS METRIC</td><td colspan="3" rowspan="8"> THIRD ANGLE PROJECTION</td></tr><tr><td colspan="2" rowspan="7">=0 =0 =0</td><td rowspan="5">4 PLACES 3 PLACES 2 PLACES 1 PLACE 0 PLACE</td><td rowspan="5">mm INCH</td><td rowspan="7">± --- ± --- ± 0.20 ± --- ±</td><td rowspan="7">DRAWN BY KCHO CHECKED BY PTLIM APPROVED BY MLONG MATERIAL NO.</td><td rowspan="7">DATE 2004/11/05 2004/12/08 2010/09/06</td><td colspan="5">TITLE 2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H</td></tr><tr><td colspan="5" rowspan="2">molex</td></tr><tr></tr><tr><td colspan="5">SEE TABLE</td></tr><tr><td colspan="5" rowspan="2">SD-87914-013</td></tr><tr></tr><tr><td colspan="5">DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS</td><td>SIZE A3</td><td colspan="10">THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION</td></tr></table>										SHT 7. +879140847 EC NO: S2014-0048 DRWN:ATSEE 2013/07/11 CHKD:SKANG 2013/07/11 APPR:MLONG 2013/10/09	DESCRIPTION REV	QUALITY SYMBOLS		GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION			=0 =0 =0		4 PLACES 3 PLACES 2 PLACES 1 PLACE 0 PLACE	mm INCH	± --- ± --- ± 0.20 ± --- ±	DRAWN BY KCHO CHECKED BY PTLIM APPROVED BY MLONG MATERIAL NO.	DATE 2004/11/05 2004/12/08 2010/09/06	TITLE 2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H					molex					SEE TABLE					SD-87914-013					DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS					SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									
SHT 7. +879140847 EC NO: S2014-0048 DRWN:ATSEE 2013/07/11 CHKD:SKANG 2013/07/11 APPR:MLONG 2013/10/09	DESCRIPTION REV	QUALITY SYMBOLS		GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION																																																																	
		=0 =0 =0		4 PLACES 3 PLACES 2 PLACES 1 PLACE 0 PLACE	mm INCH	± --- ± --- ± 0.20 ± --- ±	DRAWN BY KCHO CHECKED BY PTLIM APPROVED BY MLONG MATERIAL NO.	DATE 2004/11/05 2004/12/08 2010/09/06	TITLE 2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H																																																																			
									molex																																																																			
									SEE TABLE																																																																			
									SD-87914-013																																																																			
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS					SIZE A3				THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																																																																			
fb_frame_A3_P_AM_T Rev. G 2012/01/11	9		8		7		6		5		4		3		2		1																																																											

10		9		8		7		6		5		4		3		2		1	
PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION											
								A	B	F	M	P							
F	87914-5011	-----	-----	-----	-----	50	-----	1	63.50	60.96	10.92	5.84	2.79						
	87914-5021	-----	-----	-----	-----	50	-----	1	63.50	60.96	12.25	7.00	2.96						
	87914-5012	-----	-----	-----	-----	50	-----	2	63.50	60.96	10.92	5.84	2.79						
	87914-5022	-----	-----	-----	-----	50	-----	2	63.50	60.96	12.25	7.00	2.96						
	87914-5013	-----	-----	-----	-----	50	-----	3	63.50	60.96	10.92	5.84	2.79						
E	87914-5023	-----	-----	-----	-----	50	-----	3	63.50	60.96	12.25	7.00	2.96						
	87914-5014	-----	-----	-----	-----	50	-----	4	63.50	60.96	10.92	5.84	2.79						
	87914-5024	-----	-----	-----	-----	50	-----	4	63.50	60.96	12.25	7.00	2.96						
	87914-5015	-----	-----	-----	-----	50	-----	5	63.50	60.96	10.92	5.84	2.79						
	87914-5025	-----	-----	-----	-----	50	-----	5	63.50	60.96	12.25	7.00	2.96						
D	87914-5016	-----	-----	-----	-----	50	-----	6	63.50	60.96	10.92	5.84	2.79						
	87914-5026	-----	-----	-----	-----	50	-----	6	63.50	60.96	12.25	7.00	2.96						
	87914-0002	-----	-----	-----	-----	50	-----	8	63.50	60.96	18.54	11.58	4.47						
C																			
B																			
A																			
								QUALITY SYMBOLS		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE		DESIGN UNITS		THIRD ANGLE PROJECTION	
								F=0		mm INCH		DRAWN BY DATE		NTS		METRIC			
								F=0		4 PLACES ± --- ± ---		KCHO 2004/11/05				2.54MM PITCH			
								F=0		3 PLACES ± --- ± ---		CHECKED BY DATE				DUAL ROW HEADER			
										2 PLACES ± 0.20 ± ---		PTL IM 2004/12/08				SINGLE WAFER, T/H			
										1 PLACE ± --- ± ---		APPROVED BY DATE				molex			
										0 PLACE ± ±		MLONG 2010/09/06							
										ANGULAR ± 3 °		MATERIAL NO.		DOCUMENT NO.				SHEET NO.	
										DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE TABLE		SD-87914-013				30 OF 45	
										SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION							
fb_frame_A3_P_AM_T Rev. G 2012/01/11		9		8		7		6		5		4		3		2		1	

10		9		8		7		6		5		4		3		2		1	
PART NO FOR BULK PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION											
								A	B	F	M	P							
F	87914-5211	-----	-----	-----	-----	52	-----	1	66.04	63.50	10.92	5.84	2.79						
	87914-5221	-----	-----	-----	-----	52	-----	1	66.04	63.50	12.25	7.00	2.96						
	87914-5212	-----	-----	-----	-----	52	-----	2	66.04	63.50	10.92	5.84	2.79						
	87914-5222	-----	-----	-----	-----	52	-----	2	66.04	63.50	12.25	7.00	2.96						
	87914-5213	-----	-----	-----	-----	52	-----	3	66.04	63.50	10.92	5.84	2.79						
	87914-5223	-----	-----	-----	-----	52	-----	3	66.04	63.50	12.25	7.00	2.96						
E	87914-5214	-----	-----	-----	-----	52	-----	4	66.04	63.50	10.92	5.84	2.79						
	87914-5224	-----	-----	-----	-----	52	-----	4	66.04	63.50	12.25	7.00	2.96						
	87914-5215	-----	-----	-----	-----	52	-----	5	66.04	63.50	10.92	5.84	2.79						
	87914-5225	-----	-----	-----	-----	52	-----	5	66.04	63.50	12.25	7.00	2.96						
	87914-5216	-----	-----	-----	-----	52	-----	6	66.04	63.50	10.92	5.84	2.79						
	87914-5226	-----	-----	-----	-----	52	-----	6	66.04	63.50	12.25	7.00	2.96						
D																			
C																			
B																			
A																			
fb_frame_A3_P_AM_T Rev. G 2012/01/11		9	8	7	6	5	4	3	2	1									

SHT 7, +879140847 EC NO: SZ014-0048 DRWN:ATSEE 2013/07/11 CHKD:SKANG 2013/07/11 APPR:MLONG 2013/10/09	DESCRIPTION REV	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION			
		=0 =0 =0		mm	INCH	DRAWN BY	DATE	2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H molex				
			4 PLACES	± ---	± ---	KCHO	2004/11/05					
			3 PLACES	± ---	± ---	CHECKED BY	DATE					
			2 PLACES	± 0.20	± ---	PTL IM	2004/12/08					
			1 PLACE	± ---	± ---	APPROVED BY	DATE					
		0 PLACE	±	±	MLONG	2010/09/06	SD-87914-013					
		ANGULAR ± 3 °										
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS										
		SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION								

10		9		8		7		6		5		4		3		2		1	
PART NO FOR BULK PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION											
								A	B	F	M	P							
F	87914-5411	-----	-----	-----	-----	54	-----	1	68.58	66.04	10.92	5.84	2.79						
	87914-5421	-----	-----	-----	-----	54	-----	1	68.58	66.04	12.25	7.00	2.96						
	87914-5412	-----	-----	-----	-----	54	-----	2	68.58	66.04	10.92	5.84	2.79						
	87914-5422	-----	-----	-----	-----	54	-----	2	68.58	66.04	12.25	7.00	2.96						
	87914-5413	-----	-----	-----	-----	54	-----	3	68.58	66.04	10.92	5.84	2.79						
	87914-5423	-----	-----	-----	-----	54	-----	3	68.58	66.04	12.25	7.00	2.96						
E	87914-5414	-----	-----	-----	-----	54	-----	4	68.58	66.04	10.92	5.84	2.79						
	87914-5424	-----	-----	-----	-----	54	-----	4	68.58	66.04	12.25	7.00	2.96						
	87914-5415	-----	-----	-----	-----	54	-----	5	68.58	66.04	10.92	5.84	2.79						
	87914-5425	-----	-----	-----	-----	54	-----	5	68.58	66.04	12.25	7.00	2.96						
	87914-5416	-----	-----	-----	-----	54	-----	6	68.58	66.04	10.92	5.84	2.79						
	87914-5426	-----	-----	-----	-----	54	-----	6	68.58	66.04	12.25	7.00	2.96						
D																			
C																			
B																			
A	SHT 7, +879140847 EC NO: SZ014-0048 DRWN:ATSEE 2013/07/11 CHKD:SKANG 2013/07/11 APPR:MLONG 2013/10/09							QUALITY SYMBOLS =0 =0 =0	GENERAL TOLERANCES (UNLESS SPECIFIED) mm INCH 4 PLACES ± --- ± --- 3 PLACES ± --- ± --- 2 PLACES ± 0.20 ± --- 1 PLACE ± --- ± --- 0 PLACE ± ±	DIMENSION STYLE MM ONLY DRAWN BY DATE KCHO 2004/11/05 CHECKED BY DATE PTL IM 2004/12/08 APPROVED BY DATE MLONG 2010/09/06	SCALE NTS 2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H molex	DESIGN UNITS METRIC THIRD ANGLE PROJECTION	TITLE SEE TABLE SD-87914-013 SHEET NO. 32 OF 45	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE A3																

fb_frame_A3_P_AM_T
Rev. G 2012/01/11

987654321

	10		9		8		7		6		5		4		3		2		1																																																																		
	PART NO FOR BULK PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION																																																																												
									A	B	F	M	P																																																																								
F	87914-5611	-----	-----	-----	-----	56	----	1	71.12	68.58	10.92	5.84	2.79	F																																																																							
	87914-5621	-----	-----	-----	-----	56	----	1	71.12	68.58	12.25	7.00	2.96																																																																								
	87914-5612	-----	-----	-----	-----	56	----	2	71.12	68.58	10.92	5.84	2.79																																																																								
	87914-5622	-----	-----	-----	-----	56	----	2	71.12	68.58	12.25	7.00	2.96																																																																								
	87914-5613	-----	-----	-----	-----	56	----	3	71.12	68.58	10.92	5.84	2.79																																																																								
E	87914-5623	-----	-----	-----	-----	56	----	3	71.12	68.58	12.25	7.00	2.96	E																																																																							
	87914-5614	-----	-----	-----	-----	56	----	4	71.12	68.58	10.92	5.84	2.79																																																																								
	87914-5624	-----	-----	-----	-----	56	----	4	71.12	68.58	12.25	7.00	2.96																																																																								
	87914-5615	-----	-----	-----	-----	56	----	5	71.12	68.58	10.92	5.84	2.79																																																																								
	87914-5625	-----	-----	-----	-----	56	----	5	71.12	68.58	12.25	7.00	2.96																																																																								
D	87914-5616	-----	-----	-----	-----	56	----	6	71.12	68.58	10.92	5.84	2.79	D																																																																							
	87914-5626	-----	-----	-----	-----	56	----	6	71.12	68.58	12.25	7.00	2.96																																																																								
C														C																																																																							
B														B																																																																							
A														A																																																																							
<table><tr><td rowspan="5">SHT 7. +879140847 EC NO: S2014-0048 DRWN:ATSEE 2013/07/11 CHKD:SKANG 2013/07/11 APPR:MLONG 2013/10/09</td><td rowspan="5">DESCRIPTION REV</td><td rowspan="5">QUALITY SYMBOLS ▽_F=0 ▽_E=0 ▽_P=0</td><td colspan="3">GENERAL TOLERANCES (UNLESS SPECIFIED)</td><td colspan="2">DIMENSION STYLE MM ONLY</td><td>SCALE NTS</td><td>DESIGN UNITS METRIC</td><td colspan="2" rowspan="7">THIRD ANGLE PROJECTION</td></tr><tr><td rowspan="2">4 PLACES</td><td rowspan="2">± ---</td><td rowspan="2">± ---</td><td rowspan="2">DRAWN BY KCHO</td><td rowspan="2">DATE 2004/11/05</td><td colspan="4" rowspan="2">TITLE 2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H</td></tr><tr></tr><tr><td rowspan="2">3 PLACES</td><td rowspan="2">± ---</td><td rowspan="2">± ---</td><td rowspan="2">CHECKED BY PTLIM</td><td rowspan="2">DATE 2004/12/08</td><td colspan="4" rowspan="2">molex</td></tr><tr></tr><tr><td rowspan="2">2 PLACES</td><td rowspan="2">± 0.20</td><td rowspan="2">± ---</td><td rowspan="2">APPROVED BY MLONG</td><td rowspan="2">DATE 2010/09/06</td><td colspan="4" rowspan="2">SD-87914-013</td></tr><tr></tr><tr><td rowspan="2">1 PLACE</td><td rowspan="2">± ---</td><td rowspan="2">± ---</td><td colspan="3">MATERIAL NO.</td><td colspan="2">DOCUMENT NO.</td><td colspan="2">SHEET NO.</td></tr><tr></tr><tr><td colspan="3">ANGULAR ± 3 °</td><td colspan="2">SEE TABLE</td><td colspan="4">33 OF 45</td></tr><tr><td colspan="3">DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS</td><td>SIZE A3</td><td colspan="10">THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION</td></tr></table>														SHT 7. +879140847 EC NO: S2014-0048 DRWN:ATSEE 2013/07/11 CHKD:SKANG 2013/07/11 APPR:MLONG 2013/10/09	DESCRIPTION REV	QUALITY SYMBOLS ▽ _F =0 ▽ _E =0 ▽ _P =0	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		4 PLACES	± ---	± ---	DRAWN BY KCHO	DATE 2004/11/05	TITLE 2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H				3 PLACES	± ---	± ---	CHECKED BY PTLIM	DATE 2004/12/08	molex				2 PLACES	± 0.20	± ---	APPROVED BY MLONG	DATE 2010/09/06	SD-87914-013				1 PLACE	± ---	± ---	MATERIAL NO.			DOCUMENT NO.		SHEET NO.		ANGULAR ± 3 °			SEE TABLE		33 OF 45				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									
SHT 7. +879140847 EC NO: S2014-0048 DRWN:ATSEE 2013/07/11 CHKD:SKANG 2013/07/11 APPR:MLONG 2013/10/09	DESCRIPTION REV	QUALITY SYMBOLS ▽ _F =0 ▽ _E =0 ▽ _P =0	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION																																																																											
			4 PLACES	± ---	± ---	DRAWN BY KCHO	DATE 2004/11/05	TITLE 2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H																																																																													
			3 PLACES	± ---	± ---	CHECKED BY PTLIM	DATE 2004/12/08	molex																																																																													
2 PLACES	± 0.20	± ---	APPROVED BY MLONG	DATE 2010/09/06	SD-87914-013																																																																																
1 PLACE	± ---	± ---	MATERIAL NO.			DOCUMENT NO.		SHEET NO.																																																																													
ANGULAR ± 3 °			SEE TABLE		33 OF 45																																																																																
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																																																																																	
fb_frame_A3_P_AM_T Rev. G 2012/01/11	9	8	7	6	5	4	3	2	1																																																																												

	10		9		8		7		6		5		4		3		2		1					
F	PART NO FOR BULK PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION															F
	A	B	F	M	P																			
	87914-5811	-----	-----	-----	-----	58	-----	1	73.66	71.12	10.92	5.84	2.79											
	87914-5821	-----	-----	-----	-----	58	-----	1	73.66	71.12	12.25	7.00	2.96											
	87914-5812	-----	-----	-----	-----	58	-----	2	73.66	71.12	10.92	5.84	2.79											
	87914-5822	-----	-----	-----	-----	58	-----	2	73.66	71.12	12.25	7.00	2.96											
	87914-5813	-----	-----	-----	-----	58	-----	3	73.66	71.12	10.92	5.84	2.79											
	87914-5823	-----	-----	-----	-----	58	-----	3	73.66	71.12	12.25	7.00	2.96											
E	87914-5814	-----	-----	-----	-----	58	-----	4	73.66	71.12	10.92	5.84	2.79											E
	87914-5824	-----	-----	-----	-----	58	-----	4	73.66	71.12	12.25	7.00	2.96											
	87914-5815	-----	-----	-----	-----	58	-----	5	73.66	71.12	10.92	5.84	2.79											
	87914-5825	-----	-----	-----	-----	58	-----	5	73.66	71.12	12.25	7.00	2.96											
	87914-5816	-----	-----	-----	-----	58	-----	6	73.66	71.12	10.92	5.84	2.79											
	87914-5826	-----	-----	-----	-----	58	-----	6	73.66	71.12	12.25	7.00	2.96											
D																								D

10		9		8		7		6		5		4		3		2		1	
PART NO FOR BULK PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION											
								A	B	F	M	P							
F	87914-6011	-----	-----	-----	-----	60	----	1	76.20	73.66	10.92	5.84	2.79						
	87914-6021	-----	-----	-----	-----	60	----	1	76.20	73.66	12.25	7.00	2.96						
	87914-6012	-----	-----	-----	-----	60	----	2	76.20	73.66	10.92	5.84	2.79						
	87914-6022	-----	-----	-----	-----	60	----	2	76.20	73.66	12.25	7.00	2.96						
	87914-6013	-----	-----	-----	-----	60	----	3	76.20	73.66	10.92	5.84	2.79						
E	87914-6023	-----	-----	-----	-----	60	----	3	76.20	73.66	12.25	7.00	2.96						
	87914-6014	-----	-----	-----	-----	60	----	4	76.20	73.66	10.92	5.84	2.79						
	87914-6024	-----	-----	-----	-----	60	----	4	76.20	73.66	12.25	7.00	2.96						
	87914-6015	-----	-----	-----	-----	60	----	5	76.20	73.66	10.92	5.84	2.79						
	87914-6025	-----	-----	-----	-----	60	----	5	76.20	73.66	12.25	7.00	2.96						
D	87914-6016	-----	-----	-----	-----	60	----	6	76.20	73.66	10.92	5.84	2.79						
	87914-6026	-----	-----	-----	-----	60	----	6	76.20	73.66	12.25	7.00	2.96						
C																			
B																			
A	SHT 7, +879140847 EC NO: SZ014-0048 DRWN:ATSEE 2013/07/11 CHKD:SKANG 2013/07/11 APPR:MLONG 2013/10/09 DESCRIPTION REV							QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION				
								F=0 F=0 F=0			MM ONLY	NTS	METRIC	2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H molex					
									4 PLACES	± ---	± ---	DRAWN BY	DATE			TITLE			
									3 PLACES	± ---	± ---	CHECKED BY	DATE						
									2 PLACES	± 0.20	± ---	PTL IM	2004/12/08						
									1 PLACE	± ---	± ---	APPROVED BY	DATE						
								0 PLACE	±	±	MLONG	2010/09/06							
								ANGULAR ± 3 °		MATERIAL NO.	DOCUMENT NO.								
								DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE TABLE		SD-87914-013		SHEET NO.					
								SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									
D14																			

fb_frame_A3_P_AM_T

Rev. G 2012/01/11

9	8	7	6	5	4	3	2	1
---	---	---	---	---	---	---	---	---

	10		9		8		7		6		5		4		3		2		1	
	PART NO FOR BULK PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION											
									A	B	F	M	P							
F	87914-6211	-----	-----	-----	-----	62	-----	1	78.74	76.20	10.92	5.84	2.79							
	87914-6221	-----	-----	-----	-----	62	-----	1	78.74	76.20	12.25	7.00	2.96							
	87914-6212	-----	-----	-----	-----	62	-----	2	78.74	76.20	10.92	5.84	2.79							
	87914-6222	-----	-----	-----	-----	62	-----	2	78.74	76.20	12.25	7.00	2.96							
	87914-6213	-----	-----	-----	-----	62	-----	3	78.74	76.20	10.92	5.84	2.79							
	87914-6223	-----	-----	-----	-----	62	-----	3	78.74	76.20	12.25	7.00	2.96							
E	87914-6214	-----	-----	-----	-----	62	-----	4	78.74	76.20	10.92	5.84	2.79							
	87914-6224	-----	-----	-----	-----	62	-----	4	78.74	76.20	12.25	7.00	2.96							
	87914-6215	-----	-----	-----	-----	62	-----	5	78.74	76.20	10.92	5.84	2.79							
	87914-6225	-----	-----	-----	-----	62	-----	5	78.74	76.20	12.25	7.00	2.96							
	87914-6216	-----	-----	-----	-----	62	-----	6	78.74	76.20	10.92	5.84	2.79							
	87914-6226	-----	-----	-----	-----	62	-----	6	78.74	76.20	12.25	7.00	2.96							
D																				
C																				
B																				
A	SHT 7, +879140847 EC NO: SZ014-0048 DRWN:ATSEE 2013/07/11 CHKD:SKANG 2013/07/11 APPR:MLONG 2013/10/09		DESCRIPTION REV	QUALITY SYMBOLS F=0 F=0 F=0	GENERAL TOLERANCES (UNLESS SPECIFIED) mm INCH 4 PLACES ± --- ± --- 3 PLACES ± --- ± --- 2 PLACES ± 0.20 ± --- 1 PLACE ± --- ± --- 0 PLACE ± ± ANGULAR ± 3 °		DIMENSION STYLE MM ONLY DRAWN BY DATE KCHO 2004/11/05 CHECKED BY DATE PTL IM 2004/12/08 APPROVED BY DATE MLONG 2010/09/06 MATERIAL NO.	SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION 2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H molex		DOCUMENT NO. SD-87914-013		SHEET NO. 36 OF 45						
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																
	fb_frame_A3_P_AM_T Rev. G 2012/01/11		9	8	7	6	5	4	3	2	1									

	10		9		8		7		6		5		4		3		2		1				
	PART NO FOR BULK PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION														
									A	B	F	M	P										
F	87914-6411	-----	-----	-----	-----	64	----	1	81.28	78.74	10.92	5.84	2.79								F		
	87914-6421	-----	-----	-----	-----	64	----	1	81.28	78.74	12.25	7.00	2.96										
	87914-6412	-----	-----	-----	-----	64	----	2	81.28	78.74	10.92	5.84	2.79										
	87914-6422	-----	-----	-----	-----	64	----	2	81.28	78.74	12.25	7.00	2.96										
	87914-6413	-----	-----	-----	-----	64	----	3	81.28	78.74	10.92	5.84	2.79										
	87914-6423	-----	-----	-----	-----	64	----	3	81.28	78.74	12.25	7.00	2.96										
E	87914-6414	-----	-----	-----	-----	64	----	4	81.28	78.74	10.92	5.84	2.79								E		
	87914-6424	-----	-----	-----	-----	64	----	4	81.28	78.74	12.25	7.00	2.96										
	87914-6415	-----	-----	-----	-----	64	----	5	81.28	78.74	10.92	5.84	2.79										
	87914-6425	-----	-----	-----	-----	64	----	5	81.28	78.74	12.25	7.00	2.96										
	87914-6416	-----	-----	-----	-----	64	----	6	81.28	78.74	10.92	5.84	2.79										
	87914-6426	-----	-----	-----	-----	64	----	6	81.28	78.74	12.25	7.00	2.96										
D																					D		
C																					C		
B																					B		
A	SHT 7, +879140847 EC NO: SZ014-0048 DRWN:ATSE 2013/07/11 CHKD:SKANG 2013/07/11 APPR:MLONG 2013/10/09								QUALITY SYMBOLS =0 =0 =0	GENERAL TOLERANCES (UNLESS SPECIFIED) mm INCH 4 PLACES ± --- ± --- 3 PLACES ± --- ± --- 2 PLACES ± 0.20 ± --- 1 PLACE ± --- ± --- 0 PLACE ± ±		DIMENSION STYLE MM ONLY DRAWN BY KCHO DATE 2004/11/05 CHECKED BY PTL IM DATE 2004/12/08 APPROVED BY MLONG DATE 2010/09/06		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H molex		DOCUMENT NO. SD-87914-013		SHEET NO. 37 OF 45	
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																			
	D14		REV																				

fb_frame_A3_P_AM_T
Rev. G 2012/01/11

9

8

7

6

5

4

3

2

1

	10		9		8		7		6		5		4		3		2		1				
	PART NO FOR BULK PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION														
									A	B	F	M	P										
F	87914-6611	-----	-----	-----	-----	66	-----	1	83.82	81.28	10.92	5.84	2.79										
	87914-6621	-----	-----	-----	-----	66	-----	1	83.82	81.28	12.25	7.00	2.96										
	87914-6612	-----	-----	-----	-----	66	-----	2	83.82	81.28	10.92	5.84	2.79										
	87914-6622	-----	-----	-----	-----	66	-----	2	83.82	81.28	12.25	7.00	2.96										
	87914-6613	-----	-----	-----	-----	66	-----	3	83.82	81.28	10.92	5.84	2.79										
	87914-6623	-----	-----	-----	-----	66	-----	3	83.82	81.28	12.25	7.00	2.96										
E	87914-6614	-----	-----	-----	-----	66	-----	4	83.82	81.28	10.92	5.84	2.79										
	87914-6624	-----	-----	-----	-----	66	-----	4	83.82	81.28	12.25	7.00	2.96										
	87914-6615	-----	-----	-----	-----	66	-----	5	83.82	81.28	10.92	5.84	2.79										
	87914-6625	-----	-----	-----	-----	66	-----	5	83.82	81.28	12.25	7.00	2.96										
	87914-6616	-----	-----	-----	-----	66	-----	6	83.82	81.28	10.92	5.84	2.79										
	87914-6626	-----	-----	-----	-----	66	-----	6	83.82	81.28	12.25	7.00	2.96										
D																							
C																							
B																							
A	SHT 7, +879140847 EC NO: SZ014-0048 DRWN:ATSE CHKD:SKANG APPR:MLONG 2013/07/11 2013/07/11 2013/10/09 DESCRIPTION REV								QUALITY SYMBOLS		GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE		SCALE		DESIGN UNITS		THIRD ANGLE PROJECTION		2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H molex SD-87914-013 SHEET NO. 38 OF 45	
									F F F =0 =0 =0	4 PLACES	± ---	± ---	mm	INCH	DRAWN BY		DATE		TITLE				
										3 PLACES	± ---	± ---			KCHO	2004/11/05							
										2 PLACES	± 0.20	± ---			CHECKED BY	DATE							
										1 PLACE	± ---	± ---			PTL IM	2004/12/08							
										0 PLACE	±	±			APPROVED BY	DATE							
									ANGULAR ± 3 °			MATERIAL NO.		DOCUMENT NO.									
									DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SEE TABLE		SD-87914-013									
									SIZE A3			THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION											

fb_frame_A3_P_AM_T

Rev. G 2012/01/11

	9		8		7		6		5		4		3		2		1		
--	---	--	---	--	---	--	---	--	---	--	---	--	---	--	---	--	---	--	--

10		9		8		7		6		5		4		3		2		1										
PART NO FOR BULK PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION																				
								A	B	F	M	P																
F	87914-6811	-----	-----	-----	-----	68	----	1	86.36	83.82	10.92	5.84	2.79															
	87914-6821	-----	-----	-----	-----	68	----	1	86.36	83.82	12.25	7.00	2.96															
	87914-6812	-----	-----	-----	-----	68	----	2	86.36	83.82	10.92	5.84	2.79															
	87914-6822	-----	-----	-----	-----	68	----	2	86.36	83.82	12.25	7.00	2.96															
	87914-6813	-----	-----	-----	-----	68	----	3	86.36	83.82	10.92	5.84	2.79															
	87914-6823	-----	-----	-----	-----	68	----	3	86.36	83.82	12.25	7.00	2.96															
E	87914-6814	-----	-----	-----	-----	68	----	4	86.36	83.82	10.92	5.84	2.79															
	87914-6824	-----	-----	-----	-----	68	----	4	86.36	83.82	12.25	7.00	2.96															
	87914-6815	-----	-----	-----	-----	68	----	5	86.36	83.82	10.92	5.84	2.79															
	87914-6825	-----	-----	-----	-----	68	----	5	86.36	83.82	12.25	7.00	2.96															
	87914-6816	-----	-----	-----	-----	68	----	6	86.36	83.82	10.92	5.84	2.79															
	87914-6826	-----	-----	-----	-----	68	----	6	86.36	83.82	12.25	7.00	2.96															
D																												
C																												
B																												
A	SHT 7, +879140847		EC NO: S2014-0048		2013/07/11		2013/07/11		2013/10/09		QUALITY SYMBOLS		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE		DESIGN UNITS		THIRD ANGLE PROJECTION							
	DRWN:ATSE		CHKD:SKANG		APPR:MLONG		REV		DESCRIPTION		F=0		F=0		F=0		mm		INCH		DRAWN BY		DATE		TITLE			
	D14										4 PLACES		± ---		± ---		KCHO		2004/11/05		2.54MM PITCH		DUAL ROW HEADER		SINGLE WAFER, T/H			
											3 PLACES		± ---		± ---		PTL IM		2004/12/08									
											2 PLACES		± 0.20		± ---		APPROVED BY		DATE									
											1 PLACE		± ---		± ---		MLONG		2010/09/06									
											0 PLACE		±		±		MATERIAL NO.		DOCUMENT NO.						SHEET NO.			
													ANGULAR ± 3 °				SEE TABLE		SD-87914-013						39 OF 45			
													DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE		A3										THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION	

fb_frame_A3_P_AM_T Rev. G 2012/01/11

987654321

	10		9		8		7		6		5		4		3		2		1
F	PART NO FOR BULK PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION					F					
	A	B	F	M	P														
	87914-7011	-----	-----	-----	-----	70	-----	1	88.90	86.36	10.92	5.84	2.79						
	87914-7021	-----	-----	-----	-----	70	-----	1	88.90	86.36	12.25	7.00	2.96						
	87914-7012	-----	-----	-----	-----	70	-----	2	88.90	86.36	10.92	5.84	2.79						
	87914-7022	-----	-----	-----	-----	70	-----	2	88.90	86.36	12.25	7.00	2.96						
	87914-7013	-----	-----	-----	-----	70	-----	3	88.90	86.36	10.92	5.84	2.79						
	87914-7023	-----	-----	-----	-----	70	-----	3	88.90	86.36	12.25	7.00	2.96						
E	87914-7014	-----	-----	-----	-----	70	-----	4	88.90	86.36	10.92	5.84	2.79	E					
	87914-7024	-----	-----	-----	-----	70	-----	4	88.90	86.36	12.25	7.00	2.96						
	87914-7015	-----	-----	-----	-----	70	-----	5	88.90	86.36	10.92	5.84	2.79						
	87914-7025	-----	-----	-----	-----	70	-----	5	88.90	86.36	12.25	7.00	2.96						
	87914-7016	-----	-----	-----	-----	70	-----	6	88.90	86.36	10.92	5.84	2.79						
	87914-7026	-----	-----	-----	-----	70	-----	6	88.90	86.36	12.25	7.00	2.96						
D														D					

[illegible]

10		9		8		7		6		5		4		3		2		1	
PART NO FOR BULK PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION											
								A	B	F	M	P							
F	87914-7411	-----	-----	-----	-----	74	-----	1	93.98	91.44	10.92	5.84	2.79						
	87914-7421	-----	-----	-----	-----	74	-----	1	93.98	91.44	12.25	7.00	2.96						
	87914-7412	-----	-----	-----	-----	74	-----	2	93.98	91.44	10.92	5.84	2.79						
	87914-7422	-----	-----	-----	-----	74	-----	2	93.98	91.44	12.25	7.00	2.96						
	87914-7413	-----	-----	-----	-----	74	-----	3	93.98	91.44	10.92	5.84	2.79						
E	87914-7423	-----	-----	-----	-----	74	-----	3	93.98	91.44	12.25	7.00	2.96						
	87914-7414	-----	-----	-----	-----	74	-----	4	93.98	91.44	10.92	5.84	2.79						
	87914-7424	-----	-----	-----	-----	74	-----	4	93.98	91.44	12.25	7.00	2.96						
	87914-7415	-----	-----	-----	-----	74	-----	5	93.98	91.44	10.92	5.84	2.79						
	87914-7425	-----	-----	-----	-----	74	-----	5	93.98	91.44	12.25	7.00	2.96						
D	87914-7416	-----	-----	-----	-----	74	-----	6	93.98	91.44	10.92	5.84	2.79						
	87914-7426	-----	-----	-----	-----	74	-----	6	93.98	91.44	12.25	7.00	2.96						
C																			
B																			
A																			
fb_frame_A3_P_AM_T Rev. G 2012/01/11		9	8	7	6	5	4	3	2	1									

SHT 7, +879140847 EC NO: SZ014-0048 DRWN:ATSEE 2013/07/11 CHKD:SKANG 2013/07/11 APPR:MLONG 2013/10/09	DESCRIPTION REV	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION	
		=0 =0 =0			DRAWN BY KCHO	DATE 2004/11/05	2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H molex			
			4 PLACES	± ---	± ---	CHECKED BY PTL IM			DATE 2004/12/08	
			3 PLACES	± ---	± ---	APPROVED BY MLONG			DATE 2010/09/06	
			2 PLACES	± 0.20	± ---					
1 PLACE	± ---	± ---								
0 PLACE	±	±								
ANGULAR ± 3 °			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				

SEE TABLE		SD-87914-013		SHEET NO. 42 OF 45	
-----------	--	--------------	--	-----------------------	--

[illegible]

	10		9		8		7		6		5		4		3		2		1	
F	PART NO FOR BULK PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION											
									A	B	F	M	P							
	87914-7811	-----	-----	-----	-----	78	-----	1	99.06	96.52	10.92	5.84	2.79							
	87914-7821	-----	-----	-----	-----	78	-----	1	99.06	96.52	12.25	7.00	2.96							
	87914-7812	-----	-----	-----	-----	78	-----	2	99.06	96.52	10.92	5.84	2.79							
	87914-7822	-----	-----	-----	-----	78	-----	2	99.06	96.52	12.25	7.00	2.96							
	87914-7813	-----	-----	-----	-----	78	-----	3	99.06	96.52	10.92	5.84	2.79							
	87914-7823	-----	-----	-----	-----	78	-----	3	99.06	96.52	12.25	7.00	2.96							
E	87914-7814	-----	-----	-----	-----	78	-----	4	99.06	96.52	10.92	5.84	2.79							
	87914-7824	-----	-----	-----	-----	78	-----	4	99.06	96.52	12.25	7.00	2.96							
	87914-7815	-----	-----	-----	-----	78	-----	5	99.06	96.52	10.92	5.84	2.79							
	87914-7825	-----	-----	-----	-----	78	-----	5	99.06	96.52	12.25	7.00	2.96							
	87914-7816	-----	-----	-----	-----	78	-----	6	99.06	96.52	10.92	5.84	2.79							
	87914-7826	-----	-----	-----	-----	78	-----	6	99.06	96.52	12.25	7.00	2.96							
D																				
C																				
B																				
A					SHT 7, +879140847 EC NO: SZ014-0048 DRWN:ATSEE 2013/07/11 CHKD:SKANG 2013/07/11 APPR:MLONG 2013/10/09	REV D14	DESCRIPTION QUALITY SYMBOLS F=0 F=0 F=0	GENERAL TOLERANCES (UNLESS SPECIFIED) mm INCH 4 PLACES ± --- ± --- 3 PLACES ± --- ± --- 2 PLACES ± 0.20 ± --- 1 PLACE ± --- ± --- 0 PLACE ± ± ANGULAR ± 3 ° DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	DIMENSION STYLE MM ONLY DRAWN BY DATE KCHO 2004/11/05 CHECKED BY DATE PTL IM 2004/12/08 APPROVED BY DATE MLONG 2010/09/06 MATERIAL NO. SEE TABLE	SCALE NTS TITLE 2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H molex DOCUMENT NO. SD-87914-013	DESIGN UNITS METRIC THIRD ANGLE PROJECTION SHEET NO. 44 OF 45				A					
fb_frame_A3_P_AM_T Rev. G 2012/01/11		9	8	7	6	5	4	3	2	1										

	10		9		8		7		6		5		4		3		2		1	
	PART NO FOR BULK PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSIONS											
									A	B	F	M	P							
F	87914-8011	-----	-----	-----	-----	80	----	1	101.60	99.06	10.92	5.84	2.79							
	87914-8021	-----	-----	-----	-----	80	----	1	101.60	99.06	12.25	7.00	2.96							
	87914-8012	-----	-----	-----	-----	80	----	2	101.60	99.06	10.92	5.84	2.79							
	87914-8022	-----	-----	-----	-----	80	----	2	101.60	99.06	12.25	7.00	2.96							
	87914-8013	-----	-----	-----	-----	80	----	3	101.60	99.06	10.92	5.84	2.79							
	87914-8023	-----	-----	-----	-----	80	----	3	101.60	99.06	12.25	7.00	2.96							
E	87914-8014	-----	-----	-----	-----	80	----	4	101.60	99.06	10.92	5.84	2.79							
	87914-8024	-----	-----	-----	-----	80	----	4	101.60	99.06	12.25	7.00	2.96							
	87914-8015	-----	-----	-----	-----	80	----	5	101.60	99.06	10.92	5.84	2.79							
	87914-8025	-----	-----	-----	-----	80	----	5	101.60	99.06	12.25	7.00	2.96							
	87914-8016	-----	-----	-----	-----	80	----	6	101.60	99.06	10.92	5.84	2.79							
	87914-8026	-----	-----	-----	-----	80	----	6	101.60	99.06	12.25	7.00	2.96							
D																				
C																				
B																				
A	SHT 7, +879140847 EC NO: S2014-0048 DRWN:ATSEE 2013/07/11 CHKD:SKANG 2013/07/11 APPR:MLONG 2013/10/09							QUALITY SYMBOLS =0 =0 =0	GENERAL TOLERANCES (UNLESS SPECIFIED) mm INCH 4 PLACES ± --- 3 PLACES ± --- 2 PLACES ± 0.20 1 PLACE ± --- 0 PLACE ± ANGULAR ± 3 ° DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			DIMENSION STYLE MM ONLY DRAWN BY DATE KCHO2004/11/05 CHECKED BY DATE PTL IM2004/12/08 APPROVED BY DATE MLONG2010/09/06		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION 2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H molex		SHEET NO. 45 OF 45		
	D14								SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION										
	fb_frame_A3_P_AM_T Rev. G 2012/01/11		9	8	7	6	5		4	3	2	1								