


Polyester Film Capacitor

Type: **ECQM**

Designed for application where high density insertion of components is required.



■ Features

- ◆ Non-inductive construction
- ◆ Excellent moisture resistance


■ Recommended Applications

- ◆ General purpose usage
- ◆ Noise suppression for lighting products

■ Explanation of Part Numbers

1	2	3	4	5	6	7	8	9	10	11	12
E	C	Q	M							Z	
Product code		Dielectric & construction		Rated voltage		Capacitance		Cap. Tol.		Suffix	Suffix
125VAC 400VDC 600VDC				±5% ±10% ^{+65%} 0%							
1A 4 6				J K Z							

■Dimensions in mm(not to scale)




■Packaging Specifications for Bulk Package

Packing quantity : 100pcs./bag

■Taping Specifications for Automatic Insertion

●Taping style



●Packaging Specifications

Type	Rated volt.	Cap.range (μF)	Taping style						Packing
			AD	AS	B	C	D	E	
ECQM	400VDC	0.001 to 0.0039	O						Ammo
		0.0047 to 0.01			O				Ammo
		0.0027 to 0.01					O		Ammo
		0.012 to 0.068						O	Ammo
	600VDC	0.001 to 0.0015	O						Ammo
		0.0022				O			Ammo
		0.0068 to 0.022						O	Ammo

●Lead Spacing

Style	Lead Spacing
AD	5.0mm
B	5.0mm
C	5.0mm
D	7.5mm
E	7.5mm

* See the column "Rating, Dimensions & Quantity Box" for packing quantity.

■ Rating, Dimensions & Quantity/Ammo Box

● Rated voltage : 400VDC Capacitance tolerance : $\pm 5\%$ (J), $\pm 10\%$ (K)

Part No.	Cap. (μ F)	Dimensions (mm)								Quantity
		L _{max.}	T _{max.}	H _{max.}		F	S	G _{max.}	ϕ d	Ammo
				Type-1	Type-2 ₃					
ECQM4102□Z()	0.001	11.0	5.5	9.5	14.5	6.50	5.0	2	0.60	1000
ECQM4122□Z()	0.0012	11.0	6.0	10.0	15.0	6.50	5.0	2	0.60	
ECQM4152□Z()	0.0015	11.0	6.0	10.0	15.0	6.50	5.0	2	0.60	
ECQM4182□Z()	0.0018	11.0	6.0	10.0	15.0	6.50	5.0	2	0.60	
ECQM4222□Z()	0.0022	11.0	6.5	10.5	15.5	6.50	5.0	2	0.60	
ECQM4272□Z()	0.0027	12.0	6.0	10.0	15.0	7.50	5.0	2	0.60	
ECQM4332□Z()	0.0033	12.0	6.5	10.5	15.0	7.50	5.0	2	0.60	500
ECQM4392□Z()	0.0039	12.0	6.5	10.5	15.0	7.50	5.0	2	0.60	
ECQM4472□Z()	0.0047	14.0	6.0	10.0	15.0	9.50	5.0	2	0.60	
ECQM4562□Z()	0.0056	14.0	6.0	10.0	15.0	9.50	5.0	2	0.60	
ECQM4682□Z()	0.0068	14.0	6.5	10.5	15.5	9.50	5.0	3	0.60	
ECQM4822□Z()	0.0082	14.0	6.5	12.0	17.0	9.50	5.0	3	0.60	
ECQM4103□Z()	0.01	14.0	7.0	12.5	17.5	9.50	5.0	3	0.60	
ECQM4123□Z()	0.012	17.0	6.0	12.0	17.0	12.50	7.5	3	0.60	
ECQM4153□Z()	0.015	17.0	6.5	12.5	17.5	12.50	7.5	3	0.60	
ECQM4183□Z()	0.018	17.0	7.0	13.0	18.0	12.50	7.5	3	0.60	
ECQM4223□Z()	0.022	17.0	7.5	13.5	18.5	12.50	7.5	3	0.60	400
ECQM4273□Z()	0.027	20.0	7.0	14.5	19.5	15.00	10.0	3	0.70	
ECQM4333□Z()	0.033	20.0	7.5	15.0	20.0	15.00	10.0	3	0.70	
ECQM4393□Z()	0.039	20.0	8.5	16.0	21.0	15.00	10.0	3	0.70	
ECQM4473□Z()	0.047	20.0	9.0	16.5	21.5	15.00	10.0	3	0.70	
ECQM4563□Z()	0.056	23.0	8.5	15.5	20.5	18.00	12.5	3	0.70	
ECQM4683□Z()	0.068	23.0	9.0	16.5	21.5	18.00	12.5	3	0.70	—
ECQM4823□Z()	0.082	24.0	9.5	17.0	22.0	18.00	12.5	3	0.80	
ECQM4104□Z()	0.1	24.0	10.0	19.0	24.0	18.00	12.5	3	0.80	
ECQM4124□Z()	0.12	24.0	11.0	20.0	25.0	18.50	12.5	3	0.80	
ECQM4154□Z()	0.15	24.0	12.5	21.0	26.0	18.50	12.5	3	0.80	
ECQM4184□Z()	0.18	28.0	12.5	21.5	26.5	23.50	15.0	3	0.80	
ECQM4224□Z()	0.22	28.0	14.0	23.0	28.0	23.50	15.0	3	0.80	
ECQM4274□Z()	0.27	28.0	15.5	24.5	29.5	23.50	15.0	3	0.80	
ECQM4334□Z()	0.33	28.0	17.5	26.5	31.5	23.50	15.0	3	0.80	
ECQM4394□Z()	0.39	34.0	16.0	26.5	31.5	28.50	17.5	3	0.80	
ECQM4474□Z()	0.47	34.0	17.5	28.0	33.0	28.50	17.5	3	0.80	


 Suffix for lead crimped or taped type


 Cap. tol. code

 StyleD:0.001 to 0.0039 μ F
 StyleB:0.0047 to 0.47 μ F
 StyleN:0.001 to 0.0022 μ F
 StyleT:0.0027 to 0.47 μ F

■ Rating, Dimensions & Quantity/Ammo Box

● Rated voltage : 600VDC Capacitance tolerance : $\pm 5\%$ (J), $\pm 10\%$ (K)

Part No.	Cap. (μF)	Dimensions (mm)								Quantity
		L ^{max.}	T ^{max.}	H ^{max.}		F±1.25	S±0.8	G ^{max.}	∅d	Ammo
				Type-1	Type-2 ₃	Type-1	Type-2 ₃	Type-1	±0.05	
ECQM6102□Z()	0.001	13.0	7.0	11.0	15.0	7.50	7.5	3	0.60	1000
ECQM6122□Z()	0.0012	13.0	7.5	11.0	15.0	7.50	7.5	3	0.60	
ECQM6152□Z()	0.0015	13.0	7.5	11.0	15.0	7.50	7.5	3	0.60	
ECQM6182□Z()	0.0018	15.0	7.0	11.0	15.0	9.50	10.0	3	0.60	—
ECQM6222□Z()	0.0022	15.0	7.0	11.0	15.0	9.50	10.0	3	0.60	500
ECQM6272□Z()	0.0027	15.0	7.5	11.0	15.0	9.50	10.0	3	0.60	
ECQM6332□Z()	0.0033	15.0	7.5	11.0	15.0	9.50	10.0	3	0.60	
ECQM6392□Z()	0.0039	15.0	7.5	13.0	17.0	9.50	10.0	3	0.60	—
ECQM6472□Z()	0.0047	15.0	7.5	13.0	17.0	9.50	10.0	3	0.60	
ECQM6562□Z()	0.0056	15.0	8.5	14.0	18.0	9.50	10.0	3	0.60	
ECQM6682□Z()	0.0068	15.0	8.5	14.0	18.0	9.50	10.0	3	0.60	400
ECQM6822□Z()	0.0082	20.0	7.0	14.0	18.0	14.50	10.0	3	0.60	
ECQM6103□Z()	0.01	20.0	7.0	14.0	18.0	14.50	10.0	3	0.60	
ECQM6123□Z()	0.012	20.0	8.0	15.0	19.0	14.50	10.0	3	0.60	300
ECQM6153□Z()	0.015	20.0	8.0	15.0	19.0	14.50	10.0	3	0.60	
ECQM6183□Z()	0.018	20.0	9.5	16.0	20.0	14.50	10.0	3	0.60	
ECQM6223□Z()	0.022	20.0	9.5	16.0	20.0	14.50	10.0	3	0.60	—
ECQM6273□Z()	0.027	25.5	9.0	16.0	21.0	19.50	12.5	4	0.70	
ECQM6333□Z()	0.033	25.5	9.0	16.0	21.0	19.50	12.5	4	0.70	
ECQM6393□Z()	0.039	25.5	10.5	17.0	22.0	19.50	12.5	4	0.70	—
ECQM6473□Z()	0.047	25.5	10.5	17.0	22.0	19.50	12.5	4	0.70	
ECQM6563□Z()	0.056	25.5	13.5	20.0	25.0	19.50	12.5	4	0.70	
ECQM6683□Z()	0.068	25.5	13.5	20.0	25.0	19.50	12.5	4	0.70	—
ECQM6823□Z()	0.082	25.5	13.5	23.0	28.0	19.50	12.5	4	0.80	
ECQM6104□Z()	0.1	25.5	13.5	23.0	28.0	19.50	12.5	4	0.80	
ECQM6124□Z()	0.12	37.0	11.0	23.0	28.0	30.50	20.0	4	0.80	—
ECQM6154□Z()	0.15	37.0	11.0	23.0	28.0	30.50	20.0	4	0.80	
ECQM6184□Z()	0.18	37.0	13.5	25.0	30.0	30.50	20.0	4	0.80	
ECQM6224□Z()	0.22	37.0	13.5	25.0	30.0	30.50	20.0	4	0.80	—

↑
Suffix for lead crimped or taped type

—
Cap. tol. code

StyleD:0.001 to 0.0068 μ F
 StyleB:0.0082 to 0.22 μ F
 StyleN:0.001 to 0.0068 μ F
 StyleT:0.0082 to 0.22 μ F

● Rated voltage:125VAC, Capacitance tolerance : $\pm 65\%$ (Z)

Noise suppression capacitor for glow switch

Part No.	Cap. (μ F)	Dimensions (mm)			
		L _{max.}	T _{max.}	H _{max.}	G _{max.}
ECQM1A602ZS	0.006	17.5	6.5	11.5	6.0

● This capacitor is used for glow noise suppression for lighting products.

Consult us for further requirements as we have wide variety of products other than mentioned here according to type of glow, installation method etc.