



UNCONTROLLED
DOCUMENT



IMPEDANCE (Z)			
Frequency	25 MHz	100 MHz	300 MHz
Nominal (REF)	115 Ω	250 Ω	520 Ω
Minimum	- Ω	200 Ω	- Ω




FREQUENCY (MHz)
AGILENT E4991A Impedance/Material Analyzer
HP 16092A-Test Fixture

FERRITE CORE DIMENSIONS (SPEC): mm [in]

A	38.10 [1.500]	+ 0.76 [.030]
B	26.67 [1.050]	+ 0.76 [.030]
C	25.40 [1.000]	+ 0.51 [.020]
D	6.35 [.250]	+ 0.25 [.010]
E	0.84 [.033]	+ 0.25 [.010]
F	7.62 [.300]	+ 0.25 [.010]

WEIGHT/1000 30.56 kgs. 67.38 Lbs.

- NOTES:
1. ADD METAL CLIPS FOR SHIPPING P/N ASSE017-2.



DIMENSIONS ARE IN mm[INCHES].				THIS DOCUMENT CONTAINS INFORMATION WHICH IS PROPRIETARY AND CONFIDENTIAL TO STEWARD. NO PRODUCTION OR PUBLICATION OF THIS DOCUMENT IN WHOLE OR IN PART SHALL BE MADE WITHOUT WRITTEN AUTHORIZATION FROM STEWARD.			
				Steward			
D	UPDATE FORMAT & Z SPECS ADD CURVE CHANGE TOLS ON F DIMENSION	07/15/03	JRK	PROJECT/PART NUMBER:	REV	PART TYPE:	DRAWN BY:
C	UPDATE P/N FOR NEW CATALOG	7/27/95	JBE	28S2023-0M0	D	FERRITE SPLIT RIBBON	DJB
B	UPDATE	11/02/94	JBE	DATE:	SCALE:	MATERIAL:	
A	ORIGINAL DRAFT	12/17/90	DJB	12/17/90	2 : 1		
REV	DESCRIPTION	DATE	INT	CAD #	TOOL #		
				28S2023-0M0-D	S2023	STEWARD	28