

**Product number FA11212_TINA-RS**

Family	Tina	FWHM	10 degrees
Type	Assembly	Efficiency	93 %
LED	LUXEON Rebel	cd/Im	16.900
Color	Black	Gerber File	Available
Diameter	16.1 mm		
Height	9.4 mm		
Style	Round		
Optic Material	PMMA		
Holder Material	PC		
Fastening	Pin, tape		
Status	On production		

**Product number FA11209_TINA-D**

Family	Tina	FWHM	15 degrees
Type	Assembly	Efficiency	92 %
LED	LUXEON Rebel	cd/Im	5.470
Color	Black	Gerber File	Available
Diameter	16.1 mm		
Height	9.4 mm		
Style	Round		
Optic Material	PMMA		
Holder Material	PC		
Fastening	Pin, tape		
Status	On production		

**Product number FA11210_TINA-M**

Family	Tina	FWHM	28 degrees
Type	Assembly	Efficiency	83 %
LED	LUXEON Rebel	cd/Im	1.760
Color	Black	Gerber File	Available
Diameter	16.1 mm		
Height	9.4 mm		
Style	Round		
Optic Material	PMMA		
Holder Material	PC		
Fastening	Pin, tape		
Status	On production		

**Product number FA11203_TINA-O**

Family	Tina	FWHM	34+18 degrees
Type	Assembly	Efficiency	89 %
LED	LUXEON Rebel	cd/Im	2.300
Color	Black	Gerber File	Available
Diameter	16.1 mm		
Height	9.4 mm		
Style	Round		
Optic Material	PMMA		
Holder Material	PC		
Fastening	Pin, tape		
Status	On production		

**Product number** FA11211_TINA-W

Family	Tina	FWHM	44 degrees
Type	Assembly	Efficiency	88 %
LED	LUXEON Rebel	cd/Im	1.620
Color	Black	Gerber File	Available
Diameter	16.1 mm		
Height	9.4 mm		
Style	Round		
Optic Material	PMMA		
Holder Material	PC		
Fastening	Pin, tape		
Status	On production		

NOTE: The typical divergence will be changed by different color, chip size and chip position tolerance. The typical total divergence is the full angle measured where the luminous intensity is half of the peak value.



PRODUCT DATASHEET

Tina series

last update 10/10/2013

GENERAL INFORMATION

- Product series especially designed & optimized for LUXEON Rebel series of LEDs.
- Special care taken to make light distribution as uniform as possible.
- Lens material optical grade PMMA with high UV and temperature resistance. Allows use of high current and temperature conditions.


Please find more information about used material from below:

http://ledil.fi/sites/default/files/Documents/Technical/Material/PMMA%20N%20UL94_Yellow%20Card.pdf

<http://ledil.fi/sites/default/files/Documents/Technical/Material/PMMA%20N%20PLEXIGLAS-Datasheet.pdf>

- Optic holder molded by high quality PC material (120 degrees of Celcius / 248 degrees of Fahrenheit).

Relative Intensity of FA11211_Tina-RE-W



4

3

2



1

D



C

B

A



Isometric view



Materials
Lens: PMMA
Holder: PC
Tape: PU Foam

This drawing is our property.
It can't be reproduced
or communicated without
our written agreement.

LEDiL

Ledil Oy
Salorankatu 10
FIN 24240 SALO
Finland

DRAWING TITLE

Mechanical Drawing

DRAWN BY

DATE

as

10.9.2012

TINA-RE

CHECKED BY

DATE

sn

-

SIZE

PART NUMBER

REV

A4

TINA-RE

001

DESIGNED BY

DATE

-

-

SCALE

2:1

WEIGHT

1,46 g

SHEET

1/1

D

A

4

3

2

1