

FEATURES

- 50V Operation
- *Guaranteed* 1% Initial Voltage Tolerance
- *Guaranteed* 0.01%/V Line Regulation
- *Guaranteed* 0.5% Load Regulation
- *Guaranteed* 0.02%/W Thermal Regulation
- 100% Burn-in in Thermal Limit

APPLICATIONS


- Adjustable Power Supplies
- System Power Supplies
- Precision Voltage/Current Regulators
- On-Card Regulators

The LT137AHV/LM137HV negative high voltage adjustable regulators will deliver up to 1.5 Amps output current over an output voltage range of -1.2V to -47V . Linear Technology has made significant improvements in these regulators compared to previous devices, such as better line and load regulation, and a maximum output voltage error of 1% for the LT137AHV and LT337AHV.


Every effort has been made to make these devices easy to use and difficult to damage. Internal current and power limiting coupled with true thermal limiting prevents device damage due to overloads or shorts, even if the regulator is not fastened to a heat sink.

Maximum reliability is attained with Linear Technology's advanced processing techniques combined with a 100% burn-in in the thermal limit mode. This assures that all device protection circuits are working and eliminates field failures experienced with other regulators that receive only standard electrical testing. For performance curves and applications circuits see the LT137A series data sheet.

Negative Regulator



Worst Case Output Voltage Error @ $T_J = 25^\circ\text{C}$



LT137AHV/LT337AHV LM137HV/LM337HV

ABSOLUTE MAXIMUM RATINGS

Power Dissipation	Internally Limited
Input to Output Voltage Differential	50V
Operating Junction Temperature Range	
LT137AHV/LM137HV	−55°C to 150°C
LT337AHV/LM337HV	0°C to 125°C
Storage Temperature Range	
LT137AHV/LM137HV	−65°C to 150°C
LT337AHV/LM337HV	−65°C to 150°C
Lead Temperature (Soldering, 10 sec.)	300°C

PRECONDITIONING

100% THERMAL LIMIT BURN-IN

PACKAGE/ORDER INFORMATION

BOTTOM VIEW	ORDER PART NO.	BOTTOM VIEW	ORDER PART NO.
	LT137AHVK LT337AHVK LM137HVK LM337HVK		LT137AHVH LT337AHVH LM137HVH LM337HVH

ELECTRICAL CHARACTERISTICS (See Note 1)

SYMBOL	PARAMETER	CONDITIONS	LT137AHV			LM137HV			UNITS
			MIN	TYP	MAX	MIN	TYP	MAX	
V_{REF}	Reference Voltage	$ V_{IN} - V_{OUT} = 5V$, $I_{OUT} = 10mA$, $T_J = 25^\circ C$				−1.225	−1.250	−1.275	V
$\frac{\Delta V_{OUT}}{\Delta I_{OUT}}$	Load Regulation	$3V \leq V_{IN} - V_{OUT} \leq 50V$ $10mA \leq I_{OUT} \leq I_{MAX}$, $P \leq P_{MAX}$ $T_J = 25^\circ C$, $ V_{OUT} \leq 5V$ $ V_{OUT} \geq 5V$				−1.200	−1.250	−1.300	V
$\frac{\Delta V_{OUT}}{\Delta V_{IN}}$	Line Regulation	$10mA \leq I_{OUT} \leq I_{MAX}$, (See Note 2) $T_J = 25^\circ C$, $ V_{OUT} \leq 5V$ $ V_{OUT} \geq 5V$		5	25		15	25	mV
				0.1	0.5		0.3	0.5	%
				10	50		20	50	mV
				0.2	1.0		0.3	1.0	%
$\frac{\Delta V_{OUT}}{\Delta V_{IN}}$	Line Regulation	$3V \leq V_{IN} - V_{OUT} \leq 50V$ (See Note 2) $T_J = 25^\circ C$					0.01	0.02	%/V
							0.02	0.05	%/V
	Ripple Rejection	$V_{OUT} = -10V$, $f = 120Hz$ $C_{ADJ} = 0$ $C_{ADJ} = 10\mu F$				66	60	77	dB
									dB
	Thermal Regulation	$T_J = 25^\circ C$, $T = 2ms$ to $12ms$		0.002	0.02		0.002	0.02	%/W
I_{ADJ}	Adjust Pin Current			65	100		65	100	μA
ΔI_{ADJ}	Adjust Pin Current Change	$10mA \leq I_{OUT} \leq I_{MAX}$ $2.5V \leq V_{IN} - V_{OUT} \leq 50V$		0.2	2		0.5	5	μA
				2	6		3	6	μA
	Minimum Load Current	$ V_{IN} - V_{OUT} \leq 50V$ $ V_{IN} - V_{OUT} \leq 10V$		2.5	5.0		2.5	5.0	mA
				1.2	3.0		1.2	3.0	mA
I_{SC}	Current Limit	$ V_{IN} - V_{OUT} \leq 13V$ K Package H Package $ V_{IN} - V_{OUT} = 50V$ K Package H Package $T_J = 25^\circ C$		1.5	2.2		1.5	2.2	A
				0.5	0.8		0.5	0.8	A
				0.2	0.4		0.2	0.4	A
				0.1	0.17		0.1	0.17	A
$\frac{\Delta V_{OUT}}{\Delta T_{temp}}$	Temperature Stability of Output Voltage (Note 3)	$T_{MIN} \leq T \leq T_{MAX}$		0.6	1.5		0.6		%
$\frac{\Delta V_{OUT}}{\Delta Time}$	Long Term Stability	$T_A = 125^\circ C$, 1000 Hours		0.3	1.0		0.3	1.0	%
e_n	RMS Output Noise (% of V_{OUT})	$T_A = 25^\circ C$, $10Hz \leq f \leq 10kHz$		0.003			0.003		%
θ_{JC}	Thermal Resistance Junction to Case	H Package K Package		12	15		12	15	$^\circ C/W$
				2.3	3.0		2.3	3.0	$^\circ C/W$

ELECTRICAL CHARACTERISTICS (See Note 1)

SYMBOL	PARAMETER	CONDITIONS	LT337AHV			LM337HV			UNITS	
			MIN	TYP	MAX	MIN	TYP	MAX		
V _{REF}	Reference Voltage	V _{IN} - V _{OUT} = 5V, I _{OUT} = 10mA, T _J = 25°C				-1.213	-1.250	-1.287	V	
		3V ≤ V _{IN} - V _{OUT} ≤ 50V 10mA ≤ I _{OUT} ≤ I _{MAX} , P ≤ P _{MAX}	●				-1.200	-1.250	-1.300	V
$\frac{\Delta V_{OUT}}{\Delta I_{OUT}}$	Load Regulation	10mA ≤ I _{OUT} ≤ I _{MAX} (See Note 2)								
		T _J = 25°C, V _{OUT} ≤ 5V		5	25		15	50	mV	
		T _J = 25°C, V _{OUT} ≥ 5V		0.1	0.5		0.3	1.0	%	
		V _{OUT} ≤ 5V	●	10	50		20	70	mV	
		V _{OUT} ≥ 5V	●	0.2	1.0		0.3	1.5	%	
$\frac{\Delta V_{OUT}}{\Delta V_{IN}}$	Line Regulation	3V ≤ V _{IN} - V _{OUT} ≤ 50V (See Note 2) T _J = 25°C	●					0.01 0.02	0.04 0.07	%/V %/V
		Ripple Rejection	●				66	60 77		dB dB
	Thermal Regulation	T _J = 25°C, T = 2ms to 12ms		0.002	0.04		0.003	0.04	%/W	
I _{ADJ}	Adjust Pin Current		●	65	100		65	100	μA	
ΔI _{ADJ}	Adjust Pin Current Change	10mA ≤ I _{OUT} ≤ I _{MAX}	●	0.2	2		2	5	μA	
		2.5V ≤ V _{IN} - V _{OUT} ≤ 50V	●	2	6		3	6	μA	
	Minimum Load Current	V _{IN} - V _{OUT} ≤ 40V	●				2.5	10	mA	
		V _{IN} - V _{OUT} ≤ 10V	●				1	6	mA	
I _{SC}	Current Limit	V _{IN} - V _{OUT} ≤ 13V	●	1.5	2.2	3.5	1.5	2.2	3.5	A
		K Package	●	0.5	0.8	1.8	0.5	0.8	1.8	A
		H Package								
		V _{IN} - V _{OUT} = 50V		0.1	0.4	0.8	0.1	0.4	0.8	A
		K Package		0.05	0.17	0.5	0.05	0.17	0.5	A
		H Package								
$\frac{\Delta V_{OUT}}{\Delta Temp}$	Temperature Stability of Output Voltage (Note 3)		●				0.6		%	
$\frac{\Delta V_{OUT}}{\Delta Time}$	Long Term Stability	T _A = 125°C, 1000 Hours		0.3	1.0		0.3	1.0	%	
e _n	RMS Output Noise (% of V _{OUT})	T _A = 25°C, 10Hz ≤ f ≤ 10kHz		0.003			0.003		%	
θ _{JC}	Thermal Resistance Junction to Case	H Package		12	15		12	15	°C/W	
		K Package		2.3	3.0		2.3	3.0	°C/W	

VOLTAGE REGULATORS

3

The ● denotes the specifications which apply over the full operating temperature range.

The shaded electrical specifications indicate those parameters which have been improved or guaranteed test limits provided for the first time.


Note 1: Unless otherwise indicated, these specifications apply:

$|V_{IN} - V_{OUT}| = 5V$; and $I_{OUT} = 0.1A$ for the H package, $I_{OUT} = 0.5A$ for the K package. Power dissipation is internally limited. However, these specifications apply for power dissipation up to 2W for the H package and 20W for the K package. $I_{MAX} = 1.5A$ for the K package, and 0.2A for the H package.

Note 2: Testing is done using a pulsed low duty cycle technique. See thermal regulation specifications for output changes due to heating effects. Load regulation is measured on the output pin at a point 1/8 inch below the base of the K and H package.

Note 3: Guaranteed on the LT137AHV and LT337AHV, but not 100% tested in production.

SCHEMATIC DIAGRAM

**H Package 3-Lead Metal Can**

	T _J MAX	Θ _{JC}
137AHV 137HV	150°C	15°C/W
337AHV 337HV	125°C	15°C/W