


Type C Vertical Receptacle Assemblies with Solder Posts for PC Board Mount



Material

Housing — Glass filled polymer
Contacts — Copper alloy

Related Product Data

Common Bus Systems

Application — Page 4

DIN Performance Levels — Page 6

Performance Specifications —
Page 7

Mateable Connectors — Pages 17,
18, 19, 28, 52-54

PC Board Hole Layout — Page 58

Accessories — Pages 64, 67, 68


Technical Documents — Page 74:

DIN Specification 41612

IEC Specification 60603-2

Application Specification 114-9014

Instruction Sheet 408-6784




Standard Size

Number of Positions	Rows Loaded	Dimensions				Post Length	DIN Level	Part Number
		A	B	C	D			
96	A,B,C	93.98 3.700	90.00 3.543	78.74 3.100	85.00 3.346	2.49 .098	II	535089-5
								536418-5 ¹
						2.90 .114	II	9-1393640-2
								535090-5
							II	535090-4
								650963-5 ¹
							III	650963-4 ¹
								535090-9
						3.70 .145	II	7-1393641-0
								2-1393640-4
							I	2-1393640-3 ¹
								2-1393641-7 ¹
64	A,C	93.98 3.700	90.00 3.543	78.74 3.100	85.00 3.346	4.50 .177	II	3-1393641-1
								6-1393642-8
							III	535043-4
								535043-5
							II	536412-4 ¹
								6-1393640-0
						13.00 .512	II	1-1393642-1
								650458-5
						2.49 .098	II	536481-5 ¹
								1-1393640-0
							II	9-1393640-3
								9-1393640-0 ¹
64	A,C	93.98 3.700	90.00 3.543	78.74 3.100	85.00 3.346		II	9-1393642-7 ²
								650956-5
						3.30 .130	II	650983-5 ¹
								2-1393640-5
							II	3-1393641-5
								2-1393641-8 ¹
							III	6-1393642-9
								6-1393642-7 ¹
						4.57 .180	II	650408-5
								650408-4
						13.00 .512	II	1-1393642-6

¹ With Boardlocks

² Flux tight

Note: Select load available upon request, contact Product Engineering.



With Boardlocks¹