

FUSE CLIPS

- Low contact resistance
- Withstands shock and vibration
- Rated 6.3 to 30 Amps
- Custom designs and modifications available to your specifications

PC THRU MOUNT TYPES

- Available for 5mm, 1AG, 2AG, 3AG, 5AG, 7AG & 8AG sizes
- Low profile, space saving
- Snap-fit design enhances assembly and PC retention for wave soldering
- Available with orientation legs to assure proper PC installation
- Available with or without end stops

SURFACE MOUNT & RIVET TYPES

- Available for 5mm, 1AG, 2AG, 3AG, 4AG, 7AG & 8AG sizes
- Available with solder lugs or quick-fit tabs
- .187 (4.7), .205 (5.2)

Refer to pages 46-47 for Fuse Clip Layout and Mounting Details

5mm PC Clips




MATERIAL:

.020 (.51) Brass, Tin Plate
Current Rating: 15 Amps

CAT. NO.	A	B
3517	.060 (1.5)	.060 (1.5)
3518P	.060 (1.5)	.093 (2.4)

With or Without Orientation Legs

Optional cover available - Cat. No. 3517C



- With snap-in PC legs


MATERIAL:

.020 (.51) Brass, Tin Plate
Current Rating: 15 Amps

CAT. NO.	A	B
3512	.060 (1.5)	.060 (1.5)
3512P	.060 (1.5)	.093 (2.4)

With or Without Orientation Legs


Optional cover available - Cat. No. 3517C



MATERIAL:

.016 (.41) Brass, Tin Plate
Current Rating: 6.3 Amps


CAT. NO. 3520




MATERIAL:

.016 (.41) Brass, Tin Plate
Current Rating: 10 Amps

CAT. NO. 3519



Mounting Detail




2AG or 5mm




MATERIAL: .016 (.41) Brass, Tin Plate
Current Rating: 10 Amps

CAT. NO.	PC LEGS	END STOP
3521	YES	YES
3621	YES	NO
3561	NO	YES
3622	NO	NO



Mounting Detail
Cat. No. 3521 & 3621 Only




5mm/3AG




MATERIAL:

.016 (.41) Brass, Tin Plate
Current Rating: 15 Amps

CAT. NO. 3562



Mounting Detail




4AG (9/32 Dia.)



MATERIAL:

.020 (.51) Brass, Nickel Plate
Current Rating: 15 Amps

CAT. NO. 3565 (Without End Stops)




5AG (13/32 Dia.) - Solar Protection Fuse



MATERIAL:

.030 (.76) Brass, Tin Plate
Current Rating: 30 Amps

CAT. NO. 3566



Mounting Detail

