





LOC	DIST	REVISIONS					
AD	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			—	SEE SHEET 1	—	—	—

- 1
- MATERIAL:
CONTACT: PHOSPHOR BRONZE.
HOUSING: GLASS-FILLED POLYESTER.
- 2
- GENERAL PLATING SPECIFICATION: UNDERPLATING
(ENTIRE CONTACT): 1.27μm MIN NICKEL AND ACTION
PIN: 0.5μm MIN TIN\LEAD.
FOR PLATING OF MATING SURFACES SEE APPLICABLE
SPECIFICATION REFERENCE FOR EACH DASH NUMBER.
- 3
- CONFORMS TO ALL TESTING ACCORDING TO IEC 61076-4-101
PERFORMANCE LEVEL 2.
- 4
- CONFORMS TO ALL TESTING ACCORDING TO IEC 61076-4-101
PERFORMANCE LEVEL 1.
- 5
- CONNECTOR TESTED AND QUALIFIED AGAINST TELCORDIA GR-1217-CORE QUALITY LEVEL 3,
CENTRAL OFFICE APPLICATIONS.
- 6
- CONNECTOR TESTED AND QUALIFIED AGAINST TELCORDIA GR-1217-CORE QUALITY LEVEL 3,
UNCONTROLLED ENVIROMENT APPLICATIONS.
- 7
- CONNECTOR MARKED WITH PART NUMBER AND DATE CODE.
ADDITIONAL CHARACTERS OR MARKINGS, AS WELL AS THE LOCATION OF THE MARKINGS,
MAY BE ADDED FOR TRACEABILITY BASED UPON MANUFACTURERS DISCRETION.
- 8
- PLATED-THROUGH HOLES AT 2x2mm SQUARE GRID
PATTERN DEFINED BY CONTACT LAYOUT.
- 9
- FOR ACTUAL PIN LOADING SEE "CONTACT LAYOUT".
- 10
- FOR ACTUAL PIN DIMENSIONS SEE "CONTACT DIMENSIONS".
- 11
- TO BE MEASURED AT BOTTOM OF SHROUD.
- 12
- CONNECTOR LUBRICATED WITH BELCORE APPROVED LUBRICANT,
TECHNICAL REFERENCE: TR-NWT-001217 ISSUE 1, SEP 1992.
- 13
- 0.76μm MIN. GOLD PLATING AT MATING SURFACES.

THIS DRAWING IS A CONTROLLED DOCUMENT.			DRN B CARRO	14DEC05	Tyco Electronics Corporation Harrisburg, Pa 17105-3608				
			CHK G.SKIPPER	14DEC05					
DIMENSIONS: mm		TOLERANCES, UNLESS OTHERWISE SPECIFIED:	APVD G.SKIPPER	14DEC05	NAME MALE ASSEMBLY, Z-PACK 2mm HM, TYPE B				
		Ø-P-LG ± .01	PRODUCT SPEC 108-19082 APPLICATION SPEC 114-19029 WEIGHT -						
		+P-LG ± .01							
		Ø-P-LG ± .01							
		+P-LG ± .01							
MATERIAL SEE SHEET 1		FINISH SEE SHEET 1	SIZE A1				CAGE CODE 00779	DRAWING NO C=352128	RESTRICTED TO -
CUSTOMER DRAWING			SCALE 4:1			SHEET 2 OF 2		REV H	