



Double Coated Removable Foam Tape with Adhesive 100 4658F

Technical Data

September, 2011

Product Description

3M™ Double Coated Removable Foam Tape 4658F is a clear, double coated acrylic foam tape that removes cleanly from many surfaces. 3M™ Adhesive 100 is a firm acrylic adhesive system that offers high ultimate bond strength, good temperature resistance, solvent resistance and static shear holding power. 3M tape 4658F can reach high bond strengths and some high surface energy substrates and may become difficult to remove.

Construction

Product		3M Tape 4658F
Adhesive Type:		100
Foam Type:		Acrylic
Thickness:	Nominal	1/32 in., 0.031 in. (.08 mm)
	Tolerance	± 10%
Color:		Clear
Release Liner:		0.003 in. (.08 mm) Clear Polyester Film
Approximate Density:		60
Foam Only		(960)

Typical Physical Properties

Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

Peel Adhesion:		
To Stainless Steel Room Temperature 90° Angle Peel 12 in./minute Jaw Speed (308 mm/min.) 72 hour Dwell ASTM D-3330		15 lb./in. width (263 N/100 mm)
Static Shear:		
1/2 in. ² (3.23 cm ²) overlap Will hold listed gram weight for 10,000 minutes. ASTM D-3654	72°F (22°C)	1000 g.
	120°F (49°C)	750 g.
	150°F (66°C)	500 g.
Temperature Resistance:		
Short Term (Minutes, Hours)		212°F (100°C)
Long Term (Days, Weeks)		175°F (80°C)
U.V. Resistance:		Excellent resistance to direct exposure to sunlight or other sources of ultraviolet (U.V.) light.
Solvent Resistance:		No apparent degradation when exposed to splash testing of most hydrocarbon solvents.
Shelf Life:		24 months from date of manufacture when stored in original cartons at 70°F (21°C) and 50% relative humidity.

Available Sizes

*Standard Stock Sizes:	1/2 in. x 27 yds. (12 mm x 25 m)
	3/4 in. x 27 yds. (19 mm x 25 m)
	1 in. x 27 yds. (25 mm x 25 m)
Slitting Tolerance:	± 1/32 in., ± 0.031 in. (± 0.8 mm)
Maximum Width:	46 1/2 in. (1.18 m)
Maximum Roll Length:	175 yds. (160 m)

*Questions regarding other possible tape sizes and shipping quantities should be directed to either your 3M sales representative or 3M's customer service at 1-800-362-3550.

3M™ Double Coated Removable Foam Tape with Adhesive 100 4658F

Application Techniques

- Bond strength is dependent upon the amount of adhesive-to-surface contact developed. Firm application pressure helps develop better adhesive contact and improve bond strength.
- To obtain optimum adhesion, the bonding surfaces must be clean, dry and well unified. Typical surface cleaning solvents are isopropyl alcohol (rubbing alcohol) and water or heptane. **Note:** Carefully read and follow manufacturer's precautions and directions for use when using solvents.
- Ideal tape application temperature is 70°F to 100°F (21°C to 38°C). Initial tape application to surfaces at temperatures below 50°F (10°C) is not recommended because the adhesive may become too firm to adhere readily. However, once properly applied, low temperature holding is generally satisfactory.

Design Considerations


- As a general rule, four square inches of tape should be used for each pound of weight to be supported in static load. More or less tape may be required depending upon the particular application. User evaluation is, therefore, required to determine optimal tape usage.
- Care should be used when bonding to surfaces with very low internal strength such as painted plaster board, fabric or cloth, wallpaper, blown vinyl, etc. since delamination of that surface may occur.
- Care should also be taken with wood veneers and highly polished wood as very glossy surfaces may leave an image when the tape is removed.

Removal Techniques


For rigid surfaces, lever or pry apart the substrates to break the bond.



For flexible surfaces, peel back slowly to ensure clean removal.



To remove tape from substrate, pull back corner and peel off quickly.



Application Ideas

- Signs
- Smoke Alarms
- Point of Purchase and other Displays
- Holding Electronic Accessories
- Dispensers
- Nameplates
- Exhibitions
- Air Fresheners
- Picture Frame Tabs

Technical Information

The technical information, recommendations and other statements contained in this document are based upon tests or experience that 3M believes are reliable, but the accuracy or completeness of such information is not guaranteed.

Product Use

Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. Given the variety of factors that can affect the use and performance of a 3M product, user is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application.

Warranty, Limited Remedy, and Disclaimer

Unless an additional warranty is specifically stated on the applicable 3M product packaging or product literature, 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. If the 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability

Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.

ISO 9001:2008

This Industrial Adhesives and Tapes Division product was manufactured under a 3M quality system registered to ISO 9001:2008 standards.

3M

Industrial Adhesives and Tapes Division

3M Center, Building 225-3S-06
St. Paul, MN 55144-1000
800-362-3550 • 877-369-2923 (Fax)
www.3M.com/industrial



Recycled Paper
40% pre-consumer
10% post-consumer

3M is a trademark of 3M Company.
Printed in U.S.A.
©3M 2011 70070739274 (9/11)