








MATERIALS AND FINISHES:

BODY: STAINLESS STEEL
FINISH: PASSIVATED

CENTER CONTACT: BERYLLIUM COPPER
PLATED: GOLD (30μ-in) MIN
OVER NICKEL (100μ-in) MIN.


INSULATOR: PTFE


SCREW: STAINLESS STEEL
FINISH: PASSIVATED




NOTE:
PATENT PENDING

73252-0093	WITH TWO 9.5/38 SCREWS	4.32(.170) TO 7.50(.295)
73252-0092	NO SCREWS	
73252-0091	WITH TWO 6.35/25 SCREWS	1.78(.070) TO 4.19(.165)
73252-0090	WITH TWO 4.76/19 SCREWS	0.76(.030) TO 2.44(.096)
PART NO.	DESCRIPTION	PCB THICKNESS MM (IN)

CHG: DRW VIEW UPDATED, ADDED DIA FOR C/SINK HOLES ON BODY & GEN TOLERANCE VALUES. EC NO: URF-2016-0157 DRW:APRAKASH01 2015/09/01 CHK:DALLM 2015/09/01 APPR:AROBERTSON 2015/09/15	DESCRIPTION	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE MM/IN		SCALE	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION																		
			<table><tr><td></td><td>mm</td><td>INCH</td></tr><tr><td>4 PLACES</td><td>± ---</td><td>± ---</td></tr><tr><td>3 PLACES</td><td>± ---</td><td>± 0.010</td></tr><tr><td>2 PLACES</td><td>± 0.25</td><td>± ---</td></tr><tr><td>1 PLACE</td><td>± ---</td><td>± ---</td></tr><tr><td>0 PLACE</td><td>±</td><td>±</td></tr></table>				mm	INCH	4 PLACES	± ---	± ---	3 PLACES	± ---	± 0.010	2 PLACES	± 0.25	± ---	1 PLACE	± ---	± ---	0 PLACE	±	±	DRAWN BY DATE JLEE02 2011/11/22		TITLE 2.92MM JACK, PCB FIELD REPLACEABLE EWR-4834, 2.92-JR/F		
				mm	INCH																							
			4 PLACES	± ---	± ---																							
			3 PLACES	± ---	± 0.010																							
			2 PLACES	± 0.25	± ---																							
			1 PLACE	± ---	± ---																							
			0 PLACE	±	±																							
						CHECKED BY DATE SSS 2011/11/22																						
						APPROVED BY DATE JWIENER 2012/02/06																						
			MATERIAL NO.		DOCUMENT NO.		SHEET NO.																					
DRAFT WHERE APPLICABLE			SEE TABLE		SD-73252-009		1 OF 2																					
MUST REMAIN WITHIN DIMENSIONS			THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																									
REV																												
B1																												




P/N: 73252-0092




80 SETS PER TRAY
TRAY P/N: 89707-0190

FOR 73252-0092 ONLY



3200 SETS PER OUTER
CARTON BOX
P/N: 96708-0005



1600 SETS PER INNER
CARTON BOX
P/N: 96707-0001

CHG:SEE SHEET 1
EC NO: URF2016-0157
DRWN:APRAKASH01 2015/09/01
CHKD:LLM 2015/09/01
APPR:AROBERTSON 2015/09/15
REV B1

REV	DESCRIPTION
7	QUALITY SYMBOLS
6	= 0
5	= 0
4	= 0

GENERAL TOLERANCES (UNLESS SPECIFIED)		
	mm	INCH
4 PLACES	± ---	± ---
3 PLACES	± ---	± 0.010
2 PLACES	± 0.25	± ---
1 PLACE	± ---	± ---
0 PLACE	±	±
ANGULAR ± 2 °		
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		

DIMENSION STYLE MM/IN	
DRAWN BY	DATE
JLEE02	2011/11/22
CHECKED BY	DATE
SSS	2011/11/22
APPROVED BY	DATE
JWIENER	2012/02/06
MATERIAL NO.	
SEE TABLE	
SIZE	C

SCALE	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION
TITLE		
2.92MM JACK, PCB FIELD REPLACEABLE EWR-4834, 2.92-JR/F		
molex		
DOCUMENT NO.		SHEET NO.
SD-73252-009		2 OF 2
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		