

# DATA SHEET

**74LVC32A**

Quad 2-input OR gate

Product specification  
IC24 Data Handbook

1997 Jun 30

# Quad 2-input OR gate

## 74LVC32A

### FEATURES

- Wide supply voltage range of 1.2 V to 3.6 V
- In accordance with JEDEC standard no. 8-1A.
- Inputs accept voltages up to 5.5 V
- CMOS low power consumption
- Direct interface with TTL levels

### DESCRIPTION

The 74LVC32A is a high-performance, low-power, low-voltage Si-gate CMOS device and superior to most advanced CMOS compatible TTL families.

Inputs can be driven from either 3.3V or 5V devices. This feature allows the use of these devices as translators in a mixed 3.3V/5V environment.

The 74LVC32A provides the 2-input OR function.

### QUICK REFERENCE DATA

GND = 0 V;  $T_{amb} = 25^{\circ}\text{C}$ ;  $t_r = t_f \leq 2.5 \text{ ns}$

| SYMBOL            | PARAMETER                              | CONDITIONS                                          | TYPICAL | UNIT |
|-------------------|----------------------------------------|-----------------------------------------------------|---------|------|
| $t_{PHL}/t_{PLH}$ | Propagation delay<br>nA, nB to nY      | $C_L = 50 \text{ pF}$ ;<br>$V_{CC} = 3.3 \text{ V}$ | 2.6     | ns   |
| $C_I$             | Input capacitance                      |                                                     | 5.0     | pF   |
| $C_{PD}$          | Power dissipation capacitance per gate | Notes 1 and 2                                       | 28      | pF   |


#### NOTES:

- $C_{PD}$  is used to determine the dynamic power dissipation ( $P_D$  in  $\mu\text{W}$ )  
 $P_D = C_{PD} \times V_{CC}^2 \times f_i + \sum (C_L \times V_{CC}^2 \times f_o)$  where:  
 $f_i$  = input frequency in MHz;  $C_L$  = output load capacity in pF;  
 $f_o$  = output frequency in MHz;  $V_{CC}$  = supply voltage in V;  
 $\sum (C_L \times V_{CC}^2 \times f_o)$  = sum of the outputs.
- The condition is  $V_I = \text{GND to } V_{CC}$ .

### ORDERING INFORMATION

| PACKAGES                    | TEMPERATURE RANGE                             | OUTSIDE NORTH AMERICA | NORTH AMERICA | DWG NUMBER |
|-----------------------------|-----------------------------------------------|-----------------------|---------------|------------|
| 14-Pin Plastic SO           | $-40^{\circ}\text{C to } +85^{\circ}\text{C}$ | 74LVC32A D            | 74LVC32A D    | SOT108-1   |
| 14-Pin Plastic SSOP Type II | $-40^{\circ}\text{C to } +85^{\circ}\text{C}$ | 74LVC32A DB           | 74LVC32A DB   | SOT337-1   |
| 14-Pin Plastic TSSOP Type I | $-40^{\circ}\text{C to } +85^{\circ}\text{C}$ | 74LVC32A PW           | 74LVC32APW DH | SOT402-1   |

### PIN CONFIGURATION




### PIN DESCRIPTION

| PIN NUMBER   | SYMBOL   | NAME AND FUNCTION       |
|--------------|----------|-------------------------|
| 1, 4, 9, 12  | 1A – 4A  | Data inputs             |
| 2, 5, 10, 13 | 1B – 4B  |                         |
| 3, 6, 8, 11  | 1Y – 4Y  | Data outputs            |
| 7            | GND      | Ground (0 V)            |
| 14           | $V_{CC}$ | Positive supply voltage |


Quad 2-input OR gate

74LVC32A

LOGIC SYMBOL



LOGIC DIAGRAM (ONE GATE)




FUNCTION TABLE

| INPUTS |    | OUTPUTS |
|--------|----|---------|
| nA     | nB | nY      |
| L      | L  | L       |
| L      | H  | H       |
| H      | L  | H       |
| H      | H  | H       |

NOTES:  
H = HIGH voltage level  
L = LOW voltage level

LOGIC SYMBOL (IEEE/IEC)



## Quad 2-input OR gate

74LVC32A

## RECOMMENDED OPERATING CONDITIONS

| SYMBOL     | PARAMETER                                         | CONDITIONS                                           | LIMITS |          | UNIT |
|------------|---------------------------------------------------|------------------------------------------------------|--------|----------|------|
|            |                                                   |                                                      | MIN    | MAX      |      |
| $V_{CC}$   | DC supply voltage (for max. speed performance)    |                                                      | 2.7    | 3.6      | V    |
| $V_{CC}$   | DC supply voltage (for low-voltage applications)  |                                                      | 1.2    | 3.6      | V    |
| $V_I$      | DC input voltage range                            |                                                      | 0      | 5.5      | V    |
| $V_O$      | DC output voltage range; output HIGH or LOW state |                                                      | 0      | $V_{CC}$ | V    |
| $T_{amb}$  | Operating ambient temperature range in free-air   |                                                      | -40    | +85      | °C   |
| $t_r, t_f$ | Input rise and fall times                         | $V_{CC} = 1.2$ to $2.7V$<br>$V_{CC} = 2.7$ to $3.6V$ | 0<br>0 | 20<br>10 | ns/V |

ABSOLUTE MAXIMUM RATINGS<sup>1</sup>

In accordance with the Absolute Maximum Rating System (IEC 134).

Voltages are referenced to GND (ground = 0V).

| SYMBOL            | PARAMETER                                                                                                | CONDITIONS                                                                           | RATING                 | UNIT |
|-------------------|----------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------|------------------------|------|
| $V_{CC}$          | DC supply voltage                                                                                        |                                                                                      | -0.5 to +6.5           | V    |
| $I_{IK}$          | DC input diode current                                                                                   | $V_I < 0$                                                                            | -50                    | mA   |
| $V_I$             | DC input voltage                                                                                         | Note 2                                                                               | -0.5 to +6.5           | V    |
| $I_{OK}$          | DC output diode current                                                                                  | $V_O > V_{CC}$ or $V_O < 0$                                                          | ± 50                   | mA   |
| $V_O$             | DC output voltage; output HIGH or LOW state                                                              | Note 2                                                                               | -0.5 to $V_{CC} + 0.5$ | V    |
| $I_O$             | DC output source or sink current                                                                         | $V_O = 0$ to $V_{CC}$                                                                | ± 50                   | mA   |
| $I_{GND}, I_{CC}$ | DC $V_{CC}$ or GND current                                                                               |                                                                                      | ± 100                  | mA   |
| $T_{stg}$         | Storage temperature range                                                                                |                                                                                      | -65 to +150            | °C   |
| $P_{TOT}$         | Power dissipation per package<br>– plastic mini-pack (SO)<br>– plastic shrink mini-pack (SSOP and TSSOP) | above +70°C derate linearly with 8 mW/K<br>above +60°C derate linearly with 5.5 mW/K | 500<br>500             | mW   |

## NOTES:

- Stresses beyond those listed may cause permanent damage to the device. These are stress ratings only and functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.
- The input and output voltage ratings may be exceeded if the input and output current ratings are observed.

Quad 2-input OR gate

74LVC32A

DC CHARACTERISTICS

Over recommended operating conditions. Voltages are referenced to GND (ground = 0V).

| SYMBOL           | PARAMETER                                         | TEST CONDITIONS                                                                                       | LIMITS                |                  |      | UNIT |
|------------------|---------------------------------------------------|-------------------------------------------------------------------------------------------------------|-----------------------|------------------|------|------|
|                  |                                                   |                                                                                                       | Temp = -40°C to +85°C |                  |      |      |
|                  |                                                   |                                                                                                       | MIN                   | TYP <sup>1</sup> | MAX  |      |
| V <sub>IH</sub>  | HIGH level Input voltage                          | V <sub>CC</sub> = 1.2V                                                                                | V <sub>CC</sub>       |                  |      | V    |
|                  |                                                   | V <sub>CC</sub> = 2.7 to 3.6V                                                                         | 2.0                   |                  |      |      |
| V <sub>IL</sub>  | LOW level Input voltage                           | V <sub>CC</sub> = 1.2V                                                                                |                       |                  | GND  | V    |
|                  |                                                   | V <sub>CC</sub> = 2.7 to 3.6V                                                                         |                       |                  | 0.8  |      |
| V <sub>OH</sub>  | HIGH level output voltage                         | V <sub>CC</sub> = 2.7V; V <sub>I</sub> = V <sub>IH</sub> or V <sub>IL</sub> ; I <sub>O</sub> = -12mA  | V <sub>CC</sub> - 0.5 |                  |      | V    |
|                  |                                                   | V <sub>CC</sub> = 3.0V; V <sub>I</sub> = V <sub>IH</sub> or V <sub>IL</sub> ; I <sub>O</sub> = -100μA | V <sub>CC</sub> - 0.2 | V <sub>CC</sub>  |      |      |
|                  |                                                   | V <sub>CC</sub> = 3.0V; V <sub>I</sub> = V <sub>IH</sub> or V <sub>IL</sub> ; I <sub>O</sub> = -18mA  | V <sub>CC</sub> - 0.6 |                  |      |      |
|                  |                                                   | V <sub>CC</sub> = 3.0V; V <sub>I</sub> = V <sub>IH</sub> or V <sub>IL</sub> ; I <sub>O</sub> = -24mA  | V <sub>CC</sub> - 0.8 |                  |      |      |
| V <sub>OL</sub>  | LOW level output voltage                          | V <sub>CC</sub> = 2.7V; V <sub>I</sub> = V <sub>IH</sub> or V <sub>IL</sub> ; I <sub>O</sub> = 12mA   |                       |                  | 0.40 | V    |
|                  |                                                   | V <sub>CC</sub> = 3.0V; V <sub>I</sub> = V <sub>IH</sub> or V <sub>IL</sub> ; I <sub>O</sub> = 100μA  |                       |                  | 0.20 |      |
|                  |                                                   | V <sub>CC</sub> = 3.0V; V <sub>I</sub> = V <sub>IH</sub> or V <sub>IL</sub> ; I <sub>O</sub> = 24mA   |                       |                  | 0.55 |      |
| I <sub>I</sub>   | Input leakage current                             | V <sub>CC</sub> = 3.6V; V <sub>I</sub> = 5.5V or GND                                                  |                       | ± 0.1            | ± 5  | μA   |
| I <sub>CC</sub>  | Quiescent supply current                          | V <sub>CC</sub> = 3.6V; V <sub>I</sub> = V <sub>CC</sub> or GND; I <sub>O</sub> = 0                   |                       | 0.1              | 10   | μA   |
| ΔI <sub>CC</sub> | Additional quiescent supply current per input pin | V <sub>CC</sub> = 2.7V to 3.6V; V <sub>I</sub> = V <sub>CC</sub> - 0.6V; I <sub>O</sub> = 0           |                       | 5                | 500  | μA   |

**NOTE:**  
1. All typical values are at V<sub>CC</sub> = 3.3V and T<sub>amb</sub> = 25°C.

AC CHARACTERISTICS


GND = 0 V; t<sub>r</sub> = t<sub>f</sub> ≤ 2.5 ns; C<sub>L</sub> = 50 pF

| SYMBOL                                 | PARAMETER                         | WAVEFORMS | LIMITS                       |                  |     |                        |     |     |                        | UNIT |
|----------------------------------------|-----------------------------------|-----------|------------------------------|------------------|-----|------------------------|-----|-----|------------------------|------|
|                                        |                                   |           | V <sub>CC</sub> = 3.3V ±0.3V |                  |     | V <sub>CC</sub> = 2.7V |     |     | V <sub>CC</sub> = 1.2V |      |
|                                        |                                   |           | MIN                          | TYP <sup>1</sup> | MAX | MIN                    | TYP | MAX | TYP                    |      |
| t <sub>PHL</sub> /<br>t <sub>PLH</sub> | Propagation delay<br>nA, nB to nY | 1, 2      | 1.5                          | 2.6              | 4.9 | 1.5                    | 3.0 | 5.9 | 16                     | ns   |

**NOTE:**  
1. These typical values are at V<sub>CC</sub> = 3.3V and T<sub>amb</sub> = 25°C.


AC WAVEFORMS

V<sub>M</sub> = 1.5 V at V<sub>CC</sub> ≥ 2.7 V  
V<sub>M</sub> = 0.5 • V<sub>CC</sub> at V<sub>CC</sub> < 2.7 V  
V<sub>OL</sub> and V<sub>OH</sub> are the typical output voltage drop that occur with the output load.



Waveform 1. Input (nA, nB) to output (nY) propagation delays.

TEST CIRCUIT




Waveform 2. Load circuitry for switching times.

Quad 2-input OR gate

74LVC32A

SO14: plastic small outline package; 14 leads; body width 3.9 mm

SOT108-1



Quad 2-input OR gate

74LVC32A

SSOP14: plastic shrink small outline package; 14 leads; body width 5.3 mm

SOT337-1



Quad 2-input OR gate

74LVC32A

TSSOP14: plastic thin shrink small outline package; 14 leads; body width 4.4 mm

SOT402-1



---

Quad 2-input OR gate

74LVC32A

---

**NOTES**

Quad 2-input OR gate

74LVC32A

| DEFINITIONS               |                        |                                                                                                                                                                                                                                                            |
|---------------------------|------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Data Sheet Identification | Product Status         | Definition                                                                                                                                                                                                                                                 |
| Objective Specification   | Formative or in Design | This data sheet contains the design target or goal specifications for product development. Specifications may change in any manner without notice.                                                                                                         |
| Preliminary Specification | Preproduction Product  | This data sheet contains preliminary data, and supplementary data will be published at a later date. Philips Semiconductors reserves the right to make changes at any time without notice in order to improve design and supply the best possible product. |
| Product Specification     | Full Production        | This data sheet contains Final Specifications. Philips Semiconductors reserves the right to make changes at any time without notice, in order to improve design and supply the best possible product.                                                      |

Philips Semiconductors and Philips Electronics North America Corporation reserve the right to make changes, without notice, in the products, including circuits, standard cells, and/or software, described or contained herein in order to improve design and/or performance. Philips Semiconductors assumes no responsibility or liability for the use of any of these products, conveys no license or title under any patent, copyright, or mask work right to these products, and makes no representations or warranties that these products are free from patent, copyright, or mask work right infringement, unless otherwise specified. Applications that are described herein for any of these products are for illustrative purposes only. Philips Semiconductors makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

**LIFE SUPPORT APPLICATIONS**  
Philips Semiconductors and Philips Electronics North America Corporation Products are not designed for use in life support appliances, devices, or systems where malfunction of a Philips Semiconductors and Philips Electronics North America Corporation Product can reasonably be expected to result in a personal injury. Philips Semiconductors and Philips Electronics North America Corporation customers using or selling Philips Semiconductors and Philips Electronics North America Corporation Products for use in such applications do so at their own risk and agree to fully indemnify Philips Semiconductors and Philips Electronics North America Corporation for any damages resulting from such improper use or sale.

**Philips Semiconductors**  
811 East Arques Avenue  
P.O. Box 3409  
Sunnyvale, California 94088-3409  
Telephone 800-234-7381

© Copyright Philips Electronics North America Corporation 1997  
All rights reserved. Printed in U.S.A.  
  
print code  
Document order number:

Date of release: 05-96  
9397-750-04486

Let's make things better.