

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0038002096

Status:

Active

Overview:

kk

Description:

2.54mm (.100") KK® IDT Double Cantilever Contact, 6 Circuits, Tin (Sn), Feed-Through, Friction Ramp and Polarizing Rib, Brown ID Stripe



Series

image - Reference only

Documents:

- [3D Model](#)
- [Drawing \(PDF\)](#)
- [Product Specification PSX-7690S \(PDF\)](#)
- [Packaging Specification PK-7720-100 \(PDF\)](#)
- [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL

E29179

General

Product Family

Series

Comments

Crimp Quality Equipment

Overview

Product Name

IDT and Solder Connectors

7720

Version J

Yes

kk

KK®

Physical

Circuits (Loaded)

Circuits (maximum)

Color - Resin

Durability (mating cycles max)

Flammability

Gender

Glow-Wire Compliant

Lock to Mating Part

Material - Metal

Material - Plating Mating

Material - Plating Termination

Material - Resin

Number of Rows

Packaging Type

Panel Mount

Pitch - Mating Interface

Pitch - Termination Interface

Polarized to Mating Part

Stackable

Temperature Range - Operating

Termination Interface: Style

Wire Size AWG

6

6

Natural

5

94V-2

Female

No

None

Brass

Tin

Tin

Nylon

1

Bag

No

2.54mm (.100")

2.54mm (.100")

Yes

No

0°C to +50°C

IDT or Pierce

26 Stranded, 28 Solid, 28 Stranded Topcoat

Electrical

Current - Maximum per Contact

Voltage - Maximum

4A

250V

Material Info

Old Part Number

7720SC06J

Reference - Drawing Numbers

Packaging Specification

Product Specification

Sales Drawing

PK-7720-100

PSX-7690S

SDA-7720S-*N*

EU RoHS

ELV and RoHS
Compliant

REACH SVHC

Contains SVHC: No
Low-Halogen Status
Low-Halogen

China RoHS



Need more information on product
environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series

7720Series

Application Tooling | FAQ

Tooling specifications and manuals are
found by selecting the products below.
Crimp Height Specifications are then
contained in the Application Tooling
Specification document.

Global

Description

Product #

Insertion Tool for

2.54mm (.100") Pitch

KK® IDT Crimp

Terminals

0638133504

This document was generated on 10/24/2011

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION