



Date	SYM	REVISION RECORD	AUTH	DR.	CK.
10/17/09	A	CHANGED LOCATION OF SMT FEET	T. B.	B.S.	
09/02/11	B	CHANGED LOCATION OF SMT FEET TO SIDES	T. B.	B.S.	
08/23/13	C	DIM. 4.32 WAS 4.57	T. B.	B.S.	
05/16/14	D	UPDATED SPECIFICATION	T. B.	B.S.	



PCB LAYOUT

SPECIFICATIONS:

- * 0.25mm Phosphor Bronze $\frac{1}{2}$ H, Nickel plated 40u"-120u"
- * Temperature Range: -40°C to +270°C
- * Vibration test: 10-50-10 hz swept in 60 seconds
x,y,z direction: 1 hour each direction
- * Result: no dislodgement of the cell or damage
no discontinuity over 10 micro-seconds
- * Shock test: half sine wave acceleration 150g.
6 m/s 3 shock pulses each direction per axis,
total of 18 pulses
- * Result: no evidence of physical damage
- * ROHS 2 COMPLIANT

Tolerance (Except as noted)	 Memory Protection Devices, Inc 200 Broad Hollow Road, Farmingdale, New York 11735		
decimal ±.1 (.004)			Scale Drawn By B.S. Approved By T.B.
Fractional ± .2 (.008)	Title CR2032 BATTERY RETAINER, SMD		
Angular ± 1°	Date 05/16/14	Drawing Number BK-912	