

IRK.41, .56 SERIES

**THYRISTOR/ DIODE and
THYRISTOR/ THYRISTOR**

ADD-A-pak™ GEN V Power Modules

Features

- High Voltage
- Industrial Standard Package
- Thick Al metal die and double stick bonding
- Thick copper baseplate
- UL E78996 approved
- 3500V_{RMS} isolating voltage

Benefits

- Up to 1600V
- Full compatible TO-240AA
- High Surge capability
- Easy Mounting on heatsink
- Al₂O₃ DBC insulator
- Heatsink grounded

**45 A
60 A**

Mechanical Description

The Generation V of Add-A-pak module combine the excellent thermal performance obtained by the usage of Direct Bonded Copper substrate with superior mechanical ruggedness, thanks to the insertion of a solid Copper baseplate at the bottom side of the device. The Cu baseplate allow an easier mounting on the majority of heatsink with increased tolerance of surface roughness and improve thermal spread.

The Generation V of AAP module is manufactured without hard mold, eliminating in this way any possible direct stress on the leads.

The electrical terminals are secured against axial pull-out: they are fixed to the module housing via a click-stop feature already tested and proved as reliable on other IR modules.

Electrical Description

These modules are intended for general purpose high voltage applications such as high voltage regulated power supplies, lighting circuits, temperature and motor speed control circuits, UPS and battery charger.

Major Ratings and Characteristics

Parameters	IRK.41	IRK.56	Units
$I_{T(AV)}$ or $I_{F(AV)}$ @ 85°C	45	60	A
$I_{O(RMS)}$ (*)	100	135	A
I_{TSM} @ 50Hz	850	1310	A
I_{FSM} @ 60Hz	890	1370	A
I^2t @ 50Hz	3.61	8.50	KA ² s
@ 60Hz	3.30	7.82	KA ² s
$I^2\sqrt{t}$	36.1	85.0	KA ² √s
V_{RRM} range	400 to 1600		V
T_{STG}	- 40 to 125		°C
T_J	- 40 to 125		°C

(*) As AC switch.



IRK.41, .56 Series

Bulletin I27131 rev. G 10/02


International
IOR Rectifier

ELECTRICAL SPECIFICATIONS

Voltage Ratings

Type number	Voltage Code	V_{RRM} , maximum repetitive peak reverse voltage V	V_{RSM} , maximum non-repetitive peak reverse voltage V	V_{DRM} , max. repetitive peak off-state voltage, gate open circuit V	I_{RRM} , I_{DRM} 125°C mA
IRK.41/ .56	04	400	500	400	15
	06	600	700	600	
	08	800	900	800	
	10	1000	1100	1000	
	12	1200	1300	1200	
	14	1400	1500	1400	
	16	1600	1700	1600	

On-state Conduction

Parameters	IRK.41	IRK.56	Units	Conditions	
$I_{T(AV)}$ Max. average on-state current (Thyristors)	45	60	A	180° conduction, half sine wave, $T_C = 85^{\circ}\text{C}$	
$I_{F(AV)}$ Maximum average forward current (Diodes)	45	60			
$I_{O(RMS)}$ Max. continuous RMS on-state current. As AC switch	100	135			
I_{TSM} Max. peak, one cycle non-repetitive on-state or forward current I_{FSM}	850	1310		$t=10\text{ms}$ No voltage reappplied	Sinusoidal half wave, Initial $T_J = T_J$ max.
	890	1370		$t=8.3\text{ms}$	
	715	1100		$t=10\text{ms}$ 100% V_{RRM}	
	750	1150		$t=8.3\text{ms}$ reappplied	
	940	1450		$t=10\text{ms}$ $T_J = 25^{\circ}\text{C}$,	
985	1520	$t=8.3\text{ms}$ no voltage reappplied			
I^2t Max. I^2t for fusing	3.61	8.56	KA^2s	$t=10\text{ms}$ No voltage reappplied	Initial $T_J = T_J$ max.
	3.30	7.82		$t=8.3\text{ms}$	
	2.56	6.05		$t=10\text{ms}$ 100% V_{RRM}	
	2.33	5.53		$t=8.3\text{ms}$ reappplied	
	4.42	10.05		$t=10\text{ms}$ $T_J = 25^{\circ}\text{C}$,	
	4.03	9.60		$t=8.3\text{ms}$ no voltage reappplied	
$I^2\sqrt{t}$ Max. $I^2\sqrt{t}$ for fusing (1)	36.1	85.6	$\text{KA}^2\sqrt{\text{s}}$	$t=0.1$ to 10ms, no voltage reappplied	
$V_{T(TO)}$ Max. value of threshold voltage (2)	0.88	0.85	V	Low level (3)	$T_J = T_J$ max
	0.91	0.88		High level (4)	
r_t Max. value of on-state slope resistance (2)	5.90	3.53	$\text{m}\Omega$	Low level (3)	$T_J = T_J$ max
	5.74	3.41		High level (4)	
V_{TM} Max. peak on-state or forward voltage	1.81	1.54	V	$I_{TM} = \pi \times I_{T(AV)}$	$T_J = 25^{\circ}\text{C}$
V_{FM}				$I_{FM} = \pi \times I_{F(AV)}$	
di/dt Max. non-repetitive rate of rise of turned on current	150		$\text{A}/\mu\text{s}$	$T_J = 25^{\circ}\text{C}$, from 0.67 V_{DRM} , $I_{TM} = \pi \times I_{T(AV)}$, $I_g = 500\text{mA}$, $t_r < 0.5 \mu\text{s}$, $t_p > 6 \mu\text{s}$	
I_H Max. holding current	200		mA	$T_J = 25^{\circ}\text{C}$, anode supply = 6V, resistive load, gate open circuit	
I_L Max. latching current	400			$T_J = 25^{\circ}\text{C}$, anode supply = 6V, resistive load	

(1) I^2t for time $t_x = I^2\sqrt{t} \times \sqrt{t_x}$

(2) Average power = $V_{T(TO)} \times I_{T(AV)} + r_t \times (I_{T(RMS)})^2$

(3) $16.7\% \times \pi \times I_{AV} < I < \pi \times I_{AV}$

(4) $I > \pi \times I_{AV}$

Triggering

Parameters		IRK.41	IRK.56	Units	Conditions	
P _{GM}	Max. peak gate power	10	10	W		
P _{G(AV)}	Max. average gate power	2.5	2.5			
I _{GM}	Max. peak gate current	2.5	2.5	A		
-V _{GM}	Max. peak negative gate voltage	10		V	Anode supply = 6V resistive load	
V _{GT}	Max. gate voltage required to trigger	4.0				
		2.5				
		1.7				
I _{GT}	Max. gate current required to trigger	270		mA	Anode supply = 6V resistive load	
		150				
		80				
V _{GD}	Max. gate voltage that will not trigger	0.25		V	T _J = 125°C, rated V _{DRM} applied	
I _{GD}	Max. gate current that will not trigger	6		mA	T _J = 125°C, rated V _{DRM} applied	

Blocking

Parameters	IRK.41	IRK.56	Units	Conditions
I_{RRM} Max. peak reverse and off-state leakage current at V_{RRM} , V_{DRM}	15		mA	$T_J = 125^\circ\text{C}$, gate open circuit
V_{INS} RMS isolation voltage	2500 (1 min) 3500 (1 sec)		V	50 Hz, circuit to base, all terminals shorted
dv/dt Max. critical rate of rise of off-state voltage (5)	500		V/ μs	$T_J = 125^\circ\text{C}$, linear to 0.67 V_{DRM} , gate open circuit

(5) Available with $dv/dt = 1000\text{V}/\mu\text{s}$, to complete code add S90 i.e. IRKT41/16AS90.

Thermal and Mechanical Specifications

Parameters	IRK.41	IRK.56	Units	Conditions
T _J Junction operating temperature range	- 40 to 125		°C	
T _{stg} Storage temp. range	- 40 to 125			
R _{thJC} Max. internal thermal resistance, junction to case	0.23	0.20	K/W	Per module, DC operation
R _{thCS} Typical thermal resistance case to heatsink	0.1			Mounting surface flat, smooth and greased
T Mounting torque ± 10% to heatsink busbar	5		Nm	A mounting compound is recommended and the torque should be rechecked after a period of 3 hours to allow for the spread of the compound
	3			
wt Approximate weight	110 (4)		gr (oz)	
Case style	TO-240AA		JEDEC	

ΔR Conduction (per Junction)

(The following table shows the increment of thermal resistance R_{thJC} when devices operate at different conduction angles than DC)

Devices	Sine half wave conduction					Rect. wave conduction					Units
	180°	120°	90°	60°	30°	180°	120°	90°	60°	30°	
IRK.41	0.11	0.13	0.17	0.23	0.34	0.09	0.14	0.18	0.23	0.34	$^\circ\text{C}/\text{W}$
IRK.56	0.09	0.11	0.13	0.18	0.27	0.07	0.11	0.14	0.19	0.28	

IRK.41, .56 Series

Bulletin I27131 rev. G 10/02

International
IOR Rectifier


Ordering Information Table

Device Code					
IRK	T	56	/	16	A S90
1	2	3	4	5	6
1	Module type				
2	Circuit configuration (See Circuit Configuration table below)				
3	Current code **				
4	Voltage code (See Voltage Ratings table)				
5	A : Gen V				
6	dv/dt code: S90 = dv/dt 1000 V/μs No letter = dv/dt 500 V/μs				

IRK.57 types
With no auxiliary cathode

** Available with no auxiliary cathode.
To specify change: 41 to 42
56 to 57
e.g. : IRKT57/16A etc.

Outline Table



NOTE: To order the Optional Hardware see Bulletin I27900




Fig. 1 - Current Ratings Characteristics




Fig. 2 - Current Ratings Characteristics




Fig. 3 - On-state Power Loss Characteristics




Fig. 4 - On-state Power Loss Characteristics




Fig. 5 - Maximum Non-Repetitive Surge Current




Fig. 6 - Maximum Non-Repetitive Surge Current

IRK.41, .56 Series

Bulletin I27131 rev. G 10/02

International
IOR Rectifier




Fig. 7 - On-state Power Loss Characteristics




Fig. 8 - On-state Power Loss Characteristics




Fig. 9 - On-state Power Loss Characteristics




Fig. 10 - Current Ratings Characteristics




Fig. 11 - Current Ratings Characteristics




Fig. 12 - On-state Power Loss Characteristics




Fig. 13 - On-state Power Loss Characteristics




Fig. 14 - Maximum Non-Repetitive Surge Current




Fig. 15 - Maximum Non-Repetitive Surge Current

IRK.41, .56 Series

Bulletin I27131 rev. G 10/02

International
IOR Rectifier




Fig. 16 - On-state Power Loss Characteristics




Fig. 17 - On-state Power Loss Characteristics




Fig. 18 - On-state Power Loss Characteristics




Fig. 19 - On-state Voltage Drop Characteristics




Fig. 20 - On-state Voltage Drop Characteristics




Fig. 21 - Recovery Charge Characteristics




Fig. 22 - Recovery Current Characteristics




Fig. 23 - Thermal Impedance Z_{thJC} Characteristics

IRK.41, .56 Series

Bulletin I27131 rev. G 10/02

International
IR Rectifier




Fig. 24 - Gate Characteristics

Data and specifications subject to change without notice.
This product has been designed and qualified for Industrial Level.
Qualification Standards can be found on IR's Web site.

International
IR Rectifier

IR WORLD HEADQUARTERS: 233 Kansas St., El Segundo, California 90245, USA Tel: (310) 252-7105
TAC Fax: (310) 252-7309
10/02



Notice

The products described herein were acquired by Vishay Intertechnology, Inc., as part of its acquisition of International Rectifier's Power Control Systems (PCS) business, which closed in April 2007. Specifications of the products displayed herein are pending review by Vishay and are subject to the terms and conditions shown below.

Specifications of the products displayed herein are subject to change without notice. Vishay Intertechnology, Inc., or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Information contained herein is intended to provide a product description only. No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document. Except as provided in Vishay's terms and conditions of sale for such products, Vishay assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of Vishay products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Vishay for any damages resulting from such improper use or sale.

International Rectifier®, IR®, the IR logo, HEXFET®, HEXSense®, HEXDIP®, DOL®, INTERO®, and POWIRTRAIN® are registered trademarks of International Rectifier Corporation in the U.S. and other countries. All other product names noted herein may be trademarks of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Vishay:

[IRKH41/04P](#) [IRKH41/06P](#) [IRKH41/08P](#) [IRKH41/08S90P](#) [IRKH41/10P](#) [IRKH41/12P](#) [IRKH41/12S90P](#) [IRKH41/14P](#)
[IRKH41/14S90P](#) [IRKH41/16P](#) [IRKH42/06P](#) [IRKH42/08P](#) [IRKH42/10P](#) [IRKH42/12P](#) [IRKH56/04P](#) [IRKH56/06P](#)
[IRKH56/06S90P](#) [IRKH56/08P](#) [IRKH56/10P](#) [IRKH56/12P](#) [IRKH56/12S90P](#) [IRKH56/14P](#) [IRKH56/14S90P](#)
[IRKH56/16P](#) [IRKH56/16S90P](#) [IRKH57/04P](#) [IRKH57/06P](#) [IRKH57/08P](#) [IRKH57/10P](#) [IRKH57/12P](#) [IRKH57/12S90P](#)
[IRKH57/14P](#) [IRKH57/14S90P](#) [IRKH57/16P](#) [IRKH57/16S90P](#) [IRKL41/04P](#) [IRKL41/06P](#) [IRKL41/08P](#) [IRKL41/10P](#)
[IRKL41/12P](#) [IRKL41/12S90P](#) [IRKL41/14P](#) [IRKL41/16P](#) [IRKL42/06P](#) [IRKL56/04P](#) [IRKL56/06P](#) [IRKL56/06S90P](#)
[IRKL56/08P](#) [IRKL56/10P](#) [IRKL56/12P](#) [IRKL56/12S90P](#) [IRKL56/14P](#) [IRKL56/14S90P](#) [IRKL56/16P](#) [IRKL56/16S90P](#)
[IRKN56/12P](#) [IRKN56/16P](#) [IRKT41/04P](#) [IRKT41/06P](#) [IRKT41/08P](#) [IRKT41/08S90P](#) [IRKT41/10P](#) [IRKT41/10S90P](#)
[IRKT41/12P](#) [IRKT41/12S90P](#) [IRKT41/14P](#) [IRKT41/14S90P](#) [IRKT41/16P](#) [IRKT41/16S90P](#) [IRKT42/06P](#) [IRKT42/08P](#)
[IRKT42/08S90P](#) [IRKT42/10P](#) [IRKT42/12P](#) [IRKT42/12S90P](#) [IRKT42/14P](#) [IRKT42/16P](#) [IRKT56/04P](#) [IRKT56/06P](#)
[IRKT56/06S90P](#) [IRKT56/08P](#) [IRKT56/08S90P](#) [IRKT56/10P](#) [IRKT56/10S90P](#) [IRKT56/12P](#) [IRKT56/12S90P](#)
[IRKT56/14P](#) [IRKT56/14S90P](#) [IRKT56/16P](#) [IRKT56/16S90P](#) [IRKT57/04P](#) [IRKT57/06P](#) [IRKT57/08P](#) [IRKT57/10P](#)
[IRKT57/12P](#) [IRKT57/12S90P](#) [IRKT57/14P](#) [IRKT57/14S90P](#) [IRKT57/16P](#) [IRKT57/16S90P](#)