

# NTMS4503N

## Power MOSFET

28 V, 14 A, N-Channel, SOIC-8

### Features

- Low  $R_{DS(on)}$
- High Power and Current Handling Capability
- Low Gate Charge
- Pb-Free Package is Available

### Applications

- DC/DC Converters
- Motor Drives
- Synchronous Rectifier – POL
- Buck Low-Side

### MAXIMUM RATINGS ( $T_J = 25^\circ\text{C}$ unless otherwise noted)

Rating	Symbol	Value	Unit
Drain-to-Source Voltage	$V_{DS}$	28	V
Gate-to-Source Voltage – Continuous	$V_{GS}$	$\pm 20$	V
Drain Current	$I_D$		A
Continuous @ $T_A = 25^\circ\text{C}$ (Note 1)		14	
Continuous @ $T_A = 25^\circ\text{C}$ (Note 2)		12	
Continuous @ $T_A = 25^\circ\text{C}$ (Note 3)		9.0	
Single Pulse ( $t_p = 10 \mu\text{s}$ )	$I_{DM}$	40	
Total Power Dissipation	$P_D$		W
$T_A = 25^\circ\text{C}$ (Note 1)		2.5	
$T_A = 25^\circ\text{C}$ (Note 2)		1.66	
$T_A = 25^\circ\text{C}$ (Note 3)		0.93	
Operating and Storage Temperature	$T_J, T_{stg}$	$-55$ to $150$	$^\circ\text{C}$
Single Pulse Drain-to-Source Avalanche Energy – Starting $T_J = 25^\circ\text{C}$ ( $V_{DD} = 30 \text{ V}$ , $V_{GS} = 10 \text{ V}$ , $I_L = 12.2 \text{ A}$ , $L = 1.0 \text{ mH}$ , $R_G = 25 \Omega$ )	$E_{AS}$	75	mJ
Maximum Lead Temperature for Soldering Purposes, $1/8''$ from case for 10 seconds	$T_L$	260	$^\circ\text{C}$

### THERMAL RESISTANCE RATINGS

Rating	Symbol	Value	Unit
Thermal Resistance	$R_{\theta JA}$		$^\circ\text{C/W}$
Junction-to-Ambient (Note 1)		50	
Junction-to-Ambient (Note 2)		75	
Junction-to-Ambient (Note 3)		135	

Stresses exceeding Maximum Ratings may damage the device. Maximum Ratings are stress ratings only. Functional operation above the Recommended Operating Conditions is not implied. Extended exposure to stresses above the Recommended Operating Conditions may affect device reliability.


1. Surface-mounted on FR4 board using minimum recommended pad size (Cu area 0.412 in sq),  $t < 10 \text{ s}$ .
2. Surface-mounted on FR4 board using  $1''$  pad size (Cu area 1.127 in sq) steady state.
3. Surface-mounted on FR4 board using minimum recommended pad size (Cu area 0.412 in sq), steady state.



ON Semiconductor®

<http://onsemi.com>


$V_{(BR)DSS}$	$R_{DS(on)}$ Typ	$I_D$ Max (Note 1)
28 V	7.0 m $\Omega$ @ 10 V	14 A
	8.8 m $\Omega$ @ 4.5 V	



### MARKING DIAGRAM & PIN ASSIGNMENT



SOIC-8  
CASE 751  
STYLE 12



4503N = Specific Device Code  
A = Assembly Location  
Y = Year  
WW = Work Week  
▪ = Pb-Free Package

(Note: Microdot may be in either location)

### ORDERING INFORMATION

Device	Package	Shipping†
NTMS4503NR2	SOIC-8	2500/Tape & Reel
NTMS4503NR2G	SOIC-8 (Pb-Free)	2500/Tape & Reel

†For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

# NTMS4503N

## ELECTRICAL CHARACTERISTICS ( $T_J = 25^\circ\text{C}$ unless otherwise noted)

Characteristic	Symbol	Test Condition	Min	Typ	Max	Unit
----------------	--------	----------------	-----	-----	-----	------

### OFF CHARACTERISTICS

Drain-to-Source Breakdown Voltage	$V_{(BR)DSS}$	$V_{GS} = 0\text{ V}, I_D = 250\text{ }\mu\text{A}$		28	31	–	V
Drain-to-Source Breakdown Voltage Temperature Coefficient	$V_{(BR)DSS}/T_J$	–		–	22	–	mV/°C
Zero Gate Voltage Drain Current	$I_{DSS}$	$V_{GS} = 0\text{ V}, V_{DS} = 24\text{ V}$	$T_J = 25^\circ\text{C}$	–	–	1.0	$\mu\text{A}$
			$T_J = 100^\circ\text{C}$	–	–	25	
Gate-to-Source Leakage Current	$I_{GSS}$	$V_{DS} = 0\text{ V}, V_{GS} = \pm 20\text{ V}$		–	–	$\pm 100$	nA

### ON CHARACTERISTICS (Note 4)

Gate Threshold Voltage	$V_{GS(TH)}$	$V_{GS} = V_{DS}, I_D = 250\text{ }\mu\text{A}$	1.0	–	2.0	V
Negative Threshold Temperature Coefficient	$V_{GS(TH)}/T_J$	–	–	–5.0	–	mV/ $^\circ\text{C}$
Drain-to-Source On Resistance	$R_{DS(on)}$	$V_{GS} = 10\text{ V}, I_D = 14\text{ A}$	–	7.0	8.0	m $\Omega$
		$V_{GS} = 4.5\text{ V}, I_D = 10\text{ A}$	–	8.8	9.8	
Forward Transconductance	$g_{FS}$	$V_{DS} = 10\text{ V}, I_D = 14\text{ A}$	–	30	–	S

### CHARGES, CAPACITANCES AND GATE RESISTANCE

Input Capacitance	$C_{ISS}$	$V_{GS} = 0\text{ V}, f = 1.0\text{ MHz}, V_{DS} = 16\text{ V}$	–	2400	–	pF
Output Capacitance	$C_{OSS}$		–	1000	–	
Reverse Transfer Capacitance	$C_{RSS}$		–	375	–	
Total Gate Charge	$Q_{G(TOT)}$	$V_{GS} = 4.5\text{ V}, V_{DS} = 16\text{ V}, I_D = 10\text{ A}$	–	23	–	nC
Threshold Gate Charge	$Q_{G(TH)}$		–	2.0	–	
Gate-to-Source Charge	$Q_{GS}$		–	5.0	–	
Gate-to-Drain Charge	$Q_{GD}$		–	12	–	

### SWITCHING CHARACTERISTICS, $V_{GS} = V$ (Note 5)

Turn-On Delay Time	$t_{d(ON)}$	$V_{GS} = 4.5\text{ V}, V_{DD} = 16\text{ V}, I_D = 10\text{ A}, R_G = 2.0\text{ }\Omega$	–	18.5	–	ns
Rise Time	$t_r$		–	70	–	
Turn-Off Delay Time	$t_{d(OFF)}$		–	21	–	
Fall Time	$t_f$		–	23	–	

### DRAIN-SOURCE DIODE CHARACTERISTICS

Forward Diode Voltage	$V_{SD}$	$V_{GS} = 0\text{ V}, I_S = 10\text{ A}$	$T_J = 25^{\circ}\text{C}$	–	0.82	1.2	V
			$T_J = 125^{\circ}\text{C}$	–	0.65	–	
Reverse Recovery Time	$t_{RR}$	$V_{GS} = 0\text{ V},$ $dI_{SD}/d_t = 100\text{ A}/\mu\text{s},$ $I_S = 14\text{ A}$		–	48	–	ns
Charge Time	$T_a$			–	23	–	
Discharge Time	$T_b$			–	25	–	
Reverse Recovery Charge	$Q_{RR}$			–	25	–	nC

4. Pulse Test: Pulse Width  $\leq 300\text{ }\mu\text{s}$ , Duty Cycle  $\leq 2\%$ .

5. Switching characteristics are independent of operating junction temperatures.

TYPICAL PERFORMANCE CURVES




Figure 1. On-Region Characteristics




Figure 2. Transfer Characteristics




Figure 3. On-Resistance vs. Gate-to-Source Voltage




Figure 4. On-Resistance vs. Drain Current and Gate Voltage




Figure 5. On-Resistance Variation with Temperature








Figure 6. Drain-to-Source Leakage Current vs. Voltage


TYPICAL PERFORMANCE CURVES



# NTMS4503N

## PACKAGE DIMENSIONS

### SOIC-8 NB CASE 751-07 ISSUE AH



#### NOTES:


1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
2. CONTROLLING DIMENSION: MILLIMETER.
3. DIMENSION A AND B DO NOT INCLUDE MOLD PROTRUSION.
4. MAXIMUM MOLD PROTRUSION 0.15 (0.006) PER SIDE.
5. DIMENSION D DOES NOT INCLUDE DAMBAR PROTRUSION. ALLOWABLE DAMBAR PROTRUSION SHALL BE 0.127 (0.005) TOTAL IN EXCESS OF THE D DIMENSION AT MAXIMUM MATERIAL CONDITION.
6. 751-01 THRU 751-06 ARE OBSOLETE. NEW STANDARD IS 751-07.

DIM	MILLIMETERS		INCHES	
	MIN	MAX	MIN	MAX
A	4.80	5.00	0.189	0.197
B	3.80	4.00	0.150	0.157
C	1.35	1.75	0.053	0.069
D	0.33	0.51	0.013	0.020
G	1.27 BSC		0.050 BSC	
H	0.10	0.25	0.004	0.010
J	0.19	0.25	0.007	0.010
K	0.40	1.27	0.016	0.050
M	0°	8°	0°	8°
N	0.25	0.50	0.010	0.020
S	5.80	6.20	0.228	0.244

#### STYLE 12:

- PIN 1. SOURCE  
2. SOURCE  
3. SOURCE  
4. GATE  
5. DRAIN  
6. DRAIN  
7. DRAIN  
8. DRAIN

### SOLDERING FOOTPRINT\*



SCALE 6:1 (mm inches)

\*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

ON Semiconductor and are registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

## PUBLICATION ORDERING INFORMATION

### LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor  
P.O. Box 5163, Denver, Colorado 80217 USA  
Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada  
Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada  
Email: orderlit@onsemi.com

N. American Technical Support: 800-282-9855 Toll Free  
USA/Canada

Europe, Middle East and Africa Technical Support:

Phone: 421 33 790 2910

Japan Customer Focus Center

Phone: 81-3-5773-3850

ON Semiconductor Website: [www.onsemi.com](http://www.onsemi.com)

Order Literature: <http://www.onsemi.com/orderlit>

For additional information, please contact your local Sales Representative

NTMS4503N/D