

SPECIFICATIONS

Material: Casing - Stainless Steel

Seal - Fluorosilicone Rubber Gr60

Mounting Nut: Stainless Steel

Temperature Range: HEXSEALS: -94°F to +400°F

Pressure Range: Exceeds 15 psi internal and 1500 psi external.


Operational Life: 50,000 actuations (minimum).

Shelf Life: Excess of 25 years.

Resistant to: Salt spray, sunlight, ozone, weather, fungus, and most acids and lubricating oils

Agency Recognition: E-SEELS and HEXSEALS are UL-listed to UL Std. 50 types 1-13, and meet CSA standards.

Installation: If a reducing adaptor is required - see page 14 of HEXSEAL catalog HEX200 for part numbers and drawing.



B	REDRAWN and WAS 0.422" TO 0.485", WAS 0.438" TO 0.370"	09.11.09	
A	CAD COMPUTER GENERATED	10.23.02	
REV.	DESCRIPTION	DATE	
MAXIMUM AND MINIMUM MEASUREMENTS ARE STATED DIRECTLY ON EACH DIMENSION.	TITLE: ARMORED SEAL FOR PUSHBUTTON SWITCHES (1238/1 SS)	ENG.	
MAT'L: STAINLESS STEEL & FLUOROSILICONE RUBBER GR60		DWN.	K.S. 10.14.81
FINISH:	APM-HEXSEAL CORPORATION	CHKD.	J. CELLA 09.11.09
		SCALE 2 : 1	DWG. NO. (1238/1 SS) HEXSEAL®

THIS DRAWING COVERS PROPRIETARY ITEM AND IS THE PROPERTY OF THE APM-HEXSEAL CORPORATION.
THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE WRITTEN APPROVAL OF AN OFFICER OF THE APM-HEXSEAL CORPORATION.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[APM HEXSEAL:](#)

[1238/1](#)