

LOC	DIST	REVISIONS					
P	LTR	DESCRIPTION			DATE	DWN	APVD
		REVISED PER ECO-11-023039			21FEB12	KH	MS

MATERIAL:
HOUSING: THERMOPLASTIC, UL94V-2, BLACK.
TERMINAL: BRASS, BRIGHT TIN PLATED.
SCREWS: 6-32, STEEL, ZINC AND CHROMATE PLATED.

ELECTRICAL:
MAXIMUM CURRENT: 20A.
OPERATING VOLTAGE: 600V.
WIRE RANGE: 12 AWG MAX.

ENVIRONMENT:
OPERATING TEMP.: -60°C TO +105°C



- 1

WHITE INK MARKING, APPROX AS SHOWN.
- 2

NICKEL PLATED BRASS SCREW.
- 3


OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
- 4

ALL SCREWS BOTTOMED, TORQUE 2 TO 4 IN-LBS



SEE FIGURE 3

OBSOLETE	7.562	17	SSB7FP170201	1-1546972-7
	7.125	16	SSB7FP16020111	9-796602-4
2	7.125	16	SSB7FP160201	1-1546972-6
	6.687	15	SSB7FP150201	4-1437416-6
2	6.250	14	SSB7FP140203	1546561-4
	6.250	14	SSB7FP140201	4-1437416-5
2	5.812	13	SSB7FP130201	4-1437416-3
	5.375	12	SSB7FP120201	4-1437416-0
2	4.937	11	SSB7FP110201	1-1546972-1
	4.500	10	SSB7FP100203	3-1437416-6
2	4.500	10	SSB7FP100201	3-1437416-4
	4.062	9	SSB7FP090203	1-1546561-9
2	4.062	9	SSB7FP090201	1546972-9
	3.625	8	SSB7FP08020111	1986330-3
2	3.625	8	SSB7FP080203	2-1437416-9
	3.625	8	SSB7FP080201	1546972-8
2	3.187	7	SSB7FP070203	2-1437416-6
	3.187	7	SSB7FP07020111	2-1437416-5
2	3.187	7	SSB7FP070201	2-1437416-4
	2.750	6	SSB7FP06020111	1986330-2
2	2.750	6	SSB7FP060203	2-1437416-3
	2.750	6	SSB7FP060201	2-1437416-1
2	2.312	5	SSB7FP050203	2-1546972-7
	2.312	5	SSB7FP050201	1-1437416-5
2	1.875	4	SSB7FP04020111	1986330-1
	1.875	4	SSB7FP040203	1-1437416-3
2	1.875	4	SSB7FP040201	1-1437416-1
	1.437	3	SSB7FP030201	1437416-6
2	1.000	2	SSB7FP020201	1437416-2
	DIM A	NO. OF POS.	CATALOG NUMBER	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S SCHLGEL 2/10/05		TE Connectivity				
DIMENSIONS: INCHES		CHK S YODER 2/10/05						
	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± .02 3 PLC ± .010 4 PLC ± - ANGLES ± 1°		APVD S YODER 2/10/05		NAME SSB7FPXX0201			
			PRODUCT SPEC —					
			APPLICATION SPEC —					
			WEIGHT —					
MATERIAL —	FINISH —		CUSTOMER DRAWING		SIZE A3	CAGE CODE 00779	DRAWING NO C-9-796602-2	RESTRICTED TO —
				SCALE NTS		SHEET 1 OF 2		REV A

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - By -

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

FT

0

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

1

2

3

4

5

6

7

2-1437416-5

1

2

3

4

5

6

7

8

9

10

11

12

13

14

15

16

9-796602-4

1

2

3

4

5

6

7

8

1986330-3

1

2

3

4

5

6

7

8

9

10

11

12

13

14

15

16

17

18

19

20

21

22

23

24

1986330-5

1

2

3

4

1986330-1

1

2

3

4

5

6

1986330-2

1

2

3

4

5

6

7

8

1986330-3

1

2

3

4

5

6

7

8

9

10

11

12

13

14

15

16

17

18

19

20

21

22

23

24

1986330-5

2

11.937

27

SSB7FP270201

9-796602-2

11.500

26

SSB7FP260203

1-1546561-8

11.500

26

SSB7FP260201

2-1546972-6

11.062

25

SSB7FP250201

2-1546972-5

10.625

24

SSB7FP24020111

1986330-5

10.625

24

SSB7FP240201

2-1546972-4

10.187

23

SSB7FP230201

2-1546972-3

9.750

22

SSB7FP220201

2-1546972-2

9.312

21

SSB7FP210201

2-1546972-1

8.875

20

SSB7FP200201

2-1546972-0

8.437

19

SSB7FP190201

1-1546972-9

8.000

18

SSB7FP180201

1-1546972-8

DIM A

NO. OF POS.

CATALOG NUMBER

PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
INCHES

0

1

2

3

4

PLC
PLC
PLC
PLC
PLC

± -
± -
± .02
± .010
± -

ANGLES

± 1°

MATERIAL

-

FINISH

-

DWN
S SCHL GEL
2/10/05

CHK
S YODER
2/10/05

APVD
S YODER
2/10/05

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

-

CUSTOMER DRAWING

SCALE
NTS

SHEET
2 OF 2

REV
A

STE

TE Connectivity

NAME

SSB7FPXX0201

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-9-796602-2

RESTRICTED TO

-

1470-19

(3/11)